

## Globe LED

Ceiling cord Mounted • Damp Location Listed PROGRESS LED



### Description:

Distinctive Classic globe pendants are accented by striking metal caps over an opal glass shade. This pendant is ideal for Modern, Mid-Century or Farmhouse interior design styles. These versatile pendants can be displayed singularly or in groupings of two or more by mixing and matching finish options and lengths to create custom lighting designs for the home. Complimented by a Brushed Nickel finish.

### Specifications:

- Opal glass Globe
- One-light 9-watt Globe LED cord-hung pendant
- The cap holds a beautiful opal glass shade ready to emit gentle illumination.
- A distinctive classic globe pendant is accented by a striking metal brushed nickel cap.
- This versatile pendant can be displayed as a single fixture or in groups of two or more to create a custom lighting design for your home.
- Ideal for any foyer, kitchen, or dining room.
- Perfect for mid-century modern, transitional, modern, or contemporary settings.
- Measures 8" diameter x 9 3/4" H
- Overall length with cord is 122"
- Uses one LED module (9w max).
- Warm white 3000K lighting color and 90+CRI
- Ideal for classic Mid-Century interiors or Farmhouse design styles
- ENERGY STAR certified
- Replaceable light engine is California JA8 certified
- Dimmable with most Triac or ELV type dimmers
- California Title 24 compliant
- Damp location listed
- Installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 5.5 in W., 1 in ht., 5.5 in depth
- Mounting strap for outlet box included
- 120 in of wire supplied

### Performance:

Number of Modules	1
Input Power	9 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	624/66 (LM-82)
Lumens/LPW (Delivered)	439/47.2 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	Meets FCC Title 47, Part 15 Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2016


## P500147-009-30



### Dimensions:

Diameter: 8 in  
Height: 9-3/4 in  
Overall Ht. W/Cord: 122 in

Opal glass Globe  
Width: 7-7/8 in  
Height: 7-3/8 in




**Photometrics:**

# P500147-009-30

<b>ELECTRICAL DATA</b>	<b>P500147-009-30</b>
Input Voltage	120 V
Input Frequency	60 Hz
Input Current	0.075 A
Power Factor	Greater than 0.90
THD	<20%
EMI/RFI	Meets FCC Title 47, Part 15 Class B
Operating Temperature	-30 °C
Dimming	Yes*
Over-voltage, over-current, short-circuit protected	
*See Dimming Notes for more information	

**P500147-009-30**  
 LED Light Engine: 3000 K 90 CRI  
 System Wattage: 9  
 Fixture delivered lumens: 388  
 Fixture Efficacy: 41.7  
 Spacing Criteria:



CANDELA DISTRIBUTION		
DEG	CANDELA	LUMENS
0	54.6	
5	54.6	5
15	54.5	15
25	54.2	25
35	53.3	33
45	51.4	40
55	48.1	43
65	44.6	44
75	39.9	42
85	35.2	38
90	32.8	
95	29.9	33
105	24.5	26
115	18.6	19
125	13.8	12
135	8.5	7
145	4.9	3
155	2.1	1
165	1.0	0
175	0.0	0
180	0.0	

ZONAL LUMEN SUMMARY		
ZONE	LUMENS	%FIXT
0-30	46	11.8
0-40	79	20.4
0-60	162	41.7
0-90	287	74.0
90-120	77	19.9
90-130	90	23.1
90-150	100	25.7
90-180	101	26.0
0-180	388	100.0

Test 18.00159 Test Date 02/15/18

# P500147-009-30

## Dimming Notes:

---

P500147-009-30 is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## Dimming Controls:

---

Lutron\_Diva DVELV-300P

Lutron\_Nova T NTELV-300

Lutron\_Caseta

Lutron\_Ariadni AY-600P

Leviton\_Illumatech IPI06-1LZ

Leviton\_SureSlide 6672

Lutron\_Ariadni AYCL-153P

Lutron\_Skylark Contour CTCL-153P

Lutron\_Diva DVCL-153P

Lutron\_Toggler TGCL-153P

Lutron\_Maestro MACL-153M

Lutron\_Ariadni AYLV-600P

Lutron\_Nova T NTLV-600

Lutron\_Maestro MAELV-600

Lutron\_spacer/system SPSELV-600

Leviton\_Renoir II AWRMG-EAW

Lutron\_Nova N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.