

# SAFETY DATA SHEET

Revision Date 23-Jan-2020 Version 1

# 1. IDENTIFICATION

**Product identifier** 

Product Name Wiping Stain Carbon Black

Other means of identification

Product Code 15304

**SKU(s)** 15301, 15304, 15316

Recommended use of the chemical and restrictions on use
Recommended Use
Uses advised against
No information available

Details of the supplier of the safety data sheet

**Supplier Address** 

Old Masters 303 19th St. SE Orange City, IA 51041 Phone: 712-737-4993

Fax: 712-737-4997

Emergency telephone number

Emergency Telephone Chemtrec 1-800-424-9300

# 2. HAZARDS IDENTIFICATION

#### Classification

#### **OSHA Regulatory Status**

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Skin sensitization	Category 1
Germ cell mutagenicity	Category 1B
Carcinogenicity	Category 2
Aspiration toxicity	Category 1
Flammable liquids	Category 3

# **Emergency Overview**

### Danger

#### Hazard statements

May cause an allergic skin reaction May cause genetic defects Suspected of causing cancer May be fatal if swallowed and enters airways Flammable liquid and vapor



Appearance No information available Physical state Liquid Odor No information available

# **Precautionary Statements - Prevention**

Obtain special instructions before use

Do not handle until all safety precautions have been read and understood

Use personal protective equipment as required

Avoid breathing dust/fume/gas/mist/vapors/spray

Contaminated work clothing should not be allowed out of the workplace

Wear protective gloves

Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking

Keep container tightly closed

Ground/bond container and receiving equipment

Use only non-sparking tools

Take precautionary measures against static discharge

Use explosion-proof electrical/ ventilating/ lighting/ equipment

#### **Precautionary Statements - Response**

IF exposed or concerned: Get medical advice/attention

If skin irritation or rash occurs: Get medical advice/attention

Wash contaminated clothing before reuse

IF ON SKIN (or hair): Remove/Take off immediately all contaminated clothing. Rinse skin with water/shower

IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician

Do NOT induce vomiting

In case of fire: Use CO2, dry chemical, or foam for extinction

#### **Precautionary Statements - Storage**

Store locked up

Store in a well-ventilated place. Keep cool

#### **Precautionary Statements - Disposal**

Dispose of contents/container to an approved waste disposal plant

#### Hazards not otherwise classified (HNOC)

# Other Information

Unknown acute toxicity

0% of the mixture consists of ingredient(s) of unknown toxicity

# 3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical name	CAS No	Weight-%	Trade Secret
Linseed Oil	8001-26-1	30 - 60	*
Mineral Spirits (Rule 66)	64742-47-8	10 - 30	*
Carbon Black	1333-86-4	1 - 5	*
Solvent Naphtha, Medium Aliphatic	64742-88-7	1 - 5	*
Zirconium octoate	22464-99-9	1 - 5	*
Cobalt 2-ethylhexanoate	136-52-7	0.1 - 1	*
Methyl Ethyl Ketoxime	96-29-7	0.1 - 1	*
Stoddard Solvent	8052-41-3	0.1 - 1	*

<sup>\*</sup>The exact percentage (concentration) of composition has been withheld as a trade secret.

#### 4. FIRST AID MEASURES

#### **Description of first aid measures**

**Eye contact** Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids.

Consult a physician.

**Skin Contact** Wash skin with soap and water.

**Inhalation** Remove to fresh air.

**Ingestion** Clean mouth with water and drink afterwards plenty of water.

Most important symptoms and effects, both acute and delayed

**Symptoms** No information available.

Indication of any immediate medical attention and special treatment needed

#### 5. FIRE-FIGHTING MEASURES

#### Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media CAUTION: Use of water spray when fighting fire may be inefficient.

#### Specific hazards arising from the chemical

Flammable. WARNING: Spontaneous combustion (fire) may result from materials such as rags, steel wool, paper, clothing, and other waste soaked in linseed oil. Place in a sealed, water filled, metal container to prevent this.

#### **Explosion data**

Sensitivity to Mechanical Impact None. Sensitivity to Static Discharge None.

#### Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

### 6. ACCIDENTAL RELEASE MEASURES

#### Personal precautions, protective equipment and emergency procedures

Personal precautions Remove all sources of ignition. Use personal protective equipment as required.

Environmental precautions

Environmental precautions Do not flush into surface water or sanitary sewer system. See Section 12 for additional

Ecological Information.

Methods and material for containment and cleaning up

**Methods for containment** Prevent further leakage or spillage if safe to do so.

**Methods for cleaning up**Soak up with inert absorbent material.

# 7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Handle in accordance with good industrial hygiene and safety practice.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep away from heat, sparks, flame and other sources of ignition (i.e., pilot lights, electric

motors and static electricity).

**Incompatible materials**None known based on information supplied.

# 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

#### Control parameters

**Exposure Guidelines** 

Chemical name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Carbon Black	TWA: 3 mg/m³ inhalable particulate	TWA: 3.5 mg/m <sup>3</sup>	IDLH: 1750 mg/m <sup>3</sup>
1333-86-4	matter	(vacated) TWA: 3.5 mg/m <sup>3</sup>	TWA: 3.5 mg/m <sup>3</sup>
			TWA: 0.1 mg/m <sup>3</sup> Carbon black in
			presence of Polycyclic aromatic
			hydrocarbons PAH
Zirconium octoate	STEL: 10 mg/m³ Zr	TWA: 5 mg/m <sup>3</sup> Zr	IDLH: 25 mg/m <sup>3</sup> Zr
22464-99-9	TWA: 5 mg/m³ Zr	(vacated) TWA: 5 mg/m <sup>3</sup> Zr	TWA: 5 mg/m³ except Zirconium
		(vacated) STEL: 10 mg/m <sup>3</sup> Zr	tetrachloride Zr
			STEL: 10 mg/m <sup>3</sup> Zr
Stoddard Solvent	TWA: 100 ppm	TWA: 500 ppm	IDLH: 20000 mg/m <sup>3</sup>
8052-41-3		TWA: 2900 mg/m <sup>3</sup>	Ceiling: 1800 mg/m <sup>3</sup> 15 min
		(vacated) TWA: 100 ppm	TWA: 350 mg/m <sup>3</sup>
		(vacated) TWA: 525 mg/m <sup>3</sup>	

NIOSH IDLH Immediately Dangerous to Life or Health

Other Information Vacated limits revoked by the Court of Appeals decision in AFL-CIO v. OSHA, 965 F.2d 962

(11th Cir., 1992).

**Appropriate engineering controls** 

Engineering Controls Showers

Eyewash stations Ventilation systems.

Individual protection measures, such as personal protective equipment

**Eye/face protection** No special technical protective measures are necessary.

**Skin and body protection**No special technical protective measures are necessary.

**Respiratory protection** If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved

respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be

provided in accordance with current local regulations.

**General Hygiene Considerations** Handle in accordance with good industrial hygiene and safety practice.

# 9. PHYSICAL AND CHEMICAL PROPERTIES

#### Information on basic physical and chemical properties

Physical state Liquid

AppearanceNo information availableOdorNo information availableColorNo information availableOdor thresholdNo information available

<u>Property</u> <u>Values</u> <u>Remarks • Method</u>

pH No information available
Melting point / freezing point
Boiling point / boiling range
Flash point
No information available

Evaporation rate No information available Flammability (solid, gas) No information available Flammability Limit in Air

Upper flammability limit:
Lower flammability limit:
Vapor pressure
Vapor density

No information available
No information available
No information available

Specific Gravity 0.93

Water solubility No information available Solubility in other solvents No information available Partition coefficient No information available **Autoignition temperature** No information available **Decomposition temperature** No information available Kinematic viscosity No information available Dynamic viscosity No information available **Explosive properties** No information available **Oxidizing properties** No information available

#### Other Information

Softening pointNo information availableMolecular weightNo information available

Liquid Density 7.78 lbs/gal

Bulk density No information available

Percent solids by weight 74.4% Percent volatile by weight 25.6% Percent solids by volume 69.6% Actual VOC (lbs/gal) 2 Actual VOC (grams/liter) 238.9 EPA VOC (lbs/gal) 2 EPA VOC (grams/liter) 238.9 EPA VOC (lb/gal solids) 2.9

# 10. STABILITY AND REACTIVITY

#### Reactivity

No data available

### **Chemical stability**

Stable under recommended storage conditions.

# Possibility of hazardous reactions

None under normal processing.

#### **Conditions to avoid**

Extremes of temperature and direct sunlight.

### **Incompatible materials**

None known based on information supplied.

# **Hazardous decomposition products**

None known based on information supplied.

# 11. TOXICOLOGICAL INFORMATION

# Information on likely routes of exposure

Product Information No data available

**Inhalation** No data available.

**Eye contact** No data available.

**Skin Contact** No data available.

**Ingestion** No data available.

Chemical name	Oral LD50	Dermal LD50	Inhalation LC50
Linseed Oil	> 15,000 mg/kg	-	-

8001-26-1			
Mineral Spirits (Rule 66) 64742-47-8	> 5000 mg/kg (Rat)	> 2000 mg/kg ( Rabbit )	> 5.2 mg/L (Rat)4 h
Carbon Black 1333-86-4	> 15400 mg/kg (Rat)	> 3 g/kg(Rabbit)	-
Solvent Naphtha, Medium Aliphatic 64742-88-7	> 25 mL/kg ( Rat )	> 3000 mg/kg ( Rabbit )	> 13 mg/L (Rat)4 h
Zirconium octoate 22464-99-9	> 5000 mg/kg (Rat)	-	-
Cobalt 2-ethylhexanoate 136-52-7	= 1300 mg/kg (Rat)	> 5000 mg/kg ( Rabbit )	> 10 mg/L (Rat)1 h
Methyl Ethyl Ketoxime 96-29-7	= 930 mg/kg (Rat)	1000 - 1800 mg/kg(Rabbit)	> 4800 mg/m³ (Rat) 4 h
Stoddard Solvent 8052-41-3	> 5000 mg/kg (Rat)	> 3000 mg/kg (Rabbit)	-

# Symptoms related to the physical, chemical and toxicological characteristics

**Symptoms** No information available.

# Delayed and immediate effects as well as chronic effects from short and long-term exposure

SensitizationNo information available.Germ cell mutagenicityNo information available.CarcinogenicityNo information available.

Chemical name	ACGIH	IARC	NTP	OSHA
Carbon Black 1333-86-4	A3	Group 2B	-	X
Cobalt 2-ethylhexanoate 136-52-7	-	Group 2B	Reasonably Anticipated	X

ACGIH (American Conference of Governmental Industrial Hygienists)

A3 - Animal Carcinogen

IARC (International Agency for Research on Cancer)

Group 2B - Possibly Carcinogenic to Humans

Group 3 - Not classifiable as a human carcinogen

NTP (National Toxicology Program)

Reasonably Anticipated - Reasonably Anticipated to be a Human Carcinogen

OSHA (Occupational Safety and Health Administration of the US Department of Labor)

X - Present

Reproductive toxicity
STOT - single exposure
STOT - repeated exposure
No information available.
No information available.

Target organ effects Eyes, Lymphatic System, Respiratory system, Skin.

Aspiration hazard No information available.

# Numerical measures of toxicity - Product Information

The following values are calculated based on chapter 3.1 of the GHS document mg/kg

# 12. ECOLOGICAL INFORMATION

#### **Ecotoxicity**

6.86% of the mixture consists of components(s) of unknown hazards to the aquatic environment

Chemical name	Algae/aquatic plants	Fish	Crustacea
Mineral Spirits (Rule 66)	-	45: 96 h Pimephales promelas mg/L	4720: 96 h Den-dronereides
64742-47-8		LC50 flow-through 2.4: 96 h	heteropoda mg/L LC50
		Oncorhynchus mykiss mg/L LC50	
		static 2.2: 96 h Lepomis	
		macrochirus mg/L LC50 static	
Carbon Black	-	-	5600: 24 h Daphnia magna mg/L
1333-86-4			EC50
Solvent Naphtha, Medium Aliphatic	450: 96 h Pseudokirchneriella	800: 96 h Pimephales promelas	100: 48 h Daphnia magna mg/L
64742-88-7	subcapitata mg/L EC50	mg/L LC50 static	EC50
Methyl Ethyl Ketoxime	83: 72 h Desmodesmus subspicatus		750: 48 h Daphnia magna mg/L
96-29-7	mg/L EC50	promelas mg/L LC50 flow-through	EC50

. .

760: 96 h Poecilia reticulata mg/L
LC50 static 320 - 1000: 96 h
Leuciscus idus mg/L LC50 static

# Persistence and degradability

No information available.

#### Bioaccumulation

No information available.

Chemical name	Partition coefficient
Methyl Ethyl Ketoxime	0.65
96-29-7	

Other adverse effects No information available

# 13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal of wastes Disposal should be in accordance with applicable regional, national and local laws and

regulations.

Contaminated packaging Do not reuse container.

**US EPA Waste Number** D001 U220 U239 U019 U151 U165 U055

This product contains one or more substances that are listed with the State of California as a hazardous waste.

Chemical name	California Hazardous Waste Status
Cobalt 2-ethylhexanoate	Toxic
136-52-7	

# 14. TRANSPORT INFORMATION

**DOT** Not regulated

# 15. REGULATORY INFORMATION

**International Inventories** 

Complies **TSCA** Complies \* **DSL/NDSL** Complies \* **EINECS/ELINCS** Does not comply \* **ENCS IECSC** Complies \* Does not comply \* **KECL** Complies \* **PICCS AICS** Complies \*

Legend:

<sup>\*</sup> This product contains an unknown chemical, therefore, this product's compliance to the inventory list is NOT DETERMINED

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

EINECS/ELINCS - European Inventory of Existing Chemical Substances/European List of Notified Chemical Substances

**ENCS** - Japan Existing and New Chemical Substances

IECSC - China Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

# **US Federal Regulations**

#### **SARA 313**

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

#### SARA 311/312 Hazard Categories

Acute health hazard No
Chronic Health Hazard No
Fire hazard Yes
Sudden release of pressure hazard No
Reactive Hazard No

# **US State Regulations**

# **California Proposition 65**

This product contains the following Proposition 65 chemicals

Chemical name	California Proposition 65
Carbon Black - 1333-86-4	Carcinogen
Ethyl Benzene - 100-41-4	Carcinogen
Crystalline Silica - 14808-60-7	Carcinogen
Naphthalene - 91-20-3	Carcinogen
Cumene - 98-82-8	Carcinogen
Toluene - 108-88-3	Developmental
Benzene(including benzene from gasoline) - 71-43-2	Carcinogen Developmental Male Reproductive
Lead - 7439-92-1	Carcinogen Developmental Female Reproductive Male Reproductive
Mercury - 7439-97-6	Developmental
Nickel - 7440-02-0	Carcinogen
Arsenic - 7440-38-2	Carcinogen
Cadmium - 7440-43-9	Carcinogen Developmental Male Reproductive

#### U.S. State Right-to-Know Regulations

Chemical name	New Jersey	Massachusetts
Carbon Black	X	X
1333-86-4		
Xylene	X	X
1330-20-7		
Cobalt 2-ethylhexanoate	X	-
136-52-7		

Chemical name	Pennsylvania
Linseed Oil	X
8001-26-1 Carbon Black	Y
1333-86-4	^

# U.S. EPA Label Information

EPA Pesticide Registration Number Not applicable

#### Hazardous air pollutants (HAPS) content

This product contains no Hazardous Air Pollutants individually at 1% by weight, or greater.

# 16. OTHER INFORMATION, INCLUDING DATE OF PREPARATION OF THE LAST REVISION

NFPA Health hazards 1 Flammability 2 Instability 0 Physical and chemical

properties -

HMIS Health hazards 1 \* Flammability 2 Physical hazards 0 Personal protection X

Chronic Hazard Star Legend \*= Chronic Health Hazard

Revision Date 23-Jan-2020

**Revision Note** 

No information available

**Disclaimer** 

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text. Shipping information may vary based upon container size and shipping destination. Each user of this material needs to evaluate the conditions of use and design the appropriate protective mechanisms to prevent employee exposures, property damage, or release to the environment. The manufacturer assumes no responsibility for injury to the recipient or third persons, or for any damages to any property resulting from misuse of the product.

**End of Safety Data Sheet**