

LED Stone Glass Sconce

Wall Mounted • Damp Location Listed **PROGRESS LED**

Description:

The organic features of this wall sconce make it seem like it's one with nature. The handmade, clear stone glass shade steals the show with its underwater-inspired ambiance. The shade is held in place by a minimalist black frame that transforms your home into a naturally beautiful soothing place for you and your family.

Specifications:

- Clear Stone glass Square Panel
- The organic features of this wall sconce make it seem like it's one with nature.
- The handmade, clear stone glass shade steals the show with its underwater-inspired ambiance.
- The shade is held in place by a minimalist black frame that transforms your home into a naturally beautiful soothing place for you and your family.
- Ideal for bedroom, hallway, foyer, bathroom, or living room.
- Perfect for transitional, modern, or contemporary settings.
- Measures 8-inch width by 8-1/2-inch height.
- Uses one integrated LED (9.5w max).
- Compatible with many Triac dimmers (see dimming controls)
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 8 in W., 4.75 in ht., 0.75 in depth
- Mounting backplate for outlet box included
- 6 in of wire supplied
- Americans With Disabilities Act (ADA) compliant

Performance:

Number of Modules	1
Input Power	9.5 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	433/46 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cETLus Damp Location Listed Meets California Title 24 JA8-2016


P710080-031-30



Dimensions:

Width: 8 in
Height: 8-1/2 in
Depth: 3-1/4 in
H/CTR: 4 in

Clear Stone glass Square Panel
Width: 8 in
Height: 8 in




Photometrics:

P710080-031-30

ELECTRICAL DATA	P710080-031-30
Input Voltage	120 V
Input Frequency	60 Hz
THD	<20%
EMI/RFI	FCC Title 47, Part 15, Class B
Operating Temperature	-30 °C to 30 °C
Dimming	Yes*
Over-voltage, over-current, short-circuit protected	
*See Dimming Notes for more information	

P710080-031-30

LED Light Engine: 3000 K 90 CRI
 System Wattage: 9.5
 Fixture delivered lumens: 391
 Fixture Efficacy: 42.6
 Spacing Criteria:



Test **19.01537** Test Date **09/04/19**

CANDELA DISTRIBUTION

CANDELA DISTRIBUTION

	0.0	45.0	90.0	135.0	180.0	
0	0.9	0.9	0.9	0.9	0.9	0
5	4.2	4.1	2.5	1.1	1.1	0
15	13.9	17.0	9.6	4.2	3.7	3
25	23.4	22.9	16.3	6.7	4.4	7
35	37.5	29.6	23.4	8.4	3.3	13
45	53.5	38.6	29.7	8.5	2.4	20
55	69.0	49.6	34.8	8.1	1.8	28
65	82.4	61.0	39.3	7.9	1.1	36
75	91.3	69.6	42.2	7.4	0.6	42
85	95.6	73.0	43.6	7.1	0.3	45
90	96.4	73.2	44.6	7.5	0.5	
95	95.8	72.3	44.3	7.5	0.1	45
105	92.0	67.8	43.1	7.6	0.4	42
115	82.7	59.9	40.7	7.8	0.8	36
125	68.0	49.1	36.3	7.6	0.7	29
135	51.5	39.0	31.8	8.6	1.5	21
145	34.2	30.9	25.5	9.0	2.2	13
155	22.0	24.8	18.3	7.1	3.7	7
165	14.0	19.1	11.0	4.8	3.6	3
175	0.8	0.8	0.7	0.5	0.2	0
180	0.2	0.2	0.2	0.2	0.2	

ZONAL LUMEN SUMMARY

FLUX	ZONE	LUMENS	%FIXT
	0-30	10	2.7
	0-40	23	6.0
	0-60	72	18.3
	0-90	194	49.8
	90-120	123	31.5
	90-130	152	38.8
	90-150	185	47.5
	90-180	196	50.2
	0-180	391	100.0

P710080-031-30

Dimming Notes:

P710080-031-30 is designed to be compatible with many Triac/Forward Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Leviton 6681

Leviton 6672

Lutron DVCL-253P

Lutron Caseta Wireless

Lutron SCL-153P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.