



Revision Date 19-Oct-2018

SAFETY DATA SHEET

Version 1

1. IDENTIFICATION

Product identifier

Product Name Ascend Exterior Matte

Other means of identification

Product Code 71001

SKU(s) 71001, 71004, 71005

Recommended use of the chemical and restrictions on use

Recommended Use No information available.

Uses advised against No information available

Details of the supplier of the safety data sheet

Supplier Address

Old Masters
303 19th St. SE
Orange City, IA 51041
Phone: 712-737-4993
Fax: 712-737-4997

Emergency telephone number

Emergency Telephone Chemtrec 1-800-424-9300

2. HAZARDS IDENTIFICATION

Classification

OSHA Regulatory Status

This chemical is not considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Not a hazardous substance or mixture according to the Globally Harmonized System (GHS)

Emergency Overview

The product contains no substances which at their given concentration, are considered to be hazardous to health

Appearance No information available

Physical state Liquid

Odor No information available

Hazards not otherwise classified (HNOC)

Other Information

- Harmful to aquatic life with long lasting effects
- Harmful to aquatic life

Unknown acute toxicity 29.4% of the mixture consists of ingredient(s) of unknown toxicity

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical name	CAS No	Weight-%	Trade Secret
Dipropylene Glycol Butyl Ether	29911-28-2	1 - 5	*

Propylene Glycol	57-55-6	1 - 5	*
------------------	---------	-------	---

*The exact percentage (concentration) of composition has been withheld as a trade secret.

4. FIRST AID MEASURES

Description of first aid measures

Eye contact	Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a physician.
Skin Contact	Wash skin with soap and water.
Inhalation	Remove to fresh air.
Ingestion	Clean mouth with water and drink afterwards plenty of water.

Most important symptoms and effects, both acute and delayed

Symptoms No information available.

Indication of any immediate medical attention and special treatment needed

Note to physicians Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media CAUTION: Use of water spray when fighting fire may be inefficient.

Specific hazards arising from the chemical

No information available.

Explosion data

Sensitivity to Mechanical Impact None.

Sensitivity to Static Discharge None.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions Ensure adequate ventilation, especially in confined areas.

Environmental precautions

Environmental precautions See Section 12 for additional Ecological Information.

Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Use personal protective equipment as required. Dam up. Cover liquid spill with sand, earth or other non-combustible absorbent material. Take up mechanically, placing in appropriate containers for disposal. Clean contaminated surface thoroughly.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Handle in accordance with good industrial hygiene and safety practice.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep containers tightly closed in a dry, cool and well-ventilated place.

Incompatible materials None known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Control parameters****Exposure Guidelines****Appropriate engineering controls**

Engineering Controls Showers
Eyewash stations
Ventilation systems.

Individual protection measures, such as personal protective equipment

Eye/face protection No special technical protective measures are necessary.

Skin and body protection No special technical protective measures are necessary.

Respiratory protection If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

General Hygiene Considerations Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES**Information on basic physical and chemical properties**

Physical state	Liquid	Odor	No information available
Appearance	No information available	Odor threshold	No information available
Color	No information available		

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	RCD	
Melting point / freezing point	No information available	
Boiling point / boiling range	>= 100 °C / 212 °F	
Flash point	> 94 °C / > 201 °F	
Evaporation rate	No information available	
Flammability (solid, gas)	No information available	
Flammability Limit in Air		
Upper flammability limit:	No information available	
Lower flammability limit:	No information available	
Vapor pressure	No information available	
Vapor density	No information available	
Specific Gravity	1.03	
Water solubility	No information available	
Solubility in other solvents	No information available	
Partition coefficient	No information available	
Autoignition temperature	No information available	
Decomposition temperature	No information available	
Kinematic viscosity	No information available	
Dynamic viscosity	No information available	

Explosive properties No information available
Oxidizing properties No information available

Other Information

Softening point No information available
Molecular weight No information available
Liquid Density 8.63 lbs/gal
Bulk density No information available
Percent solids by weight 32.2%
Percent volatile by weight 4.6%
Percent solids by volume 29.5%
Actual VOC (lbs/gal) 0.4
Actual VOC (grams/liter) 47.3
EPA VOC (lbs/gal) 1.1
EPA VOC (grams/liter) 137
EPA VOC (lb/gal solids) 1.3

10. STABILITY AND REACTIVITY

Reactivity

No data available

Chemical stability

Stable under recommended storage conditions.

Possibility of hazardous reactions

None under normal processing.

Conditions to avoid

Extremes of temperature and direct sunlight.

Incompatible materials

None known based on information supplied.

Hazardous decomposition products

None known based on information supplied.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information No data available

Inhalation No data available.

Eye contact No data available.

Skin Contact No data available.

Ingestion No data available.

Chemical name	Oral LD50	Dermal LD50	Inhalation LC50
Dipropylene Glycol Butyl Ether 29911-28-2	= 1620 µL/kg (Rat)	= 5860 µL/kg (Rabbit)	= 42.1 ppm (Rat) 4 h
Propylene Glycol 57-55-6	= 20 g/kg (Rat)	= 20800 mg/kg (Rabbit)	-

Symptoms related to the physical, chemical and toxicological characteristics

Symptoms No information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization	No information available.
Germ cell mutagenicity	No information available.
Carcinogenicity	No information available.
<i>IARC (International Agency for Research on Cancer)</i>	
<i>Group 3 - Not classifiable as a human carcinogen</i>	
Reproductive toxicity	No information available.
STOT - single exposure	No information available.
STOT - repeated exposure	No information available.
Aspiration hazard	No information available.

Numerical measures of toxicity - Product Information

The following values are calculated based on chapter 3.1 of the GHS document mg/kg

12. ECOLOGICAL INFORMATION

Ecotoxicity

Harmful to aquatic life with long lasting effects

30.67% of the mixture consists of component(s) of unknown hazards to the aquatic environment

Chemical name	Algae/aquatic plants	Fish	Crustacea
Dipropylene Glycol Butyl Ether 29911-28-2	-	841: 96 h Poecilia reticulata mg/L LC50 static	-
Propylene Glycol 57-55-6	19000: 96 h Pseudokirchneriella subcapitata mg/L EC50	51600: 96 h Oncorhynchus mykiss mg/L LC50 static 41 - 47: 96 h Oncorhynchus mykiss mL/L LC50 static 51400: 96 h Pimephales promelas mg/L LC50 static 710: 96 h Pimephales promelas mg/L LC50	10000: 24 h Daphnia magna mg/L EC50 1000: 48 h Daphnia magna mg/L EC50 Static

Persistence and degradability

No information available.

Bioaccumulation

No information available.

Other adverse effects

No information available

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal of wastes	Disposal should be in accordance with applicable regional, national and local laws and regulations.
Contaminated packaging	Do not reuse container.

14. TRANSPORT INFORMATION

<u>DOT</u>	Not regulated
-------------------	---------------

15. REGULATORY INFORMATION

International Inventories

TSCA	Complies
DSL/NDSL	Complies *
EINECS/ELINCS	Does not comply *
ENCS	Does not comply *
IECSC	Complies *
KECL	Complies *
PICCS	Complies *
AICS	Complies *

* This product contains an unknown chemical, therefore, this product's compliance to the inventory list is NOT DETERMINED

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
 DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List
 EINECS/ELINCS - European Inventory of Existing Chemical Substances/European List of Notified Chemical Substances
 ENCS - Japan Existing and New Chemical Substances
 IECSC - China Inventory of Existing Chemical Substances
 KECL - Korean Existing and Evaluated Chemical Substances
 PICCS - Philippines Inventory of Chemicals and Chemical Substances
 AICS - Australian Inventory of Chemical Substances

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

SARA 311/312 Hazard Categories

Acute health hazard	No
Chronic Health Hazard	No
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

US State Regulations

California Proposition 65

This product does not contain any Proposition 65 chemicals

U.S. State Right-to-Know Regulations

Chemical name	New Jersey	Massachusetts
Propylene Glycol 57-55-6	X	-

Chemical name	Pennsylvania
Propylene Glycol 57-55-6	X

U.S. EPA Label Information

EPA Pesticide Registration Number Not applicable

Hazardous air pollutants (HAPS) content

This product contains no Hazardous Air Pollutants individually at 1% by weight, or greater.

16. OTHER INFORMATION, INCLUDING DATE OF PREPARATION OF THE LAST REVISION

<u>NFPA</u>	Health hazards 0	Flammability 1	Instability 0	Physical and chemical properties -
<u>HMIS</u>	Health hazards 0	Flammability 1	Physical hazards 0	Personal protection X

Revision Date 19-Oct-2018

Revision Note

No information available

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text. Shipping information may vary based upon container size and shipping destination. Each user of this material needs to evaluate the conditions of use and design the appropriate protective mechanisms to prevent employee exposures, property damage, or release to the environment. The manufacturer assumes no responsibility for injury to the recipient or third persons, or for any damages to any property resulting from misuse of the product.

End of Safety Data Sheet