



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	PACKAGE QUANTITY	MAX BUNDLE DIA [mm]	LENGTH (B) "L" +/- .3 [8]	MARKING "XXX SS"
MS4W75T30-Q6	25	4" [102]	19.6" [498]	316 SS
MS6W75T30-Q6	25	6" [152]	25.9" [658]	316 SS
MS8W75T30-Q6	25	8" [203]	32.1" [815]	316 SS
MS10W75T30-Q6	25	10" [254]	38.4" [975]	316 SS
MS12W75T30-Q6	25	12" [305]	44.7" [1135]	316 SS
MS14W75T30-Q6	25	14" [356]	50.1" [1273]	316 SS



SECTION A - A

NOTES:

1. APPLICATION TOOLS: BT75SDT, BT2HT1
2. ALL DIMENSIONS IN BRACKETS [] ARE MILLIMETERS
3. MATERIAL: 316 STAINLESS STEEL
4. MAX BUNDLE DIA FOR SINGLE LOOP APPLICATIONS.
FOR DOUBLE LOOP APPLICATIONS, DIVIDE MAX BUNDLE DIA VALUE BY 2
FOR TRIPLE LOOP APPLICATIONS, DIVIDE MAX BUNDLE DIA VALUE BY 3

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE	MATERIAL	DRAWING NUMBER	SIZE		
05A	5/13/19	BWG	JADE	JADE	(B) REVISED "L" DIMENSION LEADER LOCATION, CHART AND NOTE 4. REVISED TITLE. SEE ECN DOCUMENT FOR COMPLETE DETAILS.	046621/01	MS75 DISCRETE LENGTH TIE .75" [19.0] WIDE	SEE NOTES	N41311BS_DC	A		
04A	5/10/19	JEH	JADE	JADE	CORRECTED THE (A) "L" LENGTH SHOWN IN THE FRONT VIEW	046621	CUSTOMER DRAWING					
03A	6/19/18	RUMO	RGR0	RGR0	MODIFIED COMPONENT SHAPE; HEIGHT WAS .72 ± .03	037873						
02	01/23/17	JBN	SKB	RGR0	ADDED MS14W75T30-Q6 TO THE CHART	N41311BS-DC						
01A	08/13	ACC	RGR0	RGR0	ADDED MS4W75T30-Q6, MS6W75T30-Q6, MS8W75T30-6, AND MS12W75T30-Q6 TO THE CHART	SSECN1069						
00A	02/13	JAMB	SKB	RGR0	DRAWING RELEASED							
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY JAMB	DATE 02-13-2013	CHK SKB	SCALE NTS	SHT 1 OF 1	SIZE A