

SAFETY DATA SHEET

Revision Date 01-Dec-2016

Version 3

1. IDENTIFICATION

Product identifier Product Name

Wiping Stain Dark Walnut

Other means of identification	
Product Code	12016
SKU(s)	12001, 12004, 12016

Recommended use of the chemical and restrictions on useRecommended UseNo information available.Uses advised againstNo information available

Details of the supplier of the safety data sheet Supplier Address Old Masters 303 19th St. SE Orange City, IA 51041 Phone: 712-737-4993

Emergency telephone number

Emergency Telephone

Fax: 712-737-4997

Chemtrec 1-800-424-9300

2. HAZARDS IDENTIFICATION

Classification

OSHA Regulatory Status

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Skin sensitization	Category 1
Germ cell mutagenicity	Category 1B
Carcinogenicity	Category 1A
Specific target organ toxicity (repeated exposure)	Category 1
Aspiration toxicity	Category 1
Flammable liquids	Category 3

Emergency Overview

Danger

Hazard statements May cause an allergic skin reaction May cause genetic defects May cause cancer Causes damage to organs through prolonged or repeated exposure May be fatal if swallowed and enters airways Flammable liquid and vapor



Precautionary Statements - Prevention

Obtain special instructions before use Do not handle until all safety precautions have been read and understood Use personal protective equipment as required Contaminated work clothing should not be allowed out of the workplace Wear protective gloves Do not breathe dust/fume/gas/mist/vapors/spray Wash face, hands and any exposed skin thoroughly after handling Do not eat, drink or smoke when using this product Keep away from heat/sparks/open flames/hot surfaces. - No smoking Keep container tightly closed Ground/bond container and receiving equipment Use only non-sparking tools Take precautionary measures against static discharge Use explosion-proof electrical/ ventilating/ lighting/ equipment

Precautionary Statements - Response

IF exposed or concerned: Get medical advice/attention If skin irritation or rash occurs: Get medical advice/attention Wash contaminated clothing before reuse IF ON SKIN (or hair): Remove/Take off immediately all contaminated clothing. Rinse skin with water/shower IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician Do NOT induce vomiting In case of fire: Use CO2, dry chemical, or foam for extinction

Precautionary Statements - Storage

Store locked up Store in a well-ventilated place. Keep cool

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)

Other Information

 May be harmful if swallowed Unknown acute toxicity

3.01% of the mixture consists of ingredient(s) of unknown toxicity

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No.	Weight-%	Trade Secret
Linseed Oil	8001-26-1	30 - 60	*
Mineral Spirits (Rule 66)	64742-47-8	10 - 30	*
Crystalline Silica	14808-60-7	5 - 10	*
Solvent Naphtha, Medium Aliphatic	64742-88-7	1 - 5	*
Umber	12713-03-0	1 - 5	*
Stoddard Solvent	8052-41-3	0.1 - 1	*
Methyl Ethyl Ketoxime	96-29-7	0.1 - 1	*
Carbon Black	1333-86-4	0.1 - 1	*

Mineral Spirits	64742-48-9	0.1 - 1	*
Neo C9-13 Acid, Cobalt Salts	68955-83-9	0.1 - 1	*
Cobalt neodecanoate	27253-31-2	0.1 - 1	*

*The exact percentage (concentration) of composition has been withheld as a trade secret.

4. FIRST AID MEASURES

Description of first aid measures

General advice	Immediate medical attention is required. In case of accident or unwellness, seek medical advice immediately (show directions for use or safety data sheet if possible).	
Eye contact	Immediately flush with plenty of water. After initial flushing, remove any contact lenses and continue flushing for at least 15 minutes. Keep eye wide open while rinsing. If symptoms persist, call a physician.	
Skin Contact	Wash off immediately with plenty of water.	
Inhalation	Remove to fresh air. Call a physician. If breathing is irregular or stopped, administer artificial respiration. Avoid direct contact with skin. Use barrier to give mouth-to-mouth resuscitation.	
Ingestion	Do NOT induce vomiting. Rinse mouth. Drink plenty of water. If symptoms persist, call a physician.	
Self-protection of the first aider	Remove all sources of ignition.	
Most important symptoms and effects, both acute and delayed		
Symptoms	No information available.	
Indication of any immediate medical attention and special treatment needed		
Note to physicians	Treat symptomatically.	

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media CAUTION: Use of water spray when fighting fire may be inefficient.

Specific hazards arising from the chemical

Flammable. WARNING: Spontaneous combustion (fire) may result from materials such as rags, steel wool, paper, clothing, and other waste soaked in linseed oil. Place in a sealed, water filled, metal container to prevent this.

Explosion data Sensitivity to Mechanical Impact None. Sensitivity to Static Discharge None.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions

Remove all sources of ignition. Evacuate personnel to safe areas. Ensure adequate ventilation, especially in confined areas. Use personal protective equipment as required.

Environmental precautions

Environmental precautions	Prevent further leakage or spillage if safe to do so. Prevent product from entering drains. Do not flush into surface water or sanitary sewer system. See Section 12 for additional ecological information.	
Methods and material for containme	nt and cleaning up	
Methods for containment	Prevent further leakage or spillage if safe to do so.	
Methods for cleaning up	Pick up and transfer to properly labeled containers. Dam up. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Soak up with inert absorbent material.	
	7. HANDLING AND STORAGE	
Precautions for safe handling		
Advice on safe handling	Ensure adequate ventilation, especially in confined areas. Keep away from heat, sparks, flame and other sources of ignition (i.e., pilot lights, electric motors and static electricity). Take precautionary measures against static discharges. Use spark-proof tools and explosion-proof equipment. All equipment used when handling the product must be grounded.	

Conditions for safe storage, including any incompatibilities

Storage Conditions	Keep tightly closed in a dry and cool place. Keep in properly labeled containers. Keep away
	from heat, sparks, flame and other sources of ignition (i.e., pilot lights, electric motors and
	static electricity).

Incompatible materials None known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Crystalline Silica 14808-60-7	TWA: 0.025 mg/m³ respirable particulate matter	 TWA: 50 μg/m³ TWA: 50 μg/m³ excludes construction work, agricultural operations, and exposures that result from the processing of sorptive clays (vacated) TWA: 0.1 mg/m³ respirable dust : (250)/(%SiO2 + 5) mppcf TWA respirable fraction : (10)/(%SiO2 + 2) mg/m³ TWA respirable fraction 	IDLH: 50 mg/m ³ respirable dust TWA: 0.05 mg/m ³ respirable dust
Umber 12713-03-0	TWA: 0.02 mg/m ³ Mn respirable particulate matter TWA: 0.1 mg/m ³ Mn inhalable particulate matter	(vacated) Ceiling: 5 mg/m ³ Ceiling: 5 mg/m ³ Mn	IDLH: 500 mg/m ³ Mn TWA: 1 mg/m ³ Mn STEL: 3 mg/m ³ Mn
Stoddard Solvent 8052-41-3	TWA: 100 ppm	TWA: 500 ppm TWA: 2900 mg/m ³ (vacated) TWA: 100 ppm (vacated) TWA: 525 mg/m ³	IDLH: 20000 mg/m ³ Ceiling: 1800 mg/m ³ 15 min TWA: 350 mg/m ³
Carbon Black 1333-86-4	TWA: 3 mg/m ³ inhalable particulate matter	TWA: 3.5 mg/m ³ (vacated) TWA: 3.5 mg/m ³	IDLH: 1750 mg/m ³ TWA: 3.5 mg/m ³ TWA: 0.1 mg/m ³ Carbon black in presence of Polycyclic aromatic hydrocarbons PAH

NIOSH IDLH Immediately Dangerous to Life or Health

Other Information	Vacated limits revoked by the Court of Appeals decision in AFL-CIO v. OSHA, 965 F.2d 962 (11th Cir., 1992).
Appropriate engineering controls	
Engineering Controls	Showers Eyewash stations Ventilation systems.
Individual protection measures, su	ch as personal protective equipment
Eye/face protection	Tight sealing safety goggles.
Skin and body protection	No special technical protective measures are necessary.
Respiratory protection	If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.
General Hygiene Considerations	When using do not eat, drink or smoke. Regular cleaning of equipment, work area and clothing is recommended.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical state	liquid	
Appearance	No information available	Odor
Color	No information available	Odor threshold
Property_	Values	Remarks • Method
pH	No information available	
Melting point/freezing point	No information available	
Boiling point / boiling range	>= 117 °C / 243 °F	
Flash point	39 °C / 102 °F	
Evaporation rate	No information available	
Flammability (solid, gas)	No information available	
Flammability Limit in Air		
Upper flammability limit:	No information available	
Lower flammability limit:	No information available	
Vapor pressure	No information available	
Vapor density	No information available	
Specific Gravity	1.00	
Water solubility	No information available	
Solubility in other solvents	No information available	
Partition coefficient	No information available	
Autoignition temperature	No information available	
Decomposition temperature	No information available	
Kinematic viscosity	No information available	
Dynamic viscosity	No information available	
Explosive properties	No information available	
Oxidizing properties	No information available	
Other Information		
Softening point	No information available	
Molecular weight	No information available	
VOC Content (%)	No information available	
Density	8.37 lbs/gal	
Bulk density	No information available	
Percent solids by weight	76.2%	

No information available No information available

Percent volatile by weight	23.8%
Percent solids by volume	69.6%
Actual VOC (lbs/gal)	2
Actual VOC (grams/liter)	239.2
EPA VOC (lbs/gal)	2
EPA VOC (grams/liter)	239.2
EPA VOC (lb/gal solids)	2.9

10. STABILITY AND REACTIVITY

Reactivity_

No data available

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Conditions to avoid

Heat, flames and sparks.

Incompatible materials

None known based on information supplied.

Hazardous Decomposition Products

None known based on information supplied.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information	No data available
Inhalation	No data available.
Eye contact	No data available.
Skin Contact	No data available.
Ingestion	No data available.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Linseed Oil 8001-26-1	> 15,000 mg/kg	-	-
Vineral Spirits (Rule 66) 64742-47-8	> 5000 mg/kg (Rat)	> 2000 mg/kg (Rabbit)	> 5.2 mg/L (Rat)4 h
Crystalline Silica 14808-60-7	= 500 mg/kg (Rat)	-	-
Solvent Naphtha, Medium Aliphatic 64742-88-7	> 25 mL/kg (Rat)	> 3000 mg/kg (Rabbit)	> 13 mg/L (Rat)4 h
Stoddard Solvent 8052-41-3	-	> 3000 mg/kg (Rabbit)	-
Nethyl Ethyl Ketoxime 96-29-7	= 930 mg/kg (Rat)	1000 - 1800 mg/kg (Rabbit)	> 4800 mg/m³(Rat)4 h
Carbon Black 1333-86-4	> 15400 mg/kg (Rat)	> 3 g/kg (Rabbit)	-
/lineral Spirits 64742-48-9	> 5000 mg/kg (Rat)	> 3160 mg/kg (Rabbit)	1.1 - 1.9 mg/L (Rat)4 h

Information on toxicological effects

Symptoms

No information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization	No informat	ion available.		
Germ cell mutagenicity	No information available.			
Carcinogenicity	No informat	ion available.		
Chemical Name	ACGIH	IARC	NTP	OSHA
Crystalline Silica 14808-60-7	A2	Group 1	Known	Х
Carbon Black 1333-86-4	A3	Group 2B	-	Х
Neo C9-13 Acid, Cobalt Salts 68955-83-9	-	Group 2B	-	Х
Cobalt neodecanoate 27253-31-2	-	Group 2B	-	Х
Group 1 - Carcinogenic to Group 2B - Possibly Carci Group 3 - Not classifiable NTP (National Toxicolog Known - Known Carcinoge	inogenic to Humans as a human carcinogen by Program) fety and Health Administr No informat No informat e No informat May cause	ration of the US Department of tion available. tion available. tion available. adverse effects on the bone ral nervous system, Eyes, ki	marrow and blood-forming	

Numerical measures of toxicity - Product Information

The following values are calculated based on chapter 3.1 of the GHS document mg/kg

12. ECOLOGICAL INFORMATION

Ecotoxicity

76.4% of the mixture consists of components(s) of unknown hazards to the aquatic environment

Chemical Name	Algae/aquatic plants	Fish	Crustacea
Mineral Spirits (Rule 66) 64742-47-8	-	45: 96 h Pimephales promelas mg/L LC50 flow-through 2.2: 96 h Lepomis macrochirus mg/L LC50	4720: 96 h Den-dronereides heteropoda mg/L LC50
		static 2.4: 96 h Oncorhynchus mykiss mg/L LC50 static	
Solvent Naphtha, Medium Aliphatic 64742-88-7	450: 96 h Pseudokirchneriella subcapitata mg/L EC50	800: 96 h Pimephales promelas mg/L LC50 static	100: 48 h Daphnia magna mg/L EC50
Methyl Ethyl Ketoxime 96-29-7	83: 72 h Desmodesmus subspicatus mg/L EC50	777 - 914: 96 h Pimephales promelas mg/L LC50 flow-through 320 - 1000: 96 h Leuciscus idus mg/L LC50 static 760: 96 h Poecilia reticulata mg/L LC50 static	750: 48 h Daphnia magna mg/L EC50
Carbon Black 1333-86-4	-	-	5600: 24 h Daphnia magna mg/L EC50
Mineral Spirits 64742-48-9	-	2200: 96 h Pimephales promelas mg/L LC50	2.6: 96 h Chaetogammarus marinus mg/L LC50

Persistence and degradability

No information available.

Bioaccumulation

No information available.

Chemical Name		Partition coefficient	
Methyl Ethyl Ketoxime 0.65 96-29-7		0.65	
Other adverse effects	No information available		
13. DISPOSAL CONSIDERATIONS			
Waste treatment methods			
Disposal of wastes Disposal should be in accordance with applicable regional, national and local laws and			

Disposal of wastes	regulations.
Contaminated packaging	Do not reuse container.

US EPA Waste Number D001 U239

This product contains one or more substances that are listed with the State of California as a hazardous waste.

Chemical Name	California Hazardous Waste Status
Neo C9-13 Acid, Cobalt Salts 68955-83-9	Toxic
Cobalt neodecanoate 27253-31-2	Toxic

14. TRANSPORT INFORMATION

DOT

Not regulated

15 REGUI	ATORY INFORMATION	

International Inventories	
TSCA C	Complies
DSL/NDSL C	Complies *
EINECS/ELINCS C	Complies *
ENCS D	oes not comply [•]
IECSC C	Complies *
KECL C	Complies *
PICCS D	oes not comply [•]
AICS D	oes not comply

* This product contains an unknown chemical, therefore, this product's compliance to the inventory list is NOT DETERMINED

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List EINECS/ELINCS - European Inventory of Existing Chemical Substances/European List of Notified Chemical Substances ENCS - Japan Existing and New Chemical Substances IECSC - China Inventory of Existing Chemical Substances KECL - Korean Existing and Evaluated Chemical Substances PICCS - Philippines Inventory of Chemicals and Chemical Substances AICS - Australian Inventory of Chemical Substances

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

Chemical Name	SARA 313 - Threshold Values %	
Umber	1.0	
SARA 311/312 Hazard Categories		
Acute health hazard	Yes	

Chronic Health Hazard	Yes
Fire hazard	Yes
Sudden release of pressure hazard	No
Reactive Hazard	No

US State Regulations

California Proposition 65

This product contains the following Proposition 65 chemicals

California Proposition 65
Carcinogen
Carcinogen
Carcinogen

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts
Crystalline Silica 14808-60-7	X	Х
Solvent Naphtha, Medium Aliphatic 64742-88-7	X	-
Umber 12713-03-0	X	-
Xylene 1330-20-7	X	Х
Carbon Black 1333-86-4	X	Х
Neo C9-13 Acid, Cobalt Salts 68955-83-9	Х	-
Cobalt neodecanoate 27253-31-2	Х	-

Chemical Name	Pennsylvania
Linseed Oil	X
8001-26-1	
Crystalline Silica 14808-60-7	X
14808-60-7	
Umber	X
12713-03-0	

U.S. EPA Label Information

EPA Pesticide Registration Number Not applicable

Hazardous air pollutants (HAPS) content

This product contains no Hazardous Air Pollutants individually at 1% by weight, or greater.

<u>NFPA</u>	Health hazards 2	Flammability 2	Instability 0	Physical and Chemical
HMIS	Health hazards 2 *	Flammability 2	Physical hazards 0	Properties - Personal protection X

Chronic Hazard Star Legend

* = Chronic Health Hazard

01-Dec-2016

Revision Date Revision Note No information available

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text. Shipping information may vary based upon container size and shipping destination. Each user of this material needs to evaluate the conditions of use and design the appropriate protective mechanisms to prevent employee exposures, property damage, or release to the environment. The manufacturer assumes no responsibility for injury to the recipient or third persons, or for any damages to any property resulting from misuse of the product.

End of Safety Data Sheet