


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	G in (mm)	H in (mm)	J in (mm)	K in (mm)	MAX. PANEL THICKNESS in (mm)	MIN. LOOP TENSILE lbs (N)	CROSS SECTION	WEIGHT 100 pcs lbs (g)
	MIN. in (mm)	MAX. in (mm)														
PLWP40SD	.12 (3)	1.58 (40)	.05 (1.3)	.19 (4.8)	.46 (11.7)	.22 (5.6)	.32 (8.1)	7.0 (177.8)	.74 (18.8)	.266 (6.8)	1.3 (33)	.30 (7.6)	.118 (3.0)	50 (222)	STANDARD	.37 (168)

NOTES:

1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.

													DIMENSIONS IN PARENTHESIS ARE IN METRIC UNITS			
													PANDUIT CORP. TINLEY PARK, ILLINOIS			
													WINGED PUSH MOUNT CABLE TIE WITH CONVOLUTED TUBING BUMP TO PREVENT LATERAL AND AXIAL MOVEMENT PLWP40SD			
													UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .1(2.5) (.XXX) ± .020(.51) (.XX) ± .02(.5) ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
													DRAWN BY SO	MAT'L: HEAT STABILIZED NYLON 6.6 BLACK (-30)		SCALE
13	10/25/04	JABO		CHANGED FORMAT FOR CONSISTENCY SEE ECN FOR DETAILS				26268	13				DATE 12-14-90	DRAWING NO. SS-26268		DWG A
REV	DATE	BY	CHK	DESCRIPTION				ECN - R	CUST	SUP			CHK'D HVP	SIZE		