





# THROUGH-THE-WALL AIR CONDITIONER

8,000 BTU | ELECTRONIC




**4PATW8000**

<b>UPC CODE</b>	842149025649
<b>COOLING CAPACITY (BTU)</b>	8000
<b>ENERGY STAR</b>	Yes
<b>COVERAGE AREA (sq. ft.)</b>	350
<b>CEER</b>	10.6
<b>VOLTAGE</b>	115V
<b>AMPS</b>	7
<b>WATTS</b>	783
<b>FAN SPEEDS (cool/fan)</b>	3/3
<b>UNIT DIMENSIONS (W×H×D) (in.)</b>	24.25×14.25×20.25
<b>PKG. DIMENSIONS (W×H×D) (in.)</b>	28×17×27
<b>WEIGHT (Net/Gross) (lbs.)</b>	65/78
<b>CONTAINER QTY. (40HQ)</b>	306
<b>REFRIGERANT</b>	R410A
<b>OUTLET CONFIGURATION</b>	 15A - 115V

## CHOOSING THE RIGHT AIR CONDITIONER

### 1 MEASURE AREA OF THE ROOM



### 2 MATCH ROOM SIZE WITH CORRECT BTUs

SQ. FT.	ROOM SIZE	BTUs
150	10' × 15'	5,000
250	10' × 25'	6,000
350	17' × 20'	8,000
450	15' × 30'	10,000
550	20' × 27'	12,000
700	20' × 35'	15,000
1,000	25' × 40'	18,000
1,500	30' × 50'	25,000

### 3 MAKE ANY ADJUSTMENTS



**INCREASE BTU 10%** FOR SUNNY ROOMS. DECREASE BTU 10% FOR SHADED ROOMS.



**ADD 600 BTUs** FOR EACH ADDITIONAL PERSON OVER TWO.



**ADD 4,000 BTUs** IF UNIT IS USED IN A KITCHEN.

## FEATURES

- Fits most standard through-the-wall AC sleeves
- 3 cooling & 3 fan speeds
- 4-way adjustable air vents
- Cool, Fan, Eco, and Sleep modes
- Quick & easy installation
- Mounting kit included
- Electronic controls
- Follow-me remote control acts as portable thermostat
- 24-hour timer
- Auto-restart
- Adjustable thermostat (62-86°F)
- Easy clean tilt-out filter

