



### Specialties for Copper and Steel/PVC pipe

- Hot Tapping Saddles/Sleeves
- Line Stopping Saddles/Sleeves
- Pipe Freezing Kits
- Pipe Repair Clamps
- Extra Deep Hole Saws

### Brand Names You Can Trust!

PowerSeal ● JCM ● Jet Swet ● Smith-Blair ● Wheeler Rex  
TapMaster ● Blu-Mol ● Relton ● General Wire ● Qwik-Freezer

*Home of the Insta-Clamp™ Solder Joint Repair Clamp ½" to 6.00"*

## Mighty Deep™ Extra Depth Bi Metal and Carbide Hole Saws



Mighty Deep™ Bi Metal Hole Saws 3.25" to 3.75" Drill Depths



Mighty Deep™ Carbide Hole Saws 3.25" to 3.75" Drill Depths

**Bi Metal Recommended For:** Steel, Copper, Aluminum, Brass, PVC, Plastic or Wood

**Carbide Recommended For:** Ductile Iron, Cast Iron and A/C Pipe, Wood Laminates, Fiberglass, Plywood or Tile

### Specifications:

- **Bi Metal:** Cobalt Steel Construction - 4/6-Variable Teeth per inch
- **Carbide:** Tungsten Carbide Construction – 3-Teeth per inch
- 3.25" dd (1-1/2" to 6.00" dia.) 3.75" dd (6-5/8" to 7-7/8" dia.)
- High Speed cutting edge
- Provides shock resistant teeth
- Resists tooth strippage
- 3/16" Thick heavy duty backing plate
- Eliminates Need for Drive Plate
- All seams welded construction
- Thin Kerf thickness for fast and smooth cuts
- Better battery life when used with cordless tools
- Causes less vibration

*CAUTION: These cutting tools may break or shatter under improper use. U.S. Government regulations requires the use of safety glasses and other appropriate safety attire at all times in the area of use.*

*Limited supply in some sizes - Please call to check stock*