























## LED Outdoor Non-Cutoff and Semi-Cutoff Wall Pack WMG MODEL

#### **DESCRIPTION**

The **SOLTECH WMG** Traditional wall pack is an integrated LED solution that delivers long life and energy savings. The heavy duty cast aluminum housing offers advanced thermal management and protection against outdoor environments without compromising aesthetics.

#### **APPLICATION:**

SOLTECH Wallpack Series are ideal for brightly-lit outdoor wall mount applications in parking garages, entrances, public areas, schools, hospitals, hotels and outdoor walkways that demand long service life and low maintenance.

# Occupancy Microwave **Sensor Option**

#### **FEATURES**

#### **PERFORMANCE:**

**SOLTECH WALLPACK** lights have a variety of series which are ideal to replace metal halide fixtures. These lights can save energy and require lower maintenance costs.

Available in varying ranges:

- -30W
- -50W
- .80W
- -100W
- 120W

Lumens are from 1,320 to 13,800Lm

#### **HOUSING:**

ADC12 aluminum heat sink, outdoor powder coating finish, ideal waterproof design.

#### **FINISHES:**

The WMG is available in:

• BR= Bronze

#### **PHOTOMETRICS:**

Please see page 3 for photometric layouts. All of our IES files will be available at www.soltechlighting.com

#### **OPTICAL LENS:**

High light transmittance >93% Prismatic lens, premium appearance

#### **MOUNTING:**

Luminaire mounting designed for standard J-Box. Can be mounted directly to surface. Features multiple 1/2 NPS knockouts.conduit entries.

#### **ELECTRICAL:**

100-277V, 60Hz AC, PF≥0.9; THD<20%, with optimal quality backed by 20 years of successful manufacturing experience

LUMILEDS(LED); CRI>80, Low degradation applied adhesive on the LED soldering position on PCB for protection.

#### **CERTIFICATIONS/REGULATORY:**

UL listed, DLC listed, IP65 rating. All components have safety approvals.

#### **WARRANTY:**

We have a 5-year limited warranty, see complete warranty terms for details.

Warranty Guidelines include but are not limited to:

- Product must be rated for the application per the Product Data Sheet (PDS).
- Light must be used less than 16 hours a day
- Must be in ambient of -40°F to 120°F

#### **ADDITIONAL NOTATIONS:**

Heat sink aluminum material with excellent cooling design Competitive lumen efficacy of up to 140LM/W.

Operating Temperature:

-40° ~ 120°F, 4KV surge protection.

More information provided at www.soltechlighting.com/support













JOB NAN	1E: _		
DATE:			
TYPE:			











# LED Outdoor Non-Cutoff and Semi-Cutoff Wall Pack WMG MODEL

#### **SUMMARY**

HOUSING	ACD12 aluminum heat sink, Outdoor powder coating.
VOLTAGE	100–277V, 60Hz AC
LED	LumiLEDs
EFFICACY	140 LM/W
LUMENS@5000K	4,200–17,100 lumens
POWER FACTOR	≥0.9
BEAM ANGLE	120°
THD	<20%
OPERATING TEMP	-40°F-120°F
ALUMINUM LED BOARD	High conductive, Waterproof, Aging resistance, Salt mist resistance, Long-life.
CONTROLS / DIMMING	0–10V Dimming
ССТ	3000K, 4000K and 5000K
CRI	>80
RATED LIFE	70,000 hours

## **DARK SKY SHIELD**

If need, we have **DARK SKY SHIELD** available.



#### **ENERGY PERFORMANCE DATA**

MODEL	DIMENSION (in)	VOLTAGE (V)	WATT (w-8%-+5%)	LUMENS @ 5000K(Lm)	EFFICACY (Lm/w)	DIMMING
STLWMG30XYYZZ	8.54X8.63X9.75 in	100-277	30	4,200	140	Non-Dimmable
STLWMG50XYYZZ	15.06X9.29X7.46 in	100-277	50	7,100	142	Non-Dimmable
STLWMG80XYYZZ	15.06X9.29X7.46 in	100-277	80	11,600	145	0-10V/PWM/VR
STLWMG100XYYZZ	15.06X9.29X7.46 in	100-277	100	14,300	143	0-10V/PWM/VR
STLWMG120XYYZZ	18.29X9.09X9.4 in	100-277	120	17,100	143	0-10V/PWM/VR

### **ORDERING INFORMATION**

Sample Number: STLWMG1004WMBR

SOLTECH Wall Pack WMG 100 watt, 4000k, Wall mount installation, with a Bronze finish

installation, with a Bronze finish.								
	SERIES	WATT (w -8%-+5%)	COLOR TEMP (x)	MOUNTING OPTIONS (YY)	FINISH (zz)	VOLTAGE (V) (Blank)	OPTIC TYPE (Blank)	DIMMING (Blank)
	<b>STL</b> WMG	30	<b>3</b> =3000K	<b>WM</b> =WALL MOUNT	<b>BR</b> =BRONZE	100-277	120°	Non-Dimmable
		50	<b>4</b> =4000K					0-10V/PWM/VR
		80	<b>5</b> =5000K					
		100						

120




























# LED Outdoor Non-Cutoff and Semi-Cutoff Wall Pack

## **WMG MODEL**


#### **DIMENSIONAL DRAWING**


## 30W







# 50W, 80W & 100W





#### 120W





#### **PHOTOMETRICS:**

