




UD14-7-7-SS

Ruland UD14-7-7-SS, 7/16" x 7/16" Double Universal Joint, Friction Bearing, Stainless Steel, 0.870" OD, 4.375" Length



Description

Ruland UD14-7-7-SS is a double cardan friction bearing universal joint with 0.4375" x 0.4375" bores, 0.870" OD, and 4.375" length. It is ideal for applications with wide distances between shafts and can accommodate all forms of misalignment. This plain bearing double universal joint is comprised of pins and blocks that are precision machined, selectively heat treated, and ground for high strength, accuracy, and wear resistance. The combination of these components with precision ground and hardened yoke ears allow for a longer lifespan, increased performance in demanding applications, and greater angular misalignment of up to 90° when compared to commodity style double universal joints. UD14-7-7-SS is made from high grade stainless steel for increased corrosion resistance. It can be combined with boot UBOOT14/22-NI-KIT to protect the joints from unwanted contaminants such as dust or water and self lubricate reducing maintenance time. This double cardan universal joint is manufactured in the USA by Belden Universal for strict control of processes.

Product Specifications

Bore (B1)	0.4375 in	Small Bore (B2)	0.4375 in
B1 Max Shaft Penetration	1.030 in	B2 Max Shaft Penetration	1.030 in
Joint Outer Diameter (OD)	0.870 in	Bore Tolerance	+0.0010 in / -0.0000 in
Length (L)	4.375 in	Center Yoke Length (LC)	1.375 in
Yoke Length (LY)	1.500 in	Hub Depth (LH)	1.030 in
Peak Torque	1,125 in-lb	Rated Torque	225 in-lb
Max Operating Angle	90°	Material Specification	Yokes: 303 Stainless Steel Pins and Blocks: 416 Stainless Steel
Manufacturer	Belden Universal	Country of Origin	USA
Weight (lbs)	0.524000	Recommended Lubricant	LUBRIPLATE No. 1200-2
Matching Boot Cover	UBOOT14/22-NI-KIT	UPC	634529288337
Tariff Code	8483.60.4000	UNSPC	25173810
Note 1	Performance ratings are for guidance only. The user must determine suitability for a particular application.		
Prop 65	⚠️ WARNING This product can expose you to the chemical Nickel (metallic), known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov .		