




US14-7-7-F

Ruland US14-7-7-F, 7/16" x 7/16" Single Universal Joint, Friction Bearing, Steel, 0.870" OD, 3.000" Length



Description

Ruland US14-7-7-F is a single cardan friction bearing universal joint with 0.4375" x 0.4375" bores, 0.870" OD, and 3.000" length. It is ideal for applications with space constraints and has higher torque capacity than equivalently sized double universal joints. This plain bearing universal joint is comprised of pins and blocks that are precision machined, selectively heat treated, and ground for high strength, accuracy, and wear resistance. The combination of these components with precision ground and hardened yoke ears allow for a longer lifespan, increased performance in demanding applications, and greater angular misalignment of up to 45° when compared to commodity style single universal joints. US14-7-7-F is made from high grade alloy steel for durability and high strength. It can be combined with boot UBOOT14/22-NI-KIT to protect the joint from unwanted contaminants such as dust or water and self lubricate reducing maintenance time. This single cardan universal joint is manufactured in the USA by Belden Universal for strict control of processes.

Product Specifications

Bore (B1)	0.4375 in	Small Bore (B2)	0.4375 in
B1 Max Shaft Penetration	1.030 in	B2 Max Shaft Penetration	1.030 in
Joint Outer Diameter (OD)	0.870 in	Bore Tolerance	+0.0010 in / -0.0000 in
Length (L)	3.000 in	Yoke Length (LY)	1.500 in
Hub Depth (LH)	1.030 in	Peak Torque	1,750 in-lb
Rated Torque	350 in-lb	Max Operating Angle	45°
Material Specification	Alloy Steel	Manufacturer	Belden Universal
Country of Origin	USA	Weight (lbs)	0.340000
Recommended Lubricant	LUBRIPLATE No. 1200-2	Matching Boot Cover	UBOOT14/22-NI-KIT
UPC	634529289570	Tariff Code	8483.60.4000
UNSPC	25173810		
Note 1	Performance ratings are for guidance only. The user must determine suitability for a particular application.		
Prop 65	⚠️ WARNING This product can expose you to the chemical Ethylene Thiourea, known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov .		