

# Safety Data Sheet



## 1. Identification

**Product Name:** PTOUCH QT 2PK GLOSS BLACK **Revision Date:** 3/10/2017  
**Product Identifier:** 1979502 **Supersedes Date:** 5/15/2015  
**Product Use/Class:** Topcoat/WB Acrylic  
**Supplier:** Rust-Oleum Corporation **Manufacturer:** Rust-Oleum Corporation  
 11 Hawthorn Parkway 11 Hawthorn Parkway  
 Vernon Hills, IL 60061 USA Vernon Hills, IL 60061  
 USA  
**Preparer:** Regulatory Department  
**Emergency Telephone:** 24 Hour Hotline: 847-367-7700

## 2. Hazard Identification

### Classification

### Symbol(s) of Product

Not a hazardous substance or mixture per 2012 OSHA Hazard Communication Standard 29 CFR 1910.1200.

### Signal Word

No Signal Word has been assigned.

### Possible Hazards

3% of the mixture consists of ingredient(s) of unknown acute toxicity.

## 3. Composition/Information On Ingredients

### HAZARDOUS SUBSTANCES

<u>Chemical Name</u>	<u>CAS-No.</u>	<u>Wt.% Range</u>	<u>GHS Symbols</u>	<u>GHS Statements</u>
Dipropylene Glycol Monobutyl Ether	29911-28-2	2.5-10	Not Available	Not Available
Carbon Black	1333-86-4	0.1-1.0	Not Available	Not Available
Sodium Nitrite	7632-00-0	0.1-1.0	GHS03-GHS06	H272-301-331

## 4. First-aid Measures

**FIRST AID - EYE CONTACT:** Immediately flush eyes with plenty of water for at least 15 minutes holding eyelids open. Get medical attention. Do NOT allow rubbing of eyes or keeping eyes closed.

**FIRST AID - SKIN CONTACT:** Wash skin with soap and water. Remove contaminated clothing. Get medical attention if irritation develops or persists.

**FIRST AID - INHALATION:** Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get immediate medical attention. Do NOT use mouth-to-mouth resuscitation. If you experience difficulty in breathing, leave the area to obtain fresh air. If continued difficulty is experienced, get medical assistance immediately.

**FIRST AID - INGESTION:** Swallowing less than an ounce will not cause significant harm. For larger amounts, do not induce vomiting, but give one or two glasses of water to drink and get medical attention. If swallowed, rinse mouth with water. If feeling unwell, get medical attention.

## 5. Fire-fighting Measures

**EXTINGUISHING MEDIA:** Alcohol Film Forming Foam, Carbon Dioxide, Dry Chemical, Dry Sand, Water Fog

**UNUSUAL FIRE AND EXPLOSION HAZARDS:** FLASH POINT IS TESTED TO BE GREATER THAN 200 DEGREES F. No unusual fire or explosion hazards noted. Keep containers tightly closed.

**SPECIAL FIREFIGHTING PROCEDURES:** Water may be used to cool closed containers to prevent buildup of steam. If water is used, fog nozzles are preferred.

## 6. Accidental Release Measures

**STEPS TO BE TAKEN IF MATERIAL IS RELEASED OR SPILLED:** Dispose of according to local, state (provincial) and federal regulations. Do not incinerate closed containers. If spilled, contain spilled material and remove with inert absorbent. Dispose of contaminated absorbent, container, and unused contents in accordance with local, state, and federal regulations. Do not incinerate closed containers

## 7. Handling and Storage

**HANDLING:** Wash thoroughly after handling. Wash hands before eating. Avoid contact with eyes. Remove contaminated clothing and launder before reuse. Use only with adequate ventilation. Follow all MSDS/label precautions even after container is emptied because it may retain product residues. Avoid breathing fumes, vapors, or mist. Avoid contact with eyes, skin and clothing.

**STORAGE:** Keep from freezing. Keep container closed when not in use. Store in a dry, well ventilated place. Keep container tightly closed when not in use.

## 8. Exposure Controls/Personal Protection

Chemical Name	CAS-No.	Weight % Less Than	ACGIH TLV- TWA	ACGIH TLV- STEL	OSHA PEL-TWA	OSHA PEL- CEILING
Dipropylene Glycol Monobutyl Ether	29911-28-2	5.0	N.E.	N.E.	N.E.	N.E.
Carbon Black	1333-86-4	1.0	3 mg/m <sup>3</sup>	N.E.	3.5 mg/m <sup>3</sup>	N.E.
Sodium Nitrite	7632-00-0	1.0	N.E.	N.E.	N.E.	N.E.

### PERSONAL PROTECTION

**ENGINEERING CONTROLS:** Use process enclosures, local exhaust ventilation, or other engineering controls to control airborne levels below recommended exposure limits. Prevent build-up of vapors by opening all doors and windows to achieve cross-ventilation.

**RESPIRATORY PROTECTION:** A respiratory protection program that meets OSHA 1910.134 and ANSI Z88.2 requirements must be followed whenever workplace conditions warrant a respirator's use.

**SKIN PROTECTION:** Use gloves to prevent prolonged skin contact. Nitrile or Neoprene gloves may afford adequate skin protection.

**EYE PROTECTION:** Use safety eyewear designed to protect against splash of liquids.

**OTHER PROTECTIVE EQUIPMENT:** Refer to safety supervisor or industrial hygienist for further information regarding personal protective equipment and its application. Refer to safety supervisor or industrial hygienist for further guidance regarding types of personal protective equipment and their applications.

**HYGIENIC PRACTICES:** Wash thoroughly with soap and water before eating, drinking or smoking. Remove contaminated clothing immediately and launder before reuse.

## 9. Physical and Chemical Properties

<b>Appearance:</b>	Liquid	<b>Physical State:</b>	Liquid
<b>Odor:</b>	Solvent Like	<b>Odor Threshold:</b>	N.E.
<b>Relative Density:</b>	1.034	<b>pH:</b>	N.E.
<b>Freeze Point, °C:</b>	N.D.	<b>Viscosity:</b>	N.D.
<b>Solubility in Water:</b>	Soluble	<b>Partition Coefficient, n-octanol/water:</b>	N.D.
<b>Decomposition Temp., °C:</b>	N.D.	<b>Explosive Limits, vol%:</b>	2.6 - 12.6
<b>Boiling Range, °C:</b>	100 - 230	<b>Flash Point, °C:</b>	94
<b>Flammability:</b>	Does not Support Combustion	<b>Auto-ignition Temp., °C:</b>	N.D.
<b>Evaporation Rate:</b>	Slower than Ether	<b>Vapor Pressure:</b>	N.D.
<b>Vapor Density:</b>	Lighter than Air		

(See "Other information" Section for abbreviation legend)

## 10. Stability and Reactivity

**CONDITIONS TO AVOID:** Avoid contact with strong acid and strong bases.

**INCOMPATIBILITY:** Incompatible with strong oxidizing agents, strong acids and strong alkalies.

**HAZARDOUS DECOMPOSITION:** By open flame, carbon monoxide and carbon dioxide. When heated to decomposition, it emits acrid smoke and irritating fumes.

**HAZARDOUS POLYMERIZATION:** Will not occur under normal conditions.

**STABILITY:** This product is stable under normal storage conditions.

## 11. Toxicological information

**EFFECTS OF OVEREXPOSURE - EYE CONTACT:** Causes eye irritation. Irritating, and may injure eye tissue if not removed promptly.

**EFFECTS OF OVEREXPOSURE - SKIN CONTACT:** Substance may cause slight skin irritation. Low hazard for usual industrial handling or commercial handling by trained personnel.

**EFFECTS OF OVEREXPOSURE - INHALATION:** Low hazard for usual industrial handling or commercial handling by trained personnel. High gas, vapor, mist or dust concentrations may be harmful if inhaled. Avoid breathing fumes, spray, vapors, or mist.

**EFFECTS OF OVEREXPOSURE - INGESTION:** Substance may be harmful if swallowed.

**EFFECTS OF OVEREXPOSURE - CHRONIC HAZARDS:** Contains carbon black. Chronic inflammation, lung fibrosis, and lung tumors have been observed in some rats experimentally exposed for long periods of time to excessive concentrations of carbon black and several insoluble fine dust particles. Tumors have not been observed in other animal species (i.e., mouse and hamster) under similar circumstances and study conditions. Epidemiological studies of North American workers show no evidence of clinically significant adverse health effects due to occupational exposure to carbon black.

Carbon black is listed as a Group 2B-"Possibly carcinogenic to humans" by IARC and is proposed to be listed as A4- "not classified as a human carcinogen" by the American Conference of Governmental Industrial Hygienists. Significant exposure is not anticipated during brush application or drying. Risk of overexposure depends on duration and level of exposure to dust from repeated sanding of surfaces or spray mist and the actual concentration of carbon black in the formula.

**PRIMARY ROUTE(S) OF ENTRY:** Eye Contact, Ingestion, Inhalation, Skin Absorption, Skin Contact

### ACUTE TOXICITY VALUES

The acute effects of this product have not been tested. Data on individual components are tabulated below:

<u>CAS-No.</u>	<u>Chemical Name</u>	<u>Oral LD50</u>	<u>Dermal LD50</u>	<u>Vapor LC50</u>
1333-86-4	Carbon Black	>15400 mg/kg Rat	N.I.	N.I.
7632-00-0	Sodium Nitrite	85 mg/kg Rat	N.I.	5.5 mg/L Rat

N.I. - No Information

## 12. Ecological Information

**ECOLOGICAL INFORMATION:** Product is a mixture of listed components.

## 13. Disposal Information

**DISPOSAL INFORMATION:** Dispose of material in accordance to local, state, and federal regulations and ordinances. Do not allow to enter waterways, wastewater, soil, storm drains or sewer systems.

## 14. Transport Information

	<u>Domestic (USDOT)</u>	<u>International (IMDG)</u>	<u>Air (IATA)</u>	<u>TDG (Canada)</u>
UN Number:	N.A.	N.A.	N.A.	N.A.
Proper Shipping Name:	Not Regulated	Not Regulated	Not Regulated	Not Regulated
Hazard Class:	N.A.	N.A.	N.A.	N.A.
Packing Group:	N.A.	N.A.	N.A.	N.A.
Limited Quantity:	No	No	No	No

## 15. Regulatory Information

### U.S. Federal Regulations:

#### CERCLA - SARA Hazard Category

This product has been reviewed according to the EPA 'Hazard Categories' promulgated under Sections 311 and 312 of the Superfund Amendment and Reauthorization Act of 1986 (SARA Title III) and is considered, under applicable definitions, to meet the following categories:

Acute Health Hazard, Chronic Health Hazard

#### Sara Section 313:

This product contains the following substances subject to the reporting requirements of Section 313 of Title III of the Superfund Amendment and Reauthorization Act of 1986 and 40 CFR part 372:

<u>Chemical Name</u>	<u>CAS-No.</u>
Sodium Nitrite	7632-00-0

#### Toxic Substances Control Act:

This product contains the following chemical substances subject to the reporting requirements of TSCA 12(b) if exported from the United States:

<u>Chemical Name</u>	<u>CAS-No.</u>
Sodium Nitrite	7632-00-0

**16. Other Information****HMIS RATINGS**

Health: 1\*      Flammability: 1      Physical Hazard: 0      Personal Protection: X

**NFPA RATINGS**

Health: 1      Flammability: 1      Instability: 0

**VOLATILE ORGANIC COMPOUNDS, g/L:** 174

**SDS REVISION DATE:** 3/10/2017

**REASON FOR REVISION:** Product Composition Changed  
Substance and/or Product Properties Changed in Section(s):  
01 - Identification  
02 - Hazard Identification  
05 - Fire-fighting Measures  
09 - Physical & Chemical Properties  
15 - Regulatory Information  
16 - Other Information  
Statement(s) Changed

Legend: N.A. - Not Applicable, N.E. - Not Established, N.D. - Not Determined

The manufacturer believes, to the best of its knowledge, information and belief, the information contained herein to be accurate and reliable as of the date of this safety data sheet. However, because the conditions of handling, use, and storage of these materials are beyond our control, we assume no responsibility or liability for personal injury or property damage incurred by the use of these materials. The manufacturer makes no warranty, expressed or implied, regarding the accuracy or reliability of the data or results obtained from their use. All materials may present unknown hazards and should be used with caution. The information and recommendations in this material safety data sheet are offered for the users' consideration and examination. It is the responsibility of the user to determine the final suitability of this information and to comply with all applicable international, federal, state, and local laws and regulations.