Date Printed: 8/31/2015 Page 1 / 6

Safety Data Sheet



* Trusted Quality Since 1921 * www.rustoleum.com

1. Identification

PTOUCH UC HP 6PK FLAT WHITE PRIMER Revision Date: 8/24/2015 **Product Name:**

New SDS **Product Identifier:** 267268 Supercedes Date:

Product Use/Class: Primer/Waterbased Latex

Rust-Oleum Corporation Rust-Oleum Corporation Supplier: Manufacturer: 11 Hawthorn Parkway

11 Hawthorn Parkway Vernon Hills, IL 60061

USA

Vernon Hills, IL 60061 USA

Preparer: Regulatory Department

Emergency Telephone: 24 Hour Hotline: 847-367-7700

2. Hazard Identification

Classification

Symbol(s) of Product



Signal Word Warning

GHS HAZARD STATEMENTS

H317 May cause an allergic skin reaction. Skin Sensitizer, category 1

GHS LABEL PRECAUTIONARY **STATEMENTS**

Avoid breathing dust, fumes, gases, mists, vapors, or spray. P261

P280 Wear protective gloves/protective clothing/eye protection/face protection.

P302+P352 IF ON SKIN: Wash with plenty of soap and water.

P333+P313 If skin irritation or rash occurs: Get medical advice/attention.

GHS SDS PRECAUTIONARY STATEMENTS

P363 Wash contaminated clothing before reuse.

3. Composition/Information On Ingredients

HAZARDOUS SUBSTANCES

<u>Chemical Name</u>	CAS-No.	Wt.% Range	GHS Symbols	GHS Statements
Limestone	1317-65-3	10-25	No Information	No Information
Titanium Dioxide	13463-67-7	10-25	No Information	No Information
Dipropylene Glycol Monobutyl Ether	29911-28-2	2.5-10	No Information	No Information

Date Printed: 8/31/2015 Page 2 / 6

Zinc Phosphate	7779-90-0	1.0-2.5	No Information	No Information
Hydrotreated Heavy Paraffinic Petroleum Distillates	64742-54-7	0.1-1.0	No Information	No Information
Sodium Nitrite	7632-00-0	0.1-1.0	GHS03-GHS06	H272-301-331
Ammonia	7664-41-7	0.1-1.0	GHS05-GHS06	H302-314-331
5-Chloro-2-Methyl-4-Isothiazolin-3-One Mixture with 2-Methyl-4-Isothiazolin-3-On	55965-84-9	<0.1	GHS05-GHS06	H301-311-314-317-331

4. First-aid Measures

FIRST AID - EYE CONTACT: Immediately flush eyes with plenty of water for at least 15 minutes holding eyelids open. Get medical attention. Do NOT allow rubbing of eyes or keeping eyes closed.

FIRST AID - SKIN CONTACT: Wash skin with soap and water. Remove contaminated clothing. Get medical attention if irritation develops or persists.

FIRST AID - INHALATION: Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get immediate medical attention. Do NOT use mouth-to-mouth resuscitation. If you experience difficulty in breathing, leave the area to obtain fresh air. If continued difficulty is experienced, get medical assistance immediately.

FIRST AID - INGESTION: If swallowed, rinse mouth with water. If feeling unwell, get medical attention. Swallowing less than an ounce will not cause significant harm. For larger amounts, do not induce vomiting, but give one or two glasses of water to drink and get medical attention.

5. Fire-fighting Measures

EXTINGUISHING MEDIA: Alcohol Film Forming Foam, Carbon Dioxide, Dry Chemical, Dry Sand, Water Fog

UNUSUAL FIRE AND EXPLOSION HAZARDS: Keep containers tightly closed. FLASH POINT IS TESTED TO BE GREATER THAN 200 DEGREES F. No unusual fire or explosion hazards noted.

SPECIAL FIREFIGHTING PROCEDURES: Water may be used to cool closed containers to prevent buildup of steam. If water is used, fog nozzles are preferred.

6. Accidental Release Measures

STEPS TO BE TAKEN IF MATERIAL IS RELEASED OR SPILLED: If spilled, contain spilled material and remove with inert absorbent. Dispose of contaminated absorbent, container, and unused contents in accordance with local, state, and federal regulations. Do not incinerate closed containers Dispose of according to local, state (provincial) and federal regulations. Do not incinerate closed containers.

7. Handling and Storage

HANDLING: Wash thoroughly after handling. Wash hands before eating. Remove contaminated clothing and launder before reuse. Use only with adequate ventilation. Follow all MSDS/label precautions even after container is emptied because it may retain product residues. Avoid breathing fumes, vapors, or mist. Avoid contact with eyes, skin and clothing. Avoid contact with eyes.

STORAGE: Store in a dry, well ventilated place. Keep container tightly closed when not in use. Keep from freezing. Keep container closed when not in use.

8. Exposure Controls/Personal Protection

Chemical Name	CAS-No.	Weight % Less Than	ACGIH TLV- TWA	ACGIH TLV- STEL	OSHA PEL-TWA	OSHA PEL- CEILING
Limestone	1317-65-3	15.0	N.E.	N.E.	15 mg/m3	N.E.
Titanium Dioxide	13463-67-7	15.0	10 mg/m3	N.E.	15 mg/m3	N.E.
Dipropylene Glycol Monobutyl Ether	29911-28-2	5.0	N.E.	N.E.	N.E.	N.E.
Zinc Phosphate	7779-90-0	5.0	N.E.	N.E.	N.E.	N.E.
Hydrotreated Heavy Paraffinic Petroleum Distillates	64742-54-7	1.0	N.E.	N.E.	N.E.	N.E.
Sodium Nitrite	7632-00-0	1.0	N.E.	N.E.	N.E.	N.E.
Ammonia	7664-41-7	1.0	25 ppm	35 ppm	50 ppm	N.E.

Date Printed: 8/31/2015 Page 3 / 6

5-Chloro-2-Methyl-4-						
Isothiazolin-3-One Mixture with	55965-84-9	0.1	N.E.	N.E.	N.E.	N.E.
2-Methyl-4-Isothiazolin-3-On						

PERSONAL PROTECTION

ENGINEERING CONTROLS: Use process enclosures, local exhaust ventilation, or other engineering controls to control airborne levels below recommended exposure limits. Prevent build-up of vapors by opening all doors and windows to achieve cross-ventilation.

RESPIRATORY PROTECTION: A respiratory protection program that meets OSHA 1910.134 and ANSI Z88.2 requirements must be followed whenever workplace conditions warrant a respirator's use.

SKIN PROTECTION: Use gloves to prevent prolonged skin contact. Nitrile or Neoprene gloves may afford adequate skin protection.

EYE PROTECTION: Use safety eyewear designed to protect against splash of liquids.

OTHER PROTECTIVE EQUIPMENT: Refer to safety supervisor or industrial hygienist for further guidance regarding types of personal protective equipment and their applications. Refer to safety supervisor or industrial hygienist for further information regarding personal protective equipment and its application.

HYGIENIC PRACTICES: Wash thoroughly with soap and water before eating, drinking or smoking. Remove contaminated clothing immediately and launder before reuse.

9. Physical and Chemical Properties

Appearance: **Physical State:** Liquid Liquid Odor: **Odor Threshold:** Solvent Like N.E. Relative Density: pH: 1.283 N.A. Freeze Point, °C: N.D. Viscosity: N.D. Partition Coefficient, n-Solubility in Water: Miscible N.D. octanol/water: Decompostion Temp., °C: N.D. Boiling Range, °C: Explosive Limits, vol%: 100 - 2312.6 - 12.6Flammability: Flash Point, °C: 94 Does not Support Combustion **Evaporation Rate:** Auto-ignition Temp., °C: Slower than Ether N.D. Vapor Density: Vapor Pressure: Heavier than Air N.D.

(See "Other information" Section for abbreviation legend)

10. Stability and Reactivity

CONDITIONS TO AVOID: Avoid contact with strong acid and strong bases.

INCOMPATIBILITY: Incompatible with strong oxidizing agents, strong acids and strong alkalies.

HAZARDOUS DECOMPOSITION: By open flame, carbon monoxide and carbon dioxide. When heated to decomposition, it emits acrid smoke and irritating fumes.

HAZARDOUS POLYMERIZATION: Will not occur under normal conditions.

STABILITY: This product is stable under normal storage conditions.

11. Toxicological information

EFFECTS OF OVEREXPOSURE - EYE CONTACT: Causes eye irritation. Irritating, and may injure eye tissue if not removed promptly.

EFFECTS OF OVEREXPOSURE - SKIN CONTACT: Substance may cause slight skin irritation. Low hazard for usual industrial handling or commercial handling by trained personnel.

EFFECTS OF OVEREXPOSURE - INHALATION: High gas, vapor, mist or dust concentrations may be harmful if inhaled. Avoid breathing fumes, spray, vapors, or mist. Low hazard for usual industrial handling or commercial handling by trained personnel.

EFFECTS OF OVEREXPOSURE - INGESTION: Substance may be harmful if swallowed.

EFFECTS OF OVEREXPOSURE - CHRONIC HAZARDS: Contains Titanium Dioxide. Titanium Dioxide is listed as a Group 2B-"Possibly carcinogenic to humans" by IARC. No significant exposure to Titanium Dioxide is thought to occur during the use of products in which Titanium Dioxide is bound to other materials, such as in paints during brush application or drying. Risk of overexposure depends on duration and level of exposure to dust from repeated sanding of surfaces or spray mist and the actual concentration of Titanium Dioxide in the formula. (Ref: IARC Monograph, Vol. 93, 2010)

PRIMARY ROUTE(S) OF ENTRY: Eye Contact, Ingestion, Inhalation, Skin Absorption, Skin Contact

Date Printed: 8/31/2015 Page 4 / 6

ACUTE TOXICITY VALUES

The acute effects of this product have not been tested. Data on individual components are tabulated below:

CAS-No.	Chemical Name	Oral LD50	Dermal LD50	Vapor LC50
13463-67-7	Titanium Dioxide	>10000 mg/kg Rat	N.I.	N.I.
7779-90-0	Zinc Phosphate	>5000 mg/kg Rat	N.I.	N.I.
7632-00-0	Sodium Nitrite	85 mg/kg Rat	N.I.	5.5 mg/L Rat
7664-41-7	Ammonia	350 mg/kg Rat	N.I.	N.I.

N.I. - No Information

12. Ecological Information

ECOLOGICAL INFORMATION: Product is a mixture of listed components.

13. Disposal Information

DISPOSAL INFORMATION: Dispose of material in accordance to local, state, and federal regulations and ordinances. Do not allow to enter waterways, wastewater, soil, storm drains or sewer systems.

14. Transport Information

	Domestic (USDOT)	International (IMDG)	<u>Air (IATA)</u>	TDG (Canada)
UN Number:	N.A.	N.A.	N.A.	N.A.
Proper Shipping Name:	Not Regulated	Not Regulated	Not Regulated	Not Regulated
Hazard Class:	N.A.	N.A.	N.A.	N.A.
Packing Group:	N.A.	N.A.	N.A.	N.A.
Limited Quantity:	No	No	No	No

15. Regulatory Information

U.S. Federal Regulations:

CERCLA - SARA Hazard Category

This product has been reviewed according to the EPA 'Hazard Categories' promulgated under Sections 311 and 312 of the Superfund Amendment and Reauthorization Act of 1986 (SARA Title III) and is considered, under applicable definitions, to meet the following categories:

Acute Health Hazard, Chronic Health Hazard

Sara Section 313:

This product contains the following substances subject to the reporting requirements of Section 313 of Title III of the Superfund Amendment and Reauthorization Act of 1986 and 40 CFR part 372:

Chemical Name	<u>CAS-No.</u>
Zinc Phosphate	7779-90-0
Sodium Nitrite	7632-00-0
Ammonia	7664-41-7

Toxic Substances Control Act:

This product contains the following chemical substances subject to the reporting requirements of TSCA 12(b) if exported from the United States:

<u>Chemical Name</u>	<u>CAS-No.</u>
Sodium Nitrite	7632-00-0
Methyl-4-Isothiazolin-3-one	2682-20-4
5-Chloro-2-Methyl-4-Isothiazolin-3-one	26172-55-4

Date Printed: 8/31/2015 Page 5 / 6

16. Other Information

HMIS RATINGS

Health: 2* Flammability: 1 Physical Hazard: 0 Personal Protection: X

NFPA RATINGS

Health: 2 Flammability: 1 Instability 0

VOLATILE ORGANIC COMPOUNDS, g/L: 153

SDS REVISION DATE: 8/24/2015

REASON FOR REVISION:

Legend: N.A. - Not Applicable, N.E. - Not Established, N.D. - Not Determined

Rust-Oleum Corporation believes, to the best of its knowledge, information and belief, the information contained herein to be accurate and reliable as of the date of this safety data sheet. However, because the conditions of handling, use, and storage of these materials are beyond our control, we assume no responsibility or liability for personal injury or property damage incurred by the use of these materials. Rust-Oleum Corporation makes no warranty, expressed or implied, regarding the accuracy or reliability of the data or results obtained from their use. All materials may present unknown hazards and should be used with caution. The information and recommendations in this material safety data sheet are offered for the users' consideration and examination. It is the responsibility of the user to determine the final suitability of this information and to comply with all applicable international, federal, state, and local laws and regulations.

Date Printed: 8/31/2015 Page 6 / 6