Date Printed: 9/4/2015 Page 1 / 6

Safety Data Sheet



* Trusted Quality Since 1921 * www.rustoleum.com

1. Identification

Product Name: PTOUCH UC HP 6PK SATIN HUNT CLUB

GREEN

Revision Date:

9/3/2015

Product Identifier: 267314

Supercedes Date:

New SDS

Product Use/Class:

Water-based Styrene-Acrylic Topcoat

Supplier: Rust-Oleum Corporation

11 Hawthorn Parkway Vernon Hills, IL 60061

USA

Manufacturer:

Rust-Oleum Corporation 11 Hawthorn Parkway

Vernon Hills, IL 60061

USA

Preparer: Regulatory Department

Emergency Telephone: 24 Hour Hotline: 847-367-7700

2. Hazard Identification

Classification

Symbol(s) of Product





Signal Word Danger

GHS HAZARD STATEMENTS

Flammable Aerosol, category 1 H222 Extremely flammable aerosol.

Skin Sensitizer, category 1 H317 May cause an allergic skin reaction.

GHS LABEL PRECAUTIONARY

STATEMENTS

P211 Do not spray on an open flame or other ignition source.

P251 Do not pierce or burn, even after use.

P261 Avoid breathing dust, fumes, gases, mists, vapors, or spray.

P280 Wear protective gloves/protective clothing/eye protection/face protection.

P302+P352 IF ON SKIN: Wash with plenty of soap and water.

P333+P313 If skin irritation or rash occurs: Get medical advice/attention.

P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50°C / 122°F.

GHS SDS PRECAUTIONARY STATEMENTS

P363 Wash contaminated clothing before reuse.

3. Composition/Information On Ingredients

Date Printed: 9/4/2015 Page 2 / 6

HAZARDOUS SUBSTANCES

<u>Chemical Name</u>	CAS-No.	Wt.% Range	GHS Symbols	GHS Statements
Limestone	1317-65-3	2.5-10	No Information	No Information
Dipropylene Glycol Monobutyl Ether	29911-28-2	2.5-10	No Information	No Information
Ethanol	64-17-5	1.0-2.5	GHS02	H225
Titanium Dioxide	13463-67-7	1.0-2.5	No Information	No Information
Carbon Black	1333-86-4	0.1-1.0	No Information	No Information
Sodium Nitrite	7632-00-0	0.1-1.0	GHS03-GHS06	H272-301-331
Ammonia	7664-41-7	0.1-1.0	GHS05-GHS06	H302-314-331
N-Methyl 2-Pyrrolidone	872-50-4	0.1-1.0	GHS06	H315-319-331-335
5-Chloro-2-Methyl-4-Isothiazolin-3-One Mixture with 2-Methyl-4-Isothiazolin-3-On	55965-84-9	<0.1	GHS05-GHS06	H301-311-314-317-331
4.4 dimethyloxazolidine	51200-87-4	<0.1	No Information	No Information

4. First-aid Measures

FIRST AID - EYE CONTACT: Immediately flush eyes with plenty of water for at least 15 minutes holding eyelids open. Get medical attention. Do NOT allow rubbing of eyes or keeping eyes closed.

FIRST AID - SKIN CONTACT: Wash skin with soap and water. Remove contaminated clothing. Get medical attention if irritation develops or persists.

FIRST AID - INHALATION: Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get immediate medical attention. Do NOT use mouth-to-mouth resuscitation. If you experience difficulty in breathing, leave the area to obtain fresh air. If continued difficulty is experienced, get medical assistance immediately.

FIRST AID - INGESTION: Swallowing less than an ounce will not cause significant harm. For larger amounts, do not induce vomiting, but give one or two glasses of water to drink and get medical attention. Aspiration hazard: Do not induce vomiting or give anything by mouth because this material can enter the lungs and cause severe lung damage. Get immediate medical attention. If swallowed, get medical attention.

5. Fire-fighting Measures

EXTINGUISHING MEDIA: Alcohol Film Forming Foam, Carbon Dioxide, Dry Chemical, Dry Sand, Water Fog

UNUSUAL FIRE AND EXPLOSION HAZARDS: FLASH POINT IS LESS THAN 20°F. EXTREMELY FLAMMABLE LIQUID AND VAPOR!Water spray may be ineffective. Closed containers may explode when exposed to extreme heat due to buildup of steam. Closed containers may explode when exposed to extreme heat. Vapors may form explosive mixtures with air. Vapors can travel to a source of ignition and flash back. Keep containers tightly closed. Isolate from heat, electrical equipment, sparks and open flame. Perforation of the pressurized container may cause bursting of the can. FLASH POINT IS TESTED TO BE GREATER THAN 200 DEGREES F. No unusual fire or explosion hazards noted.

SPECIAL FIREFIGHTING PROCEDURES: Water may be used to cool closed containers to prevent pressure buildup and possible autoignition or explosion. Water may be used to cool closed containers to prevent buildup of steam. Full protective equipment including self-contained breathing apparatus should be used. Evacuate area and fight fire from a safe distance. Use water spray to keep fire-exposed containers cool. Containers may explode when heated.

6. Accidental Release Measures

STEPS TO BE TAKEN IF MATERIAL IS RELEASED OR SPILLED: Contain spilled liquid with sand or earth. DO NOT use combustible materials such as sawdust. Isolate the hazard area and deny entry to unnecessary and unprotected personnel. Remove all sources of ignition, ventilate area and remove with inert absorbent and non-sparking tools. Dispose of according to local, state (provincial) and federal regulations. Do not incinerate closed containers. Ventilate area, isolate spilled material, and remove with inert absorbent. Dispose of contaminated absorbent, container, and unused contents in accordance with local, state, and federal regulations.

7. Handling and Storage

Date Printed: 9/4/2015 Page 3 / 6

HANDLING: Wash thoroughly after handling. Wash hands before eating. Remove contaminated clothing and launder before reuse. Use only with adequate ventilation. Follow all MSDS/label precautions even after container is emptied because it may retain product residues. Avoid breathing fumes, vapors, or mist. Avoid contact with eyes, skin and clothing. Avoid contact with eyes.

STORAGE: Store in a dry, well ventilated place. Keep container tightly closed when not in use. Keep containers tightly closed. Isolate from heat, electrical equipment, sparks and open flame. Contents under pressure. Do not store above 120 ° F. Store large quantities in buildings designed and protected for storage of NFPA Class I flammable liquids. Keep away from heat, sparks, flame and sources of ignition. Keep from freezing. Keep container closed when not in use. Avoid excess heat. Product should be stored in tightly sealed containers and protected from heat, moisture, and foreign materials.

8. Exposure Controls/Personal Protection

Chemical Name	CAS-No.	Weight % Less Than	ACGIH TLV- TWA	ACGIH TLV- STEL	OSHA PEL-TWA	OSHA PEL- CEILING
Limestone	1317-65-3	10.0	N.E.	N.E.	15 mg/m3	N.E.
Dipropylene Glycol Monobutyl Ether	29911-28-2	5.0	N.E.	N.E.	N.E.	N.E.
Ethanol	64-17-5	5.0	N.E.	1000 ppm	1000 ppm	N.E.
Titanium Dioxide	13463-67-7	5.0	10 mg/m3	N.E.	15 mg/m3	N.E.
Carbon Black	1333-86-4	1.0	3 mg/m3	N.E.	3.5 mg/m3	N.E.
Sodium Nitrite	7632-00-0	1.0	N.E.	N.E.	N.E.	N.E.
Ammonia	7664-41-7	1.0	25 ppm	35 ppm	50 ppm	N.E.
N-Methyl 2-Pyrrolidone	872-50-4	1.0	N.E.	N.E.	N.E.	N.E.
5-Chloro-2-Methyl-4-						
Isothiazolin-3-One Mixture with 2-Methyl-4-Isothiazolin-3-On	55965-84-9	0.1	N.E.	N.E.	N.E.	N.E.
4.4 dimethyloxazolidine	51200-87-4	0.1	N.E.	N.E.	N.E.	N.E.

PERSONAL PROTECTION

ENGINEERING CONTROLS: Use process enclosures, local exhaust ventilation, or other engineering controls to control airborne levels below recommended exposure limits. Use explosion-proof ventilation equipment. Provide general dilution of local exhaust ventilation in volume and pattern to keep TLV of hazardous ingredients below acceptable limits. Prevent build-up of vapors by opening all doors and windows to achieve cross-ventilation.

RESPIRATORY PROTECTION: A respiratory protection program that meets OSHA 1910.134 and ANSI Z88.2 requirements must be followed whenever workplace conditions warrant a respirator's use. A NIOSH/MSHA approved air purifying respirator with organic vapor cartridge or canister may be permissible under certain circumstances where airborne concentrations are expected to exceed exposure limits.

SKIN PROTECTION: Use gloves to prevent prolonged skin contact. Nitrile or Neoprene gloves may afford adequate skin protection.

EYE PROTECTION: Use safety eyewear designed to protect against splash of liquids.

OTHER PROTECTIVE EQUIPMENT: Refer to safety supervisor or industrial hygienist for further guidance regarding types of personal protective equipment and their applications. Refer to safety supervisor or industrial hygienist for further information regarding personal protective equipment and its application.

HYGIENIC PRACTICES: Wash thoroughly with soap and water before eating, drinking or smoking. Remove contaminated clothing immediately and launder before reuse.

9. Physical and Chemical Properties

Appearance: **Physical State:** Aerosolized Mist Liquid Odor: **Odor Threshold:** Solvent Like N.E. Relative Density: 1.096 pH: N.D. Freeze Point, °C: N.D. Viscosity: N.D. Solubility in Water: Partition Coefficient, n-Miscible N.D. octanol/water: Decompostion Temp., °C: N.D. Boiling Range, °C: 64 - 231Explosive Limits, vol%: 1.1 - 36.0Flammability: Flash Point, °C: Supports Combustion 94 **Evaporation Rate:** Slower than Ether Auto-ignition Temp., °C: N.D. Vapor Density: Vapor Pressure: Heavier than Air N.D.

(See "Other information" Section for abbreviation legend)

10. Stability and Reactivity

Date Printed: 9/4/2015 Page 4 / 6

CONDITIONS TO AVOID: Avoid temperatures above 120°F (49°C). Avoid contact with strong acid and strong bases. Avoid all possible sources of ignition.

INCOMPATIBILITY: Incompatible with strong oxidizing agents, strong acids and strong alkalies.

HAZARDOUS DECOMPOSITION: By open flame, carbon monoxide and carbon dioxide. When heated to decomposition, it emits acrid smoke and irritating fumes. Contains solvents which may form carbon monoxide, carbon dioxide, and formaldehyde.

HAZARDOUS POLYMERIZATION: Will not occur under normal conditions.

STABILITY: This product is stable under normal storage conditions.

11. Toxicological information

EFFECTS OF OVEREXPOSURE - EYE CONTACT: Causes Serious Eye Irritation

EFFECTS OF OVEREXPOSURE - SKIN CONTACT: Substance may cause slight skin irritation. May cause skin irritation. Allergic reactions are possible.

EFFECTS OF OVEREXPOSURE - INHALATION: Harmful if inhaled. High gas, vapor, mist or dust concentrations may be harmful if inhaled. Avoid breathing fumes, spray, vapors, or mist. High vapor concentrations are irritating to the eyes, nose, throat and lungs. Prolonged or excessive inhalation may cause respiratory tract irritation. Low hazard for usual industrial handling or commercial handling by trained personnel.

EFFECTS OF OVEREXPOSURE - INGESTION: Harmful if swallowed.

EFFECTS OF OVEREXPOSURE - CHRONIC HAZARDS: May cause central nervous system disorder (e.g., narcosis involving a loss of coordination, weakness, fatigue, mental confusion, and blurred vision) and/or damage. High concentrations may lead to central nervous system effects (drowsiness, dizziness, nausea, headaches, paralysis, and blurred vision) and/or damage. Reports have associated repeated and prolonged occupational overexposure to solvents with permanent brain and nervous system damage. Contains carbon black. Chronic inflammation, lung fibrosis, and lung tumors have been observed in some rats experimentally exposed for long periods of time to excessive concentrations of carbon black and several insoluble fine dust particles. Tumors have not been observed in other animal species (i.e., mouse and hamster) under similar circumstances and study conditions. Epidemiological studies of North American workers show no evidence of clinically significant adverse health effects due to occupational exposure to carbon black.

Carbon black is listed as a Group 2B-"Possibly carcinogenic to humans" by IARC and is proposed to be listed as A4- "not classified as a human carcinogen" by the American Conference of Governmental Industrial Hygienists. Significant exposure is not anticipated during brush application or drying. Risk of overexposure depends on duration and level of exposure to dust from repeated sanding of surfaces or spray mist and the actual concentration of carbon black in the formula. Contains Titanium Dioxide. Titanium Dioxide is listed as a Group 2B-"Possibly carcinogenic to humans" by IARC. No significant exposure to Titanium Dioxide is thought to occur during the use of products in which Titanium Dioxide is bound to other materials, such as in paints during brush application or drying. Risk of overexposure depends on duration and level of exposure to dust from repeated sanding of surfaces or spray mist and the actual concentration of Titanium Dioxide in the formula. (Ref: IARC Monograph, Vol. 93, 2010)

PRIMARY ROUTE(S) OF ENTRY: Eye Contact, Ingestion, Inhalation, Skin Absorption, Skin Contact

ACUTE TOXICITY VALUES

The acute effects of this product have not been tested. Data on individual components are tabulated below:

CAS-No.	Chemical Name	Oral LD50	Dermal LD50	Vapor LC50
64-17-5	Ethanol	N.I.	N.I.	124.7 mg/L Rat
13463-67-7	Titanium Dioxide	>10000 mg/kg Rat	N.I.	N.I.
7632-00-0	Sodium Nitrite	85 mg/kg Rat	N.I.	5.5 mg/L Rat
7664-41-7	Ammonia	350 mg/kg Rat	N.I.	N.I.
872-50-4	N-Methyl 2-Pyrrolidone	3598 mg/kg Rat	8000 mg/kg Rabbit	3.1 mg/L Rat

N.I. - No Information

12. Ecological Information

ECOLOGICAL INFORMATION: Product is a mixture of listed components.

13. Disposal Information

DISPOSAL INFORMATION: Dispose of material in accordance to local, state, and federal regulations and ordinances. Do not allow to enter waterways, wastewater, soil, storm drains or sewer systems.

Date Printed: 9/4/2015 Page 5 / 6

14. Transport Information

	Domestic (USDOT)	International (IMDG)	<u>Air (IATA)</u>	TDG (Canada)
UN Number:	N.A.	N.A.	N.A.	N.A.
Proper Shipping Name:	Not Regulated	Not Regulated	Not Regulated	Not Regulated
Hazard Class:	N.A.	N.A.	N.A.	N.A.
Packing Group:	N.A.	N.A.	N.A.	N.A.
Limited Quantity:	No	No	No	No

15. Regulatory Information

U.S. Federal Regulations:

CERCLA - SARA Hazard Category

This product has been reviewed according to the EPA 'Hazard Categories' promulgated under Sections 311 and 312 of the Superfund Amendment and Reauthorization Act of 1986 (SARA Title III) and is considered, under applicable definitions, to meet the following categories:

Acute Health Hazard, Chronic Health Hazard

Sara Section 313:

This product contains the following substances subject to the reporting requirements of Section 313 of Title III of the Superfund Amendment and Reauthorization Act of 1986 and 40 CFR part 372:

 Chemical Name
 CAS-No.

 Sodium Nitrite
 7632-00-0

 Ammonia
 7664-41-7

 N-Methyl 2-Pyrrolidone
 872-50-4

Toxic Substances Control Act:

This product contains the following chemical substances subject to the reporting requirements of TSCA 12(b) if exported from the United States:

Chemical NameCAS-No.Sodium Nitrite7632-00-0Methyl-4-Isothiazolin-3-one2682-20-45-Chloro-2-Methyl-4-Isothiazolin-3-one26172-55-4

16. Other Information

HMIS RATINGS

Health: 2* Flammability: 1 Physical Hazard: 0 Personal Protection: X

NFPA RATINGS

Health: 2 Flammability: 1 Instability 0

VOLATILE ORGANIC COMPOUNDS, g/L: 236

SDS REVISION DATE: 9/3/2015

REASON FOR REVISION:

Legend: N.A. - Not Applicable, N.E. - Not Established, N.D. - Not Determined

Date Printed: 9/4/2015 Page 6 / 6

Rust-Oleum Corporation believes, to the best of its knowledge, information and belief, the information contained herein to be accurate and reliable as of the date of this safety data sheet. However, because the conditions of handling, use, and storage of these materials are beyond our control, we assume no responsibility or liability for personal injury or property damage incurred by the use of these materials. Rust-Oleum Corporation makes no warranty, expressed or implied, regarding the accuracy or reliability of the data or results obtained from their use. All materials may present unknown hazards and should be used with caution. The information and recommendations in this material safety data sheet are offered for the users' consideration and examination. It is the responsibility of the user to determine the final suitability of this information and to comply with all applicable international, federal, state, and local laws and regulations.