Date Printed: 11/20/2014 Page 1 / 6

Safety Data Sheet



* Trusted Quality Since 1921 * www.rustoleum.com

1. Identification

Product Name: PTOUCH HP 6PK GLOSS KONA BROWN Revision Date: 11/20/2014

Product Identifier: 1977730 Supercedes Date: New SDS

Product Use/Class: Topcoat/Latex

Supplier: Rust-Oleum Corporation Manufacturer: Rust-Oleum Corporation

11 Hawthorn Parkway Vernon Hills, IL 60061

USA

11 Hawthorn Parkway

Vernon Hills, IL 60061 USA

USA

Preparer: Regulatory Department

Emergency Telephone: 24 Hour Hotline: 847-367-7700

2. Hazard Identification

EMERGENCY OVERVIEW: Use ventilation necessary to keep exposures below recommended exposure limits, if any. May cause eye, skin, or respiratory tract irritation. KEEP OUT OF REACH OF CHILDREN. Harmful if inhaled. Causes eye irritation.

Classification

Symbol(s) of Product



Signal Word Warning

GHS HAZARD STATEMENTS

Acute Toxicity, Dermal, category 5 H313 May be harmful in contact with skin.

Skin Irritation, category 2 H315 Causes skin irritation.

Aspiration Hazard, category 2 H305 May be harmful if swallowed and enters airways.

Skin Irritation, category 3 H316 Causes mild skin irritation. Eye Irritation, category 2B H320 Causes eye irritation.

GHS PRECAUTIONARY STATEMENTS

P102 Keep out of reach of children.

P103 Read label before use.

P202 Do not handle until all safety precautions have been read and understood.

P234 Keep only in original container.

P260 Do not breathe dust/fume/gas/mist/vapours/spray.
P261 Avoid breathing dust/fume/gas/mist/vapours/spray.

P262 Do not get in eyes, on skin, or on clothing.

P264 Wash ... thoroughly after handling.

P270 Do not eat, drink or smoke when using this product.
P271 Use only outdoors or in a well-ventilated area.

P273 Avoid release to the environment.

P280 Wear protective gloves/protective clothing/eye protection/face protection.

Date Printed: 11/20/2014 Page 2 / 6

P281	Use personal protective equipment as required.
P285	In case of inadequate ventilation wear respiratory protection.
P312	Call a POISON CENTER or doctor/physician if you feel unwell.
P335	Brush off loose particles from skin.
P351	Rinse cautiously with water for several minutes.
P374	Fight fire with normal precautions from a reasonable distance.
P402	Store in a dry place.
P321	Specific treatment (see on this label).
P352	Wash with plenty of soap and water.
P362	Take off contaminated clothing and wash before reuse.
P332+P313	If skin irritation occurs: Get medical advice/attention.
P403+P233	Store in a well-ventilated place. Keep container tightly closed.
P302+P350	IF ON SKIN: Gently wash with plenty of soap and water.

3. Composition/Information On Ingredients

HAZARDOUS SUBSTANCES

<u>Chemical Name</u>	CAS-No.	Wt.% Range	GHS Symbols	GHS Statements
Dipropylene Glycol Monobutyl Ether	29911-28-2	2.5-10	No GHS Flavor/ Country combination found	No GHS Flavor/Country combination found
Ethanol	64-17-5	1.0-2.5	GHS02	H225

The text for GHS Hazard Statements shown above (if any) is given in the "16. Other Information" section.

4. First-aid Measures

FIRST AID - EYE CONTACT: Immediately flush eyes with plenty of water for at least 15 minutes holding eyelids open. Get medical attention. Do NOT allow rubbing of eyes or keeping eyes closed.

FIRST AID - SKIN CONTACT: Wash skin with soap and water. Remove contaminated clothing. Get medical attention if irritation develops or persists.

FIRST AID - INHALATION: Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get immediate medical attention. Do NOT use mouth-to-mouth resuscitation. If you experience difficulty in breathing, leave the area to obtain fresh air. If continued difficulty is experienced, get medical assistance immediately.

FIRST AID - INGESTION: Swallowing less than an ounce will not cause significant harm. For larger amounts, do not induce vomiting, but give one or two glasses of water to drink and get medical attention. If swallowed, rinse mouth with water. If feeling unwell, get medical attention.

5. Fire-fighting Measures

EXTINGUISHING MEDIA: Alcohol Film Forming Foam, Carbon Dioxide, Dry Chemical, Dry Sand, Water Fog

UNUSUAL FIRE AND EXPLOSION HAZARDS: FLASH POINT IS TESTED TO BE GREATER THAN 200 DEGREES F. No unusual fire or explosion hazards noted. Keep containers tightly closed.

SPECIAL FIREFIGHTING PROCEDURES: Water may be used to cool closed containers to prevent buildup of steam. If water is used, fog nozzles are preferred.

6. Accidental Release Measures

STEPS TO BE TAKEN IF MATERIAL IS RELEASED OR SPILLED: Dispose of according to local, state (provincial) and federal regulations. Do not incinerate closed containers. If spilled, contain spilled material and remove with inert absorbent. Dispose of contaminated absorbent, container, and unused contents in accordance with local, state, and federal regulations. Do not incinerate closed containers

7. Handling and Storage

HANDLING: Wash thoroughly after handling. Wash hands before eating. Avoid contact with eyes. Remove contaminated clothing and launder before reuse. Use only with adequate ventilation. Follow all MSDS/label precautions even after container is emptied because it may retain product residues. Avoid breathing fumes, vapors, or mist. Avoid contact with eyes, skin and clothing.

Date Printed: 11/20/2014 Page 3 / 6

STORAGE: Keep from freezing. Keep container closed when not in use. Store in a dry, well ventilated place. Keep container tightly closed when not in use.

8. Exposure Controls/Personal Protection

Chemical Name	CAS-No.	Weight % Less Than	ACGIH TLV- TWA	ACGIH TLV- STEL	OSHA PEL-TWA	OSHA PEL- CEILING
Dipropylene Glycol Monobutyl Ether	29911-28-2	5.0	N.E.	N.E.	N.E.	N.E.
Ethanol	64-17-5	5.0	N.E.	1000 ppm	1000 ppm	N.E.

PERSONAL PROTECTION

ENGINEERING CONTROLS: Use process enclosures, local exhaust ventilation, or other engineering controls to control airborne levels below recommended exposure limits. Prevent build-up of vapors by opening all doors and windows to achieve crossventilation.

RESPIRATORY PROTECTION: A respiratory protection program that meets OSHA 1910.134 and ANSI Z88.2 requirements must be followed whenever workplace conditions warrant a respirator's use.

SKIN PROTECTION: Use gloves to prevent prolonged skin contact. Nitrile or Neoprene gloves may afford adequate skin protection.

EYE PROTECTION: Use safety eyewear designed to protect against splash of liquids.

OTHER PROTECTIVE EQUIPMENT: Refer to safety supervisor or industrial hygienist for further information regarding personal protective equipment and its application. Refer to safety supervisor or industrial hygienist for further guidance regarding types of personal protective equipment and their applications.

HYGIENIC PRACTICES: Wash thoroughly with soap and water before eating, drinking or smoking. Remove contaminated clothing immediately and launder before reuse.

No Information

9. Physical and Chemical Properties

Appearance: **Physical State:** Liquid Liquid Odor: **Odor Threshold:** Mild Ammonia ND Relative Density: 1.032 pH: N.D. Freeze Point, °C: Viscosity: N.D. N.D.

Solubility in Water: Miscible Partition Coefficient, n-octanol/

Decomposition Temp., °C: No Information water:

Boiling Range, °C: 147 - 447 Explosive Limits, vol%: 1.1 - 36.0

Flammability: Does not Support Combustion Flash Point, °C: >93

Evaporation Rate: Slower than Ether Auto-ignition Temp., °C: No Information

Vapor Density: Heavier than Air Vapor Pressure: ND

(See "Other information" Section for abbreviation legend)

10. Stability and Reactivity

CONDITIONS TO AVOID: Avoid contact with strong acid and strong bases.

INCOMPATIBILITY: Incompatible with strong oxidizing agents, strong acids and strong alkalies.

HAZARDOUS DECOMPOSITION: By open flame, carbon monoxide and carbon dioxide. When heated to decomposition, it emits acrid smoke and irritating fumes.

HAZARDOUS POLYMERIZATION: Will not occur under normal conditions.

STABILITY: This product is stable under normal storage conditions.

11. Toxicological information

EFFECTS OF OVEREXPOSURE - EYE CONTACT: Causes eye irritation. Irritating, and may injure eye tissue if not removed promptly.

EFFECTS OF OVEREXPOSURE - SKIN CONTACT: Substance may cause slight skin irritation. Low hazard for usual industrial handling or commercial handling by trained personnel.

EFFECTS OF OVEREXPOSURE - INHALATION: Low hazard for usual industrial handling or commercial handling by trained personnel. High gas, vapor, mist or dust concentrations may be harmful if inhaled. Avoid breathing fumes, spray, vapors, or mist.

EFFECTS OF OVEREXPOSURE - INGESTION: Substance may be harmful if swallowed.

EFFECTS OF OVEREXPOSURE - CHRONIC HAZARDS: No Information

Date Printed: 11/20/2014 Page 4 / 6

PRIMARY ROUTE(S) OF ENTRY: Eye Contact, Ingestion, Inhalation, Skin Absorption, Skin Contact

ACUTE TOXICITY VALUES

The acute effects of this product have not been tested. Data on individual components are tabulated below:

 CAS-No.
 Chemical Name
 Oral LD50
 Dermal LD50
 Vapor LC50

 64-17-5
 Ethanol
 N.I.
 N.I.
 124.7 mg/L Rat

N.I. - No Information

12. Ecological Information

ECOLOGICAL INFORMATION: Product is a mixture of listed components.

13. Disposal Information

DISPOSAL INFORMATION: Dispose of material in accordance to local, state, and federal regulations and ordinances. Do not allow to enter waterways, wastewater, soil, storm drains or sewer systems.

14. Transport Information

	Domestic (USDOT)	International (IMDG)	Air (IATA)	TDG (Canada)
UN Number:	N.A.	N.A.	N.A.	N.A.
Proper Shipping Name:	Not Regulated	Not Regulated	Not Regulated	Not Regulated
Hazard Class:	N.A.	N.A.	N.A.	N.A.
Packing Group:	N.A.	N.A.	N.A.	N.A.
Limited Quantity:	No	No	No	No

15. Regulatory Information

U.S. Federal Regulations:

CERCLA - SARA Hazard Category

This product has been reviewed according to the EPA 'Hazard Categories' promulgated under Sections 311 and 312 of the Superfund Amendment and Reauthorization Act of 1986 (SARA Title III) and is considered, under applicable definitions, to meet the following categories:

Acute Health Hazard, Chronic Health Hazard

Sara Section 313:

This product contains the following substances subject to the reporting requirements of Section 313 of Title III of the Superfund Amendment and Reauthorization Act of 1986 and 40 CFR part 372:

No Sara 313 components exist in this product.

Toxic Substances Control Act:

This product contains the following chemical substances subject to the reporting requirements of TSCA 12(B) if exported from the United States:

Chemical NameCAS-No.Sodium Nitrite7632-00-05-Chloro-2-Methyl-4-Isothiazolin-3-one26172-55-4Methyl-4-Isothiazolin-3-one2682-20-4

Date Printed: 11/20/2014 Page 5 / 6

Inventory Information

<u>Country</u> <u>Value</u>

USA (TSCA) No Information Canada (DSL) No Information Mexico(INSQ) No Information Europe (EINECS) No Information Japan (ENCS) No Information Philippines (PICCS) No Information China (IECSC) No Information Australia (AICS) No Information No Information Korea (KECI) New Zealand (NZIOC) No Information

No Information

CALIFORNIA PROPOSITION 65:

Warning: This products contains a substance known to the State of California to cause cancer.

No Proposition 65 Carcinogens exist in this product.

CALIFORNIA PROPOSITION 65 REPRODUCTIVE TOXINS

Warning: This product contains a substance known to the State of California to cause birth defects or other reproductive

harm.

Chemical NameCAS-No.Ethanol64-17-5

International Regulations:

CANADIAN WHMIS:

This SDS has been prepared in compliance with Controlled Product Regulations except for the use of the 16 headings.

16. Other Information

HMIS RATINGS

Health: 1* Flammability: 1 Physical Hazard: 0 Personal Protection: X

CANADIAN WHMIS CLASS: D2A

NFPA RATINGS

Health: 1 Flammability: 1 Instability 0

VOLATILE ORGANIC COMPOUNDS, g/L: 250

MSDS REVISION DATE: 11/20/2014

REASON FOR REVISION: No Information

Legend: N.A. - Not Applicable, N.E. - Not Established, N.D. - Not Determined

Date Printed: 11/20/2014 Page 6 / 6

Text for GHS Hazard Statements shown in Section 3 describing each ingredient:

H225 Highly flammable liquid and vapour. HNo GHS Flavor/ <undefined>

Country combination

found

Icons for GHS Pictograms shown in Section 3 describing each ingredient:

GHS02



No GHS Flavor/ Country combination found

Rust-Oleum Corporation believes, to the best of its knowledge, information and belief, the information contained herein to be accurate and reliable as of the date of this safety data sheet. However, because the conditions of handling, use, and storage of these materials are beyond our control, we assume no responsibility or liability for personal injury or property damage incurred by the use of these materials. Rust-Oleum Corporation makes no warranty, expressed or implied, regarding the accuracy or reliability of the data or results obtained from their use. All materials may present unknown hazards and should be used with caution. The information and recommendations in this material safety data sheet are offered for the users' consideration and examination. It is the responsibility of the user to determine the final suitability of this information and to comply with all applicable international, federal, state, and local laws and regulations.