

Safety Data Sheet



1. Identification

| | | | |
|-----------------------------|--|-------------------------|--|
| Product Name: | PRO LSPR 6PK STRIPE WHITE | Revision Date: | 6/8/2023 |
| Product Identifier: | 2593838 | Supercedes Date: | 4/4/2019 |
| Recommended Use: | Striping Paint/Aerosols | | |
| Supplier: | Rust-Oleum Corporation 11 Hawthorn Parkway Vernon Hills, IL 60061 USA | Manufacturer: | Rust-Oleum Corporation 11 Hawthorn Parkway Vernon Hills, IL 60061 USA |
| Preparer: | Regulatory Department | | |
| Emergency Telephone: | 24 Hour Hotline: 847-367-7700 | | |

2. Hazards Identification

Classification

Symbol(s) of Product



Signal Word

Danger

Possible Hazards

34% of the mixture consists of ingredient(s) of unknown acute toxicity.

GHS HAZARD STATEMENTS

| | | |
|--------------------------------------|------|---|
| Carcinogenicity, category 1B | H350 | May cause cancer. |
| Flammable Aerosol, category 1 | H222 | Extremely flammable aerosol. |
| Gases under Pressure; Compressed Gas | H280 | Contains gas under pressure; may explode if heated. |
| Germ Cell Mutagenicity, category 1B | H340 | May cause genetic defects. |
| Reproductive Toxicity, category 1B | H360 | May damage fertility or the unborn child. |
| Skin Sensitizer, category 1 | H317 | May cause an allergic skin reaction. |

GHS LABEL PRECAUTIONARY STATEMENTS

| | |
|------|--|
| P201 | Obtain special instructions before use. |
| P210 | Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. NO SMOKING. |
| P211 | Do not spray on an open flame or other ignition source. |
| P251 | Do not pierce or burn, even after use. |
| P261 | Avoid breathing dust/fume/gas/mist/vapors/spray. |
| P272 | Contaminated work clothing should not be allowed out of the workplace. |
| P280 | Wear protective gloves/protective clothing/eye protection/face protection. |

| | |
|-----------|--|
| P302+P352 | IF ON SKIN: Wash with plenty of soap and water. |
| P308+P313 | IF exposed or concerned: Get medical advice/attention. |
| P321 | For specific treatment see label. |
| P333+P313 | If skin irritation or rash occurs: Get medical advice/attention. |
| P405 | Store locked up. |
| P410+P403 | Protect from sunlight. Store in a well-ventilated place. |
| P410+P412 | Protect from sunlight. Do not expose to temperatures exceeding 50°C (122°F). |
| P501 | Dispose of contents/container in accordance with local, regional and national regulations. |

GHS SDS PRECAUTIONARY STATEMENTS

P363 Wash contaminated clothing before reuse.

3. Composition / Information on Ingredients**HAZARDOUS SUBSTANCES**

| <u>Chemical Name</u> | <u>CAS-No.</u> | <u>Wt.% Range</u> | <u>GHS Symbols</u> | <u>GHS Statements</u> |
|--|----------------|-------------------|-------------------------|--|
| Propane | 74-98-6 | 10-25 | GHS04 | H280 |
| Titanium Dioxide | 13463-67-7 | 10-25 | Not Available | Not Available |
| Naphtha, Petroleum, Hydrotreated Light | 64742-49-0 | 2.5-10 | GHS08 | H304 |
| n-Butane | 106-97-8 | 2.5-10 | GHS04 | H280 |
| Aliphatic Hydrocarbon | 64742-89-8 | 2.5-10 | GHS08 | H304-340-350 |
| Acetone | 67-64-1 | 2.5-10 | GHS02-GHS07 | H225-319-332-336 |
| Hydrotreated Light Distillate | 64742-47-8 | 2.5-10 | GHS08 | H304 |
| n-Butyl Acetate | 123-86-4 | 2.5-10 | GHS02-GHS07 | H226-336 |
| Solvent Naphtha, Light Aromatic | 64742-95-6 | 1.0-2.5 | GHS07-GHS08 | H304-332-340-350 |
| Xylenes (o-, m-, p- Isomers) | 1330-20-7 | 1.0-2.5 | GHS02-GHS07 | H226-315-319-332 |
| Kaolin Clay | 1332-58-7 | 1.0-2.5 | Not Available | Not Available |
| 1,2,4-Trimethylbenzene | 95-63-6 | 1.0-2.5 | GHS02-GHS07-GHS08 | H226-304-315-319-332-335 |
| Dimethyl Carbonate | 616-38-6 | 1.0-2.5 | GHS02-GHS06 | H225-331 |
| n-Heptane | 142-82-5 | 0.1-1.0 | GHS02-GHS07-GHS08 | H225-304-315-336 |
| Octane | 111-65-9 | 0.1-1.0 | GHS02-GHS07-GHS08 | H225-304-315-336 |
| Ethylbenzene | 100-41-4 | 0.1-1.0 | GHS02-GHS07-GHS08 | H225-304-332-373 |
| Zirconium 2-Ethylhexanoate | 22464-99-9 | 0.1-1.0 | GHS07-GHS08 | H315-320-360 |
| Methyl Ethyl Ketoxime | 96-29-7 | 0.1-1.0 | GHS05-GHS06-GHS07-GHS08 | H302-312-315-317-318-331-336-350-370-373 |
| Zirconium Acetate | 5153-24-2 | <0.1 | Not Available | Not Available |

4. First-Aid Measures

FIRST AID - EYE CONTACT: Immediately flush eyes with plenty of water for at least 15 minutes holding eyelids open. Get medical attention. Do NOT allow rubbing of eyes or keeping eyes closed.

FIRST AID - SKIN CONTACT: Wash skin with soap and water. Remove contaminated clothing. Get medical attention if irritation develops or persists.

FIRST AID - INHALATION: Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get immediate medical attention. Do NOT use mouth-to-mouth resuscitation. If you experience difficulty in breathing, leave the area to obtain fresh air. If continued difficulty is experienced, get medical assistance immediately.

FIRST AID - INGESTION: Aspiration hazard: Do not induce vomiting or give anything by mouth because this material can enter the lungs and cause severe lung damage. Get immediate medical attention. If swallowed, get medical attention.

5. Fire-Fighting Measures

EXTINGUISHING MEDIA: Alcohol Film Forming Foam, Carbon Dioxide, Dry Chemical, Dry Sand, Water Fog

UNUSUAL FIRE AND EXPLOSION HAZARDS: FLASH POINT IS LESS THAN -7°C (20°F). EXTREMELY FLAMMABLE LIQUID AND VAPOR! Water spray may be ineffective. Closed containers may explode when exposed to extreme heat due to buildup of steam. Closed containers may explode when exposed to extreme heat. Vapors may form explosive mixtures with air. Vapors can travel to a source of ignition and flash back. Isolate from heat, electrical equipment, sparks and open flame. Perforation of the pressurized container may cause bursting of the can.

SPECIAL FIREFIGHTING PROCEDURES: Water may be used to cool closed containers to prevent pressure buildup and possible autoignition or explosion. Full protective equipment including self-contained breathing apparatus should be used. Evacuate area and fight fire from a safe distance. Use water spray to keep fire-exposed containers cool. Containers may explode when heated.

Special Fire and Explosion Hazard (Combustible Dust): No Information

6. Accidental Release Measures

STEPS TO BE TAKEN IF MATERIAL IS RELEASED OR SPILLED: Contain spilled liquid with sand or earth. DO NOT use combustible materials such as sawdust. Isolate the hazard area and deny entry to unnecessary and unprotected personnel. Remove all sources of ignition, ventilate area and remove with inert absorbent and non-sparking tools. Dispose of according to local, state (provincial) and federal regulations. Do not incinerate closed containers. Ventilate area, isolate spilled material, and remove with inert absorbent. Dispose of contaminated absorbent, container, and unused contents in accordance with local, state, and federal regulations.

7. Handling and Storage

HANDLING: Wash thoroughly after handling. Wash hands before eating. Remove contaminated clothing and launder before reuse. Use only in a well-ventilated area. Use only with adequate ventilation. Follow all SDS and label precautions even after container is emptied because it may retain product residues. Avoid breathing fumes, vapors, or mist. Avoid contact with eyes, skin and clothing.

STORAGE: Keep containers tightly closed. Isolate from heat, electrical equipment, sparks and open flame. Contents under pressure. Do not store above 120°F (49°C). Store large quantities in buildings designed and protected for storage of flammable aerosols. Keep away from heat, sparks, flame and sources of ignition. Contents under pressure. Do not expose to heat or store above 120°F (49°C). Avoid excess heat. Product should be stored in tightly sealed containers and protected from heat, moisture, and foreign materials.

Advice on Safe Handling of Combustible Dust: No Information

8. Exposure Controls / Personal Protection

| Chemical Name | CAS-No. | Weight % Less Than | ACGIH TLV- TWA | ACGIH TLV- STEL | OSHA PEL-TWA | OSHA PEL- CEILING |
|---|------------|-----------------------|-------------------|--------------------|--------------|----------------------|
| Propane | 74-98-6 | 15.0 | N.E. | N.E. | 1000 ppm | N.E. |
| Titanium Dioxide | 13463-67-7 | 15.0 | 0.2 mg/m3 | N.E. | 15 mg/m3 | N.E. |
| Naphtha, Petroleum, Hydrotreated Light | 64742-49-0 | 10.0 | N.E. | N.E. | N.E. | N.E. |
| n-Butane | 106-97-8 | 10.0 | N.E. | 1000 ppm | N.E. | N.E. |
| Aliphatic Hydrocarbon | 64742-89-8 | 10.0 | N.E. | N.E. | N.E. | N.E. |
| Acetone | 67-64-1 | 10.0 | 250 ppm | 500 ppm | 1000 ppm | N.E. |
| Hydrotreated Light Distillate | 64742-47-8 | 5.0 | N.E. | N.E. | N.E. | N.E. |
| n-Butyl Acetate | 123-86-4 | 5.0 | 50 ppm | 150 ppm | 150 ppm | N.E. |
| Solvent Naphtha, Light Aromatic | 64742-95-6 | 5.0 | N.E. | N.E. | N.E. | N.E. |
| Xylenes (o-, m-, p- Isomers) | 1330-20-7 | 5.0 | 20 ppm | N.E. | 100 ppm | N.E. |
| Kaolin Clay | 1332-58-7 | 5.0 | 2 mg/m3 | N.E. | 15 mg/m3 | N.E. |
| 1,2,4-Trimethylbenzene | 95-63-6 | 5.0 | 10 ppm | N.E. | N.E. | N.E. |
| Dimethyl Carbonate | 616-38-6 | 5.0 | N.E. | N.E. | N.E. | N.E. |
| n-Heptane | 142-82-5 | 1.0 | 400 ppm | 500 ppm | 500 ppm | N.E. |
| Octane | 111-65-9 | 1.0 | 300 ppm | N.E. | 500 ppm | N.E. |
| Ethylbenzene | 100-41-4 | 1.0 | 20 ppm | N.E. | 100 ppm | N.E. |

| | | | | | | |
|----------------------------|------------|-----|---------|----------|---------|------|
| Zirconium 2-Ethylhexanoate | 22464-99-9 | 1.0 | 5 mg/m3 | 10 mg/m3 | 5 mg/m3 | N.E. |
| Methyl Ethyl Ketoxime | 96-29-7 | 1.0 | 10 ppm | N.E. | N.E. | N.E. |
| Zirconium Acetate | 5153-24-2 | 0.1 | 5 mg/m3 | 10 mg/m3 | 5 mg/m3 | N.E. |

PERSONAL PROTECTION

ENGINEERING CONTROLS: Use process enclosures, local exhaust ventilation, or other engineering controls to control airborne levels below recommended exposure limits. Use explosion-proof ventilation equipment. Provide general dilution of local exhaust ventilation in volume and pattern to keep TLV of hazardous ingredients below acceptable limits. Prevent build-up of vapors by opening all doors and windows to achieve cross-ventilation.

RESPIRATORY PROTECTION: A respiratory protection program that meets OSHA 1910.134 and ANSI Z88.2 requirements must be followed whenever workplace conditions warrant a respirator's use. A NIOSH/MSHA approved air purifying respirator with organic vapor cartridge or canister may be permissible under certain circumstances where airborne concentrations are expected to exceed exposure limits.

SKIN PROTECTION: Use impervious gloves to prevent skin contact and absorption of this material through the skin.

EYE PROTECTION: Use safety eyewear designed to protect against splash of liquids.

OTHER PROTECTIVE EQUIPMENT: Refer to safety supervisor or industrial hygienist for further guidance regarding types of personal protective equipment and their applications. Refer to safety supervisor or industrial hygienist for further information regarding personal protective equipment and its application.

HYGIENIC PRACTICES: Wash thoroughly with soap and water before eating, drinking or smoking. Remove contaminated clothing immediately and launder before reuse.

Engineering Measures for Combustible Dust: No Information

9. Physical and Chemical Properties

| | | | |
|---------------------------------|---------------------|---|------------|
| Appearance: | Aerosolized Mist | Physical State: | Liquid |
| Odor: | Solvent Like | Odor Threshold: | N.E. |
| Specific Gravity: | 0.967 | pH: | N.A. |
| Freeze Point, °C: | N.D. | Viscosity: | N.D. |
| Solubility in Water: | Slight | Partition Coefficient, n-octanol/ water: | N.D. |
| Decomposition Temp., °C: | N.D. | Explosive Limits, vol%: | 0.9 - 13.0 |
| Boiling Range, °C: | -37 - 537 | Flash Point, °C: | -96 |
| Flammability: | Supports Combustion | Auto-Ignition Temp., °C: | N.D. |
| Evaporation Rate: | Faster than Ether | Vapor Pressure: | N.D. |
| Vapor Density: | Heavier than Air | | |

(See "Other information" Section for abbreviation legend)

10. Stability and Reactivity

Conditions to Avoid: Avoid temperatures above 120°F (49°C). Avoid all possible sources of ignition.

Incompatibility: Incompatible with strong oxidizing agents, strong acids and strong alkalis.

Hazardous Decomposition: By open flame, carbon monoxide and carbon dioxide. When heated to decomposition, it emits acrid smoke and irritating fumes. Contains solvents which may form carbon monoxide, carbon dioxide, and formaldehyde.

Hazardous Polymerization: Will not occur under normal conditions.

Stability: This product is stable under normal storage conditions.

11. Toxicological Information

EFFECTS OF OVEREXPOSURE - EYE CONTACT: Causes Serious Eye Irritation

EFFECTS OF OVEREXPOSURE - SKIN CONTACT: Substance may cause slight skin irritation. Prolonged or repeated contact may cause skin irritation.

EFFECTS OF OVEREXPOSURE - INHALATION: Harmful if inhaled. High gas, vapor, mist or dust concentrations may be harmful if inhaled. Avoid breathing fumes, spray, vapors, or mist. High vapor concentrations are irritating to the eyes, nose, throat and lungs. Prolonged or excessive inhalation may cause respiratory tract irritation.

EFFECTS OF OVEREXPOSURE - INGESTION: Harmful if swallowed.

EFFECTS OF OVEREXPOSURE - CHRONIC HAZARDS: May cause central nervous system disorder (e.g., narcosis involving a loss of coordination, weakness, fatigue, mental confusion, and blurred vision) and/or damage. High concentrations may lead to central nervous system effects (drowsiness, dizziness, nausea, headaches, paralysis, and blurred vision) and/or damage. Reports have associated repeated and prolonged occupational overexposure to solvents with permanent brain and nervous system damage.

Overexposure to xylene in laboratory animals has been associated with liver abnormalities, kidney, lung, spleen, eye and blood damage as well as reproductive disorders. Effects in humans, due to chronic overexposure, have included liver, cardiac abnormalities and nervous system damage. IARC lists Ethylbenzene as a possible human carcinogen (group 2B). Contains Titanium Dioxide. Titanium Dioxide is listed as a Group 2B-"Possibly carcinogenic to humans" by IARC. No significant exposure to Titanium Dioxide is thought to occur during the use of products in which Titanium Dioxide is bound to other materials, such as in paints during brush application or drying. Risk of overexposure depends on duration and level of exposure to dust from repeated sanding of surfaces or spray mist and the actual concentration of Titanium Dioxide in the formula. (Ref: IARC Monograph, Vol. 93, 2010)

PRIMARY ROUTE(S) OF ENTRY: Eye Contact, Ingestion, Inhalation, Skin Absorption, Skin Contact

ACUTE TOXICITY VALUES

The acute effects of this product have not been tested. Data on individual components are tabulated below:

| <u>CAS-No.</u> | <u>Chemical Name</u> | <u>Oral LD50</u> | <u>Dermal LD50</u> | <u>Vapor LC50</u> |
|----------------|--|------------------|---------------------|-------------------|
| 13463-67-7 | Titanium Dioxide | >10000 mg/kg Rat | 6000 | N.E. |
| 64742-49-0 | Naphtha, Petroleum, Hydrotreated Light | >5000 mg/kg Rat | >3160 mg/kg Rabbit | >4951 mg/L Rat |
| 106-97-8 | n-Butane | N.E. | N.E. | 658 mg/L Rat |
| 64742-89-8 | Aliphatic Hydrocarbon | N.E. | 3000 mg/kg Rabbit | N.E. |
| 67-64-1 | Acetone | 5800 mg/kg Rat | >15700 mg/kg Rabbit | 50.1 mg/L Rat |
| 64742-47-8 | Hydrotreated Light Distillate | >5000 mg/kg Rat | >2000 mg/kg Rabbit | >5000 mg/L Rat |
| 123-86-4 | n-Butyl Acetate | 10768 mg/kg Rat | >17600 mg/kg Rabbit | > 21 mg/L Rat |
| 64742-95-6 | Solvent Naphtha, Light Aromatic | 8400 mg/kg Rat | >2000 mg/kg Rabbit | N.E. |
| 1330-20-7 | Xylenes (o-, m-, p- Isomers) | 3500 mg/kg Rat | >4350 mg/kg Rabbit | 29.08 mg/L Rat |
| 1332-58-7 | Kaolin Clay | 5500 mg/kg | >5000 mg/kg Rat | 25 |
| 95-63-6 | 1,2,4-Trimethylbenzene | 3280 mg/kg Rat | >3160 mg/kg Rabbit | 18 mg/L Rat |
| 616-38-6 | Dimethyl Carbonate | 13000 mg/kg Rat | >5000 mg/kg Rabbit | >5.36 mg/L Rat |
| 142-82-5 | n-Heptane | N.E. | 3000 mg/kg Rabbit | >73.5 mg/L Rat |
| 111-65-9 | Octane | N.E. | N.E. | >24.88 mg/L Rat |
| 100-41-4 | Ethylbenzene | 3500 mg/kg Rat | 15400 mg/kg Rabbit | 17.4 mg/L Rat |
| 96-29-7 | Methyl Ethyl Ketoxime | 930 mg/kg Rat | 1100 mg/kg Rabbit | >4.83 mg/L Rat |

N.E. - Not Established

12. Ecological Information

ECOLOGICAL INFORMATION: Product is a mixture of listed components. Product is a mixture of listed components.

13. Disposal Information

DISPOSAL: Do not incinerate closed containers. Dispose of material in accordance to local, state, and federal regulations and ordinances. This product as supplied is a US EPA defined ignitable hazardous waste. Dispose of unusable product as a hazardous waste (D001) in accordance with local, state, and federal regulation.

14. Transport Information

| | <u>Domestic (USDOT)</u> | <u>International (IMDG)</u> | <u>Air (IATA)</u> | <u>TDG (Canada)</u> |
|------------------------------|---|-----------------------------|---------------------|---------------------|
| UN Number: | N.A. | 1950 | 1950 | N.A. |
| Proper Shipping Name: | Paint and Related Spray Products in Ltd Qty | Aerosols | Aerosols, flammable | Aerosols |
| Hazard Class: | N.A. | 2 | 2.1 | N.A. |
| Packing Group: | N.A. | N.A. | N.A. | N.A. |
| Limited Quantity: | Yes | Yes | Yes | Yes |

15. Regulatory Information

U.S. Federal Regulations:

CERCLA - SARA Hazard Category

This product has been reviewed according to the EPA 'Hazard Categories' promulgated under Sections 311 and 312 of the Superfund Amendment and Reauthorization Act of 1986 (SARA Title III) and is considered, under applicable definitions, to meet the following categories:

Gas under pressure, Carcinogenicity, Reproductive toxicity, Respiratory or Skin Sensitization, Germ cell mutagenicity

SARA Section 313

This product contains the following substances subject to the reporting requirements of Section 313 of Title III of the Superfund Amendment and Reauthorization Act of 1986 and 40 CFR part 372:

| <u>Chemical Name</u> | <u>CAS-No.</u> |
|------------------------------|----------------|
| Xylenes (o-, m-, p- Isomers) | 1330-20-7 |
| 1,2,4-Trimethylbenzene | 95-63-6 |
| Ethylbenzene | 100-41-4 |
| Barite (Ba(SO4)) | 13462-86-7 |

Toxic Substances Control Act

This product contains the following chemical substances subject to the reporting requirements of TSCA 12(b) if exported from the United States:

No TSCA 12(b) components exist in this product.

U.S. State Regulations:

California Proposition 65

WARNING:

Cancer and Reproductive Harm - www.P65Warnings.ca.gov.

16. Other Information

HMIS RATINGS

Health: 2* Flammability: 4 Physical Hazard: 0 Personal Protection: X

NFPA RATINGS

Health: 2 Flammability: 4 Instability: 0

Maximum Incremental Reactivity: 0.81

SDS REVISION DATE: 6/8/2023

REASON FOR REVISION:

Product Composition Changed
 Substance Chemical Name Changed
 Substance Hazard Threshold % Changed
 Substance and/or Product Properties Changed in Section(s):
 02 - Hazard Identification
 03 - Composition / Information on Ingredients
 08 - Exposure Controls / Personal Protection
 09 - Physical & Chemical Properties
 11 - Toxicological Information
 15 - Regulatory Information
 Substance Hazardous Flag Changed
 Revision Statement(s) Changed

Legend: N.A. - Not Applicable, N.D. - Not Determined, N.E. - Not Established

Rust-Oleum Corporation believes, to the best of its knowledge, information and belief, the information contained herein to be accurate and reliable as of the date of this safety data sheet. However, because the conditions of handling, use, and storage of these materials are beyond our control, we assume no responsibility or liability for personal injury or property damage incurred by the use of these materials. Rust-Oleum Corporation makes no warranty, expressed or implied, regarding the accuracy or reliability of the data or results obtained from their use. All materials may present unknown hazards and should be used with caution. The information and recommendations in this material safety data sheet are offered for the users' consideration and examination. It is the responsibility of the user to determine the final suitability of this information and to comply with all applicable international, federal, state, and local laws and regulations.