

# Safety Data Sheet



## 1. Identification

**Product Name:** UNVRSL SSPR 6PK METALLIC TURQUOISE **Revision Date:** 2/13/2018

**Product Identifier:** 330480 **Supersedes Date:** 2/13/2018

**Product Use/Class:** Topcoat/Aerosols

**Supplier:** Rust-Oleum Corporation  
11 Hawthorn Parkway  
Vernon Hills, IL 60061  
USA **Manufacturer:** Rust-Oleum Corporation  
11 Hawthorn Parkway  
Vernon Hills, IL 60061  
USA

**Preparer:** Regulatory Department

**Emergency Telephone:** 24 Hour Hotline: 847-367-7700

## 2. Hazard Identification

### Classification

### Symbol(s) of Product



### Signal Word

Danger

### Possible Hazards

32% of the mixture consists of ingredient(s) of unknown acute toxicity.

### GHS HAZARD STATEMENTS

Flammable Aerosol, category 1	H222	Extremely flammable aerosol.
Compressed Gas	H280	Contains gas under pressure; may explode if heated.
Germ Cell Mutagenicity, category 1B	H340	May cause genetic defects.
Carcinogenicity, category 1B	H350	May cause cancer.
STOT, single exposure, category 3, NE	H336	May cause drowsiness or dizziness.
Eye Irritation, category 2	H319	Causes serious eye irritation.

### GHS LABEL PRECAUTIONARY STATEMENTS

P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P211	Do not spray on an open flame or other ignition source.
P251	Do not pierce or burn, even after use.
P410+P412	Protect from sunlight. Do not expose to temperatures exceeding 50°C / 122°F.
P410+P403	Protect from sunlight. Store in a well-ventilated place.
P201	Obtain special instructions before use.
P280	Wear protective gloves/protective clothing/eye protection/face protection.
P308+P313	IF exposed or concerned: Get medical advice/attention.
P405	Store locked up.
P501	Dispose of contents/container in accordance with local, regional and national regulations.
P261	Avoid breathing dust/fume/gas/mist/vapors/spray.
P271	Use only outdoors or in a well-ventilated area.
P304+P340	IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P312	Call a POISON CENTER or doctor/physician if you feel unwell.
P403+P233	Store in a well-ventilated place. Keep container tightly closed.
P264	Wash hands thoroughly after handling.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P337+P313	If eye irritation persists: Get medical advice/attention.

### 3. Composition / Information On Ingredients

#### HAZARDOUS SUBSTANCES

<u>Chemical Name</u>	<u>CAS-No.</u>	<u>Wt.% Range</u>	<u>GHS Symbols</u>	<u>GHS Statements</u>
Acetone	67-64-1	25-50	GHS02-GHS07	H225-319-332-336
Propane	74-98-6	10-25	GHS04	H280
n-Butyl Acetate	123-86-4	10-25	GHS02-GHS07	H226-336

n-Butane	106-97-8	2.5-10	GHS04	H280
Naphtha, Petroleum, Hydrotreated Light	64742-49-0	2.5-10	GHS08	H304
1-Methoxy-2-Propyl Acetate	108-65-6	2.5-10	GHS02	H226
Xylenes (o-, m-, p- isomers)	1330-20-7	2.5-10	GHS02-GHS07	H226-315-319-332
Propylene Glycol Monobutyl Ether	5131-66-8	1.0-2.5	GHS07	H302-315-319
Aluminum Flake	7429-90-5	1.0-2.5	GHS02	H228-261
Ethylbenzene	100-41-4	0.1-1.0	GHS02-GHS07-GHS08	H225-304-332-351-373
Naphtha, Hydrotreated Heavy	64742-48-9	0.1-1.0	GHS08	H304-340-350
bis(1,2,2,6,6-Pentamethyl-4-Piperidiny)l Sebacate	41556-26-7	0.1-1.0	GHS07	H317
Solvent Naphtha, Light Aromatic	64742-95-6	0.1-1.0	GHS07-GHS08	H304-332-340-350
Stoddard Solvent	8052-41-3	0.1-1.0	GHS08	H304-372
Ethylene Glycol Monobutyl Ether	111-76-2	0.1-1.0	GHS07	H302-312-315-319-332
Ethanol	64-17-5	0.1-1.0	GHS02	H225

#### 4. First-Aid Measures

**FIRST AID - EYE CONTACT:** Immediately flush eyes with plenty of water for at least 15 minutes holding eyelids open. Get medical attention. Do NOT allow rubbing of eyes or keeping eyes closed.

**FIRST AID - SKIN CONTACT:** Wash skin with soap and water. Remove contaminated clothing. Get medical attention if irritation develops or persists.

**FIRST AID - INHALATION:** Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get immediate medical attention. Do NOT use mouth-to-mouth resuscitation. If you experience difficulty in breathing, leave the area to obtain fresh air. If continued difficulty is experienced, get medical assistance immediately.

**FIRST AID - INGESTION:** Aspiration hazard: Do not induce vomiting or give anything by mouth because this material can enter the lungs and cause severe lung damage. Get immediate medical attention. If swallowed, get medical attention.

#### 5. Fire-Fighting Measures

**EXTINGUISHING MEDIA:** Alcohol Film Forming Foam, Carbon Dioxide, Dry Chemical, Dry Sand, Water Fog

**UNUSUAL FIRE AND EXPLOSION HAZARDS:** FLASH POINT IS LESS THAN 20°F. EXTREMELY FLAMMABLE LIQUID AND VAPOR! Water spray may be ineffective. Closed containers may explode when exposed to extreme heat due to buildup of steam. Closed containers may explode when exposed to extreme heat. Vapors may form explosive mixtures with air. Vapors can travel to a source of ignition and flash back. Isolate from heat, electrical equipment, sparks and open flame. Perforation of the pressurized container may cause bursting of the can. No unusual fire or explosion hazards noted. Keep containers tightly closed.

**SPECIAL FIREFIGHTING PROCEDURES:** Full protective equipment including self-contained breathing apparatus should be used. Evacuate area and fight fire from a safe distance. Water may be used to cool closed containers to prevent pressure buildup and possible autoignition or explosion. Use water spray to keep fire-exposed containers cool. Containers may explode when heated.

**Special Fire and Explosion Hazard (Combustible Dust):** No Information

#### 6. Accidental Release Measures

**STEPS TO BE TAKEN IF MATERIAL IS RELEASED OR SPILLED:** Contain spilled liquid with sand or earth. DO NOT use combustible materials such as sawdust. Isolate the hazard area and deny entry to unnecessary and unprotected personnel. Remove all sources of ignition, ventilate area and remove with inert absorbent and non-sparking tools. Dispose of according to local, state (provincial) and federal regulations. Do not incinerate closed containers. Ventilate area, isolate spilled material, and remove with inert absorbent. Dispose of contaminated absorbent, container, and unused contents in accordance with local, state, and federal regulations.

## 7. Handling and Storage

**HANDLING:** Wash thoroughly after handling. Wash hands before eating. Remove contaminated clothing and launder before reuse. Use only with adequate ventilation. Follow all SDS and label precautions even after container is emptied because it may retain product residues. Avoid breathing fumes, vapors, or mist. Avoid contact with eyes, skin and clothing.

**STORAGE:** Keep containers tightly closed. Isolate from heat, electrical equipment, sparks and open flame. Contents under pressure. Do not store above 120 ° F. Store large quantities in buildings designed and protected for storage of flammable aerosols. Product should be stored in tightly sealed containers and protected from heat, moisture, and foreign materials. Store in a dry, well ventilated place. Keep container tightly closed when not in use. Keep away from heat, sparks, flame and sources of ignition. Avoid excess heat.

**Advice on Safe Handling of Combustible Dust:** No Information

## 8. Exposure Controls / Personal Protection

Chemical Name	CAS-No.	Weight % Less Than	ACGIH TLV- TWA	ACGIH TLV- STEL	OSHA PEL-TWA	OSHA PEL- CEILING
Acetone	67-64-1	30.0	250 ppm	500 ppm	1000 ppm	N.E.
Propane	74-98-6	25.0	N.E.	N.E.	1000 ppm	N.E.
n-Butyl Acetate	123-86-4	15.0	50 ppm	150 ppm	150 ppm	N.E.
n-Butane	106-97-8	10.0	N.E.	1000 ppm	N.E.	N.E.
Naphtha, Petroleum, Hydrotreated Light	64742-49-0	5.0	N.E.	N.E.	N.E.	N.E.
1-Methoxy-2-Propyl Acetate	108-65-6	5.0	N.E.	N.E.	N.E.	N.E.
Xylenes (o-, m-, p- isomers)	1330-20-7	5.0	100 ppm	150 ppm	100 ppm	N.E.
Propylene Glycol Monobutyl Ether	5131-66-8	5.0	N.E.	N.E.	N.E.	N.E.
Aluminum Flake	7429-90-5	5.0	1 mg/m <sup>3</sup>	N.E.	15 mg/m <sup>3</sup>	N.E.
Ethylbenzene	100-41-4	1.0	20 ppm	N.E.	100 ppm	N.E.
Naphtha, Hydrotreated Heavy	64742-48-9	1.0	N.E.	N.E.	N.E.	N.E.
bis(1,2,2,6,6-Pentamethyl-4- Piperidiny)l Sebacate	41556-26-7	1.0	N.E.	N.E.	N.E.	N.E.
Solvent Naphtha, Light Aromatic	64742-95-6	1.0	N.E.	N.E.	N.E.	N.E.
Stoddard Solvent	8052-41-3	1.0	100 ppm	N.E.	500 ppm	N.E.
Ethylene Glycol Monobutyl Ether	111-76-2	1.0	20 ppm	N.E.	50 ppm	N.E.
Ethanol	64-17-5	1.0	N.E.	1000 ppm	1000 ppm	N.E.

### PERSONAL PROTECTION

**ENGINEERING CONTROLS:** Use explosion-proof ventilation equipment. Provide general dilution of local exhaust ventilation in volume and pattern to keep TLV of hazardous ingredients below acceptable limits. Prevent build-up of vapors by opening all doors and windows to achieve cross-ventilation. Use process enclosures, local exhaust ventilation, or other engineering controls to control airborne levels below recommended exposure limits.

**RESPIRATORY PROTECTION:** A respiratory protection program that meets OSHA 1910.134 and ANSI Z88.2 requirements must be followed whenever workplace conditions warrant a respirator's use. A NIOSH/MSHA approved air purifying respirator with organic vapor cartridge or canister may be permissible under certain circumstances where airborne concentrations are expected to exceed exposure limits.

**SKIN PROTECTION:** Use gloves to prevent prolonged skin contact. Nitrile or Neoprene gloves may afford adequate skin protection.

**EYE PROTECTION:** Use safety eyewear designed to protect against splash of liquids.

**OTHER PROTECTIVE EQUIPMENT:** Refer to safety supervisor or industrial hygienist for further guidance regarding types of personal protective equipment and their applications.

**HYGIENIC PRACTICES:** Wash thoroughly with soap and water before eating, drinking or smoking. Remove contaminated clothing immediately and launder before reuse.

**Engineering Measures for Combustible Dust:** No Information

## 9. Physical and Chemical Properties

<b>Appearance:</b>	Aerosolized Mist	<b>Physical State:</b>	Liquid
<b>Odor:</b>	Solvent Like	<b>Odor Threshold:</b>	N.E.
<b>Relative Density:</b>	0.735	<b>pH:</b>	N.A.
<b>Freeze Point, °C:</b>	N.D.	<b>Viscosity:</b>	N.D.
<b>Solubility in Water:</b>	Slight	<b>Partition Coefficient, n-octanol/ water:</b>	N.D.
<b>Decomposition Temp., °C:</b>	N.D.	<b>Explosive Limits, vol%:</b>	0.9 - 13.0
<b>Boiling Range, °C:</b>	-37 - 537	<b>Flash Point, °C:</b>	-96
<b>Flammability:</b>	Supports Combustion	<b>Auto-ignition Temp., °C:</b>	N.D.
<b>Evaporation Rate:</b>	Faster than Ether	<b>Vapor Pressure:</b>	N.D.
<b>Vapor Density:</b>	Heavier than Air		

(See "Other information" Section for abbreviation legend)

## 10. Stability and Reactivity

**CONDITIONS TO AVOID:** Flammable hydrogen gas will evolve when product comes in contact with water or damp air. Heat will be generated. The amount of heat generated will depend upon the volume of material in contact. Avoid temperatures above 120°F (49°C). Avoid all possible sources of ignition.

**INCOMPATIBILITY:** Incompatible with strong oxidizing agents, strong acids and strong alkalis.

**HAZARDOUS DECOMPOSITION:** By open flame, carbon monoxide and carbon dioxide. When heated to decomposition, it emits acrid smoke and irritating fumes. Contains solvents which may form carbon monoxide, carbon dioxide, and formaldehyde.

**HAZARDOUS POLYMERIZATION:** Will not occur under normal conditions.

**STABILITY:** This product is stable under normal storage conditions.

## 11. Toxicological Information

**EFFECTS OF OVEREXPOSURE - EYE CONTACT:** Causes Serious Eye Irritation

**EFFECTS OF OVEREXPOSURE - SKIN CONTACT:** May cause skin sensitization, an allergic reaction, which becomes evident upon re-exposure to this material. May cause skin irritation. Allergic reactions are possible.

**EFFECTS OF OVEREXPOSURE - INHALATION:** High gas, vapor, mist or dust concentrations may be harmful if inhaled. High vapor concentrations are irritating to the eyes, nose, throat and lungs. Harmful if inhaled. Avoid breathing fumes, spray, vapors, or mist. Prolonged or excessive inhalation may cause respiratory tract irritation.

**EFFECTS OF OVEREXPOSURE - INGESTION:** Harmful if swallowed.

**EFFECTS OF OVEREXPOSURE - CHRONIC HAZARDS:** Overexposure to xylene in laboratory animals has been associated with liver abnormalities, kidney, lung, spleen, eye and blood damage as well as reproductive disorders. Effects in humans, due to chronic overexposure, have included liver, cardiac abnormalities and nervous system damage. IARC lists Ethylbenzene as a possible human carcinogen (group 2B). Reports have associated repeated and prolonged occupational overexposure to solvents with permanent brain and nervous system damage. May cause central nervous system disorder (e.g., narcosis involving a loss of coordination, weakness, fatigue, mental confusion, and blurred vision) and/or damage. High concentrations may lead to central nervous system effects (drowsiness, dizziness, nausea, headaches, paralysis, and blurred vision) and/or damage.

**PRIMARY ROUTE(S) OF ENTRY:** Eye Contact, Ingestion, Inhalation, Skin Absorption, Skin Contact

### ACUTE TOXICITY VALUES

The acute effects of this product have not been tested. Data on individual components are tabulated below:

<u>CAS-No.</u>	<u>Chemical Name</u>	<u>Oral LD50</u>	<u>Dermal LD50</u>	<u>Vapor LC50</u>
67-64-1	Acetone	5800 mg/kg Rat	>15700 mg/kg Rabbit	50.1 mg/L Rat
123-86-4	n-Butyl Acetate	10768 mg/kg Rat	>17600 mg/kg Rabbit	> 21 mg/L Rat
106-97-8	n-Butane	N.E.	N.E.	658 mg/L Rat
64742-49-0	Naphtha, Petroleum, Hydrotreated Light	>5000 mg/kg Rat	>3160 mg/kg Rabbit	>4951 mg/L Rat
108-65-6	1-Methoxy-2-Propyl Acetate	8532 mg/kg Rat	>5000 mg/kg Rabbit	N.E.
1330-20-7	Xylenes (o-, m-, p- isomers)	3500 mg/kg Rat	>4350 mg/kg Rabbit	29.08 mg/L Rat
5131-66-8	Propylene Glycol Monobutyl Ether	1900 mg/kg Rat	N.E.	N.E.
100-41-4	Ethylbenzene	3500 mg/kg Rat	15400 mg/kg Rabbit	17.4 mg/L Rat
64742-48-9	Naphtha, Hydrotreated Heavy	>6000 mg/kg Rat	>3160 mg/kg Rabbit	N.E.
41556-26-7	bis(1,2,2,6,6-Pentamethyl-4-Piperidiny) Sebacate	2615 mg/kg Rat	N.E.	N.E.
64742-95-6	Solvent Naphtha, Light Aromatic	8400 mg/kg Rat	>2000 mg/kg Rabbit	N.E.
111-76-2	Ethylene Glycol Monobutyl Ether	470 mg/kg Rat	1,060 mg/kg Rabbit	11 mg/L
64-17-5	Ethanol	7060 mg/kg Rat	15,800 mg/kg Rabbit	30,000 mg/l Rat

N.E. - Not Established

## 12. Ecological Information

**ECOLOGICAL INFORMATION:** Product is a mixture of listed components.

## 13. Disposal Information

**DISPOSAL INFORMATION:** Do not incinerate closed containers. This product as supplied is a USEPA defined ignitable hazardous waste. Dispose of unusable product as a hazardous waste (D001) in accordance with local, state, and federal regulation.

## 14. Transport Information

	<u>Domestic (USDOT)</u>	<u>International (IMDG)</u>	<u>Air (IATA)</u>	<u>TDG (Canada)</u>
<b>UN Number:</b>	N.A.	1950	1950	N.A.
<b>Proper Shipping Name:</b>	Paint Products in Limited Quantities	Aerosols	Aerosols	Paint Products in Limited Quantities
<b>Hazard Class:</b>	N.A.	2.1	2.1	N.A.
<b>Packing Group:</b>	N.A.	N.A.	N.A.	N.A.
<b>Limited Quantity:</b>	Yes	Yes	Yes	Yes

## 15. Regulatory Information

### U.S. Federal Regulations:

#### CERCLA - SARA Hazard Category

This product has been reviewed according to the EPA 'Hazard Categories' promulgated under Sections 311 and 312 of the Superfund Amendment and Reauthorization Act of 1986 (SARA Title III) and is considered, under applicable definitions, to meet the following categories:

No Information

#### Sara Section 313:

This product contains the following substances subject to the reporting requirements of Section 313 of Title III of the Superfund Amendment and Reauthorization Act of 1986 and 40 CFR part 372:

<u>Chemical Name</u>	<u>CAS-No.</u>
Xylenes (o-, m-, p- isomers)	1330-20-7
Aluminum Flake	7429-90-5
Ethylbenzene	100-41-4
Ethylene Glycol Monobutyl Ether	111-76-2

#### Toxic Substances Control Act:

This product contains the following chemical substances subject to the reporting requirements of TSCA 12(b) if exported from the United States:

No TSCA 12(b) components exist in this product.

**16. Other Information****HMIS RATINGS**

**Health:** 2\*      **Flammability:** 4      **Physical Hazard:** 0      **Personal Protection:** X

**NFPA RATINGS**

**Health:** 2      **Flammability:** 4      **Instability:** 0

**VOLATILE ORGANIC COMPOUNDS, g/L:** 550

**SDS REVISION DATE:** 2/13/2018

**REASON FOR REVISION:**

Legend: N.A. - Not Applicable, N.E. - Not Established, N.D. - Not Determined

Rust-Oleum Corporation believes, to the best of its knowledge, information and belief, the information contained herein to be accurate and reliable as of the date of this safety data sheet. However, because the conditions of handling, use, and storage of these materials are beyond our control, we assume no responsibility or liability for personal injury or property damage incurred by the use of these materials. Rust-Oleum Corporation makes no warranty, expressed or implied, regarding the accuracy or reliability of the data or results obtained from their use. All materials may present unknown hazards and should be used with caution. The information and recommendations in this material safety data sheet are offered for the users' consideration and examination. It is the responsibility of the user to determine the final suitability of this information and to comply with all applicable international, federal, state, and local laws and regulations.