Date Printed: 12/15/2020 Page 1 / 5

Safety Data Sheet



1. Identification

Product Name: MS 511 IMPREGNATOR GAL 4PK **Revision Date:** 12/15/2020

Product Identifier: 511GAL4 Supercedes Date: 2/24/2020

Recommended Use: Penetrating sealer

Rust-Oleum Corporation Manufacturer:

11 Hawthorn Parkway Vernon Hills, IL 60061

USA

Rust-Oleum Corporation Supplier: 11 Hawthorn Parkway

Vernon Hills, IL 60061

USA

Preparer: Regulatory Department

24 Hour Hotline: 847-367-7700 **Emergency Telephone:**

2. Hazards Identification

Classification

Symbol(s) of Product





Signal Word

Danger

Possible Hazards

3% of the mixture consists of ingredient(s) of unknown acute toxicity.

GHS HAZARD STATEMENTS

H227 Flammable liquid, category 4 Combustible liquid.

Carcinogenicity, category 2 H351 Suspected of causing cancer.

Aspiration Hazard, category 1 H304 May be fatal if swallowed and enters airways.

Skin Irritation, category 2 H315 Causes skin irritation. Eye Irritation, category 2A H319 Causes serious eye irritation.

GHS LABEL PRECAUTIONARY STATEMENTS

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. NO

SMOKING.

P280 Wear protective gloves/protective clothing/eye protection/face protection.

P370+P378 In case of fire: Use alcohol film forming foam, carbon dioxide, dry chemical, dry sand to extinguish.

P403+P235 Store in a well-ventilated place. Keep cool.

P501 Dispose of contents/container in accordance with local, regional and national regulations.

P201 Obtain special instructions before use.

P308+P313 IF exposed or concerned: Get medical advice/attention.

P405 Store locked up.

P301+P310 IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician. Date Printed: 12/15/2020 Page 2 / 5

P331 Do NOT induce vomiting.

P264 Wash hands thoroughly after handling.

P302+P352 IF ON SKIN: Wash with plenty of soap and water.

P321 For specific treatment see label.

P332+P313 If skin irritation occurs: Get medical advice/attention.
P362+P364 Take off contaminated clothing and wash it before reuse.

P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present

and easy to do. Continue rinsing.

P337+P313 If eye irritation persists: Get medical advice/attention.

3. Composition / Information on Ingredients

HAZARDOUS SUBSTANCES

Chemical Name	CAS-No.	<u>Wt.%</u> <u>Range</u>	GHS Symbols	GHS Statements
Hydrotreated Light Distillate	64742-47-8	75-100	GHS08	H304
3-Aminopropyltriethoxysilane	919-30-2	1.0-2.5	GHS05-GHS06	H302-314-331
Xylenes (o-, m-, p- Isomers)	1330-20-7	1.0-2.5	GHS02-GHS07	H226-315-319-332
Naphtha, Hydrotreated Heavy	64742-48-9	1.0-2.5	GHS08	H304
Ethylbenzene	100-41-4	0.1-1.0	GHS02-GHS07- GHS08	H225-304-332-351-373
n-Butyl Acetate	123-86-4	0.1-1.0	GHS02-GHS07	H226-336
Stannane, dioctylbis[(1-oxododecyl)oxy]-	3648-18-8	<0.1	Not Available	Not Available

4. First-Aid Measures

FIRST AID - EYE CONTACT: Immediately flush eyes with plenty of water for at least 15 minutes holding eyelids open. Get medical attention. Do NOT allow rubbing of eyes or keeping eyes closed.

FIRST AID - SKIN CONTACT: Wash skin with soap and water. Remove contaminated clothing. Get medical attention if irritation develops or persists.

FIRST AID - INHALATION: Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get immediate medical attention. Do NOT use mouth-to-mouth resuscitation. If you experience difficulty in breathing, leave the area to obtain fresh air. If continued difficulty is experienced, get medical assistance immediately.

FIRST AID - INGESTION: If swallowed, get medical attention.

5. Fire-Fighting Measures

EXTINGUISHING MEDIA: Alcohol Film Forming Foam, Carbon Dioxide, Dry Chemical, Dry Sand, Water Fog

UNUSUAL FIRE AND EXPLOSION HAZARDS: No unusual fire or explosion hazards noted. Closed containers may explode when exposed to extreme heat due to buildup of steam. Keep containers tightly closed. Combustible liquid and vapor.

SPECIAL FIREFIGHTING PROCEDURES: Evacuate area and fight fire from a safe distance. Use water spray to keep fire-exposed containers cool. Containers may explode when heated.

Special Fire and Explosion Hazard (Combustible Dust): No Information

6. Accidental Release Measures

STEPS TO BE TAKEN IF MATERIAL IS RELEASED OR SPILLED: Dispose of according to local, state (provincial) and federal regulations. Do not incinerate closed containers. Remove all sources of ignition, ventilate area and remove with inert absorbent and non-sparking tools.

Date Printed: 12/15/2020 Page 3 / 5

7. Handling and Storage

HANDLING: Wash thoroughly after handling. Wash hands before eating. Remove contaminated clothing and launder before reuse. Use only with adequate ventilation. Follow all SDS and label precautions even after container is emptied because it may retain product residues. Avoid breathing fumes, vapors, or mist. Avoid contact with eyes, skin and clothing.

STORAGE: Store in a dry, well ventilated place. Keep container tightly closed when not in use. Keep containers tightly closed. Isolate from heat, electrical equipment, sparks and open flame. Avoid excess heat.

Advice on Safe Handling of Combustible Dust: No Information

8. Exposure Controls / Personal Protection

Chemical Name	CAS-No.	Weight % Less Than	ACGIH TLV- TWA	ACGIH TLV- STEL	OSHA PEL-TWA	OSHA PEL- CEILING
Hydrotreated Light Distillate	64742-47-8	90.0	N.E.	N.E.	N.E.	N.E.
3-Aminopropyltriethoxysilane	919-30-2	5.0	N.E.	N.E.	N.E.	N.E.
Xylenes (o-, m-, p- Isomers)	1330-20-7	5.0	100 ppm	150 ppm	100 ppm	N.E.
Naphtha, Hydrotreated Heavy	64742-48-9	5.0	N.E.	N.E.	N.E.	N.E.
Ethylbenzene	100-41-4	1.0	20 ppm	N.E.	100 ppm	N.E.
n-Butyl Acetate	123-86-4	1.0	50 ppm	150 ppm	150 ppm	N.E.
Stannane, dioctylbis[(1- oxododecyl)oxy]-	3648-18-8	0.1	0.1 mg/m3	0.2 mg/m3	0.1 mg/m3	N.E.

PERSONAL PROTECTION

ENGINEERING CONTROLS: Use process enclosures, local exhaust ventilation, or other engineering controls to control airborne levels below recommended exposure limits. Prevent build-up of vapors by opening all doors and windows to achieve crossventilation.

RESPIRATORY PROTECTION: A respiratory protection program that meets OSHA 1910.134 and ANSI Z88.2 requirements must be followed whenever workplace conditions warrant a respirator's use.

SKIN PROTECTION: Use gloves to prevent prolonged skin contact. Nitrile or Neoprene gloves may afford adequate skin protection.

EYE PROTECTION: Use safety eyewear designed to protect against splash of liquids.

OTHER PROTECTIVE EQUIPMENT: Refer to safety supervisor or industrial hygienist for further guidance regarding types of personal protective equipment and their applications.

HYGIENIC PRACTICES: Wash thoroughly with soap and water before eating, drinking or smoking. Remove contaminated clothing immediately and launder before reuse.

Engineering Measures for Combustible Dust: No Information

9. Physical and Chemical Properties

Appearance:	Liquid	Physical State:	Liquid
Odor:	Solvent Like	Odor Threshold:	N.E.
Specific Gravity:	0.814	pH:	N.A.
Freeze Point, °C:	N.D.	Viscosity:	N.D.
Solubility in Water:	Slight	Partition Coefficient, n-octanol/	ND
Decomposition Temp., °C:	N.D.	water:	N.D.
Boiling Range, °C:	128 - 537	Explosive Limits, vol%:	0.7 - 17.5
Flammability:	Supports Combustion	Flash Point, °C:	70
Evaporation Rate:	Slower than Ether	Auto-Ignition Temp., °C:	N.D.
Vapor Density:	Heavier than Air	Vapor Pressure:	N.D.

(See "Other information" Section for abbreviation legend)

10. Stability and Reactivity

Conditions to Avoid: No Information

Incompatibility: Incompatible with strong oxidizing agents, strong acids and strong alkalies.

Hazardous Decomposition: When heated to decomposition, it emits acrid smoke and irritating fumes. Contains solvents which may form carbon monoxide, carbon dioxide, and formaldehyde.

Hazardous Polymerization: Will not occur under normal conditions.

Stability: This product is stable under normal storage conditions.

Date Printed: 12/15/2020 Page 4 / 5

11. Toxicological Information

EFFECTS OF OVEREXPOSURE - EYE CONTACT: Substance causes moderate eye irritation.

EFFECTS OF OVEREXPOSURE - SKIN CONTACT: Substance may cause slight skin irritation.

EFFECTS OF OVEREXPOSURE - INHALATION: High gas, vapor, mist or dust concentrations may be harmful if inhaled. Avoid breathing fumes, spray, vapors, or mist. High vapor concentrations are irritating to the eyes, nose, throat and lungs. Prolonged or excessive inhalation may cause respiratory tract irritation.

EFFECTS OF OVEREXPOSURE - INGESTION: Irritating to the nose, throat and respiratory tract. Harmful if swallowed.

EFFECTS OF OVEREXPOSURE - CHRONIC HAZARDS: IARC lists Ethylbenzene as a possible human carcinogen (group 2B). Overexposure to xylene in laboratory animals has been associated with liver abnormalities, kidney, lung, spleen, eye and blood damage as well as reproductive disorders. Effects in humans, due to chronic overexposure, have included liver, cardiac abnormalities and nervous system damage. Reports have associated repeated and prolonged occupational overexposure to solvents with permanent brain and nervous system damage.

PRIMARY ROUTE(S) OF ENTRY: Eye Contact, Ingestion, Inhalation, Skin Absorption, Skin Contact

ACUTE TOXICITY VALUES

The acute effects of this product have not been tested. Data on individual components are tabulated below:

CAS-No.	Chemical Name	Oral LD50	Dermal LD50	Vapor LC50
64742-47-8	Hydrotreated Light Distillate	>5000 mg/kg Rat	>2000 mg/kg Rabbit	>5000 mg/L Rat
919-30-2	3-Aminopropyltriethoxysilane	1780 mg/kg Rat	4290 mg/kg Rabbit	>7.35 mg/L Rat
1330-20-7	Xylenes (o-, m-, p- Isomers)	3500 mg/kg Rat	>4350 mg/kg Rabbit	29.08 mg/L Rat
64742-48-9	Naphtha, Hydrotreated Heavy	>6000 mg/kg Rat	>3160 mg/kg Rabbit	N.E.
100-41-4	Ethylbenzene	3500 mg/kg Rat	15400 mg/kg Rabbit	17.4 mg/L Rat
123-86-4	n-Butyl Acetate	10768 mg/kg Rat	>17600 mg/kg Rabbit	> 21 mg/L Rat
3648-18-8	Stannane, dioctylbis[(1-oxododecyl)oxy]-	6450 mg/kg Rat	N.E.	N.E.

N.E. - Not Established

12. Ecological Information

ECOLOGICAL INFORMATION: Product is a mixture of listed components.

13. Disposal Information

DISPOSAL INFORMATION: Do not incinerate closed containers. Dispose of material in accordance to local, state, and federal regulations and ordinances.

14. Transport Information

UN Number:	Domestic (USDOT)	International (IMDG)	<u>Air (IATA)</u>	TDG (Canada)
	N.A.	N.A.	N.A.	N.A.
Proper Shipping Name:	Not Regulated	Not Regulated	Not Regulated	Not Regulated
Hazard Class: Packing Group: Limited Quantity:	N.A.	N.A.	N.A.	N.A.
	N.A.	N.A.	N.A.	N.A.
	No	No	No	No

15. Regulatory Information

U.S. Federal Regulations:

CERCLA - SARA Hazard Category

This product has been reviewed according to the EPA 'Hazard Categories' promulgated under Sections 311 and 312 of the Superfund Amendment and Reauthorization Act of 1986 (SARA Title III) and is considered, under applicable definitions, to meet the following categories:

Date Printed: 12/15/2020 Page 5 / 5

Flammable (gases, aerosols, liquids, or solids), Carcinogenicity, Skin Corrosion or Irritation, Serious eye damage or eye irritation, Aspiration Hazard

SARA Section 313

This product contains the following substances subject to the reporting requirements of Section 313 of Title III of the Superfund Amendment and Reauthorization Act of 1986 and 40 CFR part 372:

Chemical NameCAS-No.Xylenes (o-, m-, p- Isomers)1330-20-7Ethylbenzene100-41-4

Toxic Substances Control Act

This product contains the following chemical substances subject to the reporting requirements of TSCA 12(b) if exported from the United States:

No TSCA 12(b) components exist in this product.

U.S. State Regulations:

California Proposition 65

WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov.

16. Other Information

HMIS RATINGS

Health: 2* Flammability: 2 Physical Hazard: 0 Personal Protection: X

NFPA RATINGS

Health: 2 Flammability: 2 Instability: 0

Volatile Organic Compounds: 741 g/L

SDS REVISION DATE: 12/15/2020

REASON FOR REVISION: Product Composition Changed

Substance and/or Product Properties Changed in Section(s):

02 - Hazard Identification 14 - Transport Information 16 - Other Information Revision Statement(s) Changed

Legend: N.A. - Not Applicable, N.D. - Not Determined, N.E. - Not Established

The manufacturer believes, to the best of its knowledge, information and belief, the information contained herein to be accurate and reliable as of the date of this safety data sheet. However, because the conditions of handling, use, and storage of these materials are beyond our control, we assume no responsibility or liability for personal injury or property damage incurred by the use of these materials. The manufacturer makes no warranty, expressed or implied, regarding the accuracy or reliability of the data or results obtained from their use. All materials may present unknown hazards and should be used with caution. The information and recommendations in this material safety data sheet are offered for the users' consideration and examination. It is the responsibility of the user to determine the final suitability of this information and to comply with all applicable international, federal, state, and local laws and regulations.