Date Printed: 6/1/2023 Page 1 / 4

Safety Data Sheet



* Trusted Quality Since 1921 * www.rustoleum.com

1. Identification

Product Name: MS POULTICE PLUS 1LB 3PK **Revision Date:** 6/1/2023

POULTPLUS3 Product Identifier: Supercedes Date: 8/3/2018

Recommended Use: Stain removing powder

Rust-Oleum Corporation Rust-Oleum Corporation Supplier: Manufacturer: 11 Hawthorn Parkway 11 Hawthorn Parkway

USA

Vernon Hills, IL 60061

Vernon Hills, IL 60061

USA

Preparer: Regulatory Department

24 Hour Hotline: 847-367-7700 **Emergency Telephone:**

2. Hazards Identification

Classification

Symbol(s) of Product

No symbol is required per 2012 OSHA Hazard Communication Standard 29 CFR 1910.1200.

Signal Word

No Signal Word has been assigned.

3. Composition / Information on Ingredients

HAZARDOUS SUBSTANCES

Chemical Name CAS-No. Wt.% **GHS Symbols GHS Statements** Range

No hazardous items exist

4. First-Aid Measures

FIRST AID - EYE CONTACT: Immediately flush eyes with plenty of water for at least 15 minutes holding eyelids open. Get medical attention. Do NOT allow rubbing of eyes or keeping eyes closed.

FIRST AID - SKIN CONTACT: Wash skin with soap and water. Remove contaminated clothing. Get medical attention if irritation develops or persists.

FIRST AID - INHALATION: Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get immediate medical attention. Do NOT use mouth-to-mouth resuscitation. If you experience difficulty in breathing, leave the area to obtain fresh air. If continued difficulty is experienced, get medical assistance immediately.

FIRST AID - INGESTION: If swallowed, rinse mouth with water. If feeling unwell, get medical attention.

Date Printed: 6/1/2023 Page 2 / 4

5. Fire-Fighting Measures

EXTINGUISHING MEDIA: None Known

UNUSUAL FIRE AND EXPLOSION HAZARDS: Keep containers tightly closed. FLASH POINT IS TESTED TO BE GREATER THAN 200 DEGREES F. No unusual fire or explosion hazards noted.

SPECIAL FIREFIGHTING PROCEDURES: Water may be used to cool closed containers to prevent buildup of steam.

Special Fire and Explosion Hazard (Combustible Dust): No Information

6. Accidental Release Measures

STEPS TO BE TAKEN IF MATERIAL IS RELEASED OR SPILLED: Dispose of according to local, state (provincial) and federal regulations. Do not incinerate closed containers. Sweep up gently to avoid dust cloud formation.

7. Handling and Storage

HANDLING: Wash thoroughly after handling. Wash hands before eating. Remove contaminated clothing and launder before reuse. Use only with adequate ventilation. Follow all SDS and label precautions even after container is emptied because it may retain product residues. Avoid breathing fumes, vapors, or mist. Avoid contact with eyes, skin and clothing.

STORAGE: Store in a dry, well ventilated place. Keep container tightly closed when not in use.

Advice on Safe Handling of Combustible Dust: No Information

8. Exposure Controls / Personal Protection

Chemical Name	CAS-No.	Weight % Less Than	ACGIH TLV- TWA	ACGIH TLV- STEL	OSHA PEL- TWA	OSHA PEL- CEILING
No hazardous items exist						

PERSONAL PROTECTION

ENGINEERING CONTROLS: Use process enclosures, local exhaust ventilation, or other engineering controls to control airborne levels below recommended exposure limits. Prevent build-up of vapors by opening all doors and windows to achieve crossventilation.

RESPIRATORY PROTECTION: A respiratory protection program that meets OSHA 1910.134 and ANSI Z88.2 requirements must be followed whenever workplace conditions warrant a respirator's use.

SKIN PROTECTION: Use gloves to prevent prolonged skin contact. Nitrile or Neoprene gloves may afford adequate skin protection.

EYE PROTECTION: Use safety eyewear designed to protect against splash of liquids.

OTHER PROTECTIVE EQUIPMENT: Refer to safety supervisor or industrial hygienist for further guidance regarding types of personal protective equipment and their applications.

HYGIENIC PRACTICES: Wash thoroughly with soap and water before eating, drinking or smoking. Remove contaminated clothing immediately and launder before reuse.

Engineering Measures for Combustible Dust: No Information

9. Physical and Chemical Properties

Appearance: Physical State: Solid Solid Odor: **Odor Threshold:** None N.E. Specific Gravity: pH: 2.350 N.A. Freeze Point. °C: Viscosity: N.D. N.D. Solubility in Water: None Partition Coefficient, n-octanol/ N.D. water: Decomposition Temp., °C: N.D. Boiling Range, °C: 537 - 537 Explosive Limits, vol%: N.A. - N.A. Flammability: Flash Point, °C: 94 Does not Support Combustion **Evaporation Rate:** Auto-Ignition Temp., °C: Slower than Ether N.D. Vapor Pressure: Vapor Density: Heavier than Air N.D.

(See "Other information" Section for abbreviation legend)

Date Printed: 6/1/2023 Page 3 / 4

10. Stability and Reactivity

Conditions to Avoid: No Information

Incompatibility: Incompatible with strong oxidizing agents, strong acids and strong alkalies.

Hazardous Decomposition: When heated to decomposition, it emits acrid smoke and irritating fumes.

Hazardous Polymerization: Will not occur under normal conditions. **Stability:** This product is stable under normal storage conditions.

11. Toxicological Information

EFFECTS OF OVEREXPOSURE - EYE CONTACT: Irritating, and may injure eye tissue if not removed promptly.

EFFECTS OF OVEREXPOSURE - SKIN CONTACT: Low hazard for usual industrial handling or commercial handling by trained personnel.

EFFECTS OF OVEREXPOSURE - INHALATION: High gas, vapor, mist or dust concentrations may be harmful if inhaled. Avoid breathing fumes, spray, vapors, or mist.

EFFECTS OF OVEREXPOSURE - INGESTION: Expected to be a low ingestion hazard.

EFFECTS OF OVEREXPOSURE - CHRONIC HAZARDS: No Information

PRIMARY ROUTE(S) OF ENTRY: No Information

ACUTE TOXICITY VALUES

The acute effects of this product have not been tested. Data on individual components are tabulated below:

<u>CAS-No. Chemical Name</u> <u>Oral LD50</u> <u>Dermal LD50</u> <u>Vapor LC50</u>

No hazardous items exist.

N.E. - Not Established

12. Ecological Information

ECOLOGICAL INFORMATION: Product is a mixture of listed components.

13. Disposal Information

DISPOSAL: Dispose of material in accordance to local, state, and federal regulations and ordinances.

14. Transport Information

	<u>Domestic (USDOT)</u>	<u>International (IMDG)</u>	<u>Air (IATA)</u>	TDG (Canada)
UN Number:	N.A.	N.A.	N.A.	N.A.
Proper Shipping Name:	Not Regulated	Not Regulated	Not Regulated	Not Regulated
Hazard Class:	N.A.	N.A.	N.A.	N.A.
Packing Group:	N.A.	N.A.	N.A.	N.A.
Limited Quantity:	No	No	No	No

15. Regulatory Information

U.S. Federal Regulations:

CERCLA - SARA Hazard Category

This product has been reviewed according to the EPA 'Hazard Categories' promulgated under Sections 311 and 312 of the Superfund Amendment and Reauthorization Act of 1986 (SARA Title III) and is considered, under applicable definitions, to meet the following categories:

Date Printed: 6/1/2023 Page 4 / 4

None Known

SARA Section 313

This product contains the following substances subject to the reporting requirements of Section 313 of Title III of the Superfund Amendment and Reauthorization Act of 1986 and 40 CFR part 372:

No Sara 313 components exist in this product.

Toxic Substances Control Act

This product contains the following chemical substances subject to the reporting requirements of TSCA 12(b) if exported from the United States:

No TSCA 12(b) components exist in this product.

U.S. State Regulations:

California Proposition 65

WARNING: No Prop. 65 warning is required.

16. Other Information

HMIS RATINGS

Health: 1 Flammability: 0 Physical Hazard: 0 Personal Protection: X

NFPA RATINGS

Health: 0 Flammability: 0 Instability: 0

Volatile Organic Compounds: 0.00% SDS REVISION DATE: 6/1/2023

REASON FOR REVISION: Revision Description Changed

Substance and/or Product Properties Changed in

Section(s): 01 - Identification

03 - Composition / Information on Ingredients

09 - Physical & Chemical Properties15 - Regulatory InformationRevision Statement(s) Changed

Legend: N.A. - Not Applicable, N.D. - Not Determined, N.E. - Not Established

The manufacturer believes, to the best of its knowledge, information and belief, the information contained herein to be accurate and reliable as of the date of this safety data sheet. However, because the conditions of handling, use, and storage of these materials are beyond our control, we assume no responsibility or liability for personal injury or property damage incurred by the use of these materials. The manufacturer makes no warranty, expressed or implied, regarding the accuracy or reliability of the data or results obtained from their use. All materials may present unknown hazards and should be used with caution. The information and recommendations in this material safety data sheet are offered for the users' consideration and examination. It is the responsibility of the user to determine the final suitability of this information and to comply with all applicable international, federal, state, and local laws and regulations.