

UNI-04



UNIVERSAL[®] GLOSS, FLAT AND MATTE ENAMEL SPRAYS

DESCRIPTION AND USES

Universal[®] Gloss, Flat and Matte Enamel Sprays provide long-lasting protection and durability. These sprays apply easily, provide excellent coverage and dry fast to a tough attractive finish. Universal Gloss & Flat Enamel Sprays are ideal for plastic, wood, metal, wicker, and aluminum. Universal features a comfort grip trigger that reduces fatigue caused by continuous spraying and an any-angle tip which allows you to spray at any angle.

TIP: Some plastics made of polyethylene such as plastic storage containers are manufactured in a way that may hinder maximum paint adhesion. Test paint in a hidden area first.

PRODUCTS

SKU	DESCRIPTION (Aerosol)		
245196	Gloss Black		
245199	Gloss White		
245211	Gloss Cardinal Red		
245212	Gloss Cobalt Blue		
245213	Gloss Canary Yellow		
245214	Gloss Hunter Green		
245215	Gloss Espresso Brown		
247562	Gloss Crimson Red		
249339	Gloss Slate Gray		
284959	Gloss Dark Cherry		
284960	Gloss Deep Turquoise		
245198	Flat Black		
247564	Flat White		
282813	Matte Citron		
282814	Matte Harvest Orange		
282815	Matte Castle Rock		
282816 Matte French Cream			
282817	282817 Matte Burlap		
282818	Matte Iced Gray		
282819	Matte Bittersweet		
330505	Matte Farmhouse Black		
376723	Matte Farmhouse Slate Blue		
376724	Matte Farmhouse Greige		
376725	Matte Farmhouse White		

PRODUCT APPLICATION

SURFACE PREPARATION

Remove all dirt, grease, oil, salt and chemical contaminants by washing the surface with a commercial detergent, or other suitable cleaning method. Rinse with fresh water and allow to thoroughly dry. Remove loose paint and rust with a wire brush or sandpaper. Previously coated surfaces must be sound and in good condition. Smooth, hard, or glossy finishes should be scarified by sanding to create a surface profile.

PRODUCT APPLICATION (cont.)

SURFACE PREPARATION (cont.)

WARNING! If you scrape, sand or remove old paint from any surface, you may release lead paint dust. LEAD IS TOXIC. EXPOSURE TO LEAD DUST CAN CAUSE SERIOUS ILLNESS, SUCH AS BRAIN DAMAGE; ESPECIALLY IN CHILDREN. PREGNANT WOMEN SHOULD ALSO AVOID EXPOSURE. Wear a NIOSH approved respirator to control lead exposure. Clean up carefully with a HEPA vacuum and a wet mop. Before you start, find out how to protect yourself and your family by contacting the National Lead Information Hotline at 1-800-424-LEAD or log on to www.epa.gov/lead.

APPLICATION

Use outdoors or in a well ventilated area such as an open garage. Use when temperature is between 50-90°F (10-32°C) and humidity is below 65% to ensure proper drying. Do not use on objects that may exceed 200°F (93°C) surface temperature.

Do not apply to galvanized steel. Avoid spraying in very windy and dusty conditions. Cover surrounding area to protect from spray mist.

Shake can vigorously for one minute after the mixing ball begins to rattle. If mixing ball fails to rattle DO NOT STRIKE CAN. Contact Rust-Oleum. Shake often during use. Prior to use, slide off the red safety clip from the trigger. Hold can upright 8-12" from surface and spray in a steady back-and-forth motion, slightly overlapping each stroke. Keep the can the same distance from the surface. Keep the can in motion while spraying. Apply two or more light coats a few minutes apart. For best results, apply several light coats versus one heavy coat. Do not use near open flame.

DRY & RECOAT

Dry and recoat times are based on 70°F and 50% relative humidity. Allow more time at cooler temperatures. Dries to touch in 30 minutes, to handle in 1 hour, and is fully dry in 24 hours. Recoat within 1 hour or after 48 hours.

CLEAN-UP

When finished spraying, wipe off tip before storing. Clean up wet paint with xylene or mineral spirits. Properly discard empty container. Do not burn or place in home trash compactor.



TECHNICAL DATA

UNI-04

UNIVERSAL[®] GLOSS, FLAT AND MATTE ENAMEL SPRAYS

PHYSICAL PROPERTIES

		UNIVERSAL ENAMEL SPRAYS
Resin Type		Modified Alkyd
Pigment Type		Varies with color
Solvents		Acetone, Ketone blend
MIR		Gloss 0.95, Flats 0.80, Matte 0.80
Fill Weight		12 oz.
Recommended Dry Film Thickness (DFT) per Coat		1.0-2.0 mils (25-50µ)
Practical Coverage at Recommended DFT (assume 15% material loss)		10-15 sq. ft./can (0.9-1.4 m²/can)
Dry Times at 70-80°F (21-27ºC) and 50% Relative Humidity	Touch	30 minutes
	Handle	1 hour
	Recoat	Within 1 hour or after 48 hours
Dry Heat Resistance		200°F (93°C)
Shelf Life		5 years
Flash Point		-156°F (-104°C)
Safety Information		For additional information, see SDS

Calculated values are shown and may vary from the actual manufactured material.

The technical data and suggestions for use contained herein are correct to the best of our knowledge, and offered in good faith. The statements of this literature do not constitute a warranty, express, or implied, as to the performance of these products. As conditions and use of our materials are beyond our control, we can guarantee these products only to conform to our standards of quality, and our liability, if any, will be limited to replacement of defective materials. All technical information is subject to change without notice.



Rust-Oleum Corporation 11 Hawthorn Parkway Vernon Hills, Illinois 60061

Phone: 877·385·8155 www.rustoleum.com