


Includes medium base E-26 screw-in adapter that fits any standard incandescent downlight

## DIMENSIONS:

6" x 6"



**SDL6-BF-27K**      **SDL6-BF-30K**  
**SDL6-BF-41K**      **SDL6-BF-50K**

## LED ULTRA SLIM RECESSED LIGHTS

Ideal for New as well as old residential and commercial constructions.

### ELECTRICAL SPECIFICATIONS:

- Voltage: 120VAC
- Wattage: 15W
- Power factor: >0.90
- Efficacy: 80LM/W

### HOUSING SPECIFICATIONS:

- Die-cast Aluminum with white powder coat finish
- Can rotate after installation to align
- Maximum Ambient Temperature: 104°F
- Lifespan: 50,000 Hrs.
- Suitable for damp locations when gasket is used

MODEL	WATTS	VOLTAGE	LUMENS	COLOR TEMP
SDL6-BF-27K	15W	120VAC	1200LM	2700K
SDL6-BF-30K	15W	120VAC	1200LM	3000K
SDL6-BF-41K	15W	120VAC	1200LM	4000K
SDL6-BF-50K	15W	120VAC	1200LM	5000K

### LIGHTING SPECIFICATIONS:

- Dimming: Dimmable down to 10% using a standard TRIAC LED dimmer
- Lens: 0.125" white translucent acrylic
- Optics: White translucent acrylic
- LED: Seoul DOB (Driver On Board) Technology
- Total lumens: 1200LM
- Color temperature: 2700K/3000K/4000K/5000K
- Color rendering index: 90

**WARRANTY:** 5 years

### CERTIFICATIONS: ETL,ES

