



JOB NAME: _____

DATE: _____

TYPE: _____



ULR-IN-16F-SO-27K
 ULR-IN-16F-SO-30K
 ULR-IN-16F-SO-40K
 ULR-IN-16F-SO-50K

24V INDOOR STANDARD OUTPUT LED RIBBON

Ideal for undercabinet, soffit, display cases and toe kick lighting.

ELECTRICAL SPECIFICATIONS:

- Voltage: 24VDC (LED driver required)
- Wattage: 1.5W per ft.
- Max Run: 49ft.
- Efficacy: 66LM/W per ft.

HOUSING SPECIFICATIONS:

- Cutting increment: Every 4 inches
- 3M double sided tape(9474LE) is preinstalled
- Includes 1 female ribbon-to-power supply connector (Prewired) and 1 male plug for connection to next ribbon (Prewired)
- IP rating: IP20

CERTIFICATIONS: UL



DIMENSIONS:

16.4'(L) x 0.31"(W)

MODEL	WATTS PER FT.	VOLTAGE	LUMENS PER FT.	COLOR TEMP	REEL LENGTH	MAX RUN
ULR-IN-16F-SO-27K	1.5W	24VDC	100LM	2700K	16.4FT.	49FT.
ULR-IN-16F-SO-30K	1.5W	24VDC	100LM	3000K	16.4FT.	49FT.
ULR-IN-16F-SO-40K	1.5W	24VDC	100LM	4000K	16.4FT.	49FT.
ULR-IN-16F-SO-50K	1.5W	24VDC	100LM	5000K	16.4FT.	49FT.

OPTIONAL ACCESSORIES:



ULR-IN-SO-COUP-6I-WR
 ULR-IN-SO-COUP-3F-WR



ULR-IN-SO-COUP-NO-WR



ULR-IN-SO-CONN-6I-WR
 ULR-IN-SO-CONN-3F-WR

MODEL	DESCRIPTION
ULR-IN-SO-COUP-6I-WR	Coupling to connect 2 standard output ribbons, 6"
ULR-IN-SO-COUP-3F-WR	Coupling to connect 2 standard output ribbons, 3'
ULR-IN-SO-COUP-NO-WR	Coupling to connect 2 standard output ribbons, no wire
ULR-IN-SO-CONN-6I-WR	Power feed cable to connect standard output ribbon to power, 6'
ULR-IN-SO-CONN-3F-WR	Power feed cable to connect standard output ribbon to power, 3'

LIGHTING SPECIFICATIONS:

- Dimming: Dimmable using a magnetic driver
- LED: SMD2216 chip spaced 5/8" on center, 19 per foot, 0.08 wats each chip
- LED Type: SMD2216
- Total lumens: 100LM per ft.
- Color temperature: 2700K/3000K/4000K/5000K
- Color rendering index: 90
- Beam Angle: 120°

WARRANTY: 5 years

