Date Printed: 8/3/2018 Page 1 / 6

Safety Data Sheet



1. Identification

Product Name: MS Mira Matte QT 6pk Revision Date: 8/3/2018

Product Identifier: MATTE6QT Supercedes Date: 8/3/2018

Recommended Use: Natural Stone Color Enhancer

Supplier: Rust-Oleum Corporation Manufacturer: Rust-Oleum Corporation 11 Hawthorn Parkway 11 Hawthorn Parkway

11 Hawthorn Parkway Vernon Hills, IL 60061

USA

Vernon Hills, IL 60061 USA

Preparer: Regulatory Department

Emergency Telephone: 24 Hour Hotline: 847-367-7700

2. Hazard Identification

Classification

Symbol(s) of Product







Signal Word Danger

GHS HAZARD STATEMENTS

Flammable Liquid, category 3 H226 Flammable liquid and vapour.

Germ Cell Mutagenicity, category 1B H340 May cause genetic defects.

Carcinogenicity, category 1B H350 May cause cancer.

Reproductive Toxicity, category 2 H361 Suspected of damaging fertility or the unborn child.

STOT, single exposure, category 3, RTI H335 May cause respiratory irritation.

Acute Toxicity, Inhalation, category 4 H332 Harmful if inhaled.

Skin Irritation, category 2 H315 Causes skin irritation.

Eye Irritation, category 2 H319 Causes serious eye irritation.

Date Printed: 8/3/2018 Page 2 / 6

GHS LABEL PRECAUTIONARY STATEMENTS

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P280 Wear protective gloves/protective clothing/eye protection/face protection.

P303+P361+P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/

shower.

P370+P378 In case of fire: Use alcohol film forming foam, carbon dioxide, dry chemical, dry sand to extinguish.

P403+P235 Store in a well-ventilated place. Keep cool.

P501 Dispose of contents/container in accordance with local, regional and national regulations.

P201 Obtain special instructions before use.

P308+P313 IF exposed or concerned: Get medical advice/attention.

P405 Store locked up.

P261 Avoid breathing dust/fume/gas/mist/vapors/spray.

P271 Use only outdoors or in a well-ventilated area.

P304+P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.

P312 Call a POISON CENTER or doctor/physician if you feel unwell.

P403+P233 Store in a well-ventilated place. Keep container tightly closed.

P264 Wash hands thoroughly after handling.

P302+P352 IF ON SKIN: Wash with plenty of soap and water.

P321 For specific treatment see label

P332+P313 If skin irritation occurs: Get medical advice/attention.

P362+P364 Take off contaminated clothing and wash it before reuse.

P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present

and easy to do. Continue rinsing.

P337+P313 If eye irritation persists: Get medical advice/attention.

GHS SDS PRECAUTIONARY STATEMENTS

Date Printed: 8/3/2018 Page 3 / 6

P240 Ground/bond container and receiving equipment.

P241 Use explosion-proof electrical/ventilating/lighting/equipment.

P242 Use only non-sparking tools.

P243 Take precautionary measures against static discharge.

3. Composition / Information On Ingredients

HAZARDOUS SUBSTANCES				
Chemical Name	CAS-No.	Wt.% Range	GHS Symbols	GHS Statements
Solvent Naphtha, Light Aromatic	64742-95-6	25-50	GHS07-GHS08	H304-332-340-350
1,2,4-Trimethylbenzene	95-63-6	10-25	GHS02-GHS07- GHS08	H226-304-315-319-332-335
Ethylene Glycol Monobutyl Ether	111-76-2	2.5-10	GHS07	H302-312-315-319-332
Xylenes (o-, m-, p- isomers)	1330-20-7	1.0-2.5	GHS02-GHS07	H226-315-319-332
Stoddard Solvent	8052-41-3	0.1-1.0	GHS08	H304-372
Cumene	98-82-8	0.1-1.0	GHS02-GHS07- GHS08	H226-302-304-332-335-351
Toluene	108-88-3	0.1-1.0	GHS02-GHS07- GHS08	H225-304-315-332-336-361-373

4. First-Aid Measures

FIRST AID - EYE CONTACT: Immediately flush eyes with plenty of water for at least 15 minutes holding eyelids open. Get medical attention. Do NOT allow rubbing of eyes or keeping eyes closed.

FIRST AID - SKIN CONTACT: Wash skin with soap and water. Remove contaminated clothing. Get medical attention if irritation develops or persists.

FIRST AID - INHALATION: Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get immediate medical attention. Do NOT use mouth-to-mouth resuscitation. If you experience difficulty in breathing, leave the area to obtain fresh air. If continued difficulty is experienced, get medical assistance immediately.

FIRST AID - INGESTION: If swallowed, get medical attention.

5. Fire-Fighting Measures

EXTINGUISHING MEDIA: Alcohol Film Forming Foam, Carbon Dioxide, Dry Chemical, Dry Sand, Water Fog

UNUSUAL FIRE AND EXPLOSION HAZARDS: No unusual fire or explosion hazards noted. Closed containers may explode when exposed to extreme heat due to buildup of steam. Keep containers tightly closed. Combustible liquid and vapor.

SPECIAL FIREFIGHTING PROCEDURES: Evacuate area and fight fire from a safe distance. Use water spray to keep fire-exposed containers cool. Containers may explode when heated.

Special Fire and Explosion Hazard (Combustible Dust): No Information

6. Accidental Release Measures

Date Printed: 8/3/2018 Page 4 / 6

STEPS TO BE TAKEN IF MATERIAL IS RELEASED OR SPILLED: Dispose of according to local, state (provincial) and federal regulations. Do not incinerate closed containers. Remove all sources of ignition, ventilate area and remove with inert absorbent and non-sparking tools.

7. Handling and Storage

HANDLING: Wash thoroughly after handling. Wash hands before eating. Remove contaminated clothing and launder before reuse. Use only with adequate ventilation. Follow all SDS and label precautions even after container is emptied because it may retain product residues. Avoid breathing fumes, vapors, or mist. Avoid contact with eyes, skin and clothing.

STORAGE: Store in a dry, well ventilated place. Keep container tightly closed when not in use. Keep containers tightly closed. Isolate from heat, electrical equipment, sparks and open flame. Avoid excess heat.

Advice on Safe Handling of Combustible Dust: No Information

8. Exposure Controls / Personal Protection

Chemical Name	CAS-No.	Weight % Less Than	ACGIH TLV- TWA	ACGIH TLV- STEL	OSHA PEL-TWA	OSHA PEL- CEILING
Solvent Naphtha, Light Aromatic	64742-95-6	50.0	N.E.	N.E.	N.E.	N.E.
1,2,4-Trimethylbenzene	95-63-6	25.0	N.E.	N.E.	N.E.	N.E.
Ethylene Glycol Monobutyl Ether	111-76-2	10.0	20 ppm	N.E.	50 ppm	N.E.
Xylenes (o-, m-, p- isomers)	1330-20-7	5.0	100 ppm	150 ppm	100 ppm	N.E.
Stoddard Solvent	8052-41-3	1.0	100 ppm	N.E.	500 ppm	N.E.
Cumene	98-82-8	1.0	50 ppm	N.E.	50 ppm	N.E.
Toluene	108-88-3	1.0	20 ppm	N.E.	200 ppm	300 ppm

PERSONAL PROTECTION

ENGINEERING CONTROLS: Use process enclosures, local exhaust ventilation, or other engineering controls to control airborne levels below recommended exposure limits. Prevent build-up of vapors by opening all doors and windows to achieve crossventilation.

RESPIRATORY PROTECTION: A respiratory protection program that meets OSHA 1910.134 and ANSI Z88.2 requirements must be followed whenever workplace conditions warrant a respirator's use.

SKIN PROTECTION: Use gloves to prevent prolonged skin contact. Nitrile or Neoprene gloves may afford adequate skin protection.

EYE PROTECTION: Use safety eyewear designed to protect against splash of liquids.

OTHER PROTECTIVE EQUIPMENT: Refer to safety supervisor or industrial hygienist for further guidance regarding types of personal protective equipment and their applications.

HYGIENIC PRACTICES: Wash thoroughly with soap and water before eating, drinking or smoking. Remove contaminated clothing immediately and launder before reuse.

Engineering Measures for Combustible Dust: No Information

9. Physical and Chemical Properties

Appearance:	Liquid	Physical State:	Liquid
Odor:	Solvent Like	Odor Threshold:	N.E.
Relative Density:	0.909	pH:	N.A.
Freeze Point, °C:	N.D.	Viscosity:	N.D.
Solubility in Water:	Slight	Partition Coefficient, n-octanol/	ND
Decompostion Temp., °C:	N.D.	water:	N.D.
Boiling Range, °C:	157 - 537	Explosive Limits, vol%:	0.9 - 7.0
Flammability:	Supports Combustion	Flash Point, °C:	47
Evaporation Rate:	Slower than Ether	Auto-ignition Temp., °C:	N.D.
Vapor Density:	Heavier than Air	Vapor Pressure:	N.D.

(See "Other information" Section for abbreviation legend)

10. Stability and Reactivity

CONDITIONS TO AVOID: No Information

INCOMPATIBILITY: Incompatible with strong oxidizing agents, strong acids and strong alkalies.

Date Printed: 8/3/2018 Page 5 / 6

HAZARDOUS DECOMPOSITION: When heated to decomposition, it emits acrid smoke and irritating fumes. Contains solvents which may form carbon monoxide, carbon dioxide, and formaldehyde.

HAZARDOUS POLYMERIZATION: Will not occur under normal conditions.

STABILITY: This product is stable under normal storage conditions.

11. Toxicological Information

EFFECTS OF OVEREXPOSURE - EYE CONTACT: Substance causes moderate eye irritation.

EFFECTS OF OVEREXPOSURE - SKIN CONTACT: May be absorbed through the skin in harmful amounts. Substance may cause slight skin irritation.

EFFECTS OF OVEREXPOSURE - INHALATION: High gas, vapor, mist or dust concentrations may be harmful if inhaled. Avoid breathing fumes, spray, vapors, or mist. High vapor concentrations are irritating to the eyes, nose, throat and lungs. Prolonged or excessive inhalation may cause respiratory tract irritation.

EFFECTS OF OVEREXPOSURE - INGESTION: Irritating to the nose, throat and respiratory tract. Harmful if swallowed.

EFFECTS OF OVEREXPOSURE - CHRONIC HAZARDS: Overexposure to xylene in laboratory animals has been associated with liver abnormalities, kidney, lung, spleen, eye and blood damage as well as reproductive disorders. Effects in humans, due to chronic overexposure, have included liver, cardiac abnormalities and nervous system damage. Reports have associated repeated and prolonged occupational overexposure to solvents with permanent brain and nervous system damage.

PRIMARY ROUTE(S) OF ENTRY: Eye Contact, Ingestion, Inhalation, Skin Absorption, Skin Contact

ACUTE TOXICITY VALUES

The acute effects of this product have not been tested. Data on individual components are tabulated below:

CAS-No.	Chemical Name	Oral LD50	Dermal LD50	Vapor LC50
64742-95-6	Solvent Naphtha, Light Aromatic	8400 mg/kg Rat	>2000 mg/kg Rabbit	N.E.
95-63-6	1,2,4-Trimethylbenzene	3280 mg/kg Rat	>3160 mg/kg Rabbit	18 mg/L Rat
111-76-2	Ethylene Glycol Monobutyl Ether	470 mg/kg Rat	1,060 mg/kg Rabbit	11 mg/L
1330-20-7	Xylenes (o-, m-, p- isomers)	3500 mg/kg Rat	>4350 mg/kg Rabbit	29.08 mg/L Rat
98-82-8	Cumene	1400 mg/kg Rat	10583 mg/kg Rabbit	N.E.
108-88-3	Toluene	2600 mg/kg Rat	12000 mg/kg Rabbit	12.5 mg/L Rat

N.E. - Not Established

12. Ecological Information

ECOLOGICAL INFORMATION: Product is a mixture of listed components.

13. Disposal Information

DISPOSAL INFORMATION: Do not incinerate closed containers. Dispose of material in accordance to local, state, and federal regulations and ordinances. Do not allow to enter waterways, wastewater, soil, storm drains or sewer systems.

14. Transport Information

	Domestic (USDOT)	International (IMDG)	<u>Air (IATA)</u>	TDG (Canada)
UN Number:	N.A.	1263	1263	N.A.
Proper Shipping Name:	Not Regulated	Paint	Paint	Not Regulated
Hazard Class:	N.A.	3	3	N.A.
Packing Group:	N.A.	III	III	N.A.
Limited Quantity:	No	Yes, >5L No	Yes, >5L No	No

15. Regulatory Information

Date Printed: 8/3/2018 Page 6 / 6

U.S. Federal Regulations:

CERCLA - SARA Hazard Category

This product has been reviewed according to the EPA 'Hazard Categories' promulgated under Sections 311 and 312 of the Superfund Amendment and Reauthorization Act of 1986 (SARA Title III) and is considered, under applicable definitions, to meet the following categories:

Flammable (gases, aerosols, liquids, or solids), Carcinogenicity, Acute Toxicity (any route of exposure), Reproductive toxicity, Skin Corrosion or Irritation, Serious eye damage or eye irritation, Specific target organ toxicity (single or repeated exposure), Germ cell mutagenicity

Sara Section 313:

This product contains the following substances subject to the reporting requirements of Section 313 of Title III of the Superfund Amendment and Reauthorization Act of 1986 and 40 CFR part 372:

 Chemical Name
 CAS-No.

 1,2,4-Trimethylbenzene
 95-63-6

 Ethylene Glycol Monobutyl Ether
 111-76-2

 Xylenes (o-, m-, p- isomers)
 1330-20-7

 Toluene
 108-88-3

Toxic Substances Control Act:

This product contains the following chemical substances subject to the reporting requirements of TSCA 12(b) if exported from the United States:

No TSCA 12(b) components exist in this product.

16. Other Information

HMIS RATINGS

Health: 2* Flammability: 2 Physical Hazard: 0 Personal Protection: X

NFPA RATINGS

Health: 2 Flammability: 2 Instability 0

Volatile Organic Compounds 749 g/L SDS REVISION DATE: 8/3/2018

REASON FOR REVISION: Substance and/or Product Properties Changed in Section(s):

01 - Identification

Legend: N.A. - Not Applicable, N.E. - Not Established, N.D. - Not Determined

The manufacturer believes, to the best of its knowledge, information and belief, the information contained herein to be accurate and reliable as of the date of this safety data sheet. However, because the conditions of handling, use, and storage of these materials are beyond our control, we assume no responsibility or liability for personal injury or property damage incurred by the use of these materials. The manufacturer makes no warranty, expressed or implied, regarding the accuracy or reliability of the data or results obtained from their use. All materials may present unknown hazards and should be used with caution. The information and recommendations in this material safety data sheet are offered for the users' consideration and examination. It is the responsibility of the user to determine the final suitability of this information and to comply with all applicable international, federal, state, and local laws and regulations.