

TECHNICAL DATA SHEET

HYDRO-LOK™

ALL SURFACE WATER REPELLENT with MICRO-LOKTM

PRODUCT DESCRIPTION

Rainguard HYDRO-LOK is a single component nano-based super hydrophobic treatment that creates a moisture barrier on almost any surface. HYDRO-LOK does not contain any harmful solvents and is not flammable either in liquid or dried form. HYDRO-LOK is completely clear when dry and does not create a dark, hazy or frosted appearance. It is packaged in an easy to use trigger spray bottle, not a pressurized aerosol can. HYDRO-LOK creates a clear, deep-penetrating, and non-film-forming chemically-reactive water repellent that contains no silicone oils, paraffin wax, or ure-thanes.

HYDRO-LOK contains MICRO-LOK which creates a micro-molecular chemical and mechanical bond between the water-repellent chemicals and the substrate. HYDRO-LOK penetrates deep into porous masonry surfaces to provide long-lasting and virtually indestructible water-repellent protection that is not affected by weather or sunlight.

HYDRO-LOK provides superior grade, water-repellent performance on a wide variety of vertical surfaces. This material is **Ready To Use - Do Not Dilute**.

PRODUCT FEATURES

- Mold and Mildew Inhibitor
- Protection not effected by weathering or UV light
- V.O.C. compliant
- Contains no known carcinogens
- Does not darken surfaces
- Breathable does not trap moisture
- Can be used in cold temperature applications
- Will not yellow

Part Numbers: USA International TPC-1000CA TPC-1000CA

RECOMMENDED USES:

- Work Boots
- Gloves
- Tents
- Patio Furniture
- Driveways
- Wood
- Leather
- Metal Surfaces
- Concrete
- Canvas
- Masonry block
- Stucco
- Porous stone
- Unglazed tile
- Aluminum

COVERAGE RATES (THEORETICAL):

All Substrates Sq Ft/ bottle

First Coat 20 Second Coat 40

Special Considerations:

Porous surfaces that allow water penetration will require two coats. If a surface darkens when sprinkled with water, two coats are recommended.

PRECAUTIONS & LIMITATIONS

All surfaces to be coated should be clean of any dirt and grime, efflorescence, lime run, form oils and release agents, grease, mud, excess mortar, and mold and mildew, etc.

DO NOT DILUTE. HYDRO-LOK IS SUPPLIED READY TO USE.

Do not apply to surfaces if moisture content is greater than 22% as measured with an electronic moisture meter. Do not apply materials in climates where freezing temperatures have existed prior to application. Allow adequate time for surfaces to thaw. Establish that air, surface, and material temperatures are above 35°F (2°C) and at least 5°F above the dew point prior to painting. Do not apply at temperatures below 35°F or when temperatures are expected to drop below 35°F within 48 hours of application. Do not apply if rain, snow, or lower temperatures are expected within 48 hours. Do not apply if relative humidity is greater than 80%

Use material in a well-ventilated area. Protect the work of other trades. Protect shrubbery and other plants with drop cloths. Protect automobiles and all other areas not to be coated from overspray. Remove overspray from any windows, automobiles, metal, etc. as soon as possible should it occur. To prevent permanent staining, clean spills or leaks in a timely manner.

Store materials in a well-protected area between 45° and 90°F. Avoid freezing temperatures, direct sunlight, and moisture. Keep away from heat sources.

TEST PANEL

Always apply material to a test areal. Test actual surface area to determine acceptable color, surface porosity, application rates, and methods before starting general application.

FOLLOW THESE SIMPLE STEPS

- HYDRO-LOK should be applied using low-pressure trigger spray bottle
- 2. Saturate surface with as much HYDRO-LOK it can absorb without dripping.
- 3. Avoid application in windy weather.
- 4. A second coat can be applied after one hour.
- 5. HYDRO-LOK can be re-applied at any time for added performance and water protection

TECHNICAL DATA

Material Type Fluoropolymer dispersion

Color of Material Milky White

Odor Slight Ammonia Odor V.O.C. 7 gm/L V.O.C. Compliant

Flash Point Non-Flammable pH Value Approximately 6.5

Viscosity 10.6 Seconds No. 4 Ford Cup Weight Approximately 9.0 lbs./gal.
Surface Dry/Recoat Approx. 30 minutes

Full Chemical Cure 2 hours

SATISFACTION GUARANTEE

Rainguard backs Hydro-Lok with an unconditional satisfaction guarantee. If unsatisfied, provide proof of purchase and application details to Rainguard for refund or replacement. Refund of purchase price or replacement of product used are only options covered by this guarantee.