

SAFETY DATA SHEET

Issuing Date 07-Aug-2018

NGHS / English



The supplier identified below generated this SDS using the UL SDS template. UL did not test, certify, or approve the substance described in this SDS, and all information in this SDS was provided by the supplier or was reproduced from publically available regulatory data sources. UL makes no representations or warranties regarding the completeness or accuracy of the information in this SDS and disclaims all liability in connection with the use of this information or the substance described in this SDS. The layout, appearance and format of this SDS is © 2014 UL LLC. All rights reserved.

1. IDENTIFICATION

Product identifier M327
Product Name Victor® Roach and Insect Trap

Recommended use of the chemical and restrictions on use

Recommended Use Trap and/or Bait Station
Restrictions on use No information available

Details of the supplier of the safety data sheet

Supplier Identification Woodstream Corporation
Address 69 North Locust St.
Lititz
Pennsylvania
17543
United States
Telephone Phone:(800) 800-1819
Fax:(800) 800-1819
E-mail aodonnell@woodstream.com

Emergency telephone number

Company Emergency Phone Number (717) 626-2125

2. HAZARDS IDENTIFICATION

Classification

Not classified.



The product contains no substances which at their given concentration, are considered to be hazardous to health

Appearance Clear to semi-clear

Physical state Solid

Odor Mild

GHS Label elements, including precautionary statements

Hazard statements

Not classified.

Other information

Unknown acute toxicity 99.85 % of the mixture consists of ingredient(s) of unknown toxicity

99.85 % of the mixture consists of ingredient(s) of unknown acute oral toxicity

99.85 % of the mixture consists of ingredient(s) of unknown acute dermal toxicity

99.85 % of the mixture consists of ingredient(s) of unknown acute inhalation toxicity (gas)

99.85 % of the mixture consists of ingredient(s) of unknown acute inhalation toxicity (vapor)

99.85 % of the mixture consists of ingredient(s) of unknown acute inhalation toxicity (dust/mist)

3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance

Not applicable.

Mixture

The product contains no substances which at their given concentration, are considered to be hazardous to health.

4. FIRST AID MEASURES

First aid measures

Inhalation Remove to fresh air.

Eye contact Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a physician.

Skin contact Wash skin with soap and water.

Ingestion Clean mouth with water and drink afterwards plenty of water.

Most important symptoms and effects, both acute and delayed

Symptoms No information available.

Indication of any immediate medical attention and special treatment needed



Note to physicians Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media	Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Large Fire	CAUTION: Use of water spray when fighting fire may be inefficient.
Unsuitable extinguishing media	Do not scatter spilled material with high pressure water streams.
Specific hazards arising from the chemical	No information available.
Hazardous Combustion Products	Carbon oxides.
Explosion Data	
Sensitivity to Mechanical Impact	None.
Sensitivity to Static Discharge	None.
Special protective equipment for fire-fighters	Firefighters should wear self-contained breathing apparatus and full firefighting turnout gear. Use personal protection equipment.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions Avoid contact with eyes.

Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Pick up and transfer to properly labeled containers.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Handle in accordance with good industrial hygiene and safety practice.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep containers tightly closed in a dry, cool and well-ventilated place.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION



Control parameters

Exposure Limits	This product, as supplied, does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies.
Other Exposure Guidelines	See section 15 for national exposure control parameters.

Appropriate engineering controls

Engineering controls	Showers Eyewash stations Ventilation systems.
-----------------------------	---

Individual protection measures, such as personal protective equipment

Eye/face protection	No special protective equipment required.
Skin and body protection	No special protective equipment required.
Respiratory protection	No protective equipment is needed under normal use conditions. If exposure limits are exceeded or irritation is experienced, ventilation and evacuation may be required.
General hygiene considerations	Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES**Physical and Chemical Properties**

Physical state	Solid
Appearance	Clear to semi-clear
Odor	Mild
Color	No information available
Odor Threshold	No information available

<u>Property</u>	<u>Values</u>	<u>Remarks</u>	<u>Method</u>
pH	No data available	None known	
Melting / freezing point	No data available	None known	
Boiling point / boiling range	No data available	None known	
Flash Point	No data available	None known	
Evaporation Rate	No data available	None known	
Flammability (solid, gas)	No data available	None known	
Flammability Limit in Air		None known	
Upper flammability limit	No data available		
Lower flammability limit	No data available		
Vapor pressure	No data available	None known	
Vapor density	No data available	None known	
Relative density	No data available	None known	
Water Solubility	Insoluble		
Solubility(ies)	No data available	None known	
Partition coefficient: n-octanol/water₀			
Autoignition temperature	No data available	None known	
Decomposition temperature	No data available	None known	
Kinematic viscosity	No data available	None known	
Dynamic viscosity	No data available	None known	

Other Information

Explosive properties	No information available
-----------------------------	--------------------------



Oxidizing properties	No information available
Softening Point	No information available
Molecular Weight	No information available
VOC Content (%)	No information available
Liquid Density	No information available
Bulk Density	No information available
Particle Size	No information available
Particle Size Distribution	No information available

10. STABILITY AND REACTIVITY

Reactivity	No information available.
Chemical stability	Stable under normal conditions.
Possibility of Hazardous Reactions	None under normal processing.
Hazardous Polymerization	Hazardous polymerization does not occur.
Conditions to avoid	None known based on information supplied.
Incompatible materials	None known based on information supplied.
Hazardous Decomposition Products	Carbon oxides.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information

Inhalation	Specific test data for the substance or mixture is not available.
Eye contact	Specific test data for the substance or mixture is not available.
Skin contact	Specific test data for the substance or mixture is not available.
Ingestion	Specific test data for the substance or mixture is not available.

Information on toxicological effects

Symptoms	No information available.
-----------------	---------------------------

Numerical measures of toxicity

Acute Toxicity

Unknown acute toxicity	99.85 % of the mixture consists of ingredient(s) of unknown toxicity
	99.85 % of the mixture consists of ingredient(s) of unknown acute oral toxicity
	99.85 % of the mixture consists of ingredient(s) of unknown acute dermal toxicity
	99.85 % of the mixture consists of ingredient(s) of unknown acute inhalation toxicity (gas)
	99.85 % of the mixture consists of ingredient(s) of unknown acute inhalation toxicity (vapor)
	99.85 % of the mixture consists of ingredient(s) of unknown acute inhalation toxicity (dust/mist)

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Skin corrosion/irritation	No information available.
Serious eye damage/eye irritation	No information available.
Respiratory or skin sensitization	No information available.
Germ cell mutagenicity	No information available.
Carcinogenicity	No information available.
Reproductive toxicity	No information available.
STOT - single exposure	No information available.
STOT - repeated exposure	No information available.
Aspiration hazard	No information available.

12. ECOLOGICAL INFORMATION

Ecotoxicity	The environmental impact of this product has not been fully investigated.
Persistence and Degradability	No information available.
Bioaccumulation	There is no data for this product.
Mobility	No information available.
Other adverse effects	No information available.

13. DISPOSAL CONSIDERATIONS**Waste treatment methods**

Waste from residues/unused products	Dispose of in accordance with local regulations. Dispose of waste in accordance with environmental legislation.
Contaminated packaging	Do not reuse empty containers.
California Waste Codes	331

14. TRANSPORT INFORMATION

<u>DOT</u>	NOT REGULATED
-------------------	---------------



Proper Shipping Name	NON-REGULATED
Hazard Class	N/A
<u>TDG</u>	Not regulated
<u>MEX</u>	Not regulated
<u>ICAO</u>	Not regulated
<u>IATA</u>	Not regulated
Proper Shipping Name	NON REGULATED
Hazard Class	N/A
<u>IMDG/IMO</u>	Not regulated
Hazard Class	N/A
<u>RID</u>	Not regulated
<u>ADR</u>	Not regulated
<u>ADN</u>	Not regulated

15. REGULATORY INFORMATION

Safety, health and environmental regulations/legislation specific for the substance or mixture

International Regulations

Ozone-depleting substances (ODS) Not applicable

Persistent Organic Pollutants Not applicable

Export Notification requirements Not applicable

International Inventories

TSCA	Contact supplier for inventory compliance status.
DSL/NDSL	Contact supplier for inventory compliance status.
EINECS/ELINCS	Contact supplier for inventory compliance status.
ENCS	Contact supplier for inventory compliance status.
KECL	Contact supplier for inventory compliance status.
PICCS	Contact supplier for inventory compliance status.
AICS	Contact supplier for inventory compliance status.

Legend

- TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory
- DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List
- EINECS/ELINCS** - European Inventory of Existing Chemical Substances/European List of Notified Chemical Substances
- ENCS** - Japan Existing and New Chemical Substances
- KECL** - Korean Existing and Evaluated Chemical Substances
- PICCS** - Philippines Inventory of Chemicals and Chemical Substances
- AICS** - Australian Inventory of Chemical Substances

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372



SARA 311/312 Hazard Categories

Should this product meet EPCRA 311/312 Tier reporting criteria at 40 CFR 370, refer to Section 2 of this SDS for appropriate classifications. Under the amended regulations at 40 CFR 370, EPCRA 311/312 Tier II reporting for the 2017 calendar year will need to be consistent with updated hazard classifications.

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

US State Regulations**California Proposition 65**

This product does not contain any Proposition 65 chemicals.

U.S. State Right-to-Know Regulations

This product does not contain any substances above threshold limits that are regulated by state right-to-know.

16. OTHER INFORMATION

<u>NFPA</u>	Health hazards 1	Flammability 0	Instability 0	Physical and Chemical Properties -
<u>HMIS</u>	Health hazards 1	Flammability 0	Physical hazards 0	Personal Protection X

Prepared By Product Stewardship
23 British American Blvd.
Latham, NY 12110
1-800-572-6501

Issuing Date 07-Aug-2018

Revision Date 08-Aug-2018

Revision Note No information available

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet

