

Super Stucco

Primer/Sealer Concentrate with Micro-Lok®

TECHNICAL DATA SHEET
100% Penetrating Water Repellent



Product	U/M	Code
Super Stucco	1 Gallon	CR-0300

Description

Rainguard Super Stucco Primer/Sealer Concentrate with Micro-Lok Clear Water Repellent is a water based, modified polysilane/siloxane repellent composed of high quality chemical solids, blended to create a clear, deep penetrating and non-film-forming chemically reactive masonry water repellent that contains no silicone oils, paraffin wax, or urethanes. This product will not re-emulsify.

Micro-Lok creates a micro-molecular chemical and mechanical bond between the water repellent chemicals and the stucco material. Super Stucco Primer/Sealer Concentrate penetrates deep into dense masonry surfaces to provide long lasting and virtually indestructible water repellent protection that is not affected by weather or sunlight. It helps prevent spalling and cracking caused by freeze/thaw cycles. It also helps prevent chloride ion intrusion and efflorescence.

Dilution

Floor-Lok sealer Concentrate must be diluted with nine parts clean water with one part concentrate prior to application.

Features

- Mold and mildew inhibitor
- Protects against weathering and UV light
- Single coat application
- V.O.C. compliant
- Contains no known carcinogens
- UV Stable

Recommended Uses

- EFIS or cement plaster
- Primer for stucco
- Sealer for stucco
- An excellent primer for paint applications

Coverage Rates* (Theoretical)

Substrate	Sq Ft / Gallon
EFIS	75-100
Clay Tile	100-150
Cement Plaster	100-150
Clay Block	100-150
Cast Concrete	150-175
Stucco	150-200

**Extremely porous stucco may require multiple coats*

**Use of fluted, scored block or raked joints will increase surface areas by 20%-30% or more, with decreased coverage rates. Take into consideration this increased surface area when determining material requirements.*

Test Panel

Always apply material to a mock wall or test panel. Test wall or actual surface area to determine acceptable color, surface porosity, application rates and methods before starting general application.

Application

1. Super Stucco Primer/Sealer should be applied using low pressure airless spray equipment, pump sprayer, or juicebox.
2. Avoid atomizing material by using a spray tip size of .035 to .051. Spray head should be held 8 to 12 inches from the surface so that the flood coat runs down the wall approx. 6-12 inches below the point of application.
3. Avoid application in windy weather.
4. Trigger gun off at the end of each pass to avoid using excessive materials.
5. Multiple coats may be applied.

Rainguard® Super Stucco



Rainguard® Super Stucco

Precautions & Limitations

All surfaces to be coated shall be clean of any dirt and grime, efflorescence, lime run, form oils and release agents, grease, mud, excess mortar, mold and mildew, etc. All cracks shall be pointed or caulked. All voids, bee holes, masonry surface defects and openings such as conduits, pipes, drains, door frames, vents, air conditioner openings, electrical openings, control joints, or any dissimilar materials shall be repaired using urethane or other approved patching. May be applied to fresh concrete/stucco after 48 hours.

Do not apply to surfaces if moisture content is greater than 25% as measured with an electronic moisture meter. Do not apply materials in climates where freezing temperatures have existed prior to application. Allow adequate time for surfaces to thaw. Establish that air, surface, and material temperatures are above 40°F (4.4°C) and at least 5°F above the dew point prior to application. Do not apply at temperatures below 40°F or when temperatures are expected to drop below 40°F within 48 hours of application. Do not apply if rain, snow, or lower temperatures are expected within 48 hours. Do not apply if relative humidity is greater than 90%.

Use material in a well-ventilated area. Protect the work of other trades. Protect shrubbery and other plants with drop cloths. Protect automobiles and all other areas not to be coated from over spray. Remove over spray from any windows, automobiles, metal, etc. as soon as possible should it occur. To prevent permanent staining, clean spills or leaks in a timely manner.

Store materials in a well-protected area between 45° and 90°F. Avoid freezing temperatures, direct sunlight, and moisture.

Warranty

The information contained herein is offered in good faith and is believed to be accurate. To be eligible for a Rainguard Warranty the following must occur:

1. A site visit must be conducted by an employee or agent of Rainguard and a Field Inspection Report completed. Please verify with a RainguardPro representative if a pre and post inspection is required.
2. A Warranty Application must be fully completed by the applicator.
3. Field Inspection Report, Warranty Application, and a copy of the distributor's invoice must be submitted to and approved by Rainguard.

This material is only warranted when applied in accordance with the manufacturer's guidelines and warranty procedures. Without adherence to these specific guidelines, no expressed or implied warranty of this product is given. Please contact Rainguard for additional information.



Test Data

Wind Driven Rain	ASTM E-514-86., 96.2% Leak Red
Water Pen Fed Spec	SS-W-110C, 75% Min Req, 96.8 Leak Red Chloride Ion Intr
Pounding NCHRP No. 244	Allowed 25% Obtained 13%
Water Abs CMU ASTM C140-75	89% Effective
Water Vapor Trans ASTM D-1653	100% Vapor Perm
Water Repellency ASTM C67-87	97% Effective
Weathering ASTM G-53	2500 Hours - No Change

Technical Data

Material Type	Modified Polysilane/Siloxane
Active Content	Approximately 11% after Dilution
Color of Material	Clear to Slightly Cloudy
Odor	Slight Ammonia Odor
V.O.C.	<15 g/L V.O.C. Compliant
Flash Point	Non-Flammable
pH Value	Approximately 7.5
Viscosity	9.6 Seconds No. 4 Ford Cup
Weight	Approximately 8.5 lbs./Gal.
Surface Dry/Recoat	Approx 1 Hour
Full Chemical Cure	24 to 36 Hours

Rainguard® Super Stucco