
1. PRODUCT IDENTIFICATION

1.1. Product Identifiers

Product name : **OutLAST™ Pro Foaming Agent**

1.2. Other Means of Identification

Product synonyms : none

1.3. Recommended Uses/Restrictions to Use

Uses : Surfactant based foaming agent

Restrictions : See product label for details

1.4. Supplier Details

Company : Rockwell Labs Ltd
1257 Bedford Avenue
North Kansas City, MO 64116-4308
USA

Telephone : 1 816-283-3167

1.5. Emergency Contact

Outside normal business hours

Emergency Phone # : 1 800-424-9300 (USA & Canada)
1 703-527-3887 (Outside USA & Canada)

2. HAZARDS IDENTIFICATION

2.1. Classification of Substance or Mixture

Skin irritation (Category 3)

Eye irritation (Category 2B)

Acute aquatic toxicity (Category 2)

Chronic aquatic toxicity (Category 3)

2.2. GHS label elements, including precautionary statements

Pictogram(s) none

Signal word Warning

Hazard statement(s)

H316 Causes mild skin irritation

H320 Causes eye irritation

H401 Toxic to aquatic life

H412 Harmful to aquatic life with long lasting effects

Precautionary statement(s)

OutLAST™ Pro Foaming Agent

P264	Wash exposed skin thoroughly after handling.
P273	Avoid release to the environment.
P305 + P351 + P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P332 + P313	If skin irritation occurs: Get medical advice/attention.
P337 + P313	If eye irritation persists: Get medical advice/attention.
P501	Dispose of contents/container in accordance with local/state regulations

2.3. Other hazards which do not result in classification

none

3. COMPOSITION/INFORMATION ON INGREDIENTS
3.1. Substances

Not applicable

3.2. Mixtures

Hazardous component(s) or components of note:

Chemical Identity	Contains (% w/w)	CAS-No.	Hazard Classification
Sodium Lauryl Sulfate	1-10	151-21-3	Skin irritant (Cat. 3) Eye irritant (Cat. 2B)
Disodium lauryl sulfosuccinate	1-10	26838-05-1	Skin irritant (Cat. 3) Eye irritant (Cat. 2B)
Proprietary Ingredients	3	-----	Aquatic acute / chronic (Cat. 2, 3)

4. FIRST AID MEASURES
4.1. Description of first aid measures
General advice

Consult a physician or poison control center. Provide this safety data sheet to medical personnel. Move out of hazardous areas.

If inhaled

Move person to fresh air. If person is not breathing, call 911 or an ambulance, then give artificial respiration, preferably mouth to mouth if possible. Call a poison control center or doctor for further treatment advice.

In case of skin contact

Take off contaminated clothing. Rinse skin immediately with plenty of water for 15-20 minutes. Call a poison control center or doctor for treatment advice.

In case of eye contact

Hold eye open and rinse slowly and gently with water for 15-20 minutes. Remove contact lenses, if present, after the first 5 minutes, then continue rinsing eye. Call a poison control center or doctor for treatment advice.

OutLAST™ Pro Foaming Agent

If swallowed

Call a poison control center or doctor for treatment advice. Have person sip a glass of water if able to swallow. Do not induce vomiting unless told to do so by a poison control center or doctor. Do not give anything by mouth to an unconscious person.

4.2. Most important symptoms and effects, both acute and delayed

No data available

4.3. Indication of any immediate medical attention and special treatment needed, if necessary

No data available

5. FIRE FIGHTING MEASURES

5.1. Extinguishing media

Suitable extinguishing media: Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide.

5.2. Specific hazards arising from the chemical

Oxides of carbon, sulfur, and nitrogen.

5.3. Special protective equipment and precautions for fire fighters

Wear self contained breathing apparatus for firefighting if deemed necessary.

Additional information: none.

5.4. Further information

Avoid release of material to environment.

6. ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Avoid contact with spilled product and contaminated surfaces. Evacuate personnel to safe areas during emergencies. For safe handling instructions see section 7. For proper PPE see section 8.

6.2. Environmental precautions

Prevent further leakage or spillage if safe to do so. Avoid release to the environment.

6.3. Methods and materials for containment and cleaning up

Wipe up any spilled material and dispose of according to instructions in section 13. Wash contaminated surfaces with soap and water.

7. HANDLING AND STORAGE

7.1. Precautions for safe handling

Handle in accordance with good industrial hygiene practices. Wash hands thoroughly with soap and water after use and before eating, drinking, chewing gum, using tobacco, or using the toilet. For additional precautions see section 2.2

7.2. Conditions for safe storage, including any incompatibilities

Store in a cool dry place. Store in original container. Do not store where children or animals may gain access.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

Components with workplace parameters

OutLAST™ Pro Foaming Agent

Component	CAS-No.	Value	Control parameters	Basis
none	-----	-----	-----	-----

8.2. Appropriate engineering controls

Ensure relevant engineering controls are employed to prevent exceeding threshold values for the listed control parameters in section 8.1.

8.3. Individual protection measures, such as personal protective equipment

In normal use and handling conditions refer to the product label for required PPE. In all other cases the following recommendations would apply.

Eye/face protection

Safety glasses or other similar eye protection conforming to ANSI Z87.1 standards recommended when handling product.

Skin protection

Chemical resistant nitrile rubber or similarly compatible gloves recommended when handling product. Dispose of contaminated gloves after use in accordance with applicable local and state regulations. Wash exposed skin with soap and water immediately. Wash all contaminated clothing prior to reuse.

Respiratory protection

Not required under normal use conditions.

Thermal hazards

None known

9. PHYSICAL AND CHEMICAL PROPERTIES
9.1. Information on basic physical and chemical properties

Appearance;	Clear/yellowish liquid
Odor;	Mildly sweet solvent
Odor threshold;	No data available
pH;	5.63 (25.0 °C)
Melting point/freezing point;	No data available
Initial boiling point and boiling range;	No data available
Flash point;	> 93 °C (200 °F)
Evaporation rate;	No data available
Flammability (solid, gas);	No data available
Upper/lower flammability or explosive limits;	No data available
Vapor pressure;	No data available

OutLAST™ Pro Foaming Agent

Vapor density;	No data available
Relative density;	1.03 g/mL
Solubility;	water
Partition coefficient: n-octanol/water;	No data available
Auto-ignition temperature;	No data available
Decomposition temperature;	No data available
Kinematic Viscosity;	121 cP (25 °C)

9.2. Additional Information

No data available

10. STABILITY AND REACTIVITY

10.1. Reactivity

No data available

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

No data available

10.4. Conditions to avoid

Avoid excessive heat for prolonged periods of time.

10.5. Incompatible materials

Strong oxidizing agents. Strong reducing agent.

10.6. Hazardous decomposition products

Other decomposition products – no data available

In the event of a fire: see section 5

11. TOXICOLOGICAL INFORMATION

11.1. Information on toxicological effects

Acute Toxicity

LD50 Oral – Rat – limit test - > 5000 mg/kg

LD50 Dermal – Rat – limit test - > 5000 mg/kg

LD50 Inhalation – no data available

Skin corrosion/irritation

Skin – Rabbit

Results: moderate skin irritation

(OECD Test Guideline 404)

Serious eye damage/irritation

Eye – Rabbit

Results: moderate eye irritation

(OECD Test Guideline 405)

Respiratory or skin sensitization

Not a known sensitizer

Germ cell mutagenicity

Not a known mutagen

Carcinogenicity

IARC: No component of this product presents at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

ACGIH: No component of this product presents at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by ACGIH.

NTP: No component of this product presents at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by NTP.

OSHA: No component of this product presents at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by OSHA.

Reproductive toxicity

No data available

Specific target organ toxicity – single exposure

No data available

Specific target organ toxicity – repeated exposure

No data available

Aspiration hazard

No data available

11.2. Other information

No data available

12. ECOLOGICAL INFORMATION

12.1. Toxicity Estimate

Toxicity to fish LC50 – Pimephales promelas (fathead minnow) - 6 mg/l – 96 h

Toxicity to daphnia and other aquatic invertebrates EC50 – Daphnia magna (Water flea) – 1847 mg/l – 48 h

12.2. Persistence and degradability

No data available

12.3. Bioaccumulative potential

No data available

12.4. Mobility in soil

No data available

12.5. Other adverse effects

No data available

13. DISPOSAL CONSIDERATIONS

OutLAST™ Pro Foaming Agent

13.1. Disposal Methods.

The best disposal method is to use the entire quantity per label directions. If it is necessary to dispose of unused material then follow the label instructions and relevant local, state and federal waste disposal guidelines.

Product Disposal:

Do not contaminate water, food or feed by storage or disposal.

Packaging Disposal:

If empty: Place in trash or offer for recycling if available. If partly filled: Call your local solid waste agency or 1-800-CLEANUP which is managed as a public-private partnership.

See section 8 for proper PPE and precautionary handling measures.

14. TRANSPORT INFORMATION

DOT

Not dangerous goods

IMDG

Not dangerous goods

IATA

Not dangerous goods

15. REGULATORY INFORMATION

This product is a pesticide registered by the California Department of Pesticide Regulation and the Washington State Department of Agriculture and is subject to certain labeling requirements under state pesticide law(s). These requirements differ from the classification criteria and hazard information required for safety data sheets, and for workplace labels of non-pesticide products. Following is the hazard information as required on the pesticide label:

KEEP OUT OF THE REACH OF CHILDREN

CAUTION

SARA 302 Components

No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

SARA 311/312 Hazards

Acute Health Hazard

California Proposition 65 Components

This product does not contain any chemicals known to the state of California to cause cancer, birth defects, or reproductive harm.

TSCA

All components of this product are listed, exempted, or excluded from listing on the U.S. Toxic Substances Control Act chemical substance inventory.

16. OTHER INFORMATION

Acronyms and abbreviations used

LD50 Lethal Dose, 50%

OutLAST™ Pro Foaming Agent

OECD	Organization for Economic Cooperation and Development
IARC	International Agency for Research on Cancer
ACGIH	American Conference of Industrial Hygienists
NTP	National Toxicology Program
OSHA	Occupational Safety and Health Administration
DOT	Department of Transportation
IMDG	International Maritime Dangerous Goods
IATA	International Air Transport Association
SARA	Superfund Amendments and Reauthorization Act
TSCA	Toxic Substances Control Act
CAS-No.	Chemical Abstract Services - Number
PPE	Personal Protective Equipment
HMIS	Hazardous Materials Identification System
NFPA	National Fire Protection Association
PPM	Parts Per Million

Hazard Rating System Crossover
HMIS Rating

Health Hazard:	1
Flammability:	0
Reactivity:	0

NFPA Rating

Health Hazard:	1
Flammability:	0
Reactivity:	0

Preparation information

Prepared by:	Rockwell Labs Ltd
Version:	1.1
Revision Date:	August 28, 2020
Reason for revision:	Minor reformatting changes

Notice to Reader: The information provided in this Safety Data Sheet has been obtained from sources believed to be reliable. Rockwell Labs Ltd provides no warranties, express or implied, and assumes no responsibility for the accuracy and completeness of the data contained herein. The customer assumes all responsibility for safety and use not in accordance with label instructions. The product names are trademarks of Rockwell Labs Ltd.