

Safety Data Sheet

Issue Date 04-May-2020

Revision/Review Date: 04-May-2020

Version 1.0

1. IDENTIFICATION

Product Identifier

Product Name White Lotion Soap

Other Means of Identification

Product Code GJO03109

Recommended Use of the Chemical and Restrictions on Use

Recommended Use Hand soap RTU. For industrial / institutional use.

Details of the Supplier of the Safety Data Sheet

S.P. Richards Co.
4300 Wildwood Parkway
Suite 100
Atlanta, GA 30339

Emergency Telephone Number

Company Phone Number Phone: 1-888-436-6881
Emergency Telephone (24 hr) INFOTRAC 1-352-323-3500 (International) Customer Number: 37171
1-800-535-5053 (North America)

2. HAZARDS IDENTIFICATION

Appearance White

Physical State Liquid

Odor Cherry

Classification

This chemical does not meet the hazardous criteria set forth by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200). However, this Safety Data Sheet (SDS) contains valuable information critical to the safe handling and proper use of this product. This SDS should be retained and available for employees and other users of this product.

Unknown Acute Toxicity

None known.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No	Weight-%
Water	7732-18-5	60-100
Detergent Blend	Proprietary	3-7
Sodium Chloride	7647-14-5	1-5

If Chemical Name/CAS No is "proprietary" and/or Weight-% is listed as a range, the specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. FIRST-AID MEASURES

First Aid Measures

Eye Contact Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. If eye irritation persists: Get medical advice/attention.

Skin Contact If skin irritation occurs, rinse affected area with water.

Inhalation No known hazardous effects. If symptoms occur, remove to fresh air.

Ingestion Drink plenty of water. If any discomfort persists, obtain medical attention.

Most Important Symptoms and Effects

Symptoms Direct contact with eyes may cause temporary irritation. Prolonged or repeated skin contact may cause irritation.

Indication of Any Immediate Medical Attention and Special Treatment Needed

Notes to Physician Treat symptomatically.

5. FIRE-FIGHTING MEASURES**Suitable Extinguishing Media**

Water spray (fog). Carbon dioxide (CO₂). Dry chemical. Foam.

Unsuitable Extinguishing Media

Not determined.

Specific Hazards Arising from the Chemical

None known.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES**Personal Precautions, Protective Equipment and Emergency Procedures**

Personal Precautions Use personal protective equipment as required.

Environmental Precautions Avoid release to the environment.

Methods and Material for Containment and Cleaning Up

Methods for Containment Prevent further leakage or spillage if safe to do so.

Methods for Clean-Up Collect spillage. Collect in a clean, dry waste container for disposal. After cleaning, flush away traces with water.

7. HANDLING AND STORAGE**Precautions for Safe Handling**

Advice on Safe Handling Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Use personal protection recommended in Section 8. Avoid contact with eyes. Observe good industrial hygiene practices.

Conditions for Safe Storage, Including Any Incompatibilities

Storage Conditions Keep containers tightly closed in a dry, cool and well-ventilated place. Keep locked up and out of reach of children. Keep from freezing.

Incompatible Materials None known.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Exposure Guidelines No exposure limits noted for ingredient(s)

Appropriate Engineering Controls

Engineering Controls Ventilation systems.

Individual Protection Measures, such as Personal Protective Equipment

Eye/Face Protection	No protective equipment is needed under normal use conditions.
Skin and Body Protection	No protective equipment is needed under normal use conditions.
Respiratory Protection	No protective equipment is needed under normal use conditions.
General Hygiene Considerations	Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES**Information on Basic Physical and Chemical Properties**

Physical State	Liquid	Odor	Cherry
Appearance	Opaque	Odor Threshold	Not determined
Color	White		
<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>	
pH	7.0 – 8.5		
Melting Point/Freezing Point	~ 0 °C / ~32 °F		
Boiling Point/Boiling Range	~ 100 °C / ~212 °F		
Flash Point	Not applicable	Tag Open Cup	
Evaporation Rate	Not determined		
Flammability (Solid, Gas)	na/-liquid		
Upper Flammability Limits	Not determined		
Lower Flammability Limit	Not determined		
Vapor Pressure	Not determined		
Vapor Density	Not determined		
Specific Gravity	1.03		
Water Solubility	Completely soluble	@ 25 °C (77 °F)	
Solubility in other solvents	Not determined		
Partition Coefficient	Not determined		
Auto-ignition Temperature	Not determined		
Decomposition Temperature	Not determined		
Kinematic Viscosity	Not determined		
Dynamic Viscosity	Not determined		
Explosive Properties	Not determined		
Oxidizing Properties	Not determined		

10. STABILITY AND REACTIVITY**Reactivity**

Not reactive under normal conditions.

Chemical Stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Hazardous Polymerization

Hazardous polymerization does not occur.

Conditions to Avoid

Keep out of reach of children. Keep from freezing.

Incompatible Materials

None known.

Hazardous Decomposition Products

When exposed to fire, produces normal products of combustion.

11. TOXICOLOGICAL INFORMATION

Information on Likely Routes of Exposure

Product Information

Eye Contact	Avoid contact with eyes.
Skin Contact	Avoid prolonged contact with skin.
Inhalation	Avoid breathing vapors or mists.
Ingestion	Do not taste or swallow.

Component Information

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Sodium Chloride 7647-14-5	= 3 g/kg (Rat)	> 10 g/kg (Rabbit)	> 42 g/m ³ (Rat) 1 h

Information on Physical, Chemical and Toxicological Effects

Symptoms Please see section 4 of this SDS for symptoms.

Delayed and Immediate Effects as well as Chronic Effects from Short and Long-Term Exposure

Carcinogenicity This product does not contain any carcinogens or potential carcinogens as listed by OSHA, IARC or NTP.

Numerical Measures of Toxicity

Not determined

Unknown Acute Toxicity

None known

12. ECOLOGICAL INFORMATION

Ecotoxicity

An environmental hazard cannot be excluded in the event of unprofessional handling or disposal.

Chemical Name	Algae/aquatic plants	Fish	Toxicity to microorganisms	Crustacea
Sodium Chloride 7647-14-5	-	5560 - 6080: 96 h <i>Lepomis macrochirus</i> mg/L LC50 flow-through 12946: 96 h <i>Lepomis macrochirus</i> mg/L LC50 static 6020 - 7070: 96 h <i>Pimephales promelas</i> mg/L LC50 static 7050: 96 h <i>Pimephales promelas</i> mg/L LC50 semi-static 6420 - 6700: 96 h <i>Pimephales promelas</i> mg/L LC50 static 4747 - 7824: 96 h <i>Oncorhynchus mykiss</i> mg/L LC50 flow-through	-	1000: 48 h <i>Daphnia magna</i> mg/L EC50 340.7 - 469.2: 48 h <i>Daphnia magna</i> mg/L EC50 Static

Persistence/Degradability

Not determined

Bioaccumulation

Not determined

Mobility

Not determined

Other Adverse Effects

Not determined

13. DISPOSAL CONSIDERATIONS

Waste Treatment Methods

Disposal of Wastes Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated Packaging Disposal should be in accordance with applicable regional, national and local laws and regulations.

14. TRANSPORT INFORMATION

DOT Not regulated

IATA Not regulated

IMDG Not regulated

15. REGULATORY INFORMATION

International Inventories

Canada – Domestic Substances List (DSL) All ingredients are listed or exempt.
 TSCA (Toxic Substances Control Act) All ingredients are listed or exempt.

Legend:
TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

CERCLA

Chemical Name	Hazardous Substances RQs	CERCLA/SARA RQ	Reportable Quantity (RQ)
None Listed	-	-	-

SARA 311/312 Hazard Categories

Acute Health Hazard Yes

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

CWA (Clean Water Act)

Component	CWA - Reportable Quantities	CWA - Toxic Pollutants	CWA - Priority Pollutants	CWA - Hazardous Substances
None Listed	-	-	-	-

US State Regulations

California Proposition 65

This product does not contain any Proposition 65 chemicals.

U.S. State Right-to-Know Regulations

Chemical Name	State List
None Listed	

- | | |
|--|--|
| AZ- Arizona Ambient Air Quality Guidelines | IL- Illinois Toxic Air Contaminant- Carcinogenic |
| CT- Connecticut Hazardous Air Pollutants | MA- Massachusetts Right to Know List |
| CA- California Director's List of Hazardous Substances | MN- Minnesota Hazardous Substances List |
| CAP65- California Prop65 | NJ- New Jersey Right to Know List |
| FL- Florida Substances List | PA- Pennsylvania Right to Know List |
| ID- Idaho Non-Carcinogen Toxic Air Pollutants | RI- Rhode Island Hazardous Substances List |

6. OTHER INFORMATION

<u>NFPA</u>	Health Hazards Not determined	Flammability Not determined	Instability Not determined	Special Hazards Not determined
<u>HMIS</u>	Health Hazards 1	Flammability 0	Physical Hazards 0	Personal Protection Not determined

Issue Date 04-May-2020
Revision/Review Date: 04-May-2020
Revision Note Version 1.0

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

Keep Out of Reach of Children. For Industrial and Institutional Use Only.

*Denotes changes from last version.

End of Safety Data Sheet