



SAFETY DATA SHEET

P-Screen - Linen Breeze [US Variant]

According to Appendix D, OSHA Hazard Communication Standard 29 CFR §1910.1200

1. Identification

Product identifier

Product name P-Screen - Linen Breeze [US Variant]
Product number P-SCRN LINEN US, VTSPSCRNLIN
Internal identification VA-21-114-US-D

Recommended use of the chemical and restrictions on use

Application Urinal Screen
Uses advised against Use only for intended applications.

Details of the supplier of the safety data sheet

Supplier Vectair Systems Inc.
 2095 Spicer Cove, Covington Way Distribution Centre, Memphis, TN 38134, USA
 +1 901 373 7818
 info@vectairsystems.com

Contact Person Product development

Emergency telephone number

Emergency telephone Vectair Systems Inc +1 901 373 7818 (during normal office hours)
National emergency telephone number INFOTRAC +1 800 535 5053 INTERNATIONAL +1 352 323 3500

2. Hazard(s) identification

Classification of the substance or mixture

Physical hazards Not Classified
Health hazards Eye Dam. 1 - H318 Skin Sens. 1 - H317
Environmental hazards Aquatic Acute 3 - H402 Aquatic Chronic 3 - H412

Classification in accordance with Directive 1907/2006/EEC

Label elements

Hazard symbols



Signal word Danger

P-Screen - Linen Breeze [US Variant]

Hazard statements	H318 Causes serious eye damage. H317 May cause an allergic skin reaction. H412 Harmful to aquatic life with long lasting effects.
Precautionary statements	P280 Wear protective gloves. P302+P352 If on skin: Wash with plenty of water. P305+P351+P338 If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. P333+P313 If skin irritation or rash occurs: Get medical advice/ attention. P501 Dispose of contents/ container in accordance with national regulations.
Contains	Benzenesulfonic acid, C10-13-alkyl derivatives, sodium salts, 4-tert-butylcyclohexyl acetate, Alpha-Pinenes, (R)-p-mentha-1,8-diene, citral, Citrus limon (L.) Burm. F., citrus limon l. burm. f. peel oil c.p, Pine oil

Other hazards

This product does not contain any substances classified as PBT or vPvB.

3. Composition/information on ingredients

Mixtures

Ethylene vinyl acetate copolymer CAS number: 24937-78-8	30-60%
Sodium Chloride CAS number: 7647-14-5	10-30%
Polypropylene (PP) CAS number: 9003-07-0	5-10%
Benzenesulfonic acid, C10-13-alkyl derivatives, sodium salts CAS number: 68411-30-3	5-10%
4-tert-butylcyclohexyl acetate CAS number: 32210-23-4	1-5%
Benzyl acetate CAS number: 140-11-4	1-5%
dipropylene glycol methyl ether acetate CAS number: 88917-22-0	1-5%
Cocamide MEA CAS number: 68140-00-1	<1%
Glycerin CAS number: 56-81-5	<1%

P-Screen - Linen Breeze [US Variant]

Pin-2(10)-ene CAS number: 127-91-3	<1%
Alpha-Pinenes CAS number: 80-56-8	<1%
Orange Terpenes CAS number: 68647-72-3	<1%
(Z)-3,4,5,6,6-pentamethylhept-3-en-2-one CAS number: 81786-73-4	<1%
Methyl N-methylantranilate CAS number: 85-91-6	<1%
stearic acid, pure CAS number: 57-11-4	<1%
Citric Acid CAS number: 77-92-9	<1%
methyl salicylate CAS number: 119-36-8	<1%
Citrus limon (L.) Burm. F. CAS number: 68917-33-9	<1%
citrus limon l. burm. f. peel oil c.p CAS number: 8008-56-8	<1%
(R)-p-mentha-1,8-diene CAS number: 5989-27-5	<1%
Linalool CAS number: 78-70-6	<1%
Ethyl benzoate CAS number: 93-89-0	<1%
citral CAS number: 5392-40-5	<1%

P-Screen - Linen Breeze [US Variant]

p-methoxybenzaldehyde CAS number: 123-11-5	<1%
2-tert-Butylcyclohexyl acetate CAS number: 88-41-5	<1%
Distillates (petroleum), hydrotreated light CAS number: 64742-47-8	<1%
A mixture of: cis-tetrahydro-2-isobutyl-4- methylpyran-4-ol; trans-tetrahydro-2-isobutyl-4- methylpyran-4-ol CAS number: 63500-71-0	<1%
Pine oil CAS number: 8002-09-3	<1%

4. First-aid measures

Description of first aid measures

General information	Get medical attention if any discomfort continues. Show this Safety Data Sheet to the medical personnel.
Inhalation	Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Loosen tight clothing such as collar, tie or belt. Get medical attention if symptoms are severe or persist.
Ingestion	Rinse mouth thoroughly with water. Get medical advice/attention if you feel unwell. Do not induce vomiting unless under the direction of medical personnel.
Skin Contact	It is important to remove the substance from the skin immediately. In the event of any sensitization symptoms developing, ensure further exposure is avoided. Remove contamination with soap and water or recognized skin cleansing agent. Get medical attention if symptoms are severe or persist after washing.
Eye contact	Rinse immediately with plenty of water. Do not rub eye. Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 15 minutes and get medical attention.
Protection of first aiders	First aid personnel should wear appropriate protective equipment during any rescue.

Most important symptoms and effects, both acute and delayed

General information	The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
Inhalation	No specific symptoms known.
Ingestion	May cause sensitization or allergic reactions in sensitive individuals.
Skin contact	May cause skin sensitization or allergic reactions in sensitive individuals. Prolonged contact may cause dryness of the skin.
Eye contact	Causes serious eye damage. Symptoms following overexposure may include the following: Pain. Profuse watering of the eyes. Redness.

Indication of immediate medical attention and special treatment needed

Notes for the doctor	Treat symptomatically. May cause sensitization or allergic reactions in sensitive individuals.
-----------------------------	--

P-Screen - Linen Breeze [US Variant]

5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media The product is not flammable. Extinguish with alcohol-resistant foam, carbon dioxide, dry powder or water fog. Use fire-extinguishing media suitable for the surrounding fire.

Unsuitable extinguishing media Do not use water jet as an extinguisher, as this will spread the fire.

Special hazards arising from the substance or mixture

Specific hazards None known.

Hazardous combustion products Thermal decomposition or combustion products may include the following substances: Harmful gases or vapors.

Advice for firefighters

Protective actions during firefighting Avoid breathing fire gases or vapors. Evacuate area. Cool containers exposed to heat with water spray and remove them from the fire area if it can be done without risk. Cool containers exposed to flames with water until well after the fire is out. Avoid discharge to the aquatic environment. Control run-off water by containing and keeping it out of sewers and watercourses. If risk of water pollution occurs, notify appropriate authorities.

Special protective equipment for firefighters Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing. Standard Firefighter's clothing including helmets, protective boots and gloves will provide a basic level of protection for chemical incidents.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Personal precautions Wear protective clothing as described in Section 8 of this safety data sheet. No action shall be taken without appropriate training or involving any personal risk. Avoid contact with skin and eyes.

Environmental precautions

Environmental precautions Avoid discharge into drains or watercourses or onto the ground. Avoid discharge to the aquatic environment.

Methods and material for containment and cleaning up

Methods for cleaning up Wear protective clothing as described in Section 8 of this safety data sheet. Clear up spills immediately and dispose of waste safely. Collect spillage with a shovel and broom, or similar and reuse, if possible. Collect and place in suitable waste disposal containers and seal securely. Flush contaminated area with plenty of water. Wash thoroughly after dealing with a spillage. Dangerous for the environment. Do not empty into drains. For waste disposal, see Section 13.

Reference to other sections For personal protection, see Section 8. See Section 11 for additional information on health hazards. See Section 12 for additional information on ecological hazards. For waste disposal, see Section 13.

7. Handling and storage

Precautions for safe handling

Usage precautions Read and follow manufacturer's recommendations. Wear protective clothing as described in Section 8 of this safety data sheet. Keep away from food, drink and animal feeding stuffs. Keep container tightly sealed when not in use. Avoid discharge to the aquatic environment. Do not handle until all safety precautions have been read and understood. Do not handle broken packages without protective equipment. Do not reuse empty containers.

P-Screen - Linen Breeze [US Variant]

Advice on general occupational hygiene Wash promptly if skin becomes contaminated. Take off contaminated clothing and wash before reuse. Wash contaminated clothing before reuse.

Conditions for safe storage, including any incompatibilities

Storage precautions Keep only in the original container. Keep container tightly closed, in a cool, well ventilated place. Keep containers upright. Protect containers from damage.

Storage class Miscellaneous hazardous material storage.

Specific end uses(s)

Specific end use(s) The identified uses for this product are detailed in Section 1.

8. Exposure controls/Personal protection

Control parameters

Occupational exposure limits

Benzyl acetate

Long-term exposure limit (8-hour TWA): ACGIH 10 ppm 61 mg/m³
A4

Glycerin

Long-term exposure limit (8-hour TWA): OSHA 5 mg/m³ respirable fraction
Long-term exposure limit (8-hour TWA): OSHA 15 mg/m³ total dust

Pin-2(10)-ene

Long-term exposure limit (8-hour TWA): ACGIH 20 ppm 112 mg/m³
Long-term exposure limit (8-hour TWA): ACGIH 20 ppm 112 mg/m³
A4, A4, DSens, DSens

Alpha-Pinenes

Long-term exposure limit (8-hour TWA): ACGIH 20 ppm 112 mg/m³
A4, DSens

ACGIH = American Conference of Governmental Industrial Hygienists.
OSHA = Occupational Safety and Health Administration.
A4 = Not Classifiable as a Human Carcinogen.
DSens = Dermal sensitizer.

Ingredient

Exposure controls

Protective equipment



Appropriate engineering controls

Provide adequate ventilation. Observe any occupational exposure limits for the product or ingredients.

Eye/face protection

Wear tight-fitting, chemical splash goggles or face shield. If inhalation hazards exist, a full-face respirator may be required instead.

Hand protection

It is recommended that chemical-resistant, impervious gloves are worn. The most suitable glove should be chosen in consultation with the glove supplier/manufacturer, who can provide information about the breakthrough time of the glove material. To protect hands from chemicals, gloves should comply with OSHA 1910.138 and be demonstrated to be impervious to the chemical and resist degradation. Considering the data specified by the glove manufacturer, check during use that the gloves are retaining their protective properties and change them as soon as any deterioration is detected. Frequent changes are recommended.

P-Screen - Linen Breeze [US Variant]

Other skin and body protection	May cause skin sensitization or allergic reactions in sensitive individuals. Wear appropriate clothing to prevent repeated or prolonged skin contact.
Hygiene measures	Wash hands thoroughly after handling. Wash at the end of each work shift and before eating, smoking and using the toilet. Do not eat, drink or smoke when using this product.
Respiratory protection	Ensure all respiratory protective equipment is suitable for its intended use and is NIOSH approved. Check that the respirator fits tightly and the filter is changed regularly. Gas and combination filter cartridges should comply with OSHA 1910.134. Full face mask respirators with replaceable filter cartridges should comply with OSHA 1910.134. Half mask and quarter mask respirators with replaceable filter cartridges should comply with OSHA 1910.134.
Environmental exposure controls	Keep container tightly sealed when not in use. Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels.

9. Physical and chemical properties

Information on basic physical and chemical properties

Appearance	Solid.
Color	Blue.
Odor	Characteristic.
Odor threshold	Not determined.
pH	Not determined.
Melting point	Undetermined.
Initial boiling point and range	>100°C/>212°F
Flash point	>100°C/>212°F
Evaporation rate	Not determined.
Evaporation factor	Not available.
Flammability (solid, gas)	Not applicable.
Upper/lower flammability or explosive limits	Not determined.
Other flammability	Not available.
Vapor pressure	Not determined.
Vapor density	Not determined.
Relative density	Not determined.
Bulk density	Not available.
Solubility(ies)	Not miscible or difficult to mix.
Partition coefficient	Not determined.
Auto-ignition temperature	Product is not self igniting.
Decomposition Temperature	Not determined.
Viscosity	Not determined.
Explosive properties	Product does not present an explosion hazard.

P-Screen - Linen Breeze [US Variant]

Explosive under the influence of a flame Not considered to be explosive.

Oxidizing properties Not available.

Organic solvents

10. Stability and reactivity

Reactivity There are no known reactivity hazards associated with this product.

Stability Stable at normal ambient temperatures and when used as recommended. Stable under the prescribed storage conditions.

Possibility of hazardous reactions No potentially hazardous reactions known.

Conditions to avoid There are no known conditions that are likely to result in a hazardous situation.

Materials to avoid No specific material or group of materials is likely to react with the product to produce a hazardous situation.

Hazardous decomposition products Does not decompose when used and stored as recommended. Thermal decomposition or combustion products may include the following substances: Harmful gases or vapors.

11. Toxicological information

Information on toxicological effects

Acute toxicity - oral

Notes (oral LD₅₀) Based on available data the classification criteria are not met.

ATE oral (mg/kg) 6,329.11

Acute toxicity - dermal

Notes (dermal LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - inhalation

Notes (inhalation LC₅₀) Based on available data the classification criteria are not met.

Skin corrosion/irritation

Animal data Based on available data the classification criteria are not met.

Serious eye damage/irritation

Serious eye damage/irritation Eye Dam. 1 - H318 Causes serious eye damage.

Respiratory sensitization

Respiratory sensitization Based on available data the classification criteria are not met.

Skin sensitization

Skin sensitization May cause skin sensitization or allergic reactions in sensitive individuals.

Germ cell mutagenicity

Genotoxicity - in vitro Based on available data the classification criteria are not met.

Carcinogenicity

Carcinogenicity Based on available data the classification criteria are not met.

P-Screen - Linen Breeze [US Variant]

IARC carcinogenicity	Contains a substance which may be potentially carcinogenic. IARC Group 3 Not classifiable as to its carcinogenicity to humans.
<u>Reproductive toxicity</u>	
Reproductive toxicity - fertility	Based on available data the classification criteria are not met.
Reproductive toxicity - development	Based on available data the classification criteria are not met.
<u>Specific target organ toxicity - single exposure</u>	
STOT - single exposure	Not classified as a specific target organ toxicant after a single exposure.
<u>Specific target organ toxicity - repeated exposure</u>	
STOT - repeated exposure	Not classified as a specific target organ toxicant after repeated exposure.
<u>Aspiration hazard</u>	
Aspiration hazard	Not relevant. Solid.
General information	
	The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
Inhalation	No specific symptoms known.
Ingestion	May cause sensitization or allergic reactions in sensitive individuals.
Skin Contact	May cause skin sensitization or allergic reactions in sensitive individuals. Prolonged contact may cause dryness of the skin.
Eye contact	Causes serious eye damage. Symptoms following overexposure may include the following: Pain. Profuse watering of the eyes. Redness.
Route of exposure	Ingestion Inhalation Skin and/or eye contact
Target Organs	No specific target organs known.
Medical considerations	Skin disorders and allergies.

12. Ecological information

Toxicity	Aquatic Chronic 3 - H412 Harmful to aquatic life with long lasting effects.
<u>Persistence and degradability</u>	
Persistence and degradability	The degradability of the product is not known.
<u>Bioaccumulative potential</u>	
Bio-Accumulative Potential	No data available on bioaccumulation.
Partition coefficient	Not determined.
<u>Mobility in soil</u>	
Mobility	No data available.
<u>Other adverse effects</u>	
Other adverse effects	None known.

13. Disposal considerations

Waste treatment methods

P-Screen - Linen Breeze [US Variant]

General information	The generation of waste should be minimized or avoided wherever possible. Reuse or recycle products wherever possible. This material and its container must be disposed of in a safe way. When handling waste, the safety precautions applying to handling of the product should be considered. Care should be taken when handling emptied containers that have not been thoroughly cleaned or rinsed out. Empty containers or liners may retain some product residues and hence be potentially hazardous.
Disposal methods	Dispose of surplus products and those that cannot be recycled via a licensed waste disposal contractor. Waste, residues, empty containers, discarded work clothes and contaminated cleaning materials should be collected in designated containers, labeled with their contents. Incineration or landfill should only be considered when recycling is not feasible.

14. Transport information

General	The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, DOT).
<u>UN Number</u>	
UN No. (International)	Not applicable.
<u>UN proper shipping name</u>	
Proper shipping name (International)	Not applicable.
<u>Transport hazard class(es)</u>	
Transport Labels (International)	No transport warning sign required.
<u>Packing group</u>	
Packing group (International)	Not applicable.
<u>Environmental hazards</u>	
Environmentally Hazardous Substance	
No.	
<u>Special precautions for user</u>	
Not applicable.	
Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code	Not applicable.

15. Regulatory information

US Federal Regulations

SARA Section 302 Extremely Hazardous Substances Tier II Threshold Planning Quantities

None of the ingredients are listed or exempt.

CERCLA/Superfund, Hazardous Substances/Reportable Quantities (EPA)

None of the ingredients are listed or exempt.

SARA Extremely Hazardous Substances EPCRA Reportable Quantities

None of the ingredients are listed or exempt.

SARA 313 Emission Reporting

None of the ingredients are listed or exempt.

P-Screen - Linen Breeze [US Variant]

CAA Accidental Release Prevention

None of the ingredients are listed or exempt.

FDA - Essential Chemical

None of the ingredients are listed or exempt.

FDA - Precursor Chemical

None of the ingredients are listed or exempt.

SARA (311/312) Hazard Categories

None of the ingredients are listed or exempt.

OSHA Highly Hazardous Chemicals

None of the ingredients are listed or exempt.

US State Regulations

California Proposition 65 Carcinogens and Reproductive Toxins

None of the ingredients are listed or exempt.

California Air Toxics "Hot Spots" (A-I)

None of the ingredients are listed or exempt.

California Air Toxics "Hot Spots" (A-II)

None of the ingredients are listed or exempt.

California Directors List of Hazardous Substances

The following ingredients are listed or exempt:

Benzyl acetate

Present.

Massachusetts "Right To Know" List

The following ingredients are listed or exempt:

Glycerin

Present.

Alpha-Pinenes

Present.

Rhode Island "Right To Know" List

The following ingredients are listed or exempt:

Glycerin

Present.

methyl salicylate

Present.

Minnesota "Right To Know" List

The following ingredients are listed or exempt:

Glycerin

Present.

Benzyl acetate

Present.

New Jersey "Right To Know" List

The following ingredients are listed or exempt:

P-Screen - Linen Breeze [US Variant]

Glycerin

Present.

Benzyl acetate

Present.

Alpha-Pinenes

Present.

Pennsylvania "Right To Know" List

The following ingredients are listed or exempt:

Glycerin

Present.

methyl salicylate

Present.

Alpha-Pinenes

Present.

Inventories

US - TSCA

The following ingredients are listed or exempt:

Pin-2(10)-ene

Present.

p-methoxybenzaldehyde

Present.

Citric Acid

Present.

Glycerin

Present.

2-tert-Butylcyclohexyl acetate

Present.

dipropylene glycol methyl ether acetate

Present.

A mixture of: cis-tetrahydro-2-isobutyl-4- methylpyran-4-ol; trans-tetrahydro-2-isobutyl-4- methylpyran-4-ol

Present.

Benzyl acetate

Present.

4-tert-butylcyclohexyl acetate

Present.

methyl salicylate

Present.

Citrus limon (L.) Burm. F.

Present.

Sodium Chloride

Present.

citrus limon l. burm. f. peel oil c.p

Present.

Alpha-Pinenes

Present.

P-Screen - Linen Breeze [US Variant]

Orange Terpenes

Present.

US - TSCA 12(b) Export Notification

None of the ingredients are listed or exempt.

16. Other information

Training advice	Only trained personnel should use this material.
Revision comments	Revised formulation.
Issued by	Compliance Lead
Revision date	9/8/2021
Revision	5
Supersedes date	9/16/2020
SDS No.	5507
Hazard statements in full	H317 May cause an allergic skin reaction. H318 Causes serious eye damage. H402 Harmful to aquatic life. H412 Harmful to aquatic life with long lasting effects.

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.