



SAFETY DATA SHEET

V-Air Solid - Cucumber Melon [US Variant]

According to Appendix D, OSHA Hazard Communication Standard 29 CFR §1910.1200

1. Identification

Product identifier

Product name V-Air Solid - Cucumber Melon [US Variant]
Product number V-SOLID MELON, VTSSOLIDMEL
Internal identification VA-21-506-US-D

Recommended use of the chemical and restrictions on use

Application Air freshener
Uses advised against Use only for intended applications.

Details of the supplier of the safety data sheet

Supplier Vectair Systems Inc.
 2095 Spicer Cove, Covington Way Distribution Centre, Memphis, TN 38134, USA
 +1 901 373 7818
 info@vectairsystems.com

Contact Person Product development

Emergency telephone number

Emergency telephone Vectair Systems Inc +1 901 373 7818 (during normal office hours)
National emergency telephone number INFOTRAC +1 800 535 5053 INTERNATIONAL +1 352 323 3500

2. Hazard(s) identification

Classification of the substance or mixture

Physical hazards Not Classified
Health hazards Skin Sens. 1 - H317
Environmental hazards Aquatic Chronic 3 - H412

Classification in accordance
 with Directive 1907/2006/EEC

Label elements

Hazard symbols



Signal word Warning

V-Air Solid - Cucumber Melon [US Variant]

Hazard statements	H317 May cause an allergic skin reaction. H412 Harmful to aquatic life with long lasting effects.
Precautionary statements	P280 Wear protective gloves. P302+P352 If on skin: Wash with plenty of water. P333+P313 If skin irritation or rash occurs: Get medical advice/ attention. P501 Dispose of contents/ container in accordance with national regulations.
Contains	2-Methyl-3-(p-isopropylphenyl)propionaldehyde, alpha-Amylcinnamaldehyde, Eucalyptus Oil (Eucalyptus Globulus Labille), Benzyl salicylate, Geraniol, alpha-Ionone

Other hazards

This product does not contain any substances classified as PBT or vPvB.

3. Composition/information on ingredients

Mixtures

calcium sulfate semi hydrate CAS number: 10034-76-1	30-60%
Aqua CAS number: 7732-18-5	10-30%
ethyl acetoacetate CAS number: 141-97-9	1-5%
Diethyl Malonate CAS number: 105-53-3	1-5%
A mixture of: cis-tetrahydro-2-isobutyl-4- methylpyran-4-ol; trans-tetrahydro-2-isobutyl-4- methylpyran-4-ol CAS number: 63500-71-0	1-5%
Polyethylene glycol mono (octylphenyl) ether CAS number: 9036-19-5	1-5%
dipropylene glycol methyl ether acetate CAS number: 88917-22-0	1-5%
2-Methyl-3-(p-isopropylphenyl)propionaldehyde CAS number: 103-95-7	1-5%
Propylene Glycol CAS number: 57-55-6	1-5%
alpha-Amylcinnamaldehyde CAS number: 122-40-7	1-5%

V-Air Solid - Cucumber Melon [US Variant]

Eucalyptus Oil (Eucalyptus Globulus Labille) CAS number: 8000-48-4	<1%
triethylene glycol CAS number: 112-27-6	<1%
triacetin CAS number: 102-76-1	<1%
2-tert-Butylcyclohexyl acetate CAS number: 88-41-5	<1%
Carrageenan CAS number: 9000-07-1	<1%
Bornan-2-one CAS number: 76-22-2	<1%
Eucalyptol CAS number: 470-82-6	<1%
1,4-Dioxacycloheptadecane-5,17-dione CAS number: 105-95-3	<1%
Citronellol CAS number: 106-22-9	<1%
Benzyl salicylate CAS number: 118-58-1	<1%
benzyl benzoate CAS number: 120-51-4	<1%
Linalool CAS number: 78-70-6	<1%
2-Phenoxyethyl isobutyrate CAS number: 103-60-6	<1%
p-methoxybenzaldehyde CAS number: 123-11-5	<1%

V-Air Solid - Cucumber Melon [US Variant]

menthol CAS number: 89-78-1	<1%
Geraniol CAS number: 106-24-1	<1%
alpha-Ionone CAS number: 127-41-3	<1%

4. First-aid measures

Description of first aid measures

General information	Get medical attention if any discomfort continues. Show this Safety Data Sheet to the medical personnel.
Inhalation	Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Loosen tight clothing such as collar, tie or belt. Get medical attention if symptoms are severe or persist.
Ingestion	Rinse mouth thoroughly with water. Get medical advice/attention if you feel unwell. Do not induce vomiting unless under the direction of medical personnel.
Skin Contact	It is important to remove the substance from the skin immediately. In the event of any sensitization symptoms developing, ensure further exposure is avoided. Remove contamination with soap and water or recognized skin cleansing agent. Get medical attention if symptoms are severe or persist after washing.
Eye contact	Rinse with water. Get medical attention if any discomfort continues.
Protection of first aiders	First aid personnel should wear appropriate protective equipment during any rescue.

Most important symptoms and effects, both acute and delayed

General information	The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
Inhalation	No specific symptoms known.
Ingestion	May cause sensitization or allergic reactions in sensitive individuals.
Skin contact	May cause skin sensitization or allergic reactions in sensitive individuals. Prolonged contact may cause dryness of the skin.
Eye contact	No specific symptoms known. May be slightly irritating to eyes.

Indication of immediate medical attention and special treatment needed

Notes for the doctor	Treat symptomatically. May cause sensitization or allergic reactions in sensitive individuals.
-----------------------------	--

5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media The product is not flammable. Extinguish with alcohol-resistant foam, carbon dioxide, dry powder or water fog. Use fire-extinguishing media suitable for the surrounding fire.

Unsuitable extinguishing media Do not use water jet as an extinguisher, as this will spread the fire.

Special hazards arising from the substance or mixture

V-Air Solid - Cucumber Melon [US Variant]

Specific hazards	None known.
Hazardous combustion products	Thermal decomposition or combustion products may include the following substances: Harmful gases or vapors.
<u>Advice for firefighters</u>	
Protective actions during firefighting	Avoid breathing fire gases or vapors. Evacuate area. Cool containers exposed to heat with water spray and remove them from the fire area if it can be done without risk. Cool containers exposed to flames with water until well after the fire is out. Avoid discharge to the aquatic environment. Control run-off water by containing and keeping it out of sewers and watercourses. If risk of water pollution occurs, notify appropriate authorities.
Special protective equipment for firefighters	Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing. Standard Firefighter's clothing including helmets, protective boots and gloves will provide a basic level of protection for chemical incidents.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Personal precautions	Wear protective clothing as described in Section 8 of this safety data sheet. No action shall be taken without appropriate training or involving any personal risk. Avoid contact with skin and eyes.
-----------------------------	---

Environmental precautions

Environmental precautions	Avoid discharge into drains or watercourses or onto the ground. Avoid discharge to the aquatic environment.
----------------------------------	---

Methods and material for containment and cleaning up

Methods for cleaning up	Wear protective clothing as described in Section 8 of this safety data sheet. Clear up spills immediately and dispose of waste safely. Collect spillage with a shovel and broom, or similar and reuse, if possible. Collect and place in suitable waste disposal containers and seal securely. Flush contaminated area with plenty of water. Wash thoroughly after dealing with a spillage. Dangerous for the environment. Do not empty into drains. For waste disposal, see Section 13.
--------------------------------	--

Reference to other sections	For personal protection, see Section 8. See Section 11 for additional information on health hazards. See Section 12 for additional information on ecological hazards. For waste disposal, see Section 13.
------------------------------------	---

7. Handling and storage

Precautions for safe handling

Usage precautions	Read and follow manufacturer's recommendations. Wear protective clothing as described in Section 8 of this safety data sheet. Keep away from food, drink and animal feeding stuffs. Keep container tightly sealed when not in use. Avoid discharge to the aquatic environment. Do not handle until all safety precautions have been read and understood. Do not handle broken packages without protective equipment. Do not reuse empty containers.
--------------------------	---

Advice on general occupational hygiene	Wash promptly if skin becomes contaminated. Take off contaminated clothing and wash before reuse. Wash contaminated clothing before reuse.
---	--

Conditions for safe storage, including any incompatibilities

Storage precautions	Keep only in the original container. Keep container tightly closed, in a cool, well ventilated place. Keep containers upright. Protect containers from damage.
----------------------------	--

Storage class	Miscellaneous hazardous material storage.
----------------------	---

Specific end uses(s)

V-Air Solid - Cucumber Melon [US Variant]

Specific end use(s) The identified uses for this product are detailed in Section 1.

8. Exposure controls/Personal protection

Control parameters

Occupational exposure limits

Bornan-2-one

Long-term exposure limit (8-hour TWA): ACGIH 2 ppm 12 mg/m³

Short-term exposure limit (15-minute): ACGIH 3 ppm 19 mg/m³

A4

Long-term exposure limit (8-hour TWA): OSHA 2 mg/m³

ACGIH = American Conference of Governmental Industrial Hygienists.

A4 = Not Classifiable as a Human Carcinogen.

OSHA = Occupational Safety and Health Administration.

Ingredient

Bornan-2-one (CAS: 76-22-2)

Immediate danger to life and health 200 mg/m³

Exposure controls

Protective equipment



Appropriate engineering controls

Provide adequate ventilation. Observe any occupational exposure limits for the product or ingredients.

Eye/face protection

Unless the assessment indicates a higher degree of protection is required, the following protection should be worn: Tight-fitting safety glasses.

Hand protection

It is recommended that chemical-resistant, impervious gloves are worn. The most suitable glove should be chosen in consultation with the glove supplier/manufacture, who can provide information about the breakthrough time of the glove material. To protect hands from chemicals, gloves should comply with OSHA 1910.138 and be demonstrated to be impervious to the chemical and resist degradation. Considering the data specified by the glove manufacturer, check during use that the gloves are retaining their protective properties and change them as soon as any deterioration is detected. Frequent changes are recommended.

Other skin and body protection

May cause skin sensitization or allergic reactions in sensitive individuals. Wear appropriate clothing to prevent repeated or prolonged skin contact.

Hygiene measures

Wash hands thoroughly after handling. Wash at the end of each work shift and before eating, smoking and using the toilet. Do not eat, drink or smoke when using this product.

Respiratory protection

Ensure all respiratory protective equipment is suitable for its intended use and is NIOSH approved. Check that the respirator fits tightly and the filter is changed regularly. Gas and combination filter cartridges should comply with OSHA 1910.134. Full face mask respirators with replaceable filter cartridges should comply with OSHA 1910.134. Half mask and quarter mask respirators with replaceable filter cartridges should comply with OSHA 1910.134.

Environmental exposure controls

Keep container tightly sealed when not in use. Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels.

V-Air Solid - Cucumber Melon [US Variant]

9. Physical and chemical properties

Information on basic physical and chemical properties

Appearance	Semi-Solid
Color	Off-white.
Odor	Characteristic.
Odor threshold	Not determined.
pH	Not determined.
Melting point	Undetermined.
Initial boiling point and range	>100°C/>212°F
Flash point	>100°C/>212°F
Evaporation rate	Not determined.
Evaporation factor	Not available.
Flammability (solid, gas)	Not applicable.
Upper/lower flammability or explosive limits	Not determined.
Other flammability	Not available.
Vapor pressure	Not determined.
Vapor density	Not determined.
Relative density	Not determined.
Bulk density	Not available.
Solubility(ies)	Not miscible or difficult to mix.
Partition coefficient	Not determined.
Auto-ignition temperature	Product is not self igniting.
Decomposition Temperature	Not determined.
Viscosity	Not determined.
Explosive properties	Product does not present an explosion hazard.
Explosive under the influence of a flame	Not considered to be explosive.
Oxidizing properties	Not available.

Organic solvents

10. Stability and reactivity

Reactivity	There are no known reactivity hazards associated with this product.
Stability	Stable at normal ambient temperatures and when used as recommended. Stable under the prescribed storage conditions.
Possibility of hazardous reactions	No potentially hazardous reactions known.

V-Air Solid - Cucumber Melon [US Variant]

Conditions to avoid	There are no known conditions that are likely to result in a hazardous situation.
Materials to avoid	No specific material or group of materials is likely to react with the product to produce a hazardous situation.
Hazardous decomposition products	Does not decompose when used and stored as recommended. Thermal decomposition or combustion products may include the following substances: Harmful gases or vapors.

11. Toxicological information

Information on toxicological effects

Acute toxicity - oral

Notes (oral LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - dermal

Notes (dermal LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - inhalation

Notes (inhalation LC₅₀) Based on available data the classification criteria are not met.

Skin corrosion/irritation

Animal data Based on available data the classification criteria are not met.

Serious eye damage/irritation

Serious eye damage/irritation Based on available data the classification criteria are not met.

Respiratory sensitization

Respiratory sensitization Based on available data the classification criteria are not met.

Skin sensitization

Skin sensitization May cause skin sensitization or allergic reactions in sensitive individuals.

Germ cell mutagenicity

Genotoxicity - in vitro Based on available data the classification criteria are not met.

Carcinogenicity

Carcinogenicity Based on available data the classification criteria are not met.

IARC carcinogenicity

None of the ingredients are listed or exempt.

Reproductive toxicity

Reproductive toxicity - fertility Based on available data the classification criteria are not met.

Reproductive toxicity - development

Based on available data the classification criteria are not met.

Specific target organ toxicity - single exposure

STOT - single exposure Not classified as a specific target organ toxicant after a single exposure.

Specific target organ toxicity - repeated exposure

STOT - repeated exposure Not classified as a specific target organ toxicant after repeated exposure.

Aspiration hazard

Aspiration hazard Not relevant. Solid.

General information

The severity of the symptoms described will vary dependent on the concentration and the length of exposure.

V-Air Solid - Cucumber Melon [US Variant]

Inhalation	No specific symptoms known.
Ingestion	May cause sensitization or allergic reactions in sensitive individuals.
Skin Contact	May cause skin sensitization or allergic reactions in sensitive individuals. Prolonged contact may cause dryness of the skin.
Eye contact	No specific symptoms known.
Route of exposure	Ingestion Inhalation Skin and/or eye contact
Target Organs	No specific target organs known.
Medical considerations	Skin disorders and allergies.

12. Ecological information

Toxicity Aquatic Chronic 3 - H412 Harmful to aquatic life with long lasting effects.

Persistence and degradability

Persistence and degradability The degradability of the product is not known.

Bioaccumulative potential

Bio-Accumulative Potential No data available on bioaccumulation.

Partition coefficient Not determined.

Mobility in soil

Mobility No data available.

Other adverse effects

Other adverse effects None known.

13. Disposal considerations

Waste treatment methods

General information The generation of waste should be minimized or avoided wherever possible. Reuse or recycle products wherever possible. This material and its container must be disposed of in a safe way. When handling waste, the safety precautions applying to handling of the product should be considered. Care should be taken when handling emptied containers that have not been thoroughly cleaned or rinsed out. Empty containers or liners may retain some product residues and hence be potentially hazardous.

Disposal methods Dispose of surplus products and those that cannot be recycled via a licensed waste disposal contractor. Waste, residues, empty containers, discarded work clothes and contaminated cleaning materials should be collected in designated containers, labeled with their contents. Incineration or landfill should only be considered when recycling is not feasible.

14. Transport information

General The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, DOT).

UN Number

UN No. (International) Not applicable.

UN proper shipping name

Proper shipping name (International) Not applicable.

V-Air Solid - Cucumber Melon [US Variant]

Transport hazard class(es)

Transport Labels (International) No transport warning sign required.

Packing group

Packing group (International) Not applicable.

Environmental hazards

Environmentally Hazardous Substance
No.

Special precautions for user

Not applicable.

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not applicable.

15. Regulatory information

US Federal Regulations

SARA Section 302 Extremely Hazardous Substances Tier II Threshold Planning Quantities

None of the ingredients are listed or exempt.

CERCLA/Superfund, Hazardous Substances/Reportable Quantities (EPA)

None of the ingredients are listed or exempt.

SARA Extremely Hazardous Substances EPCRA Reportable Quantities

None of the ingredients are listed or exempt.

SARA 313 Emission Reporting

None of the ingredients are listed or exempt.

CAA Accidental Release Prevention

None of the ingredients are listed or exempt.

FDA - Essential Chemical

None of the ingredients are listed or exempt.

FDA - Precursor Chemical

None of the ingredients are listed or exempt.

SARA (311/312) Hazard Categories

None of the ingredients are listed or exempt.

OSHA Highly Hazardous Chemicals

None of the ingredients are listed or exempt.

US State Regulations

California Proposition 65 Carcinogens and Reproductive Toxins

None of the ingredients are listed or exempt.

California Air Toxics "Hot Spots" (A-I)

None of the ingredients are listed or exempt.

V-Air Solid - Cucumber Melon [US Variant]

California Air Toxics "Hot Spots" (A-II)

None of the ingredients are listed or exempt.

California Directors List of Hazardous Substances

None of the ingredients are listed or exempt.

Massachusetts "Right To Know" List

The following ingredients are listed or exempt:

ethyl acetoacetate

Present.

Rhode Island "Right To Know" List

The following ingredients are listed or exempt:

triethylene glycol

Present.

Propylene Glycol

Present.

Minnesota "Right To Know" List

The following ingredients are listed or exempt:

Propylene Glycol

Present.

New Jersey "Right To Know" List

The following ingredients are listed or exempt:

Propylene Glycol

Present.

Diethyl Malonate

Present.

Pennsylvania "Right To Know" List

The following ingredients are listed or exempt:

triethylene glycol

Present.

Propylene Glycol

Present.

ethyl acetoacetate

Present.

Inventories

US - TSCA

The following ingredients are listed or exempt:

triethylene glycol

Present.

alpha-Ionone

Present.

Eucalyptus Oil (Eucalyptus Globulus Labille)

Present.

p-methoxybenzaldehyde

Present.

V-Air Solid - Cucumber Melon [US Variant]

alpha-Amylcinnamaldehyde

Present.

Eucalyptol

Present.

Propylene Glycol

Present.

1,4-Dioxacycloheptadecane-5,17-dione

Present.

menthol

Present.

dipropylene glycol methyl ether acetate

Present.

2-tert-Butylcyclohexyl acetate

Present.

Citronellol

Present.

Benzyl salicylate

Present.

ethyl acetoacetate

Present.

A mixture of: cis-tetrahydro-2-isobutyl-4- methylpyran-4-ol; trans-tetrahydro-2-isobutyl-4- methylpyran-4-ol

Present.

Diethyl Malonate

Present.

US - TSCA 12(b) Export Notification

None of the ingredients are listed or exempt.

16. Other information

Training advice	Only trained personnel should use this material.
Revision comments	Revised formulation.
Issued by	Compliance Lead
Revision date	10/27/2021
Revision	5
Supersedes date	10/5/2020
SDS No.	5540
Hazard statements in full	H317 May cause an allergic skin reaction. H412 Harmful to aquatic life with long lasting effects.

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.