



ELEMENT SPECS		
PART NUMBER	35P	
MATERIAL	Polyester	
FLOW RATE	275 CFM	467 m <sup>3</sup> /hr
SURFACE AREA	4.0 ft <sup>2</sup>	0.4 m <sup>2</sup>
I.D.	SEE DRAWING	SEE DRAWING
O.D.	SEE DRAWING	SEE DRAWING
HEIGHT	SEE DRAWING	SEE DRAWING

THE INFORMATION CONTAINED HEREIN IS CONFIDENTIAL AND THE PROPERTY OF SOLBERG MANUFACTURING INC. AND IT IS FURNISHED TO YOU WITH THE EXPRESS UNDERSTANDING THAT IT WILL NOT BE REPRODUCED, COPIED IN ANY MANNER, LOANED OR OTHERWISE TRANSFERRED TO OTHERS ENTIRELY OR IN PART, NOR USED FOR ANY PURPOSE OTHER THAN FOR WHICH IT WAS FURNISHED. IT WILL BE RETURNED UPON REQUEST TO SOLBERG MANUFACTURING INC. THE ABOVE RESTRICTION IS IN ADDITION TO, AND DOES NOT IN ANY WAY ALTER, ANY OTHER RESTRICTIONS WHICH MAY APPLY TO THE INFORMATION CONTAINED HEREIN.

**TOLERANCES**  
 DIMENSIONS ARE FOR REFERENCE ONLY. ALL DIMENSIONS ARE SUBJECT TO CHANGE UPON PRODUCTION.  
 UNLESS OTHERWISE SPECIFIED:  
 -DIMENSIONS ARE IN INCHES  
 -REF: APPROXIMATE DIMENSIONS, NO TOLERANCES APPLY  
 -FINISH: BREAK EDGES TO .005-.020 RADIUS/CHAMFER

MODEL NUMBER: 35P		SHEET: 1 OF 1	
DESCRIPTION: 35P, POLY			
PROJECT:	DRAWN BY: RWK	APPROVED BY: EZR	REV:
	DATE: 9/6/2019	DATE: 9/6/2019	