



| ELEMENT SPECS | |
|---------------|---|
| PART NUMBER | 274 |
| MATERIAL | Paper |
| FLOW RATE | 1100 CFM 1869 m ³ /hr |
| SURFACE AREA | 45.4 ft ² 4.2 m ² |
| I.D. | SEE DRAWING |
| O.D. | SEE DRAWING |
| HEIGHT | SEE DRAWING |