



REV	DESCRIPTION	ECN #	CHG BY	DATE	APP'D
A	UPDATED TB	PER CCS	NAD	09/01/15	CCS
B	UPDATED TO 3-D .IDW	-	RWK	09/05/19	NAD



ELEMENT SPECS		
PART NUMBER	345P	
MATERIAL	Polyester	
FLOW RATE	1100 CFM	1869 m ³ /hr
SURFACE AREA	22.1 ft ²	2.1 m ²
I.D.	6.00"	152mm
O.D.	9.75"	248mm
HEIGHT	14.50"	368mm

SOLBERG
Filtration • Separation • Silencing
630.773.1363 • www.solbergmfg.com

THE INFORMATION CONTAINED HEREIN IS CONFIDENTIAL AND THE PROPERTY OF SOLBERG MANUFACTURING INC. AND IT IS FURNISHED TO YOU WITH THE EXPRESS UNDERSTANDING THAT IT WILL NOT BE REPRODUCED, COPIED IN ANY MANNER, LOANED OR OTHERWISE TRANSFERRED TO OTHERS ENTIRELY OR IN PART, NOR USED FOR ANY PURPOSE OTHER THAN FOR WHICH IT WAS FURNISHED. IT WILL BE RETURNED UPON REQUEST TO SOLBERG MANUFACTURING INC. THE ABOVE RESTRICTION IS IN ADDITION TO, AND DOES NOT IN ANY WAY ALTER, ANY OTHER RESTRICTIONS WHICH MAY APPLY TO THE INFORMATION CONTAINED HEREIN.

TOLERANCES
DIMENSIONS ARE FOR REFERENCE ONLY. ALL DIMENSIONS ARE SUBJECT TO CHANGE UPON PRODUCTION.
UNLESS OTHERWISE SPECIFIED:
-DIMENSIONS ARE IN INCHES
-REF: APPROXIMATE DIMENSIONS, NO TOLERANCES APPLY
-FINISH: BREAK EDGES TO .005-.020 RADIUS/CHAMFER

MODEL NUMBER: 345P		SHEET: 1 OF 1	
DESCRIPTION: 345P, POLY			
PROJECT: SD18922	DRAWN BY: CRW	APPROVED BY: MC	REV: B
	DATE: 7/28/2011	DATE: 7/28/2011	