

SAFETY DATA SHEET

SECTION 1**PRODUCT AND COMPANY IDENTIFICATION****PRODUCT****Product Name:** SANTOPRENE™ THERMOPLASTIC VULCANIZATE - BLACK GRADES**Product Description:** Elastomer, see Section 16 for applicable grades.**Intended Use:** Automotive Application, Food-contact, Personal care, Pharmaceutical, Miscellaneous industrial applications**COMPANY IDENTIFICATION****Supplier:** Celanese Sales U.S Ltd.
222 West Las Colinas Boulevard Suite 900N
TX 75039 Irving

Email Address of the person responsible for the SDS:	HazCom@celanese.com
Telephone number:	+1 972-443-4000
Emergency Telephone number	Domestic North America: 800-424-9300 International Call +1 703-527-3887 (Collect calls accepted)

SECTION 2**HAZARDS IDENTIFICATION**

This material is not hazardous according to regulatory guidelines (see (M)SDS Section 15).

LABEL ELEMENTS:**Hazard Statements:****Supplemental:**

EUH210: Safety data sheet available on request.

EUH208: Contains: TIN DICHLORIDE May produce an allergic reaction.

Other hazard information:**Physical / Chemical Hazards:**

WARNING: May form combustible dust concentrations in air (during processing/handling). Thermal burn hazard - contact with hot material may cause thermal burns. Spilled pellets present a slipping hazard on hard surfaces.

Health Hazards:

Product Name: SANTOPRENE™ THERMOPLASTIC VULCANIZATE - BLACK GRADES

Revision Date: 07 Jun 2021

Page 2 of 10

If dust is generated, it could scratch the eyes and cause minor irritation to the respiratory tract. When heated, the vapour/fumes given off may cause respiratory tract irritation.

Environmental Hazards:

No significant hazards.

SECTION 3 COMPOSITION / INFORMATION ON INGREDIENTS

This material is defined as a mixture.

Reportable Hazardous Substance(s) or Complex Substance(s)

Name	CAS#	Concentration*	GHS Hazard Codes
CARBON BLACK	1333-86-4	0.4 - 3.6%	None
TIN DICHLORIDE	7772-99-8	< 0.4%	H290, H302, H317, H332, H335, H314(1B), H373, H400(M factor 1), H412
zinc oxide	1314-13-2	0.1 - < 1%	H400(M factor 1), H410(M factor 1)

* All concentrations are percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

SECTION 4 FIRST AID MEASURES**INHALATION**

At ambient/normal handling temperatures, no adverse effects due to inhalation of dust are expected. In case of adverse exposure to vapours and / or aerosols formed at elevated temperatures, immediately remove the affected victim from exposure. Administer artificial respiration if breathing is stopped. Keep at rest.

SKIN CONTACT

Wash contact areas with soap and water. For hot product: Immediately immerse in or flush affected area with large amounts of cold water to dissipate heat. Cover with clean cotton sheeting or gauze and get prompt medical attention.

EYE CONTACT

Flush thoroughly with water for at least 15 minutes. Get medical assistance.

INGESTION

First aid is normally not required. Seek medical attention if discomfort occurs.

NOTE TO PHYSICIAN

None

SECTION 5 FIRE FIGHTING MEASURES**EXTINGUISHING MEDIA**

Appropriate Extinguishing Media: Use water fog, foam, dry chemical or carbon dioxide (CO₂) to extinguish flames.

Inappropriate Extinguishing Media: Straight streams of water

FIRE FIGHTING

Fire Fighting Instructions: Assure an extended cooling down period to prevent re-ignition. Evacuate area. Prevent run-off from fire control or dilution from entering streams, sewers or drinking water supply. Fire-fighters should use standard protective equipment and in enclosed spaces, self-contained breathing apparatus (SCBA). Use water spray to cool fire exposed surfaces and to protect personnel.

Unusual Fire Hazards: Explosion: Avoid generating dust; fine dust dispersed in air in sufficient concentration and in the presence of an ignition source is a potential dust explosion hazard.

Hazardous Combustion Products: Flammable hydrocarbons, Formaldehyde, Incomplete combustion products, Oxides of carbon, Smoke, Fume

FLAMMABILITY PROPERTIES

Flash Point [Method]: N/A

Flammable Limits (Approximate volume % in air): LEL: N/A UEL: N/A

Autoignition Temperature: N/A

SECTION 6	ACCIDENTAL RELEASE MEASURES
------------------	------------------------------------

NOTIFICATION PROCEDURES

In the event of a spill or accidental release, notify relevant authorities in accordance with all applicable regulations.

PROTECTIVE MEASURES

Avoid contact with spilled material. Dust Deposits should not be allowed to accumulate on surfaces, as these may form an explosive mixture if they are released into the atmosphere in sufficient concentration. Avoid dispersal of dust in the air (for example, clearing dust surfaces with compressed air). Prevent dust exposure to ignition sources. For example, use non-sparking tools and prohibit smoking, flares, sparks or flames in immediate area. See Section 5 for fire fighting information. See the Hazard Identification Section for Significant Hazards. See Section 4 for First Aid Advice. See Section 8 for advice on the minimum requirements for personal protective equipment. Additional protective measures may be necessary, depending on the specific circumstances and/or the expert judgment of the emergency responders.

SPILL MANAGEMENT

Land Spill: Spilled pellets present a slipping hazard on hard surfaces. Prevent dust cloud. Small Dry Spills: With clean shovel, place material into clean, dry container and cover loosely; move containers from spill area.

Water Spill: Stop leak if you can do so without risk. Confine the spill immediately with booms. Warn other shipping. Skim from surface

Water spill and land spill recommendations are based on the most likely spill scenario for this material; however, geographic conditions, wind, temperature, (and in the case of a water spill) wave and current direction and speed may greatly influence the appropriate action to be taken. For this reason, local experts should be consulted. Note: Local regulations may prescribe or limit action to be taken.

ENVIRONMENTAL PRECAUTIONS

Prevent entry into waterways, sewers, basements or confined areas.

SECTION 7	HANDLING AND STORAGE
------------------	-----------------------------

HANDLING

Minimize dust generation and accumulation. Routine housekeeping should be instituted to ensure that dusts do not accumulate on surfaces. Dust from material can accumulate electrostatic charges due to friction from transfer and mixing operations and cause an electrical spark (ignition source). Provide adequate precautions to ignition sources, such as electrical grounding and bonding, inert atmosphere or non-sparking tools. However, bonding and grounds may not eliminate the hazard for static accumulation. Consult local applicable standards for guidance. Refer to NFPA 654, Standard for the Prevention of Fire and Dust Explosions from the Manufacturing, Processing, and Handling of Combustible Particulate Solids and EN 61241, Electrical Apparatus for Use in the Presence of Combustible Dust for safe handling. Avoid elevated temperatures for prolonged periods of time. Eliminate all ignition sources (no smoking, flares, sparks or flames in immediate area). Avoid vapour from heated materials to prevent exposure to potentially toxic/irritating fumes. Provide adequate ventilation if fumes or vapour are generated. Prevent small spills and leakage to avoid slip hazard. Care should be taken when storing and handling this product. Apart from the specific nature of the polymer product, conditions such as humidity, sunlight and temperature have an influence on the way the product behaves during storage and handling. Special attention should be paid to avoid inappropriate stacking of palletised bags or other package units. Indeed, polymer products may be dimensionally unstable under certain conditions. Avoid conditions generating heat during transfer operations.

Loading/Unloading Temperature: [Ambient]

Transport Temperature: [Ambient]

Transport Pressure: [Ambient]

Static Accumulator: This material is not a static accumulator.

STORAGE

Store in a cool, dry place. Do not store in open or unlabelled containers.

Storage Temperature: [Ambient]

Storage Pressure: [Ambient]

Suitable Containers/Packing: Bags (20/25kg); Boxes

Suitable Materials and Coatings (Chemical Compatibility): Polyethylene; Aluminium

SECTION 8
EXPOSURE CONTROLS / PERSONAL PROTECTION
EXPOSURE LIMIT VALUES

Exposure limits/standards (Note: Exposure limits are not additive):

Substance Name	Form	Limit/Standard			Note	Source
CARBON BLACK	Inhalable fraction.	TWA	3 mg/m ³			ACGIH
TIN DICHLORIDE [as Sn]	Inhalable fraction.	TWA	2 mg/m ³			ACGIH
Zinc oxide	Respirable fraction.	STEL	10 mg/m ³			ACGIH
Zinc oxide		TWA	2 mg/m ³			ACGIH

	Respirable fraction.					
--	----------------------	--	--	--	--	--

Note: Information about recommended monitoring procedures can be obtained from the relevant agency(ies)/institute(s):

ENGINEERING CONTROLS

The level of protection and types of controls necessary will vary depending upon potential exposure conditions. Control measures to consider:

Adequate ventilation should be provided so that exposure limits are not exceeded. **SPECIAL PRECAUTIONS:** Should significant vapors/fumes be generated during thermal processing of this product, it is recommended that work stations be monitored for the presence of thermal degradation by-products which may evolve at elevated temperatures (for example, oxygenated components). Processors of this product should assure that adequate ventilation or other controls are used to control exposure. It is recommended that the current ACGIH-TLVs for thermal degradation by-products be observed. Contact your local sales representative for further information. It is recommended that all dust control equipment such as local exhaust ventilation and material transport systems involved in handling of this product are designed and maintained to minimize dust generation and accumulation. Ensure that dust-handling systems (such as exhaust ducts, dusts collectors, vessels, and processing equipment) are designed to minimize the potential for dust ignition and prevent explosion propagation. For example, use explosion relief vents, an explosion suppression system or inert equipment internals. Additional examples of proper equipment include using only appropriately classified electrical equipment and powered industrial trucks.

PERSONAL PROTECTION

Personal protective equipment selections vary based on potential exposure conditions such as applications, handling practices, concentration and ventilation. Information on the selection of protective equipment for use with this material, as provided below, is based upon intended, normal usage.

Respiratory Protection: If engineering controls do not maintain airborne contaminant concentrations at a level which is adequate to protect worker health, an approved respirator may be appropriate. Respirator selection, use, and maintenance must be in accordance with regulatory requirements, if applicable. Types of respirators to be considered for this material include:

Particulate air-purifying respirator approved for dust or oil mist is recommended. European Committee for Standardization (CEN) standards EN 136, 140 and 405 provide respirator masks and EN 149 and 143 provide filter recommendations.

For high airborne concentrations, use an approved supplied-air respirator, operated in positive pressure mode. Supplied air respirators with an escape bottle may be appropriate when oxygen levels are inadequate, gas/vapour warning properties are poor, or if air purifying filter capacity/rating may be exceeded.

Hand Protection: Any specific glove information provided is based on published literature and glove manufacturer data. Glove suitability and breakthrough time will differ depending on the specific use conditions. Contact the glove manufacturer for specific advice on glove selection and breakthrough times for your use conditions. Inspect and replace worn or damaged gloves. The types of gloves to be considered for this material include:

If product is hot, thermally protective, chemical resistant gloves are recommended. If contact with forearms is likely, wear gauntlet style gloves. CEN standards EN 420 and EN 374 provide general requirements and lists of glove types.

Eye Protection: If contact is likely, safety glasses with side shields are recommended.

Skin and Body Protection: Any specific clothing information provided is based on published literature or manufacturer data. The types of clothing to be considered for this material include:

If product is hot, thermally protective, chemical resistant apron and long sleeves are recommended.

Specific Hygiene Measures: Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants. Discard contaminated clothing and footwear that cannot be cleaned. Practise good housekeeping.

ENVIRONMENTAL CONTROLS

Comply with applicable environmental regulations limiting discharge to air, water and soil. Protect the environment by applying appropriate control measures to prevent or limit emissions.

SECTION 9

PHYSICAL AND CHEMICAL PROPERTIES

Note: Physical and chemical properties are provided for safety, health and environmental considerations only and may not fully represent product specifications. Contact the Supplier for additional information.

GENERAL INFORMATION

Physical State: Solid

Form: Pellet

Colour: Black

Odour: Rubberlike

Odour Threshold: N/D

IMPORTANT HEALTH, SAFETY, AND ENVIRONMENTAL INFORMATION

Relative Density (at 23 °C): 0.89 - 1 [In-house method]

Flammability (Solid, Gas): N/A

Flash Point [Method]: N/A

Flammable Limits (Approximate volume % in air): LEL: N/A UEL: N/A

Autoignition Temperature: N/A

Boiling Point / Range: N/A

Decomposition Temperature: N/D

Vapour Density (Air = 1): N/A

Vapour Pressure: N/A

Evaporation Rate (n-butyl acetate = 1): N/A

pH: N/A

Log Pow (n-Octanol/Water Partition Coefficient): N/A

Solubility in Water: Negligible

Viscosity: N/A

Oxidizing Properties: See Hazards Identification Section.

OTHER INFORMATION

Freezing Point: N/D

Melting Point: 175°C (347°F) - 230°C (446°F) [In-house method]

Hygroscopic: Yes

DMSO Extract (mineral oil only), IP-346: < 3 %wt

SECTION 10	STABILITY AND REACTIVITY
-------------------	---------------------------------

STABILITY: Material is stable under normal conditions.

CONDITIONS TO AVOID: Avoid elevated temperatures for prolonged periods of time. Elevated temperatures. >260 °C (500 °F)

MATERIALS TO AVOID: Acetal resins, Halogenated compounds, Phenolic resins, Strong oxidisers

HAZARDOUS DECOMPOSITION PRODUCTS: Material does not decompose at ambient temperatures.

POSSIBILITY OF HAZARDOUS REACTIONS: Hazardous polymerization will not occur.

SECTION 11	TOXICOLOGICAL INFORMATION
-------------------	----------------------------------

INFORMATION ON TOXICOLOGICAL EFFECTS

Hazard Class	Conclusion / Remarks
Inhalation	
Acute Toxicity: No end point data for material.	Minimally Toxic. Based on chemical structure (polymers).
Irritation: No end point data for material.	Elevated temperatures or mechanical action may form vapours, mist, or fumes which may be irritating to the eyes, nose, throat, or lungs.
Ingestion	
Acute Toxicity: No end point data for material.	Minimally Toxic. Based on chemical structure (polymers).
Skin	
Acute Toxicity: No end point data for material.	Minimally Toxic. Based on chemical structure (polymers).
Skin Corrosion/Irritation: No end point data for material.	Negligible irritation to skin at ambient temperatures. Based on chemical structure (polymers).
Eye	
Serious Eye Damage/Irritation: No end point data for material.	May cause mild, short-lasting discomfort to eyes. Based on chemical structure (polymers).
Sensitisation	
Respiratory Sensitization: No end point data for material.	Not expected to be a respiratory sensitizer.
Skin Sensitization: No end point data for material.	Not expected to be a skin sensitizer. Based on chemical structure (polymers).
Aspiration: No end point data for material.	Not expected to be an aspiration hazard. Based on physico-chemical properties of the material.
Germ Cell Mutagenicity: No end point data for material.	Not expected to be a germ cell mutagen. Based on chemical structure (polymers).
Carcinogenicity: No end point data for material.	Not expected to cause cancer. Based on chemical structure (polymers).
Reproductive Toxicity: No end point data for material.	Not expected to be a reproductive toxicant. Based on chemical structure (polymers).
Lactation: No end point data for material.	Not expected to cause harm to breast-fed children.
Specific Target Organ Toxicity (STOT)	
Single Exposure: No end point data for	Not expected to cause organ damage from a single exposure.

Product Name: SANTOPRENE™ THERMOPLASTIC VULCANIZATE - BLACK GRADES

Revision Date: 07 Jun 2021

Page 8 of 10

material.	
Repeated Exposure: No end point data for material.	Not expected to cause organ damage from prolonged or repeated exposure. Based on chemical structure (polymers).

OTHER INFORMATION**For the product itself:**

Dust may be irritating to the eyes and respiratory tract.

Component concentrations in this formulation would not be expected to cause skin sensitization, based on tests of the components, this formulation, or similar formulations.

Contains:

Carbon black: Certain carbon blacks have proved carcinogenic in animal studies. Inhalation animal studies of high concentrations resulted in chronic inflammation, lung fibrosis and lung tumours. Epidemiology studies of workers include findings of bronchitis, pneumonia, emphysema and excess cancer. Substances bound in a polymer or other matrix should present little or no hazard. Additives that are encapsulated in the polymer. Under the normal conditions for processing and use of this polymer the encapsulated additives are not expected to pose any health hazard. However, grinding of the polymer is not recommended without the use of appropriate measures to control exposure (see Section 8 - Engineering Controls).

SECTION 12 ECOLOGICAL INFORMATION

The information given is based on data for the material, components of the material, or for similar materials, through the application of bridging principals.

ECOTOXICITY

Material -- Not expected to be harmful to aquatic organisms.

Material -- Not expected to demonstrate chronic toxicity to aquatic organisms

MOBILITY

Material -- Low solubility and floats and is expected to migrate from water to the land. Expected to partition to sediment and wastewater solids.

PERSISTENCE AND DEGRADABILITY**Biodegradation:**

Material -- Expected to be persistent.

NOTE: Material contains additives that are encapsulated in the polymer. Under normal conditions of processing and use the encapsulated additives are expected to have very limited solubility in water and, as a result, are not expected to cause adverse effects in the aquatic environment.

SECTION 13 DISPOSAL CONSIDERATIONS

Disposal recommendations based on material as supplied. Disposal must be in accordance with current applicable laws and regulations, and material characteristics at time of disposal.

DISPOSAL RECOMMENDATIONS

Suitable routes of disposal are supervised incineration, preferentially with energy recovery, or appropriate recycling methods in accordance with applicable regulations and material characteristics at the time of disposal.

Product Name: SANTOPRENE™ THERMOPLASTIC VULCANIZATE - BLACK GRADES

Revision Date: 07 Jun 2021

Page 9 of 10

SECTION 14	TRANSPORT INFORMATION
-------------------	------------------------------

LAND (ADR/RID): Not Regulated for Land Transport

SEA (IMDG): Not Regulated for Sea Transport according to IMDG-Code

Marine Pollutant: No

AIR (IATA): Not Regulated for Air Transport

SECTION 15	REGULATORY INFORMATION
-------------------	-------------------------------

This material is not considered hazardous according to the Classification of Chemicals based on Globally Harmonized System of Classification and Labelling of Chemicals (GHS).

REGULATORY STATUS AND APPLICABLE LAWS AND REGULATIONS

Listed or exempt from listing/notification on the following chemical inventories : Please contact Customer Service (see Section 1 for supplier contact information).

SECTION 16	OTHER INFORMATION
-------------------	--------------------------

N/D = Not determined, N/A = Not applicable

KEY TO THE H-CODES CONTAINED IN SECTION 3 OF THIS DOCUMENT (for information only):

H290: May be corrosive to metals; Corrosive to Metals

H302: Harmful if swallowed; Acute Tox Oral, Cat 4

H314(1B): Causes severe skin burns and eye damage; Skin Corr/Irritation, Cat 1B

H317: May cause allergic skin reaction; Skin Sensitisation, Cat 1

H332: Harmful if inhaled; Acute Tox Inh, Cat 4

H335: May cause respiratory irritation; Target Organ Single, Resp Irr

H373: May cause damage to organs through prolonged or repeated exposure; Target Organ, Repeated, Cat 2

H400: Very toxic to aquatic life; Acute Env Tox, Cat 1

H410: Very toxic to aquatic life with long lasting effects; Chronic Env Tox, Cat 1

H412: Harmful to aquatic life with long lasting effects; Chronic Env Tox, Cat 3

THIS SAFETY DATA SHEET CONTAINS THE FOLLOWING REVISIONS:

Section 16: Materials Covered information was modified.

THIS SDS COVERS THE FOLLOWING MATERIALS: SANTOPRENE™ TPV | 101-55 | 101-60W261 | 101-64 | 101-73 | 101-80 | 101-87 | 103-40 | 103-50 | 111-35 | 111-45 | 121-40B265 | 121-50E500 | 121-50M100 | 121-55W241 | 121-58W175 | 121-60E400 | 121-60M200 | 121-62M100 | 121-65B200 | 121-65M300 | 121-67W175 | 121-70B230 | 121-70B260 | 121-70B265 | 121-70E400 | 121-73W175 | 121-75M100 | 121-75M200 | 121-79W233 | 121-80 | 121-80B200 | 121-80B230 | 121-80B260 | 121-80B265 | 121-80M300 | 121-80W175 | 121-85M100 | 121-87 | 123-40 | 123-50W175 | 171-64 | 171-73 | 181-55MED | 591-55W175 | 591-56W175 | 591-65W175 | 591-73W175 | 9101-80E | 9101-80E100 | TPV 345B

Product Name: SANTOPRENE™ THERMOPLASTIC VULCANIZATE - BLACK GRADES

Revision Date: 07 Jun 2021

Page 10 of 10

The information and recommendations contained herein are, to the best of Celanese's knowledge and belief, accurate and reliable as of the date issued. You can contact Celanese to insure that this document is the most current available from Celanese. The information and recommendations are offered for the user's consideration and examination. It is the user's responsibility to satisfy itself that the product is suitable for the intended use. If buyer repackages this product, it is the user's responsibility to insure proper health, safety and other necessary information is included with and/or on the container. Appropriate warnings and safe-handling procedures should be provided to handlers and users. Alteration of this document is strictly prohibited. Except to the extent required by law, re-publication or retransmission of this document, in whole or in part, is not permitted.

Internal Use Only

MHC: 0, 0, 0, 0, 0, 0

DGN: 4409020GAA (1015432)
