



LED T8 Ballast Compatibility Chart

Ballast Brand*	Part Number	# Of Lamps	Start Method	1 Lamp		2 Lamps		3 Lamps		4 Lamps		Ballast Type	Factor Value
				120V	277V	120V	277V	120V	277V	120V	277V		
Act	ACT 2P32ISUNVE	2	IS	✓	✓	✓	✓	-	-	-	-	N	0.89
Antron Electronics	A32T8MICLO	2	IS	✓	✓	✓	✓	-	-	-	-	L	0.78
Arcata	ACT 3P32ISUNVLE	3	IS	-	-	✓	✓	✓	✓	-	-	L	0.78
Cooper Lighting	CL-432ISUNV-R1-B	4	IS	-	-	-	-	✓	✓	✓	✓	H	1.18
Eiko	PM-2X32T8-UNV-IS-L	2	IS	✓	✓	✓	✓	-	-	-	-	L	0.77
Eiko	PM-2X32T8-UNV-IS	2	IS	✓	✓	✓	✓	-	-	-	-	N	0.87
Espen	VE232MVHIPE	2	IS	✓	✓	✓	✓	-	-	-	-	N	0.89
Espen	VE232MVHIPE	2	IS	✓	✓	✓	✓	-	-	-	-	L	0.77
General Electric	GE-232-MV-N	2	IS	✓	✓	✓	✓	-	-	-	-	N	0.88
General Electric	GE232MAX-N/ULTRA	2	IS	✓	✓	✓	✓	-	-	-	-	N	0.88
General Electric	GE432MAX-H/ULTRA	4	IS	-	-	-	-	✓	✓	✓	✓	H	1.18
General Electric	GE432MAX-L/ULTRA	4	IS	-	-	-	-	✓	✓	✓	✓	L	0.78
General Electric	GE432MAX-G-N	4	IS	-	-	-	-	✓	✓	✓	✓	N	0.88
General Electric	GE132MAXP-N/ULTRA	1	IS	✓	✓	-	-	-	-	-	-	N	0.88
General Electric	GE232MV-N-DIY	2	IS	✓	✓	✓	✓	-	-	-	-	N	0.88
General Electric	GE332MV-N	3	IS	-	-	✓	P	✓	P	-	-	N	0.87
General Electric	GE332MAX-N/ULTRA	3	IS	-	-	✓	P	✓	✓	-	-	N	0.88
General Electric	GE332MAX-L/ULTRA	3	IS	-	-	✓	P	✓	P	-	-	L	0.78
General Electric	GE332MAX-G-N	3	IS	-	-	✓	P	✓	✓	-	-	N	0.87
General Electric	GE432-120-RES	4	IS	-	-	-	-	✓	NA	✓	NA	N	0.83
General Electric	GE432MAX-N/ULTRA	4	IS	-	-	-	-	✓	✓	✓	✓	N	0.88
General Electric	GE332MAXP-L/ULTRA	3	IS	-	-	✓	✓	✓	✓	-	-	L	0.77
General Electric	GE232MAX-G-N	2	IS	✓	✓	✓	✓	-	-	-	-	N	0.88
General Electric	GE-232-MV-PS-N	2	PS	✓	✓	✓	✓	-	-	-	-	N	0.88
General Electric	GE132MVPSN-V03 **	1	DPS	✓	✓	-	-	-	-	-	-	N	0.88
General Electric	GE432MAX347-N	4	-	-	-	-	-	✓ _{347V}	-	✓ _{347V}	-	N	0.94
Halco	EP232IS/MV/HE	2	IS	✓	✓	✓	✓	-	-	-	-	N	0.88
Halco	EP332IS/MV/HE	3	IS	-	-	✓	✓	✓	✓	-	-	N	0.87
Halco	EP432IS/L/MV/HE	4	IS	-	-	-	-	✓	✓	✓	✓	L	0.78
Halco	EP232IS/L/MV/HE	2	IS	✓	✓	✓	✓	-	-	-	-	L	0.78
Halco	EP332IS/L/MV/HE	3	IS	-	-	✓	✓	✓	✓	-	-	L	0.78
Halco	EP432IS/120/MC	4	IS	-	-	-	-	✓	✓	✓	✓	N	0.88
Hatch	HL232BIS/UV/HE/W	2	IS	✓	✓	✓	✓	-	-	-	-	N	0.9
Hatch	HL432BIS/UV/HE/W	4	IS	-	-	-	-	✓	P	✓	✓	N	0.9
Howard Industries	EP3/32IS/MV/SC/HE	3	IS	-	-	✓	✓	✓	✓	-	-	N	0.87
Howard Industries	EPL4/32IS/MV/MC/HE	4	IS	-	-	-	-	✓	✓	✓	✓	L	0.77
Howard Industries	E2/32IS-120MC	2	IS	P,T	NA	P,T	NA	-	-	-	-	N	0.85
Howard Industries	EPL2/32IS/MV/MC/HE	2	IS	✓	P,T	✓	P	-	-	-	-	L	0.78
Howard Industries	EPL3/32IS/MV/SC/HE	3	IS	-	-	✓	✓	✓	✓	-	-	L	0.78
Howard Industries	EP4/32IS/MV/MC/HE	4	IS	-	-	-	-	✓	✓	✓	✓	N	0.88
Howard Industries	EP2/32IS/MV/MC/HE	2	IS	✓	✓	✓	✓	-	-	-	-	N	0.89
Howard Industries	EP3/32IS/MV/MC/HE	3	IS	-	-	✓	✓	✓	✓	-	-	N	0.88
Howard Industries	EPH3/32IS/MV/MC/HE	3	IS	-	-	✓	P	✓	P	-	-	N	0.91
Howard Industries	EP4/32PPRS/MV/SC/HE	4	PRS	-	-	-	-	✓	✓	✓	✓	N	-
Keystone	KTEB-432RIS-1-TP-SL	4	IS	-	-	-	-	✓	NA	✓	NA	N	0.8
Keystone	KTEB-332-UV-IS-N-P	3	IS	-	-	✓	✓	✓	✓	-	-	N	0.87
Keystone	KTEB-232LBF-1-TP-PIC-EV	2	IS	✓	NA	✓	NA	-	-	-	-	N	0.88
Keystone	KTEB-432-UV-PS-N-P	4	PS	-	-	-	-	✓	✓	✓	✓	N	-
Keystone	KTEB-232-UV-PS-L-P	2	PS	✓	✓	✓	✓	-	-	-	-	L	-
Keystone	KTLD-2T8LED-UV-IS-VDIM **	2	DPS	✓	✓	✓	✓	-	-	-	-	N	1.18
Lighting Products Limited	EB-332EBF-UV-TP-HE	3	IS	-	-	✓	✓	✓	✓	-	-	L	0.78
Maxlite	SKEU322HEL/SC	2	IS	✓	✓	✓	✓	-	-	-	-	L	0.77
Maxlite	SKEU324HE/SC	4	IS	-	-	-	-	✓	✓	✓	✓	N	0.88
Maxlite	SKEU323L/SC	3	IS	-	-	✓	✓	✓	✓	-	-	L	0.78
Maxlite	MLEU322HEL/SC	2	IS	✓	✓	✓	✓	-	-	-	-	N	0.83
Osram	QHE 2x32T8/347 PSN-SC	2	-	✓ _{347V}	-	✓ _{347V}	-	-	-	-	-	N	0.88
Osram Sylvania	QTP 2X32T8/UNV ISN-SC	2	IS	✓	✓	✓	✓	-	-	-	-	N	0.88
Osram Sylvania	QHE 2X32T8/UNV ISN-SC	2	IS	✓	✓	✓	✓	-	-	-	-	N	0.88
Osram Sylvania	QHE 2X32T8/UNV ISL-SC	2	IS	✓	✓	✓	✓	-	-	-	-	L	0.78
Osram Sylvania	QHE 4X32T8/UNV ISN-SC	4	IS	-	-	-	-	✓	✓	✓	✓	N	0.88
Osram Sylvania	QHE 4X32T8/UNV ISL-SC	4	IS	-	-	-	-	✓	✓	✓	✓	L	0.78
Osram Sylvania	QHE 1X32T8/UNV ISN-SC	1	IS	✓	✓	-	-	-	-	-	-	N	0.88
Osram Sylvania	QHE 1X32T8/UNV ISL-SC	1	IS	✓	✓	-	-	-	-	-	-	L	0.78
Osram Sylvania	QTP 3X32T8/UNV ISN-SC	3	IS	-	-	✓	✓	✓	✓	-	-	N	0.88
Osram Sylvania	QHE 3X32T8/UNV ISN-SC	4	IS	-	-	-	-	✓	✓	✓	✓	N	0.88
Osram Sylvania	QHE 3X32T8/UNV ISL-SC	3	IS	-	-	✓	✓	✓	✓	-	-	L	0.78
Osram Sylvania	QTP2x32T8/277 ISN-D	2	IS	NA	✓	NA	✓	-	-	-	-	L	0.78
Osram Sylvania	QTP 2X32T8/UNV ISL-SC	2	IS	✓	✓	✓	✓	-	-	-	-	L	0.78
Osram Sylvania	QHE 1X32T8/UNV ISH-SC	1	IS	✓	✓	-	-	-	-	-	-	L	0.77
Osram Sylvania	QHE 2X32T8/UNV PSH-HT	2	PRS	NA	NA	✓	✓	-	-	-	-	H	1.18
Osram Sylvania	QHE 2X32T8/UNV PSN-MC	2	PRS	✓	✓	✓	✓	-	-	-	-	N	0.88
Osram Sylvania	QHE 4X32T8/UNV PSN-SC	4	PRS	-	-	-	-	✓	✓	✓	✓	N	0.88
Osram Sylvania	QT 2x32/347 ISH-SC	2	-	-	-	✓ _{347V}	-	-	-	-	-	H	1.2



LED T8 Ballast Compatibility Chart

Ballast Brand*	Part Number	# Of Lamps	Start Method	1 Lamp		2 Lamps		3 Lamps		4 Lamps		Ballast Type	Factor Value
				120V	277V	120V	277V	120V	277V	120V	277V		
Pacific Fluorescent	EB-232IS-120-RES	2	IS	✓	NA	✓	NA	-	-	-	-	N	-
Philips-Advance	IOPA-2P32-N	2	IS	✓	✓	✓	✓	-	-	-	-	N	0.89
Philips-Advance	IOP-2P32-LW-N	2	IS	✓	✓	✓	✓	-	-	-	-	L	0.77
Philips-Advance	IOP-4P32-N	4	IS	-	-	-	-	✓	✓	✓	✓	N	0.87
Philips-Advance	IOP-4P32-LW-N	4	IS	-	-	-	-	✓	✓	✓	✓	L	0.77
Philips-Advance	IOP-1P32-N	1	IS	✓	P	-	-	-	-	-	-	N	0.89
Philips-Advance	REB-4P32-SC	4	IS	-	-	-	-	✓	NA	✓	NA	N	0.81
Philips-Advance	VEL-2P32-SC	2	IS	NA	P,T	NA	✓	-	-	-	-	N	0.88
Philips-Advance	IOPA-4P32-SC	4	IS	-	-	-	-	✓	✓	✓	✓	N	0.92
Philips-Advance	ICN-132-MC	1	IS	✓	P	-	-	-	-	-	-	N	0.88
Philips-Advance	ICN-3P32-SC	3	IS	-	-	✓	✓	✓	✓	-	-	N	0.89
Philips-Advance	VEL-3P32-SC	3	IS	-	-	✓	✓	✓	✓	-	-	N	0.88
Philips-Advance	IOPA-2P32-LW-N	2	IS	✓	✓	✓	✓	-	-	-	-	L	-
Philips-Advance	IOP-1P32-LW-N	1	IS	✓	P	-	-	-	-	-	-	L	0.77
Philips-Advance	IOP-1P32-SC	1	IS	✓	✓	-	-	-	-	-	-	N	0.87
Philips-Advance	IOP-1P32-LW-SC	1	IS	✓	✓	-	-	-	-	-	-	L	0.77
Philips-Advance	IOP-3PSP32-SC	3	PS	-	-	NA	NA	✓	✓	-	-	N	0.88
Philips-Advance	IOP-4PSP32-SC	4	PS	-	-	-	-	✓	✓	✓	✓	N	0.89
Philips-Advance	IOP-4PSP32-LW-SC	4	PS	-	-	-	-	✓	✓	✓	✓	L	0.69
Plusrite	BAF232IS/MV	2	IS	✓	✓	✓	✓	-	-	-	-	N	0.89
Plusrite	BAF332IS/MV	3	IS	-	-	✓	✓	✓	✓	-	-	N	0.88
Plusrite	BAF332IS/MV/L	3	IS	-	-	✓	✓	✓	✓	-	-	L	0.78
Plusrite	BAF432IS/MV	4	IS	-	-	-	-	✓	✓	✓	✓	N	0.88
Plusrite	BAF432IS/MV/L	4	IS	-	-	-	-	✓	✓	✓	✓	L	0.78
Prolume	EP232IS/L/MV/SL	2	IS	✓	✓	✓	✓	-	-	-	-	L	0.78
Prolume	E432IS/120/R/SL	4	IS	-	-	-	-	-	NA	✓	NA	N	0.87
Sola	E-758-U-232-MC	2	IS	✓	P	✓	✓	-	-	-	-	N	0.88
Sunpark	120-1/32IS HPF	1	IS	P,T	NA	-	-	-	-	-	-	N	0.88
Sunpark	U-2/32ISE-LBF	2	IS	✓	✓	✓	✓	-	-	-	-	L	0.78
Sunpark	U-3/32ISE	3	IS	-	-	✓	✓	✓	✓	-	-	N	0.88
Sunpark	120-3/32IS MPF	3	IS	-	-	✓	NA	✓	NA	-	-	N	0.88
Sunpark	U-4/32IS HP,F	4	IS	-	-	-	-	✓	✓	✓	✓	N	0.88
Sunpark	U-4/32ISE-LBF	4	IS	-	-	-	-	✓	✓	✓	✓	L	0.77
Sunpark	U-1/32PSE	1	PS	✓	✓	-	-	-	-	-	-	N	0.88
Sunpark	SL15T	2	RS	NA	NA	P,T	NA	-	-	-	-	N	0.88
Sunpark	LC 12013T	1	PS	P,T	NA	-	-	-	-	-	-	-	-
Superior Life	70210	2	PS	✓	✓	✓	✓	-	-	-	-	N	0.88
Superior Life	70211	4	PS	-	-	-	-	✓	✓	✓	✓	N	0.87
Sylvania	QT 3x32/277 IS	3	IS	-	-	✓	✓	✓	✓	-	-	N	0.9
Sylvania	QT 4X32/347LP	4	-	-	-	-	-	T, 347V	-	T, 347V	-	-	-
TCP	E3P32ISUNVE	3	IS	-	-	✓	✓	✓	✓	-	-	N	0.88
TCP	E4P32ISUNVE	4	IS	-	-	-	-	✓	✓	✓	✓	N	0.88
Ultrasave	UT232347	2	-	✓347V	-	✓347V	-	-	-	-	-	-	-
Universal Lighting Technologies	B232IUNVHP-N	2	IS	✓	✓	✓	✓	-	-	-	-	N	0.88
Universal Lighting Technologies	B232IUNVEL-A	2	IS	✓	✓	✓	✓	-	-	-	-	L	0.77
Universal Lighting Technologies	B233IUNVHE-A	2	IS	✓	✓	✓	✓	-	-	-	-	N	0.87
Universal Lighting Technologies	B432IUNVHE L-A	4	IS	-	-	-	-	✓	✓	✓	✓	L	0.77
Universal Lighting Technologies	B332IUNVHP-A	3	IS	-	-	✓	✓	✓	✓	-	-	N	0.88
Universal Lighting Technologies	B432IUNVHP-A	4	IS	-	-	-	-	✓	✓	✓	✓	N	0.88
Universal Lighting Technologies	B232I120RES-A	2	IS	✓	NA	✓	NA	-	-	-	-	N	0.88
Universal Lighting Technologies	B132IUNVHP-N	1	IS	✓	✓	-	-	-	-	-	-	N	0.88
Universal Lighting Technologies	B232IUNVHP-B	2	IS	✓	✓	✓	✓	-	-	-	-	N	0.88
Universal Lighting Technologies	B432IUNVHE-A	4	IS	-	-	-	-	✓	✓	✓	✓	N	0.87
Universal Lighting Technologies	B432IUNVHEH-E	4	IS	-	-	-	-	✓	✓	✓	✓	H	1.15
Universal Lighting Technologies	B232I277RH-A	4	IS	-	-	-	-	NA	P,T	NA	✓	H	1.09
Universal Lighting Technologies	B132IUNVEL-A	1	IS	✓	✓	-	-	-	-	-	-	L	0.77
Universal Lighting Technologies	B432PUNVHE-A	4	PS	-	-	-	-	✓	✓	✓	✓	N	0.87
Universal Lighting Technologies	B232PUNVHE-B	2	PS	✓	✓	✓	✓	-	-	-	-	N	0.88
Universal Lighting Technologies	B332PUNVHE-A	3	PS	-	-	✓	✓	✓	✓	-	-	N	0.88
Universal Lighting Technologies	B232SR277S30	2	RS	NA	NA	NA	✓	-	-	-	-	-	-
Universal Lighting Technologies	B432I347HE-A	4	-	-	-	-	-	✓347V	-	✓347V	-	N	0.88
Universal Lighting Technologies	B432I347HP	4	-	-	-	-	-	✓347V	-	✓347V	-	-	-



LED T8 Ballast Compatibility Chart

Ballast Brand*	Part Number	# Of Lamps	Start Method	1 Lamp		2 Lamps		3 Lamps		4 Lamps		Ballast Type	Factor Value
				120V	277V	120V	277V	120V	277V	120V	277V		
Watran	DB-232N-MV-TP-HE	2	IS	✓	✓	✓	✓	-	-	-	-	N	0.87
Watran	DB-332N-MV-TP-HE	3	IS	-	-	✓	✓	✓	✓	-	-	N	0.87
Watran	DB-432N-MV-TP-HE	4	IS	-	-	-	-	✓	✓	✓	✓	N	0.87
Watran	DB-432L-MV-TP-HE	4	IS	-	-	-	-	✓	✓	✓	✓	L	0.77
Watran	DB-232N-MV-TP-HE	2	IS	✓	✓	✓	✓	-	-	-	-	N	0.87
Work Horse	WHSG3-UNV-T8-IS	3	IS	-	-	✓	✓	✓	✓	-	-	N	0.99
Work Horse	WHSG4-UNV-T8-IS	4	IS	-	-	-	-	✓	✓	✓	✓	N	0.96

Applies to the following Satco products:

S11740, S11741, S11742, S11743

- ** Dimmable ballast
- P PF <0.85
- T THD >30%
- NC Not compatible
- NA Not applicable

- Ballast Factors:**
- L - Low
 - N - Normal
 - H - High

This list is current as of August, 2021. We are continuously testing for compatible ballasts. Please check back for updates.

* All trademarks are the property of their respective owners

110 Heartland Blvd.
Brentwood, NY 11717
PH 631-243-2022
FX 631-243-2027

Distribution Centers
New York, Florida,
Texas, Washington,
California, Puerto Rico

National Toll-Free
800-43-SATCO
(800-437-2826)
www.satco.com

Copyright© 2021
Satco Products, Inc.
All Rights Reserved.
Rev: August 12, 2021