

## Our most versatile band sealer: suitable for nearly all bag sizes

HL-M1120LD is suitable for sealing all types of thermoplastic materials and bags. The vertical configuration is ideal for sealing stand up pouches and liquid-type products. This sealer can be used in a variety of fields such as the food, medical, and cosmetic industries. HL-M1120LD is equipped with an adjustable sealing head and conveyor suitable providing a wide range of bag heights. HL-M1120LD utilizes dry ink coding to print numbers or letters on the seal line.



### Standard Features:

- Durable stainless steel construction
- Easy to operate – minimal operator training
- Fast warm up time
- Ideal for medium to heavy duty applications
- Solid state digital temperature controller to maintain seal bars at proper temperature for consistent seal quality
- Motorized rubber conveyor for speed control
- Knurled pressure rolls with variable pressure adjustment
- Sealing method – constant/direct heat accompanied with a pair each of cooling and heating blocks
- Fully adjustable conveyor
- Unit feeds right to left
- Spare parts includes: PC Board, PTFE belt, wheel belt, fuse, motor brush, heating element, silica gel ring, silicone pin, and type set

### Options:

- Dry ink coding – font size – 10.5PT (standard is 18PT)
- Left to right feed
- Digital counter to keep track of sealed packages
- 220V Voltage

SPECIFICATIONS			
UNIQUE FEATURES	ADJUSTABLE SEALING HEAD	SINGLE CONVEYOR LOAD	11-LBS
FEEDING	RIGHT TO LEFT	MAX. CONVEYOR LOAD	33-LBS
POWER	110V / 60Hz	BAG SIZE (FILLED)	3.9" – 27.0"
MOTOR POWER	230W (1/3 HP)	DISTANCE FROM CONVEYOR TO FLOOR	19.6" – 41.3"
SEALING SPEED	0-394 INCHES / MIN	CHARACTER SIZE	18PT (3X5X7MM) – 2 LINES 10.5PT (2X3X7MM) – 3 LINES OPTIONAL 20 CHARACTERS/LINE
SEAL WIDTH	8MM	PRINTING HEATING POWER	40 X 2
TEMPERATURE RANGE	0-300°C	DIMENSIONS	57" X 27" X 58"
SEALING POWER	300 X 2	SHIPPING DIMENSIONS	62" X 29" X 69"
CONVEYOR SIZE	55" X 10"	WEIGHT (LBS)	NET: 344   GROSS: 404

Our most versatile band sealer: suitable for nearly all bag sizes

