

TOP & BOTTOM DRIVE BELT ADJUSTABLE VALUE CARTON SEALER

Model: CS-6050

Value unit – excellent for taller cartons



The **CS-6050 Semi-Automatic Uniform Carton Sealer with Easy Manual Carton Size Adjustment** has a 4-belt design (2 top and 2 bottom). The machine comes complete with infeed / exit conveyors, casters, power cord and plug.

The operator simply folds the top flaps of the corrugated carton and feeds it into the machine. The CS-6050 applies a single tape to both the top and bottom of the case simultaneously. The CS-6050 can be easily adjusted in only seconds to process a different size carton. Excellent for taller, heavier boxes.

Standard Features:

- Side Pressure Rollers to Close Box Top
- 2 Top & 2 Bottom Drive Belts for Positive Feed
- Infeed / Exit Conveyors
- Casters

Optional Features:

- 3" (72mm) Tape Heads
- Stainless Steel Frame

SPECIFICATIONS	
CARTON SIZE	
LENGTH:	6" TO INFINITE
WIDTH:	6.3" MIN TO 19.7" MAX
HEIGHT:	5.9" MIN TO 23.6" MAX
MACHINE SIZE:	69"L X 32"W X (38"-63")H
MACHINE SPEED:	65.6FT./MIN UP TO 15 CARTONS PER MINUTE PRODUCTION RATE DEPENDS ON CARTON SIZE AND OPERATOR DEXTERITY
ELECTRICAL:	110V, 1 PHASE, 10 AMP
WEIGHT:	330-LBS (SHIPPING WEIGHT: 385-LBS)
MAX BOX WEIGHT:	55-LBS
TAPE HEAD SPECS:	2" (48MM) WIDE – 1,000 YARD OR 1,500 YARD ROLLS

TOP & BOTTOM DRIVE BELT ADJUSTABLE CARTON SEALER

Model: CS-6050

