

## Seal & print w/ a wider 15mm seal width

FRM-1010 band sealer presents a combination of elegance and functionality. Providing a wider seal (15mm), the FRM-1010 provides the most professional and efficient band sealer on the market. The FRM-1010 band sealer is a heavier duty model compared to our CBS and HLM band sealer lines and also provides better sealing quality. The FRM-1010 is suitable for sealing all types of thermoplastic materials and bags. This sealer can be used in a variety of fields such as the food, medical, and cosmetic industries. Can seal 20-30 6" poly bags in one minute.



### Standard Features:

- Durable stainless steel construction
- Easy to operate – minimal operator training
- Fast warm up time
- Seal width: 15mm (Optional: 20mm)
- Solid state digital temperature controller to maintain seal bars at proper temperature for consistent seal quality
- Motorized rubber conveyor for speed control
- Knurled pressure rolls with variable pressure adjustment
- Sealing method – constant/direct heat accompanied with a pair each of cooling and heating blocks
- Unit feeds right to left
- Spare parts includes: PC Board, PTFE belt, wheel belt, fuse, motor brush, heating element, silica gel ring, silicone pin, and type set

### Options:

- Stainless steel stand for horizontal models
- Dry ink coding – font size – 10.5PT (standard is 18PT)
- 20mm seal width
- Left to right feed
- Digital counter to keep track of sealed packages
- 220V Voltage


SPECIFICATIONS	
POWER	110V / 60Hz
MOTOR POWER	50W
SEALING SPEED	0-472 INCHES/MINUTE
SEAL WIDTH	15 MM (OPTIONAL: 20MM)
SEALING POWER	300 X 2
TEMPERATURE RANGE	0-300°C
CONVEYOR SIZE	42" X 8"
SINGLE CONVEYOR LOAD	2.2LBS
MAX CONVEYOR LOAD	6.6LBS
BAG SIZE (FILLED)- VERTICAL UNIT	MINIMUM - 7 7/8" / MAXIMUM – 12"
CHARACTER SIZE	18PT (3X5X7MM) – 2 LINES 10.5PT (2X3X7MM) – 3 LINES - OPTIONAL 20 CHARACTERS/LINE
PRINTING HEATING POWER	40 X 2
DIMENSIONS	H: 42" X 18" X 20" / V: 42" X 18" X 25"



# IMPRESSÉ BAND SEALER DRY INK CODING – WIDER SEAL WIDTH

Model: FRM-1010

FRM-1010II - Vertical



FRM-1010I - Horizontal



Control Panel

