

Heavy duty system capable of 10-15pkgs/min



Shown with optional 180° degree curved conveyor

Our SS-1622MK-Combo L-bar sealer and shrink tunnel is the first fully adjustable combination L-bar sealer with attached shrink tunnel including the latest “Micro-Knife” technology. No more seal wires to replace! The L-bar sealer is mounted on linear bearings which can easily move forward or backward to center the product into the tunnel. The discharge conveyor also adjusts up or down. The shrink tunnel (18”W x 8”H x 28”L) features a fully re-circulating chamber with live roller rod conveyor. A convenience crank handle allows the operator to move the tunnel up or down to match sealer conveyor height. Unibody frame makes this unit easy to move around. Includes one 8ft. power cord. Capable of 10-15 packages/minutes.

Standard Features of L-Bar Sealer:

- Micro-Knife band ribbon
- Power belted discharge conveyor
- Dual magnet clamping
- Pin perforated hole punch
- Variable dwell/seal time
- Variable conveyor time
- Stainless steel compensators
- Seal size: 16”W x 22”L
- Seal head return cylinder
- Stainless steel film clamps
- Locking casters
- Linear bearings allow movement forward or backward
- Easy load film cradle with brake
- Option: Air-operated unit with dual push button air operation seal head (Model: SS-1622MKA-Combo)
- Recommended film: POF (PVC not recommended)


Standard Features of Shrink Tunnel:

- Fully re-circulating air chamber
- Live or dead roller rod conveyor
- Digital temperature control
- Adjustable air velocity control
- State of the art AC variable speed drive
- Chromed conveyor rollers and shafts (no rust)
- Automatic tunnel cool down with shut off
- Sealed bearings on drive and idler shafts
- Chamber size: 18”W x 8”H x 28”L
- Quietest tunnel on the market
- Heats up to 300°F in less than 10 minutes
- Thermal overload protection on all motors
- Anti-jam safety feature on conveyor
- Easily adjustable crank handle allows for tunnel height adjustment

SPECIFICATIONS	SS-1622MK-Combo	SS-1622MKA-Combo
POWER	220V / 1PHASE / 45AMPS	220V / 1PHASE / 45AMPS
WEIGHT	950-LBS	950-LBS
DIMENSIONS	103”L X 32”W X 62”H	103”L X 32”W X 62”H
SEAL SIZE	16”W X 22”L	16”W X 22”L
TUNNEL OPENING	28”L X 18”W X 8”H	28”L X 18”W X 8”H
MAX. FILM WIDTH	20”	20”
AIR REQUIREMENTS	N/A	4 CFM @ 80 PSI

COMBO L-SEALER AND SHRINK TUNNEL

Model: SS-1622MK-Combo



8820 Baird Avenue • Northridge, CA 91324 • T: 818-718-8818 • F: 818-718-8857

✉ contact@sealersales.com

🌐 www.sealersales.com