



Ideal for sealing thicker materials

- Single or double sealing switch selector
- Plug-in electronic timer for variable control
- All metal construction
- Heavy duty
- No warm-up time
- Sits on rectangular base for stability

More Details:

W-Series double impulse foot sealers are ideal for sealing thicker materials. Available in 12", 18", and 24" lengths with a 5mm seal width, the W-Series foot sealers are capable of sealing materials up to 20mil total thickness. Equipped with a single and double sealing selector switch provides this sealer with the flexibility of sealing various types materials. Depending on the thickness of the material, the user has the choice of one or two elements for top and bottom sealing.

Sealers are equipped with a steel frame for added safety and stability. A height adjustable working plate is also included. The manufacturer's replacement kit includes two elements. A taller stand and tension rod is also available, adding 10" in height. Working height is 30 ¼" but the extended standing tube provides a 42 ½" working height.

Easy to Operate: Set the timer. Insert the bag between the two sealing bars and press down on the foot board. Hold down the foot board for an additional 2-3 seconds after the timer light goes off to set the seal.

Features:

	W-300T	W-450T	W-600T
Power Supply	110V / 50Hz	110V / 50Hz	110V / 50Hz
Watts	1000W	1900W	2800W
Seal Length	11.8"	17.6"	23.4"
Seal Width	5mm	5mm	5mm
Standing Height	33 ½"	33 ½"	33 ½"
Tray Dimensions	12" x 6"	12" x 6"	12" x 6"
Tray Adjustment Height	Up to 6.5"	Up to 6.5"	Up to 6.5"
Throat Depth	1 ½"	1 ½"	1 ½"
Dimensions	13" x 14" 34"	21" x 14" x 34"	26 ½" x 14" 34"
Weight (lbs)	34 / 28	44 / 28	47 / 28