



## ArtiLink300

### Practical Diagnostics

The ArtiLink 300 is an easy-to-use diagnostic tool that offers more advanced features for essential automobile coding work. The ArtiLink 300 builds off the ArtiLink 200 by introducing O2 Sensor Tests and a DTC Lookup Library, expanding your testing capabilities. The ArtiLink 300 will raise the value of your services by performing even more tests and coding adjustments to your client's car.

#### Features

- Supports Full Modes of OBDII Diagnostics for most 1996 and newer vehicles
- Reads and Clears Codes
- Supports CAN, ISO9141, KWP2000, J1850 PWM, and J1859VPW Protocols
- No External Battery Required - Just Plug & Play
- Turns off The Check Engine Light and Retrieves I/M Readiness Status for an Easy Smog Test
- Provides Freeze Frame Data Retrieval and Views Vehicle Records
- Includes a DTC Lookup Library for Detailed Information
- Multilingual Menu
- Live Data, monitor and evaluate running conditions.

#### Specs

- Display: 1.77 in Color Display
- Operating Voltage: 9 to 18V
- Storage Temperature: -20°C to 70°C
- Working Temperature: -10°C to 50°C
- Dimensions: 119.9\*71.7\*23.3 mm
- Product Weight: 210 g

#### What's in the Box

- 1 ArtiLink 300 Code Reader
- 1 Quick Start Guide
- 1 User Manual

#### Comparison Chart

AL200	AL300	AL400	AL500	AL600
<b>Features</b>				
<ul style="list-style-type: none"> <li>• Reads &amp; Clears DTCs</li> <li>• Viewing Freeze Frame Data</li> <li>• Retrieving I/M Readiness Status</li> <li>• Viewing Vehicle Information</li> <li>• Multilingual Menu (5): English, French, German, Spanish, Dutch</li> </ul>	<ul style="list-style-type: none"> <li>• All ArtiLink 200 Features plus:</li> <li>• O2 Sensor Test</li> <li>• On-board Monitor Test</li> <li>• DTC Lookup</li> <li>• EVAP Test</li> <li>• Multilingual Menu (7): English, French, German, Spanish, Portuguese, Italian, Russian</li> </ul>	<ul style="list-style-type: none"> <li>• All ArtiLink 200 Features plus:</li> <li>• O2 Sensor Test</li> <li>• On-board Monitor Test</li> <li>• DTC Lookup</li> <li>• Graph Live Data</li> <li>• OBDII Connector LED Light</li> <li>• Free Software Updates</li> <li>• EVAP Test</li> <li>• Multilingual Menu (7): English, French, German, Spanish, Portuguese, Italian, Japanese</li> </ul>	<ul style="list-style-type: none"> <li>• All ArtiLink 200 Features plus:</li> <li>• O2 Sensor Test</li> <li>• On-board Monitor Test</li> <li>• DTC Lookup</li> <li>• Graph Live Data</li> <li>• OBDII Connector LED Light</li> <li>• Free Software Updates</li> <li>• EVAP Test</li> <li>• Print Via PC</li> <li>• Multilingual Menu (7): English, French, German, Spanish, Portuguese, Russian, Japanese</li> </ul>	<ul style="list-style-type: none"> <li>• All ArtiLink 200 Features plus:</li> <li>• O2 Sensor Test</li> <li>• On-board Monitor Test</li> <li>• DTC Lookup</li> <li>• Graph Live Data</li> <li>• OBDII Connector LED Light</li> <li>• Free Software Updates</li> <li>• EVAP Test</li> <li>• Print Via PC</li> <li>• Access to ECU Information; Read &amp; Clear DTCs; Live Data Stream; and Active Tests.</li> <li>• Oil Reset, SAS, BMS</li> <li>• Multilingual Menu (8): English, French, German, Spanish, Portuguese, Russian, Italian, Japanese</li> </ul>
<b>Specs</b>				
<ul style="list-style-type: none"> <li>• Display: 128x64 pixel display</li> <li>• Operating Voltage: 9 to 16V</li> <li>• Weight: 181.44 g</li> </ul>	<ul style="list-style-type: none"> <li>• Display: 1.77 in Color Display</li> <li>• Operating Voltage: 9~18V</li> <li>• Weight: 210 g</li> <li>• Storage Temperature: -20°C ~70°C</li> <li>• Operating Temperature: -10°C ~50°C</li> <li>• Dimensions: 119.9 * 71.7 * 23.3 mm</li> </ul>	<ul style="list-style-type: none"> <li>• Display: 2.4" Color</li> <li>• Operating Voltage: 9V~18V DC</li> <li>• Weight: 221.13g</li> <li>• Storage Temperature: -20°C ~70°C</li> <li>• Operating Temperature: -10°C ~50°C</li> <li>• Dimensions: 114.02*74.93*23.38 mm</li> </ul>	<ul style="list-style-type: none"> <li>• Display: LCD 2.8-Inch, 320*240 pixels</li> <li>• Operating voltage: 9 to 18V</li> <li>• Weight: 270 g</li> <li>• Storage Temperature: -20°C ~70°C</li> <li>• Operating Temperature: -10°C ~50°C</li> <li>• Dimension: 163.58*94.23*31.24 mm</li> </ul>	<ul style="list-style-type: none"> <li>• Display: 3.5-Inch LCD; 320*480 pixels</li> <li>• Operating Voltage: 9 to 18V</li> <li>• Weight: 535 g</li> <li>• Storage Temperature: -20°C ~70°C</li> <li>• Operating Temperature: -10°C ~50°C</li> <li>• Dimension: 215*114.1*34.5 mm</li> </ul>

**CONTACT US**     @topdonofficial

# TOPDON®

**TOPDON TECHNOLOGY Co., Ltd. | WWW.TOPDON.COM**

sales@topdon.com | +86-755-21612590 +1-833-629-4832 (North America)

Unit 2005 20/F, No.3040 Xinghai Avenue, Qianhai Shima Tower, Qianhai Shenzhen-Hong Kong Cooperation Zone, Shenzhen, P.R.China | 518000