



MECHANICAL CONNECTOR

The Tempo Communications field installable mechanical connector can be used in all FTT(x) applications. Cleaving the field fiber with a products like the FCL200, 915CL, 920CL or FCL100 fiber optic cleavers provides a precision cleave needed for optimum performance.


The mechanical connector is available in SC/APC and SC/UPC. Low insertion loss and low return loss specifications guarantee the fiber optic link will deliver high bandwidth connections. The connector can be installed in less than one minute with no epoxy.

SPECIFICATIONS:

OPTICAL PERFORMANCE		
ITEM	TYPICAL (dB)	MAX (dB)
Insertion Loss	≤ 0.2	≤ 0.4
Return Loss	--	≥ 45 UPC, ≥ 55 APC
ENVIRONMENT		
Storage Temperature	-40°C ~ +85°C	
Operating Temperature	-40°C ~ +85°C	
v	≤ 85% (+30°C)	
MECHANICAL		
Re-assembly	Five Times	
Tensile Strength	30N, Δ IL ≤ 0.3 dB	
Durability	500 times, Δ IL ≤ 0.3 dB	
Ferrule Material	Ceramic	
Ferrule Diameter	2.5mm	
Ferrule End Face	0° UPC, 8° APC	
Fiber Type	Singlemode (G.657B3)	
Fiber Geometry	Core diameter (9µm), coating (125µm)	
Cable	3.0mm Round Cable, 3.0 x 2.0mm Drop Cable	
	250/900 micron cable	
Operating Wavelength	1310nm to 1625nm	
Connection Method in Port	Push - Pull	
Average Assembly Time	< One Minute	

ORDERING INFORMATION:

CAT. NO.	DESCRIPTION
SCUPCMCM2590	SCUPC Connector
SCAPCMCM2590	SCAPC Connector



Specifications subject to change without notice.

1390 Aspen Way Vista, CA • 92081 TC-SCUPPCMCM 2/22

Latin America Phone : 1.760.510.0558 | EMEA Phone: +44 (0) 1633 927 050
©2020 Tempo Communications Inc. • An ISO 9001 Company

EMEA: Tempo Europe Limited • Brecon House,
William Brown Close • Cwmbran • NP44 3AB • UK