Printing date 08.10.2022 Revision: 08.10.2022

SECTION 1: Identification of the substance/mixture and of the company/undertaking

· 1.1 Product identifier

· Trade name: <u>Clean-all v.6</u> · Article number: 100433

• 1.2 Relevant identified uses of the substance or mixture and uses advised against No further relevant information available.

- · Application of the substance / the mixture All-purpose cleaner
- · 1.3 Details of the supplier of the Safety Data Sheet
- · Manufacturer/Supplier:

Theochem Laboratories 7373 Rowlett Park Drive Tampa, FL 33610

Phone: 813-237-6463

- · Further information obtainable from: Product Safety Department
- · 1.4 Emergency telephone number:

ChemTel Inc.

(800)255-3924, +1 (813)248-0585

SECTION 2: Hazards identification

- · 2.1 Classification of the substance or mixture
- · Classification according to Regulation (EC) No 1272/2008

Classifications listed also are applicable to the OSHA GHS Hazard Communication Standard (29CFR1910.1200).



Skin Irrit. 2 H315 Causes skin irritation.

Eye Irrit. 2 H319 Causes serious eye irritation.

· Classification according to Directive 67/548/EEC or Directive 1999/45/EC



R36/38: Irritating to eyes and skin.

· Information concerning particular hazards for human and environment:

The product has to be labelled due to the calculation procedure of the "General Classification guideline for preparations of the EU" in the latest valid version.

Classification system:

The classification is according to the latest editions of the EU-lists, and extended by company and literature data.

The classification is in accordance with the latest editions of international substances lists, and is supplemented by information from technical literature and by information provided by the company.

- · 2.2 Label elements
- · Labelling according to Regulation (EC) No 1272/2008

The product is additionally classified and labelled according to the Globally Harmonized System within the United States (GHS).

(Contd. on page 2)



Printing date 08.10.2022 Revision: 08.10.2022

Trade name: Clean-all v.6

(Contd. of page 1)

The product is classified and labelled according to the CLP regulation.

· Hazard pictograms



- Signal word Warning
- · Hazard-determining components of labelling:

disodium metasilicate

· Hazard statements

H315 Causes skin irritation.

H319 Causes serious eye irritation.

· Precautionary statements

Wear protective gloves / eye protection. P280

Wash thoroughly after handling. P264

P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if

present and easy to do. Continue rinsing.

P332+P313 If skin irritation occurs: Get medical advice/attention. P337+P313 If eye irritation persists: Get medical advice/attention.

P302+P352 IF ON SKIN: Wash with plenty of water.

- · Hazard description:
- · WHMIS-symbols:

D2B - Toxic material causing other toxic effects



· NFPA ratings (scale 0 - 4)



Health = 1Fire = 1

Reactivity = 0

· HMIS-ratings (scale 0 - 4)



1 Health = 1 1 Fire = 1

HMIS Long Term Health Hazard Substances

None of the ingredients are listed.

- · 2.3 Other hazards
- · Results of PBT and vPvB assessment
- · **PBT:** Not applicable.
- · vPvB: Not applicable.

(Contd. on page 3)

Printing date 08.10.2022 Revision: 08.10.2022

Trade name: Clean-all v.6

(Contd. of page 2)

SECTION 3: Composition/information on ingredients

- · 3.2 Mixtures
- · Description: Mixture of substances listed below with nonhazardous additions.

· Dangerous components:		
CAS: 111-76-2 EINECS: 203-905-0 Index number: 603-014-00-0	2-butoxyethanol Xn R20/21/22; Xi R36/38	≤ 2,5%
CAS: 6834-92-0 EINECS: 229-912-9 Index number: 014-010-00-8	disodium metasilicate C R34; Xi R37 Met. Corr.1, H290; Skin Corr. 1B, H314 TOT SE 3, H335	≤ 2,5%
CAS: 68131-39-5 NLP: 500-195-7	alcohols, C12-15, ethoxylated Xi R41; N R50 Eye Dam. 1, H318 Aquatic Acute 1, H400	< 1%

· Additional information: For the wording of the listed risk phrases refer to section 16.

SECTION 4: First aid measures

- · 4.1 Description of first aid measures
- · General information: Immediately remove any clothing soiled by the product.
- · After inhalation: Supply fresh air; consult doctor in case of complaints.
- · After skin contact:

Immediately rinse with water.

If skin irritation continues, consult a doctor.

· After eye contact:

Remove contact lenses if worn.

Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.

· After swallowing:

Rinse out mouth and then drink plenty of water.

Do not induce vomiting; call for medical help immediately.

· 4.2 Most important symptoms and effects, both acute and delayed

Headache

Gastric or intestinal disorders.

Dizziness

Irritant to skin and mucous membranes.

Irritant to eyes.

- · Hazards Danger of gastric perforation.
- 4.3 Indication of any immediate medical attention and special treatment needed

 No further relevant information available.

(Contd. on page 4)

Printing date 08.10.2022 Revision: 08.10.2022

Trade name: Clean-all v.6

(Contd. of page 3)

SECTION 5: Firefighting measures

- · 5.1 Extinguishing media
- · Suitable extinguishing agents: Use fire extinguishing methods suitable to surrounding conditions.
- · For safety reasons unsuitable extinguishing agents: None.
- · 5.2 Special hazards arising from the substance or mixture

Formation of toxic gases is possible during heating or in case of fire.

- · 5.3 Advice for firefighters
- · Protective equipment:

Wear self-contained respiratory protective device.

Wear fully protective suit.

· Additional information No further relevant information available.

SECTION 6: Accidental release measures

· 6.1 Personal precautions, protective equipment and emergency procedures

Use respiratory protective device against the effects of fumes/dust/aerosol.

Wear protective equipment. Keep unprotected persons away.

Ensure adequate ventilation

Particular danger of slipping on leaked/spilled product.

- · 6.2 Environmental precautions: Do not allow to enter sewers/ surface or ground water.
- · 6.3 Methods and material for containment and cleaning up:

Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).

Send for recovery or disposal in suitable receptacles.

Clean the affected area carefully; suitable cleaners are:

Warm water

Dispose contaminated material as waste according to item 13.

· 6.4 Reference to other sections

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

SECTION 7: Handling and storage

· 7.1 Precautions for safe handling

Use only in well ventilated areas.

Prevent formation of aerosols.

- · Information about fire and explosion protection: No special measures required.
- · 7.2 Conditions for safe storage, including any incompatibilities
- · Storage:
- · Requirements to be met by storerooms and receptacles:

Store in a cool location.

Unsuitable material for receptacle: aluminium.

· Information about storage in one common storage facility:

Do not store together with acids.

(Contd. on page 5)

Printing date 08.10.2022 Revision: 08.10.2022

Trade name: Clean-all v.6

(Contd. of page 4)

Store away from foodstuffs.

Store away from oxidising agents.

- Further information about storage conditions: Store in cool, dry conditions in well sealed receptacles.
- · 7.3 Specific end use(s) No further relevant information available.

SECTION 8: Exposure controls/personal protection

- · Additional information about design of technical facilities: No further data; see item 7.

· 8.1 Control parameters			
· Ingredients with limit values that require monitoring at the workplace:			
111-76-2 2-butoxyethanol			
IOELV (EU)	Short-term value: 246 mg/m³, 50 ppm Long-term value: 98 mg/m³, 20 ppm Skin		
PEL (USA)	Long-term value: 240 mg/m³, 50 ppm Skin		
REL (USA)	Long-term value: 24 mg/m³, 5 ppm Skin		
TLV (USA)	Long-term value: 97 mg/m³, 20 ppm BEI		
EL (Canada)	Long-term value: 20 ppm		
EV (Canada)	Long-term value: 20 ppm Skin		
· Ingredients v	Ingredients with biological limit values:		
111-76-2 2-bu	utoxyethanol		
M	00 mg/g creatinine edium: urine me: end of shift arameter: Butoxyacetic acid with hydrolysis		

- · Additional information: The lists valid during the making were used as basis.
- · 8.2 Exposure controls
- · Personal protective equipment:
- · General protective and hygienic measures:

Keep away from foodstuffs, beverages and feed.

Immediately remove all soiled and contaminated clothing.

Wash hands before breaks and at the end of work.

Avoid contact with the eyes and skin.

Respiratory protection:

Use suitable respiratory protective device in case of insufficient ventilation.

For spills, respiratory protection may be advisable.

(Contd. on page 6)

Printing date 08.10.2022 Revision: 08.10.2022

Trade name: Clean-all v.6

· Protection of hands:

(Contd. of page 5)



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation. Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation.

Material of gloves

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

· Penetration time of glove material

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· For the permanent contact gloves made of the following materials are suitable:

Butyl rubber, BR Neoprene gloves Nitrile rubber, NBR

· Eye protection:



Safety glasses

Goggles recommended during refilling

- · Body protection: Protective work clothing
- · Limitation and supervision of exposure into the environment

No further relevant information available.

· Risk management measures

See Section 7 for additional information. No further relevant information available.

SECTION 9: Physical and chemical properties

- · 9.1 Information on basic physical and chemical properties
- · General Information
- · Appearance:

Form: Liquid Colour: Violet · Odour: Aromatic · Odour threshold: Not determined. 12,0-13,0

· pH-value at 20 °C:

· Change in condition

Melting point/Melting range: Not Determined. **Boiling point/Boiling range:** 100 °C (212 °F)

(Contd. on page 7)

Printing date 08.10.2022 Revision: 08.10.2022

Trade name: Clean-all v.6

(Contd. of page 6)

Flash point: > 93,3 °C (>200 °F)
 Flammability (solid, gaseous): Not applicable.

· Auto/Self-ignition temperature:

Decomposition temperature: Not determined.

· **Self-igniting**: Product is not self-igniting.

· Danger of explosion: Product does not present an explosion hazard.

· Explosion limits:

Lower: Not determined. Upper: Not determined.

Vapour pressure at 20 °C:
Density at 20 °C:
Relative density
Vapour density
Evaporation rate

23 hPa

1,02 g/cm³

Not determined.

Not determined.

Not determined.

· Solubility in / Miscibility with

water: Fully miscible.Partition coefficient (n-octanol/water): Not determined.

· Viscosity:

Dynamic: Not determined. **Kinematic:** Not determined.

• 9.2 Other information No further relevant information available.

SECTION 10: Stability and reactivity

- · 10.1 Reactivity
- · 10.2 Chemical stability
- Thermal decomposition / conditions to be avoided:

No decomposition if used according to specifications.

· 10.3 Possibility of hazardous reactions

Strong exothermic reaction with acids.

Corrosive action on metals.

Reacts with strong oxidising agents.

- 10.4 Conditions to avoid No further relevant information available.
- 10.5 Incompatible materials: No further relevant information available.
- 10.6 Hazardous decomposition products: Possible in traces.

(Contd. on page 8)

Printing date 08.10.2022 Revision: 08.10.2022

Trade name: Clean-all v.6

(Contd. of page 7)

SECTION 11: Toxicological information

- · 11.1 Information on toxicological effects
- · Acute toxicity:
- · Primary irritant effect:
- · on the skin: Irritant to skin and mucous membranes.
- · on the eye: Irritating effect.
- · Sensitisation: No sensitising effects known.
- · Additional toxicological information:

The product shows the following dangers according to the calculation method of the General EU Classification Guidelines for Preparations as issued in the latest version:

Irritant

SECTION 12: Ecological information

- · 12.1 Toxicity
- · Aquatic toxicity: No further relevant information available.
- · 12.2 Persistence and degradability biodegradable
- 12.3 Bioaccumulative potential Does not accumulate in organisms.
- 12.4 Mobility in soil No further relevant information available.
- **Ecotoxical effects:**
- · Remark: Harmful to fish
- · Additional ecological information:
- · General notes:

Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

Harmful to aquatic organisms

Rinse off of bigger amounts into drains or the aquatic environment may lead to increased pH-values. A high pH-value harms aquatic organisms. If the dilution of the use-level pH-value is considerably reduced, the aqueous waste, emptied into drains, is only low water-dangerous.

Water Hazard Class (Self-classification) in the concentrate.

- · 12.5 Results of PBT and vPvB assessment
- · PBT: Not applicable.
- · vPvB: Not applicable.
- 12.6 Other adverse effects No further relevant information available.

SECTION 13: Disposal considerations

- · 13.1 Waste treatment methods
- · Recommendation

Small amounts may be diluted with plenty of water and washed away. Dispose of bigger amounts in accordance with Local Authority requirements.

- · Uncleaned packaging:
- · Recommendation: Disposal must be made according to official regulations.

(Contd. on page 9)

Printing date 08.10.2022 Revision: 08.10.2022

Trade name: Clean-all v.6

· Recommended cleansing agents: Water only.

(Contd. of page 8)

SECTION 14: Transport information

· 14.1 UN-Number

· DOT, ADR, ADN, IMDG, IATA Not Regulated

· 14.2 UN proper shipping name

· DOT, ADR, ADN, IMDG, IATA Not Regulated

· 14.3 Transport hazard class(es)

· DOT, ADR, ADN, IMDG, IATA

· Class Not Regulated

· 14.4 Packing group

· DOT, ADR, IMDG, IATA Not Regulated

· 14.5 Environmental hazards:

· Marine pollutant: No

• 14.6 Special precautions for user Not applicable.

· 14.7 Transport in bulk according to Annex II of

MARPOL73/78 and the IBC Code Not applicable.

UN "Model Regulation":

SECTION 15: Regulatory information

- · 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture
- · United States (USA)
- ·SARA
- · Section 355 (extremely hazardous substances):

None of the ingredients are listed.

· Section 313 (Specific toxic chemical listings):

111-76-2 2-butoxyethanol

· TSCA (Toxic Substances Control Act):

All ingredients are listed.

- Proposition 65 (California):
- · Chemicals known to cause cancer:

Ethanol - listing refers specifically to alcoholic beverage consumption and is not applicable for product. 64-17-5 ethanol

· Chemicals known to cause reproductive toxicity for females:

None of the ingredients are listed.

· Chemicals known to cause reproductive toxicity for males:

None of the ingredients are listed.

· Chemicals known to cause developmental toxicity:

Ethanol - listing refers specifically to alcoholic beverage consumption and is not applicable for product.

64-17-5 ethanol

(Contd. on page 10)

Printing date 08.10.2022 Revision: 08.10.2022

Trade name: Clean-all v.6

	(Contd. of page 9)
· Carcinogenic Categories	
· EPA (Environmental Protection Agency)	
111-76-2 2-butoxyethanol	NL
IARC (International Agency for Research on Cancer)	
111-76-2 2-butoxyethanol	3
64-17-5 ethanol	1
TLV (Threshold Limit Value established by ACGIH)	
111-76-2 2-butoxyethanol	A3
64-17-5 ethanol	A3
NIOSH-Ca (National Institute for Occupational Safety and Health)	
None of the ingredients are listed.	
· Canada	
· Canadian Domestic Substances List (DSL)	
All ingredients are listed.	
· Canadian Ingredient Disclosure list (limit 0.1%)	
64-17-5 ethanol	
Canadian Ingredient Disclosure list (limit 1%)	
111-76-2 2-butoxyethanol	
6834-92-0 disodium metasilicate	

- · National regulations:
- · Other regulations, limitations and prohibitive regulations

This product has been classified in accordance with hazard criteria of the Controlled Products Regulations and the SDS contains all the information required by the Controlled Products Regulations.

· Substances of very high concern (SVHC) according to REACH, Article 57

None of the ingredients are listed.

· 15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· Relevant phrases

H290 May be corrosive to metals.

H302 Harmful if swallowed.

H312 Harmful in contact with skin.

H314 Causes severe skin burns and eye damage.

H315 Causes skin irritation.

H318 Causes serious eye damage.

H319 Causes serious eye irritation.

H332 Harmful if inhaled.

H335 May cause respiratory irritation.

(Contd. on page 11)

Printing date 08.10.2022 Revision: 08.10.2022

Trade name: Clean-all v.6

(Contd. of page 10)

H400 Very toxic to aquatic life.

R20/21/22 Harmful by inhalation, in contact with skin and if swallowed.

R34 Causes burns.

R36/38 Irritating to eyes and skin.
R37 Irritating to respiratory system.
R41 Risk of serious damage to eyes.
R50 Very toxic to aquatic organisms.

· Abbreviations and acronyms:

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

DOT: US Department of Transportation

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

ACGIH: American Conference of Governmental Industrial Hygienists

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

NFPA: National Fire Protection Association (USA)

HMIS: Hazardous Materials Identification System (USA)

WHMIS: Workplace Hazardous Materials Information System (Canada)

VOC: Volatile Organic Compounds (USA, EU)

Met. Corr.1: Corrosive to metals, Hazard Category 1

Acute Tox. 4: Acute toxicity, Hazard Category 4

Skin Corr. 1B: Skin corrosion/irritation, Hazard Category 1B

Skin Irrit. 2: Skin corrosion/irritation, Hazard Category 2

Eye Dam. 1: Serious eye damage/eye irritation, Hazard Category 1

Eye Irrit. 2: Serious eye damage/eye irritation, Hazard Category 2

STOT SE 3: Specific target organ toxicity - Single exposure, Hazard Category 3

Aquatic Acute 1: Hazardous to the aquatic environment - AcuteHazard, Category 1

Sources

SDS Prepared by:

ChemTel Inc.

1305 North Florida Avenue

Tampa, Florida USA 33602-2902

Toll Free North America 1-888-255-3924 Intl. +01 813-248-0573

Website: www.chemtelinc.com