

# Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA  
GHS

Printing date: 27 March 2019

Revision: 27 March 2019

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- Trade name: **Day & Night v.3**
- Article number: 100309
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
- Application of the substance / the mixture: Odour neutralising agent
- Uses advised against: No further relevant information available.
- **1.3 Details of the supplier of the Safety Data Sheet**
- **Manufacturer/Supplier:**  
Theochem Laboratories  
7373 Rowlett Park Drive  
Tampa, FL 33610  
Phone: 813-237-6463
- **1.4 Emergency telephone number:**  
ChemTel Inc.  
(800)255-3924 (North America)  
+1 (813)248-0585 (International)



## SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**  
The product is not classified as hazardous according to OSHA GHS regulations within the United States.  
Aquatic Chronic 3 H412 Harmful to aquatic life with long lasting effects.

---

- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008**  
The product is not classified as hazardous according to OSHA GHS regulations within the United States.  
The product is classified and labelled according to the CLP regulation.
- **Hazard pictograms** Not Regulated
- **Signal word** Not Regulated
- **Hazard statements**  
Not applicable within the USA; only applicable for the EU.  
H412 Harmful to aquatic life with long lasting effects.
- **Precautionary statements**  
Not applicable within the USA; only applicable for the EU.  
P273 Avoid release to the environment.  
P501 Dispose of contents/container in accordance with local/regional/national/international regulations.
- **NFPA ratings (scale 0 - 4)**



Health = 0  
Fire = 0  
Reactivity = 0

- **HMIS-ratings (scale 0 - 4)**

(Cont'd. on page 2)

# Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA  
GHS

Printing date: 27 March 2019

Revision: 27 March 2019

**Trade name: Day & Night v.3**

(Cont'd. from page 1)

HEALTH	0	Health = 0
FIRE	0	Fire = 0
REACTIVITY	0	Reactivity = 0

- **2.3 Other hazards** There are no other hazards not otherwise classified that have been identified.
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

## SECTION 3: Composition/information on ingredients

### · 3.2 Mixtures

#### · Components:

CAS: 64-17-5 EINECS: 200-578-6 Index number: 603-002-00-5 Reg.nr.: 01-2119457610-43-XXXX	Ethanol ⚠ Flam. Liq. 2, H225 ⚠ Eye Irrit. 2, H319	<5%
CAS: 68439-46-3 EC number: 614-482-0 Reg.nr.: 01-2119980051-45-XXXX	Alcohols, C9-11, ethoxylated ⚠ Eye Irrit. 2, H319	<5%
CAS: 68424-85-1 EINECS: 270-325-2 Reg.nr.: 01-2119983287-23-XXXX	Quaternary ammonium compounds, benzyl-C12-16-alkyldimethyl, chlorides ⚠ Skin Corr. 1B, H314; Eye Dam. 1, H318 ⚠ Aquatic Acute 1, H400; Aquatic Chronic 1, H410 ⚠ Acute Tox. 4, H302	<1%
CAS: 8007-35-0 EINECS: 232-357-5	Terpinyl acetate (Isomer mixture) ⚠ Aquatic Chronic 2, H411	<1%

- **Additional information:** For the wording of the listed Hazard Statements refer to section 16.

## SECTION 4: First aid measures

### · 4.1 Description of first aid measures

- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:**  
Clean with water and soap.  
Seek medical treatment in case of complaints.
- **After eye contact:**  
Remove contact lenses if worn.  
Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.
- **After swallowing:**  
Rinse out mouth and then drink plenty of water.  
Do not induce vomiting; call for medical help immediately.
- **4.2 Most important symptoms and effects, both acute and delayed**  
Gastric or intestinal disorders when ingested.  
Nausea in case of ingestion.

(Cont'd. on page 3)

# Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA  
GHS

Printing date: 27 March 2019

Revision: 27 March 2019

**Trade name: Day & Night v.3**

(Cont'd. from page 2)

Slight irritant effect on eyes.  
Slight irritant effect on skin and mucous membranes.

· **4.3 Indication of any immediate medical attention and special treatment needed**

No further relevant information available.

## SECTION 5: Firefighting measures

· **5.1 Extinguishing media**

· **Suitable extinguishing agents:** CO<sub>2</sub>, powder or water spray. Fight larger fires with water spray.

· **For safety reasons unsuitable extinguishing agents:** None.

· **5.2 Special hazards arising from the substance or mixture**

Formation of toxic gases is possible during heating or in case of fire.

· **5.3 Advice for firefighters**

· **Protective equipment:**

Wear self-contained respiratory protective device.

Wear fully protective suit.

## SECTION 6: Accidental release measures

· **6.1 Personal precautions, protective equipment and emergency procedures**

Use personal protective equipment as required.

Ensure adequate ventilation

· **6.2 Environmental precautions**

Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

· **6.3 Methods and material for containment and cleaning up**

Towel or mop up material and collect in a suitable container.

For larger spills, add sawdust, chalk or other inert binding material, then sweep up and discard.

· **6.4 Reference to other sections**

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

## SECTION 7: Handling and storage

· **7.1 Precautions for safe handling**

Keep receptacles tightly sealed.

Avoid splashes or spray in enclosed areas.

Keep out of reach of children.

· **7.2 Conditions for safe storage, including any incompatibilities**

· **Requirements to be met by storerooms and receptacles:**

Store in cool, dry conditions in well sealed receptacles.

· **Information about storage in one common storage facility:** Store away from foodstuffs.

· **7.3 Specific end use(s)** No further relevant information available.

(Cont'd. on page 4)

# Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA  
GHS

Printing date: 27 March 2019

Revision: 27 March 2019

Trade name: Day &amp; Night v.3

(Cont'd. from page 3)

## SECTION 8: Exposure controls/personal protection

### · 8.1 Control parameters

#### · Ingredients with limit values that require monitoring at the workplace:

##### 64-17-5 Ethanol

EL (Canada)	Short-term value: 1000 ppm
EV (Canada)	Long-term value: 1,900 mg/m <sup>3</sup> , 1,000 ppm
WEL (Great Britain)	Long-term value: 1920 mg/m <sup>3</sup> , 1000 ppm
OEL (Ireland)	Short-term value: 1000 ppm
PEL (USA)	Long-term value: 1900 mg/m <sup>3</sup> , 1000 ppm
REL (USA)	Long-term value: 1900 mg/m <sup>3</sup> , 1000 ppm
TLV (USA)	Short-term value: 1880 mg/m <sup>3</sup> , 1000 ppm

### · 8.2 Exposure controls

#### · General protective and hygienic measures:

- Wash hands before breaks and at the end of work.
- Avoid contact with the eyes.
- Avoid close or long term contact with the skin.
- Avoid breathing mist/vapours/spray.

#### · Respiratory protection:

- Not required under normal conditions of use.
- Use suitable respiratory protective device in case of insufficient ventilation.

#### · Protection of hands:

- Gloves are advised for repeated or prolonged contact.
- Wear protective gloves to handle contents of damaged or leaking units.
- The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

#### · Material of gloves Rubber gloves

#### · Eye protection: Follow relevant national guidelines concerning the use of protective eyewear.

#### · Body protection: Protective work clothing

#### · Limitation and supervision of exposure into the environment: Avoid release to the environment.

#### · Risk management measures: No further relevant information available.

## SECTION 9: Physical and chemical properties

### · 9.1 Information on basic physical and chemical properties

#### · Appearance

Form: Liquid

Colour: Pale

· Odour: Aromatic

· Odour threshold: Not determined.

· pH-value at 20 °C (68 °F): 7,0

· Melting point/freezing point: Not determined.

· Initial boiling point and boiling range: 100 °C (212 °F)

(Cont'd. on page 5)

# Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA  
GHS

Printing date: 27 March 2019

Revision: 27 March 2019

Trade name: Day &amp; Night v.3

(Cont'd. from page 4)

· <b>Flash point:</b>	Product not expected to support sustained combustion. Not applicable.
· <b>Flammability (solid, gas):</b>	Not applicable.
· <b>Auto/Self-ignition temperature:</b>	Not determined.
· <b>Decomposition temperature:</b>	Not determined.
· <b>Explosive properties:</b>	Product does not present an explosion hazard.
· <b>Explosion limits</b>	
Lower:	Not determined.
Upper:	Not determined.
· <b>Oxidising properties</b>	Non-oxidising.
· <b>Vapour pressure:</b>	Not determined.
· <b>Density:</b>	
Relative density:	0,9-1,0
Vapour density:	Not determined.
Evaporation rate:	Not determined.
· <b>Solubility in / Miscibility with water:</b>	Fully miscible.
· <b>Partition coefficient: n-octanol/water:</b>	Not determined.
· <b>Viscosity</b>	
Dynamic:	Not determined.
Kinematic:	Not determined.
· <b>9.2 Other information</b>	No further relevant information available.

## SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**  
No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions**  
Reacts with strong acids and alkali.  
Reacts with strong oxidising agents.
- **10.4 Conditions to avoid** Excessive heat.
- **10.5 Incompatible materials** Oxidisers, strong bases, strong acids
- **10.6 Hazardous decomposition products**  
Under fire conditions only:  
Carbon monoxide and carbon dioxide

## SECTION 11: Toxicological information

(Cont'd. on page 6)

# Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA  
GHS

Printing date: 27 March 2019

Revision: 27 March 2019

Trade name: Day &amp; Night v.3

(Cont'd. from page 5)

- **11.1 Information on toxicological effects**

- **Acute toxicity:** Based on available data, the classification criteria are not met.

- **LD/LC50 values relevant for classification:**

<b>68424-85-1 Quaternary ammonium compounds, benzyl-C12-16-alkyldimethyl, chlorides</b>		
Oral	LD50	344 mg/kg (rat)
Dermal	LD50	3340 mg/kg (rabbit)

- **Primary irritant effect**

- **Skin corrosion/irritation:** Slight irritant effect on skin and mucous membranes.

- **Serious eye damage/irritation:** Based on available data, the classification criteria are not met.

- **Respiratory or skin sensitisation:** Based on available data, the classification criteria are not met.

- **Carcinogenic categories**

- **IARC (International Agency for Research on Cancer):**

64-17-5	Ethanol	1
---------	---------	---

- **Probable routes of exposure:**

- Ingestion.

- Inhalation.

- Eye contact.

- Skin contact.

- **Germ cell mutagenicity:** Based on available data, the classification criteria are not met.

- **Carcinogenicity:** Based on available data, the classification criteria are not met.

- **Reproductive toxicity:** Based on available data, the classification criteria are not met.

- **STOT-single exposure:** Based on available data, the classification criteria are not met.

- **STOT-repeated exposure:** Based on available data, the classification criteria are not met.

- **Aspiration hazard:** Based on available data, the classification criteria are not met.

## SECTION 12: Ecological information

- **12.1 Toxicity**

- **Aquatic toxicity:**

- Harmful to aquatic life with long lasting effects.

<b>68424-85-1 Quaternary ammonium compounds, benzyl-C12-16-alkyldimethyl, chlorides</b>		
LC50	0,28 mg/l	(pimephales promelas)
EC50	0,0059 mg/l	(daphnia)

- **12.2 Persistence and degradability** No further relevant information available.

- **12.3 Bioaccumulative potential** Does not accumulate in organisms.

- **12.4 Mobility in soil** No further relevant information available.

- **Additional ecological information:**

- **General notes:**

- Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

- **12.5 Results of PBT and vPvB assessment**

- **PBT:** Not applicable.

- **vPvB:** Not applicable.

(Cont'd. on page 7)

# Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA  
GHS

Printing date: 27 March 2019

Revision: 27 March 2019

**Trade name: Day & Night v.3**

(Cont'd. from page 6)

- **12.6 Other adverse effects** No further relevant information available.

## SECTION 13: Disposal considerations

### · 13.1 Waste treatment methods

#### · Recommendation

The user of this material has the responsibility to dispose of unused material, residues and containers in compliance with all relevant local, state and federal laws and regulations regarding treatment, storage and disposal for hazardous and nonhazardous wastes.

#### · Uncleaned packaging:

- **Recommendation:** Disposal must be made according to official regulations.

## SECTION 14: Transport information

### · 14.1 UN-Number

- DOT, ADR/RID/ADN, IMDG, IATA Not Regulated

### · 14.2 UN proper shipping name

- DOT, ADR/RID/ADN, IMDG, IATA Not Regulated

### · 14.3 Transport hazard class(es)

- DOT, ADR/RID/ADN, IMDG, IATA
- Class Not Regulated

### · 14.4 Packing group

- DOT, ADR/RID/ADN, IMDG, IATA Not Regulated

### · 14.5 Environmental hazards:

- Marine pollutant: No

### · 14.6 Special precautions for user

Not applicable.

### · 14.7 Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable.

## SECTION 15: Regulatory information

### · 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

- United States (USA)
- SARA

#### · Section 302 (extremely hazardous substances):

None of the ingredients are listed.

#### · Section 355 (extremely hazardous substances):

(Cont'd. on page 8)

# Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA  
GHS

Printing date: 27 March 2019

Revision: 27 March 2019

Trade name: Day &amp; Night v.3

(Cont'd. from page 7)

None of the ingredients are listed.

- **Section 313 (Specific toxic chemical listings):**

None of the ingredients are listed.

- **TSCA (Toxic Substances Control Act):**

All ingredients are listed.

- **Proposition 65 (California):**

- **Chemicals known to cause cancer:**

Ethanol - listing refers specifically to alcoholic beverage consumption and is not applicable for product.

64-17-5 Ethanol

- **Chemicals known to cause developmental toxicity for females:**

None of the ingredients are listed.

- **Chemicals known to cause developmental toxicity for males:**

None of the ingredients are listed.

- **Chemicals known to cause developmental toxicity:**

Ethanol - listing refers specifically to alcoholic beverage consumption and is not applicable for product.

64-17-5 Ethanol

- **EPA (Environmental Protection Agency)**

None of the ingredients are listed.

- **IARC (International Agency for Research on Cancer)**

64-17-5 Ethanol

1

- **Canadian Domestic Substances List (DSL) (Substances not listed)**

All ingredients are listed.

- **Other regulations, limitations and prohibitive regulations**

- **Substances of very high concern (SVHC) according to REACH, Article 57**

None of the ingredients are listed.

- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

## SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Relevant phrases**

H225 Highly flammable liquid and vapour.

H302 Harmful if swallowed.

H314 Causes severe skin burns and eye damage.

H318 Causes serious eye damage.

H319 Causes serious eye irritation.

H400 Very toxic to aquatic life.

H410 Very toxic to aquatic life with long lasting effects.

H411 Toxic to aquatic life with long lasting effects.

- **Abbreviations and acronyms:**

(Cont'd. on page 9)



# Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA  
GHS

Printing date: 27 March 2019

Revision: 27 March 2019

**Trade name: Day & Night v.3**

(Cont'd. from page 8)

ADR: European Agreement concerning the International Carriage of Dangerous Goods by Road  
IMDG: International Maritime Code for Dangerous Goods  
DOT: US Department of Transportation  
IATA: International Air Transport Association  
GHS: Globally Harmonised System of Classification and Labelling of Chemicals  
EINECS: European Inventory of Existing Commercial Chemical Substances  
ELINCS: European List of Notified Chemical Substances  
CAS: Chemical Abstracts Service (division of the American Chemical Society)  
LC50: Lethal concentration, 50 percent  
LD50: Lethal dose, 50 percent  
PBT: Persistent, Bio-accumulable, Toxic  
SVHC: Substances of Very High Concern  
vPvB: very Persistent and very Bioaccumulative  
Flam. Liq. 2: Flammable liquids – Category 2  
Acute Tox. 4: Acute toxicity – Category 4  
Skin Corr. 1B: Skin corrosion/irritation – Category 1B  
Eye Dam. 1: Serious eye damage/eye irritation – Category 1  
Eye Irrit. 2: Serious eye damage/eye irritation – Category 2  
Aquatic Acute 1: Hazardous to the aquatic environment - acute aquatic hazard – Category 1  
Aquatic Chronic 1: Hazardous to the aquatic environment - long-term aquatic hazard – Category 1  
Aquatic Chronic 2: Hazardous to the aquatic environment - long-term aquatic hazard – Category 2  
Aquatic Chronic 3: Hazardous to the aquatic environment - long-term aquatic hazard – Category 3

**Sources**

Website, European Chemicals Agency ([echa.europa.eu](http://echa.europa.eu))  
Website, US EPA Substance Registry Services ([ofmpub.epa.gov/sorinternet/registry/substreg/home/overview/home.do](http://ofmpub.epa.gov/sorinternet/registry/substreg/home/overview/home.do))  
Website, Chemical Abstracts Registry, American Chemical Society ([www.cas.org](http://www.cas.org))  
Patty's Industrial Hygiene, 6th ed., Rose, Vernon, ed. ISBN: 978-0-470-07488-6  
Casarett and Doull's Toxicology: The Basic Science of Poisons, 8th Ed., Klaassen, Curtis D., ed., ISBN: 978-0-07-176923-5.  
Safety Data Sheets, Individual Manufacturers

SDS Prepared by:

ChemTel Inc.

1305 North Florida Avenue

Tampa, Florida USA 33602-2902

Toll Free North America 1-888-255-3924 Intl. +01 813-248-0573

Website: [www.chemtelinc.com](http://www.chemtelinc.com)