



MAXX COLD

ICONIC BRANDS, LEADING INNOVATION

Upright Reach-In Refrigerators & Freezers



010521



www.maxx-cold.com

3355 Enterprise Avenue • Suite 160 | Fort Lauderdale, FL 33331
Tel: 954.202.7419 | Fax: 954.202.7337 | www.maxx-cold.com

A DIVISION OF
THE LEGACY COMPANIES



MCR-23FDHC
MCF-23FDHC
26.75"W x 31"D x 82.75"H



MCR-49FDHC
MCF-49FDHC
54"W x 31"D x 82.75"H



MCR-72FDHC
MCF-72FDHC
81"W x 31"D x 82.75"H

Refrigerators:

- MCR-23FDHC** - Upright reach-in refrigerator; stainless steel exterior
- MCR-49FDHC** - Upright reach-in refrigerator; stainless steel exterior
- MCR-72FDHC** - Upright reach-in refrigerator; stainless steel exterior

Freezers:

- MCF-23FDHC** - Upright reach-in freezer; stainless steel exterior
- MCF-49FDHC** - Upright reach-in freezer; stainless steel exterior
- MCF-72FDHC** - Upright reach-in freezer; stainless steel exterior

All Models Feature:

- Self-closing door(s) with easy to grip recessed handle(s)
- Automatic interior lighting
- Lock and key set for security
- Equipped with four (4) or six (6) 5" diameter swivel casters
- Electronic control panel with digital display
- Automatic defrost system
- Open door alert beeps if door has been open for five minutes
- Supplied with integrated condensate evaporator therefore no drain line connection is needed
- Polyurethane foam insulation provides outstanding thermal regulation and energy efficiency



MODEL	EXTERNAL DIMENSIONS	INTERNAL DIMENSIONS	NET CAPACITY	HOLDING TEMPERATURE RANGE	AMP DRAW	HP	UNIT WEIGHT	REFRIGERANT AND CHARGE SIZE	DOORS / SHELVES	ELECTRICAL
MCR-23FDHC	26.75" x 31" x 82.75" (680 x 787 x 2102 mm)	22.8" x 24.1" x 53.7" (578 x 613 x 1364 mm)	18.9 Cu Ft (535 L)	33°F to 41°F (1°C to 5°C)	2.0A	1/4	271 lbs (123 kg)	R-290a 2.53 oz (72 g)	1 / 3	115V / 60Hz / 1Ph
MCR-49FDHC	54" x 31" x 82.75" (1372 x 787 x 2102 mm)	49.8" x 24.1" x 53.7" (1264 x 613 x 1364 mm)	42.8 Cu Ft (1212 L)	33°F to 41°F (1°C to 5°C)	2.4A	1/4	397 lbs (180 kg)	R-290a 3.46 oz (98 g)	2 / 6	115V / 60Hz / 1Ph
MCR-72FDHC	81" x 31" x 82.75" (2057 x 787 x 2102 mm)	77.3" x 24.1" x 53.7" (1963 x 613 x 1364 mm)	66.7 Cu Ft (1889 L)	33°F to 41°F (1°C to 5°C)	5.5A	1/2	634 lbs (287 kg)	R-290a 5.22 oz (148 g)	3 / 9	115V / 60Hz / 1Ph
MCF-23FDHC	26.75" x 31" x 82.75" (680 x 787 x 2102 mm)	22.8" x 24.1" x 53.7" (578 x 613 x 1364 mm)	18.9 Cu Ft (535 L)	-10°F to 10°F (-23°C to -12°C)	5.6A	1/2	284 lbs (129 kg)	R-290a 2.33 oz (66 g)	1 / 3	115V / 60Hz / 1Ph
MCF-49FDHC	54" x 31" x 82.75" (1372 x 787 x 2102 mm)	49.8" x 24.1" x 53.7" (1264 x 613 x 1364 mm)	42.8 Cu Ft (1212 L)	-10°F to 10°F (-23°C to -12°C)	4.6A	1/2	403 lbs (183 kg)	R-290a 4.44 oz (126 g)	2 / 6	115V / 60Hz / 1Ph
MCF-72FDHC	81" x 31" x 82.75" (2057 x 787 x 2102 mm)	77.3" x 24.1" x 53.7" (1963 x 613 x 1364 mm)	66.7 Cu Ft (1889 L)	-10°F to 10°F (-23°C to -12°C)	9.9A	1	650 lbs (295 kg)	R-290a 5.08 oz (144 g)	3 / 9	220V / 60Hz / 1Ph

TOP-MOUNT REACH-IN REFRIGERATORS & FREEZERS



MCRT-23FDHC
MCFT-23FDHC
26.75"W x 31"D x 82.75"H



MCRT-49FDHC
MCFT-49FDHC
54"W x 31"D x 82.75"H



MCRT-72FDHC
MCFT-72FDHC
81"W x 31"D x 82.75"H

Refrigerators:

MCRT-23FDHC - Upright reach-in refrigerator; stainless steel exterior

MCRT-49FDHC - Upright reach-in refrigerator; stainless steel exterior

MCRT-72FDHC* - Upright reach-in refrigerator; stainless steel exterior

Freezers:

MCFT-23FDHC - Upright reach-in freezer; stainless steel exterior

MCFT-49FDHC - Upright reach-in freezer; stainless steel exterior

MCFT-72FDHC - Upright reach-in freezer; stainless steel exterior

All Models Feature:

- Self-closing door(s) with wavy to grip recessed handle(s)
- Automatic interior lighting
- Lock and key set for security
- Supplied with four (4) or six (6) 5" diameter swivel casters
- Electronic control panel with digital display
- Automatic defrost system
- Open door alert beeps if door has been open for five minutes
- Equipped with integrated condensate evaporator therefore no drain line connection is needed
- Polyurethane foam insulation provides outstanding thermal regulation and energy efficiency



*MCRT-72FDHC not Energy Star Listed

MODEL	EXTERNAL DIMENSIONS	INTERNAL DIMENSIONS	NET CAPACITY	HOLDING TEMPERATURE RANGE	AMP DRAW	HP	UNIT WEIGHT	REFRIGERANT AND CHARGE SIZE	DOORS / SHELVES	ELECTRICAL
MCRT-23FDHC	27" x 31" x 82" (681 x 787 x 2078 mm)	22.8" x 24.1" x 53.7" (578 x 613 x 1364 mm)	18.9 Cu Ft (535 L)	33°F to 41°F (1°C to 5°C)	3.0A	1/4	264 lbs (120 kg)	R-290a 2.61 oz (74 g)	1 / 3	115V / 60Hz / 1Ph
MCRT-49FDHC	54" x 31" x 82" (1370 x 787 x 2078 mm)	49.8" x 24.1" x 53.7" (1264 x 613 x 1364 mm)	42.8 Cu Ft (1212 L)	33°F to 41°F (1°C to 5°C)	3.2A	1/4	388 lbs (190 kg)	R-290a 3.67 oz (104 g)	2 / 6	115V / 60Hz / 1Ph
MCRT-72FDHC	81" x 31" x 82" (2060 x 787 x 2078 mm)	77.3" x 24.1" x 53.7" (1963 x 613 x 1364 mm)	66.7 Cu Ft (1889 L)	33°F to 41°F (1°C to 5°C)	6.3A	1/2	567 lbs (257 kg)	R-290a 5.22 oz (148 g)	3 / 9	115V / 60Hz / 1Ph
MCFT-23FDHC	27" x 31" x 82" (681 x 787 x 2078 mm)	22.8" x 24.1" x 53.7" (578 x 613 x 1364 mm)	18.9 Cu Ft (535 L)	-10°F to 10°F (-23°C to -12°C)	4.9A	1/4	273 lbs (124 kg)	R-290a 2.82 oz (80 g)	1 / 3	115V / 60Hz / 1Ph
MCFT-49FDHC	54" x 31" x 82" (1370 x 787 x 2078 mm)	49.8" x 24.1" x 53.7" (1264 x 613 x 1364 mm)	42.8 Cu Ft (1212 L)	-10°F to 10°F (-23°C to -12°C)	6.8A	1/4	418 lbs (190 kg)	R-290a 4.44 oz (126 g)	2 / 6	115V / 60Hz / 1Ph
MCFT-72FDHC	81" x 31" x 82" (2060 x 787 x 2078 mm)	77.3" x 24.1" x 53.7" (1963 x 613 x 1364 mm)	66.7 Cu Ft (1889 L)	-10°F to 10°F (-23°C to -12°C)	8.4A	1/2	595 lbs (270 kg)	R-290a 5.22 oz (148 g)	3 / 9	220V / 60Hz / 1Ph



MXCR-19FDHC
MXCF-19FDHC

26.75"W x 31.5"D x 77.6"H

MXCR-23FDHC
MXCF-23FDHC

26.75"W x 32.7"D x 82.25"H

MXCR-49FDHC
MXCF-49FDHC

54"W x 32.7"D x 82.25"H

MXCR-72FDHC
MXCF-72FDHC

81"W x 32.7"D x 82.25"H

Refrigerators:

- MXCR-19FDHC** - Upright reach-in refrigerator; stainless steel exterior
- MXCR-23FDHC** - Upright reach-in refrigerator; stainless steel exterior
- MXCR-49FDHC** - Upright reach-in refrigerator; stainless steel exterior
- MXCR-72FDHC** - Upright reach-in refrigerator; stainless steel exterior

Freezers:

- MXCF-19FDHC** - Upright reach-in freezer; stainless steel exterior
- MXCF-23FDHC** - Upright reach-in freezer; stainless steel exterior
- MXCF-49FDHC** - Upright reach-in freezer; stainless steel exterior
- MXCF-72FDHC** - Upright reach-in freezer; stainless steel exterior

All Models Feature:

- Self-closing door(s) with wasy to grip recessed handle(s)
- Field reversible door (single door models only)
- Automatic interior lighting
- Lock and key set for security
- Equipped with four (4) or six (6) 5" diameter swivel casters
- Electronic control panel with digital display
- Automatic defrost system
- Open door alert beeps if door has been open for three minutes
- Supplied with integrated condensate evaporator therefore no drain line connection is needed
- Urethane foam insulated walls and doors



MODEL	EXTERNAL DIMENSIONS	INTERNAL DIMENSIONS	NOMINAL CAPACITY	HOLDING TEMPERATURE RANGE	AMP DRAW	SHIPPING WEIGHT	REFRIGERANT AND CHARGE SIZE	DOORS / SHELVES	ELECTRICAL
MXCR-19FDHC	25.2" x 31.5" x 77.6" (640 x 800 x 1970 mm)	20.25" x 28.7" x 61.8" (514 x 730 x 1570 mm)	19 Cu Ft (538 L)	34°F to 41°F (1°C to 5°C)	3A	291 lbs (132 kg)	R-290A 3.0 oz (85 g)	1 / 3	115V / 60Hz / 1Ph
MXCR-23FDHC	26.8" x 32.7" x 82.25" (681 x 831 x 2090 mm)	21.9" x 26.5" x 52.1" (556 x 673 x 1324 mm)	23 Cu Ft (651 L)	34°F to 41°F (1°C to 5°C)	3A	311 lbs (143 kg)	R-290A 3.0 oz (85 g)	1 / 3	115V / 60Hz / 1Ph
MXCR-49FDHC	53.9" x 32.7" x 82.25" (1369 x 831 x 2090 mm)	49.1" x 26.5" x 52.1" (1246 x 673 x 1324 mm)	49 Cu Ft (1387 L)	34°F to 41°F (1°C to 5°C)	4.5A	536 lbs (244 kg)	R-290A 3.7 oz (105 g)	2 / 6	115V / 60Hz / 1Ph
MXCR-72FDHC	81" x 32.7" x 82.25" (2057 x 831 x 2090 mm)	76.1" x 26.5" x 52.1" (1933 x 673 x 1324 mm)	72 Cu Ft (2039 L)	34°F to 41°F (1°C to 5°C)	7A	639 lbs (291 kg)	R-290A 5.29 oz (150 g)	3 / 9	220V / 60Hz / 1Ph
MXCF-19FDHC	25.2" x 31.5" x 77.6" (640 x 800 x 1970 mm)	20.25" x 28.7" x 61.8" (514 x 730 x 1570 mm)	19 Cu Ft (538 L)	-10°F to 10°F (-23°C to -12°C)	8A	296 lbs (134 kg)	R-290A 3.88 oz (110 g)	1 / 3	115V / 60Hz / 1Ph
MXCF-23FDHC	26.8" x 32.7" x 82.25" (681 x 831 x 2090 mm)	21.9" x 26.5" x 52.1" (556 x 673 x 1324 mm)	23 Cu Ft (651 L)	-10°F to 10°F (-23°C to -12°C)	8A	336 lbs (140 kg)	R-290A 3.88 oz (110 g)	1 / 3	115V / 60Hz / 1Ph
MXCF-49FDHC	53.9" x 32.7" x 82.25" (1369 x 831 x 2090 mm)	49.1" x 26.5" x 52.1" (1246 x 673 x 1324 mm)	49 Cu Ft (1387 L)	-10°F to 10°F (-23°C to -12°C)	9A	502 lbs (160 kg)	R-290A 5.29oz (150 g)	2 / 6	115V / 60Hz / 1Ph
MXCF-72FDHC	81" x 32.7" x 82.25" (2057 x 831 x 2090 mm)	76.1" x 26.5" x 52.1" (1933 x 673 x 1324 mm)	72 Cu Ft (2039 L)	-10°F to 10°F (-23°C to -12°C)	9A	601 lbs (195 kg)	R-290A 5.29oz (150 g)	3 / 9	230V / 60Hz / 1Ph

GLASS DOOR REACH-IN REFRIGERATORS



MXCR-23GDHC
26.8"W x 31.9"D x 82.3"H



MXCR-49GDHC
53.9"W x 31.9"D x 82.3"H

Models:

MXCR-23GDHC - Glass door reach-in refrigerator; stainless steel exterior

MXCR-49GDHC - Glass door reach-in refrigerator; stainless steel exterior

All Models Feature:

- Durable, easy to clean stainless steel exterior and interior
- Self-closing, locking, dual-pane glass doors with easy to grip handles
- Adjustable heavy-duty wire shelves (3 per section/door)
- Open door alert beeps when door has been open for 3 minutes
- Equipped with four 4" swivel casters (2 with brakes)
- Digital control system
- LED interior lighting & temperature display
- Automatic defrost system
- Supplied with integrated condensate evaporator therefore no drain line connection is needed
- Urethane foam insulated walls



MODEL	EXTERNAL DIMENSIONS	INTERNAL DIMENSIONS	NOMINAL CAPACITY	HOLDING TEMPERATURE RANGE	AMP DRAW	SHIPPING WEIGHT	REFRIGERANT AND CHARGE SIZE	DOORS / SHELVES	ELECTRICAL
MXCR-23GDHC	26.8" x 31.9" x 82.3" (681 x 810 x 2090 mm)	22.2" x 27.6" x 50.2" (564 x 700 x 1276 mm)	23 Cu Ft (651 L)	34°F to 41°F (1°C to 5°C)	3A	366 lbs (166 kg)	R-290A 3.0 oz (85 g)	1 / 3	115V / 60Hz / 1Ph
MXCR-49GDHC	53.9" x 31.9" x 82.3" (1369 x 810 x 2090 mm)	49.4" x 27.6" x 50.2" (1254 x 700 x 1276 mm)	49 Cu Ft (1387 L)	34°F to 41°F (1°C to 5°C)	4.5A	597 lbs (272 kg)	R-290A 3.7 oz (105 g)	2 / 6	115V / 60Hz / 1Ph



MXX-23RHC
30.6"W x 29"D x 78"H



MXX-23FHC
30.6"W x 29"D x 78"H

Refrigerator:

MXX-23RHC - Economy reach-in refrigerator; painted steel exterior

Freezer:

MXX-23FHC - Economy reach-in freezer; painted steel exterior

All Models Feature:

- Easy to clean, low maintenance white painted steel exterior and white painted aluminum interior
- Field-reversible hinged door with heavy-duty recessed full-length handle
- Door lock & key set for security
- Three (3) adjustable wire shelves, one (1) fixed half shelf
- Equipped with 2.5" swivel casters (2 with brakes)
- Digital control system
- LED temperature display
- Automatic defrost system
- Door frame heaters
- Easy to clean/replace removable snap-in gaskets
- Supplied with integrated condensate evaporator therefore no drain line connection is needed
- Front-breathing bottom-mounted condensing unit
- Urethane foam insulated walls
- Not equipped with interior lighting



MODEL	EXTERNAL DIMENSIONS	INTERNAL DIMENSIONS	NOMINAL CAPACITY	HOLDING TEMPERATURE RANGE	AMP DRAW	SHIPPING WEIGHT	REFRIGERANT AND CHARGE SIZE	DOORS / SHELVES	ELECTRICAL
MXX-23RHC	30.6" x 29" x 78" (777 x 737 x 1981 mm)	26.3" x 21.6" x 58.9" (668 x 549 x 1496 mm)	23 Cu Ft (651 L)	34°F to 41°F (1°C to 5°C)	3.0A	264 lbs (120 kg)	R-290A 3.35 oz (95 g)	1 / 3	115V / 60Hz / 1Ph
MXX-23FHC	30.6" x 29" x 78" (777 x 737 x 1981 mm)	26.3" x 21.6" x 58.9" (668 x 549 x 1496 mm)	23 Cu Ft (651 L)	-10°F to 10°F (-23°C to -12°C)	7.0A	286 lbs (130 kg)	R-290A 4.23oz (120 g)	1 / 3	115V / 60Hz / 1Ph

SELECT REACH-IN REFRIGERATORS & FREEZERS



MXSR-23FDHC
MXSF-23FDHC
27"W x 32.5"D x 79.7"H



MXSR-49FDHC
MXSF-49FDHC
54.1"W x 32.5"D x 79.7"H

Refrigerators:

MXSR-23FDHC - Upright reach-in refrigerator; stainless steel exterior

MXSR-49FDHC - Upright reach-in refrigerator; stainless steel exterior

Freezers:

MXSF-23FDHC - Upright reach-in freezer; stainless steel exterior

MXSF-49FDHC - Upright reach-in freezer; stainless steel exterior

All Models Feature:

- Stainless Steel Exterior
- Interior: Painted Aluminum
- Interior lighting controlled by an automatic on-off door switch
- Field reversible door (single door models only)
- Supplied with integrated condensate evaporator therefore no drain line connection is needed
- Equipped with door locks and 4" diameter swivel casters (2 with brakes)
- Self-contained, digitally-controlled heavy-duty refrigeration system - forced air for even temperature regulation
- Automatic defrost system
- Self-closing doors with heavy-duty hinges that open to 180°
- Heavy-duty corrosion-resistant shelves and adjustable mounting clips
- Open door alert beeps when door has been open for 3 minutes
- Easy to full-length formed handles



MODEL	EXTERNAL DIMENSIONS	INTERNAL DIMENSIONS	NET CAPACITY	HOLDING TEMPERATURE RANGE	AMP DRAW	UNIT WEIGHT	REFRIGERANT AND CHARGE SIZE	DOORS / SHELVES	ELECTRICAL
MXSR-23FDHC	27" x 32.5" x 79.7" (686 x 825 x 2025 mm)	22.3" x 26.8" x 55" (566 x 680 x 1397 mm)	19.3 Cu Ft (547 L)	33°F to 41°F (1°C to 5°C)	2.8A	300 lbs (136 kg)	R-290a	1 / 3	115V / 60Hz / 1Ph
MXSR-49FDHC	54.1" x 32.5" x 79.7" (1372 x 825 x 2025 mm)	49.3" x 26.8" x 55" (1252 x 680 x 1397 mm)	42.9 Cu Ft (1215 L)	33°F to 41°F (1°C to 5°C)	6.25A	430 lbs (195 kg)	R-290a	2 / 6	115V / 60Hz / 1Ph
MXSF-23FDHC	27" x 32.5" x 79.7" (686 x 825 x 2025 mm)	22.3" x 26.8" x 55" (566 x 680 x 1397 mm)	19.3 Cu Ft (547 L)	-10°F to 10°F (-24°C to -12°C)	6A	310 lbs (141 kg)	R-290a	1 / 3	115V / 60Hz / 1Ph
MXSF-49FDHC	54.1" x 32.5" x 79.7" (1372 x 825 x 2025 mm)	49.3" x 26.8" x 55" (1252 x 680 x 1397 mm)	42.9 Cu Ft (1215 L)	-10°F to 10°F (-24°C to -12°C)	9A	460 lbs (209 kg)	R-290a	2 / 6	115V / 60Hz / 1Ph



MXSR-23GDHC
27"W x 32.5"D x 79.7"H



MXSR-49GDHC
54.1"W x 32.5"D x 79.7"H

Models:

MXSR-23GDHC - Glass door reach-in refrigerator; stainless steel exterior

MXSR-49GDHC - Glass door reach-in refrigerator; stainless steel exterior

All Models Feature:

- Stainless Steel Exterior
- Interior: Stainless Steel
- Interior lighting controlled by a manual on-off switch
- Supplied with integrated condensate evaporator therefore no drain line connection is needed
- Equipped with door locks and 4" diameter swivel casters (2 with brakes)
- Self-contained, digitally-controlled heavy-duty refrigeration system - forced air for even temperature regulation
- Automatic defrost system
- Self-closing doors with heavy-duty hinges that open to 180°
- Heavy-duty corrosion-resistant shelves and adjustable mounting clips
- Open door alert beeps when door has been open for 3 minutes
- Easy to grip curved handles



MODEL	EXTERNAL DIMENSIONS	INTERNAL DIMENSIONS	NET CAPACITY	HOLDING TEMPERATURE RANGE	AMP DRAW	UNIT WEIGHT	REFRIGERANT AND CHARGE SIZE	DOORS / SHELVES	ELECTRICAL
MXSR-23GDHC	27" x 32.5" x 79.7" (686 x 825 x 2025 mm)	22.3" x 26.8" x 55" (566 x 680 x 1397 mm)	19.3 Cu Ft (547 L)	33°F to 41°F (1°C to 5°C)	2.8A	280 lbs (127 kg)	R-290a	1 / 3	115V / 60Hz / 1Ph
MXSR-48GDHC	54.1" x 32.5" x 79.7" (1372 x 825 x 2025 mm)	49.3" x 26.8" x 55" (1252 x 680 x 1397 mm)	42.9 Cu Ft (1215 L)	33°F to 41°F (1°C to 5°C)	6.25A	440 lbs (200 kg)	R-290a	2 / 6	115V / 60Hz / 1Ph