

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA
GHS

Printing date: 22.07.2016

Revision: 22.07.2016


SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name:** Blue Max v.7
- **Article number:** 103555
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
No further relevant information available.
- **Application of the substance / the mixture:** Cleaning agent/ Cleaner
- **1.3 Details of the supplier of the Safety Data Sheet**
- **Manufacturer/Supplier:**
Theochem Laboratories
7373 Rowlett Park Drive
Tampa, FL 33610
Phone: 813-237-6463
- **1.4 Emergency telephone number:**
ChemTel Inc.
(800)255-3924, +1 (813)248-0585



SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**
Skin Irrit. 2 H315 Causes skin irritation.
Eye Irrit. 2 H319 Causes serious eye irritation.

- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008**
The product is classified and labelled according to the Globally Harmonized System within the United States.
The product is classified and labelled according to the CLP regulation.
- **Hazard pictograms**
- 
GHS07
- **Signal word** Warning
- **Hazard-determining components of labelling:**
sodium dodecylbenzenesulphonate
sodium dodecyl sulphate
- **Hazard statements**
H315 Causes skin irritation.
H319 Causes serious eye irritation.
- **Precautionary statements**
P264 Wash thoroughly after handling.
P280 Wear protective gloves / eye protection.

(Cont'd. on page 2)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA
GHS

Printing date: 22.07.2016

Revision: 22.07.2016

Trade name: Blue Max v.7

(Cont'd. from page 1)

P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
 P302+P352 IF ON SKIN: Wash with plenty of water.
 P332+P313 If skin irritation occurs: Get medical advice/attention.
 P337+P313 If eye irritation persists: Get medical advice/attention.
 P362+P364 Take off contaminated clothing and wash it before reuse.

- **NFPA ratings (scale 0 - 4)**



Health = 1
 Fire = 0
 Reactivity = 0

- **HMIS-ratings (scale 0 - 4)**



Health = 1
 Fire = 0
 Reactivity = 0

- **2.3 Other hazards** There are no other hazards not otherwise classified that have been identified.
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

SECTION 3: Composition/information on ingredients

- **3.2 Mixtures**

- **Components:**

CAS: 25155-30-0 EINECS: 246-680-4	sodium dodecylbenzenesulphonate Eye Dam. 1, H318 Acute Tox. 4, H302; Skin Irrit. 2, H315	<10%
CAS: 68585-34-2 NLP: 500-223-8	Dodecyl alcohol ethoxylate (1) Sulfate Sodium Salt Skin Irrit. 2, H315; Eye Irrit. 2, H319	<10%
CAS: 151-21-3 EINECS: 205-788-1	sodium dodecyl sulphate Eye Dam. 1, H318 Acute Tox. 4, H302; Skin Irrit. 2, H315	<3%
CAS: 1300-72-7 EINECS: 215-090-9	sodium xylenesulphonate Eye Irrit. 2, H319	<3%
CAS: 68002-97-1 NLP: 500-182-6	Alcohols, C10-C16, ethoxylated Eye Dam. 1, H318 Aquatic Acute 1, H400 Acute Tox. 4, H302; Skin Irrit. 2, H315	<1%

- **Additional information:**

For the wording of the listed Hazard Statements refer to section 16.

For the listed ingredient(s), the identity and/or exact percentages are being withheld as a trade secret.

(Cont'd. on page 3)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA
GHS

Printing date: 22.07.2016

Revision: 22.07.2016

Trade name: Blue Max v.7

(Cont'd. from page 2)

SECTION 4: First aid measures

- **4.1 Description of first aid measures**
- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:**
Immediately rinse with water.
If skin irritation continues, consult a doctor.
- **After eye contact:**
Remove contact lenses if worn.
Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.
- **After swallowing:**
Rinse out mouth and then drink plenty of water.
Do not induce vomiting; call for medical help immediately.
- **4.2 Most important symptoms and effects, both acute and delayed**
Irritating to eyes and skin.
Gastric or intestinal disorders when ingested.
Nausea in case of ingestion.
- **4.3 Indication of any immediate medical attention and special treatment needed**
Treat symptomatically.

SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:**
The product is not flammable.
Use fire extinguishing methods suitable to surrounding conditions.
- **For safety reasons unsuitable extinguishing agents:** None.
- **5.2 Special hazards arising from the substance or mixture**
Formation of toxic gases is possible during heating or in case of fire.
- **5.3 Advice for firefighters**
- **Protective equipment:**
Wear self-contained respiratory protective device.
Wear fully protective suit.

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**
Ensure adequate ventilation
Particular danger of slipping on leaked/spilled product.
Use personal protective equipment as required.
- **6.2 Environmental precautions**
Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.
- **6.3 Methods and material for containment and cleaning up**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).

(Cont'd. on page 4)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA
GHS

Printing date: 22.07.2016

Revision: 22.07.2016

Trade name: Blue Max v.7

(Cont'd. from page 3)

Clean the affected area carefully; suitable cleaners are:

Warm water

· **6.4 Reference to other sections**

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

SECTION 7: Handling and storage

· **7.1 Precautions for safe handling**

Ensure good ventilation/exhaustion at the workplace.

Prevent formation of aerosols.

Avoid contact with the eyes and skin.

Keep out of reach of children.

· **Information about fire - and explosion protection:** No special measures required.

· **7.2 Conditions for safe storage, including any incompatibilities**

· **Storage:**

· **Requirements to be met by storerooms and receptacles:**

Avoid storage near extreme heat, ignition sources or open flame.

· **Information about storage in one common storage facility:** Store away from foodstuffs.

· **Further information about storage conditions:** Store in cool, dry conditions in well sealed receptacles.

· **7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

· **8.1 Control parameters**

· **Ingredients with limit values that require monitoring at the workplace:**

The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.

· **DNELs:** No further relevant information available.

· **PNECs:** No further relevant information available.

· **8.2 Exposure controls**

· **Personal protective equipment:**

· **General protective and hygienic measures:**

The usual precautionary measures are to be adhered to when handling chemicals.

Keep away from foodstuffs, beverages and feed.

Immediately remove all soiled and contaminated clothing.

Wash hands before breaks and at the end of work.

Avoid contact with the eyes.

Do not inhale gases / fumes / aerosols.

· **Respiratory protection:**

Not required under normal conditions of use.

Use suitable respiratory protective device when aerosol or mist is formed.

For spills, respiratory protection may be advisable.

(Cont'd. on page 5)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA
GHS

Printing date: 22.07.2016

Revision: 22.07.2016

Trade name: Blue Max v.7

(Cont'd. from page 4)

- **Protection of hands:**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

- **For the permanent contact gloves made of the following materials are suitable:** Rubber gloves

- **Eye protection:**



Safety glasses

- **Body protection:**

Not required under normal conditions of use.

Protection may be required for spills.

- **Limitation and supervision of exposure into the environment:**

No further relevant information available.

- **Risk management measures:** See Section 7 for additional information.

SECTION 9: Physical and chemical properties

- **9.1 Information on basic physical and chemical properties**

- **Appearance**

Form: Liquid
Colour: Dark blue

- **Odour:** Pleasant

- **Odour threshold:** Not determined.

- **pH-value at 20 °C (68 °F):** 7,0 - 9,0

- **Melting point/Melting range:** Not determined.

- **Boiling point/Boiling range:** Not determined.

- **Flash point:** Not applicable.

- **Flammability (solid, gaseous):** Not applicable.

- **Auto/Self-ignition temperature:** Not determined.

- **Decomposition temperature:** Not determined.

- **Danger of explosion:** Product does not present an explosion hazard.

- **Explosion limits**

Lower: Not determined.

Upper: Not determined.

- **Vapour pressure:** Not determined.

- **Density at 20 °C (68 °F):** 1,02 - 1,05 g/cm³ (8,512 - 8,762 lbs/gal)

- **Relative density:** Not determined.

- **Vapour density:** Not determined.

(Cont'd. on page 6)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA
GHS

Printing date: 22.07.2016

Revision: 22.07.2016

Trade name: Blue Max v.7

(Cont'd. from page 5)

- | | |
|---|--|
| · Evaporation rate: | Not determined. |
| · Solubility in / Miscibility with water: | Fully miscible. |
| · Partition coefficient (n-octanol/water): | Not determined. |
| · Viscosity | |
| Dynamic: | Not determined. |
| Kinematic: | Not determined. |
| · 9.2 Other information | No further relevant information available. |

SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**
No decomposition if used and stored according to specifications.
- **10.3 Possibility of hazardous reactions**
Reacts with strong acids.
Reacts with strong oxidising agents.
Toxic fumes may be released if heated above the decomposition point.
- **10.4 Conditions to avoid** Store away from oxidising agents.
- **10.5 Incompatible materials**
Strong acids
Oxidizers
- **10.6 Hazardous decomposition products**
Carbon monoxide and carbon dioxide
Sulphur oxides (SO_x)

SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity:** Based on available data, the classification criteria are not met.

LD/LC50 values relevant for classification:

151-21-3 sodium dodecyl sulphate

Oral	LD50	1288 mg/kg (rat)
------	------	------------------

- **Primary irritant effect**
- **Skin corrosion/irritation:**
Causes skin irritation.
- **Serious eye damage/irritation:**
Causes serious eye irritation.
- **Respiratory or skin sensitisation:** Based on available data, the classification criteria are not met.

(Cont'd. on page 7)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA
GHS

Printing date: 22.07.2016

Revision: 22.07.2016

Trade name: Blue Max v.7

(Cont'd. from page 6)

- **Carcinogenic categories**

- **IARC (International Agency for Research on Cancer):**

None of the ingredients are listed.

- **NTP (National Toxicology Program):**

None of the ingredients are listed.

- **OSHA-Ca (Occupational Safety & Health Administration):**

None of the ingredients are listed.

- **Probable routes of exposure:**

Ingestion.

Inhalation

Eye contact.

Skin contact.

- **Acute effects (acute toxicity, irritation and corrosivity):**

Irritating to eyes and skin.

May be harmful if swallowed.

- **Repeated dose toxicity:** No further relevant information available.

- **Germ cell mutagenicity:** Based on available data, the classification criteria are not met.

- **Carcinogenicity:** Based on available data, the classification criteria are not met.

- **Reproductive toxicity:** Based on available data, the classification criteria are not met.

- **STOT-single exposure:** Based on available data, the classification criteria are not met.

- **STOT-repeated exposure:** Based on available data, the classification criteria are not met.

- **Aspiration hazard:** Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

- **12.1 Toxicity**

- **Aquatic toxicity:** The product contains materials that are harmful to the environment.

- **12.2 Persistence and degradability** Biodegradable

- **12.3 Bioaccumulative potential** Does not accumulate in organisms.

- **12.4 Mobility in soil** No further relevant information available.

- **Additional ecological information:**

- **General notes:**

Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

- **12.5 Results of PBT and vPvB assessment**

- **PBT:** Not applicable.

- **vPvB:** Not applicable.

- **12.6 Other adverse effects** No further relevant information available.

(Cont'd. on page 8)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA
GHS

Printing date: 22.07.2016

Revision: 22.07.2016

Trade name: Blue Max v.7

(Cont'd. from page 7)

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Recommendation

Small amounts may be diluted with plenty of water and washed away. Dispose of larger amounts in accordance with Local Authority requirements.

The user of this material has the responsibility to dispose of unused material, residues and containers in compliance with all relevant local, state and federal laws and regulations regarding treatment, storage and disposal for hazardous and nonhazardous wastes.

Uncleaned packaging:

Recommendation: Disposal must be made according to official regulations.

Recommended cleansing agents: Water, if necessary together with cleansing agents.

SECTION 14: Transport information

14.1 UN-Number

DOT, ADR, IMDG, IATA Not Regulated

14.2 UN proper shipping name

DOT, ADR, IMDG, IATA Not Regulated

14.3 Transport hazard class(es)

DOT, ADR, IMDG, IATA
Class Not Regulated

14.4 Packing group

DOT, ADR, IMDG, IATA Not Regulated

14.5 Environmental hazards:

Marine pollutant: No

14.6 Special precautions for user

Not applicable.

14.7 Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

United States (USA)

SARA

Section 355 (extremely hazardous substances):

None of the ingredients are listed.

(Cont'd. on page 9)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA
GHS

Printing date: 22.07.2016

Revision: 22.07.2016

Trade name: Blue Max v.7

(Cont'd. from page 8)

- **Section 313 (Specific toxic chemical listings):**

None of the ingredients are listed.

- **TSCA (Toxic Substances Control Act):**

All ingredients are listed.

- **Proposition 65 (California):**

- **Chemicals known to cause cancer:**

None of the ingredients are listed.

- **Chemicals known to cause reproductive toxicity for females:**

None of the ingredients are listed.

- **Chemicals known to cause reproductive toxicity for males:**

None of the ingredients are listed.

- **Chemicals known to cause developmental toxicity:**

None of the ingredients are listed.

- **Carcinogenic Categories**

- **EPA (Environmental Protection Agency)**

None of the ingredients are listed.

- **IARC (International Agency for Research on Cancer)**

None of the ingredients are listed.

- **NIOSH-Ca (National Institute for Occupational Safety and Health)**

None of the ingredients are listed.

- **Canadian Domestic Substances List (DSL)**

All ingredients are listed.

- **Other regulations, limitations and prohibitive regulations**

- **Substances of very high concern (SVHC) according to REACH, Article 57**

None of the ingredients are listed.

- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Relevant phrases**

H302 Harmful if swallowed.

H315 Causes skin irritation.

H318 Causes serious eye damage.

H319 Causes serious eye irritation.

H400 Very toxic to aquatic life.

- **Abbreviations and acronyms:**

ADR: European Agreement concerning the International Carriage of Dangerous Goods by Road

IMDG: International Maritime Code for Dangerous Goods

(Cont'd. on page 10)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA
GHS

Printing date: 22.07.2016

Revision: 22.07.2016

Trade name: Blue Max v.7

(Cont'd. from page 9)

DOT: US Department of Transportation
IATA: International Air Transport Association
GHS: Globally Harmonised System of Classification and Labelling of Chemicals
EINECS: European Inventory of Existing Commercial Chemical Substances
ELINCS: European List of Notified Chemical Substances
CAS: Chemical Abstracts Service (division of the American Chemical Society)
NFPA: National Fire Protection Association (USA)
HMIS: Hazardous Materials Identification System (USA)
DNEL: Derived No-Effect Level (REACH)
PNEC: Predicted No-Effect Concentration (REACH)
LC50: Lethal concentration, 50 percent
LD50: Lethal dose, 50 percent
PBT: Persistent, Bioaccumulative and Toxic
SVHC: Substances of Very High Concern
vPvB: very Persistent and very Bioaccumulative
NIOSH: National Institute for Occupational Safety
OSHA: Occupational Safety & Health
LDLo: Lowest Lethal Dose Observed
Acute Tox. 4: Acute toxicity – Category 4
Skin Irrit. 2: Skin corrosion/irritation – Category 2
Eye Dam. 1: Serious eye damage/eye irritation – Category 1
Eye Irrit. 2: Serious eye damage/eye irritation – Category 2
Aquatic Acute 1: Hazardous to the aquatic environment - acute aquatic hazard – Category 1

Sources

Website, European Chemicals Agency (echa.europa.eu)
Website, US EPA Substance Registry Services (ofmpub.epa.gov/sor internet/registry/substreg/home/overview/home.do)
Website, Chemical Abstracts Registry, American Chemical Society (www.cas.org)
Patty's Industrial Hygiene, 6th ed., Rose, Vernon, ed. ISBN: ISBN: 978-0-470-07488-6
Casarett and Doull's Toxicology: The Basic Science of Poisons, 8th Ed., Klaasen, Curtis D., ed., ISBN: 978-0-07-176923-5.
Safety Data Sheets, Individual Manufacturers

SDS Prepared by:

ChemTel Inc.

1305 North Florida Avenue

Tampa, Florida USA 33602-2902

Toll Free North America 1-888-255-3924 Intl. +01 813-248-0573

Website: www.chemtelinc.com