

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 12.05.2014

Revision: 12.05.2014

1 Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name:** Burst Low Suds v.3
- **Article number:** 100404; 210404
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
No further relevant information available.
- **Application of the substance / the mixture** Cleaning material/ Detergent
- **1.3 Details of the supplier of the Safety Data Sheet**
- **Manufacturer/Supplier:**
Theochem Laboratories
7373 Rowlett Park Drive
Tampa, FL 33610
Phone: 813-237-6463
- **1.4 Emergency telephone number:**
ChemTel Inc.
(800)255-3924, +1 (813)248-0585



2 Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**



Eye Irrit. 2 H319 Causes serious eye irritation.

- **Classification according to Directive 67/548/EEC or Directive 1999/45/EC**



Xi; Irritant

R36: Irritating to eyes.

- **Information concerning particular hazards for human and environment:**

The product has to be labelled due to the calculation procedure of the "General Classification guideline for preparations of the EU" in the latest valid version.

- **Classification system:**

The classification is according to the latest editions of the EU-lists, and extended by company and literature data.

The classification is in accordance with the latest editions of international substances lists, and is supplemented by information from technical literature and by information provided by the company.

- **2.2 Label elements**

- **Labelling according to Regulation (EC) No 1272/2008**

The product is classified and labelled according to the CLP regulation.

- **Hazard pictograms**



GHS07

(Contd. on page 2)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 12.05.2014

Revision: 12.05.2014

Trade name: **Burst v.3**

(Contd. of page 1)

- **Signal word** Warning
- **Hazard statements**
H319 Causes serious eye irritation.
- **Precautionary statements**
P264 Wash thoroughly after handling.
P280 Wear eye protection.
P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P337+P313 If eye irritation persists: Get medical advice/attention.
P501 Dispose of contents/container in accordance with local/regional/national/international regulations.
- **Hazard description:**
- **WHMIS-symbols:**
D2B - Toxic material causing other toxic effects



- **NFPA ratings (scale 0 - 4)**



- **HMIS-ratings (scale 0 - 4)**



- **HMIS Long Term Health Hazard Substances**

None of the ingredients is listed.

- **2.3 Other hazards**
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

3 Composition/information on ingredients

- **3.2 Mixtures**
- **Description:** Mixture of substances listed below with nonhazardous additions.

(Contd. on page 3)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS







Printing date 12.05.2014

Revision: 12.05.2014

Trade name: **Burst v.3**

(Contd. of page 2)

· Dangerous components:

CAS: 497-19-8 EINECS: 207-838-8 Index number: 011-005-00-2	sodium carbonate  Xi R36  Eye Irrit. 2, H319	25-50%
CAS: 10213-79-3 EINECS: 229-912-9	Disodium Metasilicate Pentahydrate  C R34;  Xi R37  Skin Corr. 1B, H314  STOT SE 3, H335	1-5%

· **Additional information:** For the wording of the listed risk phrases refer to section 16.

4 First aid measures

- **4.1 Description of first aid measures**
- **General information:** Immediately remove any clothing soiled by the product.
- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:**
Brush off loose particles from skin.
Immediately rinse with water.
If skin irritation continues, consult a doctor.
- **After eye contact:**
Remove contact lenses if worn.
Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.
- **After swallowing:**
Rinse out mouth and then drink plenty of water.
Do not induce vomiting; call for medical help immediately.
- **4.2 Most important symptoms and effects, both acute and delayed**
Slight irritant effect on skin and mucous membranes.
Irritant to eyes.
Gastric or intestinal disorders when ingested.
Nausea in case of ingestion.
- **Hazards** No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

5 Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:** Use fire extinguishing methods suitable to surrounding conditions.
- **For safety reasons unsuitable extinguishing agents:** None.
- **5.2 Special hazards arising from the substance or mixture**
Formation of toxic gases is possible during heating or in case of fire.
- **5.3 Advice for firefighters**
- **Protective equipment:**
Wear self-contained respiratory protective device.
Wear fully protective suit.

(Contd. on page 4)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 12.05.2014

Revision: 12.05.2014

Trade name: **Burst v.3**

(Contd. of page 3)

- **Additional information** No further relevant information available.

6 Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**

Use respiratory protective device against the effects of fumes/dust/aerosol.

Wear protective equipment. Keep unprotected persons away.

Ensure adequate ventilation

Product forms slippery surface when combined with water.

- **6.2 Environmental precautions:**

Do not allow to enter sewers/ surface or ground water.

Damp down dust with water spray.

- **6.3 Methods and material for containment and cleaning up:**

Pick up mechanically.

Dispose contaminated material as waste according to item 13.

Clean the affected area carefully; suitable cleaners are:

Warm water

- **6.4 Reference to other sections**

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

7 Handling and storage

- **7.1 Precautions for safe handling**

Store in cool, dry place in tightly closed receptacles.

Prevent formation of dust.

Any unavoidable deposit of dust must be regularly removed.

- **Information about fire - and explosion protection:** No special measures required.

- **7.2 Conditions for safe storage, including any incompatibilities**

- **Storage:**

- **Requirements to be met by storerooms and receptacles:**

Avoid storage near extreme heat, ignition sources or open flame.

Protect from humidity and water.

- **Information about storage in one common storage facility:**

Store away from foodstuffs.

Do not store together with oxidizing and acidic materials.

- **Further information about storage conditions:**

Store in dry conditions.

This product is hygroscopic.

- **7.3 Specific end use(s)** No further relevant information available.

(Contd. on page 5)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS


Printing date 12.05.2014

Revision: 12.05.2014

Trade name: Burst v.3

(Contd. of page 4)

8 Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see item 7.
 - **8.1 Control parameters**
 - **Ingredients with limit values that require monitoring at the workplace:**
The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.
 - **DNELs** No further relevant information available.
 - **PNECs** No further relevant information available.
 - **Additional information:** The lists valid during the making were used as basis.
 - **8.2 Exposure controls**
 - **Personal protective equipment:**
 - **General protective and hygienic measures:**
The usual precautionary measures are to be adhered to when handling chemicals.
Keep away from foodstuffs, beverages and feed.
Immediately remove all soiled and contaminated clothing.
Wash hands before breaks and at the end of work.
Do not inhale dust / smoke / mist.
Avoid close or long term contact with the skin.
Avoid contact with the eyes.
 - **Respiratory protection:**
Not required under normal conditions of use.
For spills, respiratory protection may be advisable.
 - **Protection of hands:**
Wear protective gloves to handle contents of damaged or leaking units.
The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.
Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation.
 - **Material of gloves**
The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.
 - **Penetration time of glove material**
The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.
 - **Eye protection:**
-  Safety glasses
- **Body protection:** Protective work clothing
 - **Limitation and supervision of exposure into the environment**
No further relevant information available.
 - **Risk management measures**
See Section 7 for additional information.

(Contd. on page 6)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 12.05.2014

Revision: 12.05.2014

Trade name: Burst v.3

No further relevant information available.

(Contd. of page 5)

9 Physical and chemical properties

· 9.1 Information on basic physical and chemical properties

· General Information

· Appearance:

Form: Powder

Colour: White

· Odour: Citrus.

· Odour threshold: Not determined.

· pH-value: Not applicable.

· Change in condition

Melting point/Melting range: Not Determined.

Boiling point/Boiling range: Undetermined.

· Flash point: Not applicable.

· Flammability (solid, gaseous): Not determined.

· Auto/Self-ignition temperature: Not determined.

· Decomposition temperature: Not determined.

· Self-igniting: Product is not self-igniting.

· Danger of explosion: Product does not present an explosion hazard.

· Explosion limits:

Lower: Not determined.

Upper: Not determined.

· Vapour pressure: Not applicable.

· Density at 20 °C: 1,00 - 1,20 g/cm³

· Relative density: Not determined.

· Vapour density: Not applicable.

· Evaporation rate: Not applicable.

· Solubility in / Miscibility with water:

Soluble.

· Partition coefficient (n-octanol/water): Not determined.

· Viscosity:

Dynamic: Not applicable.

Kinematic: Not applicable.

· 9.2 Other information: No further relevant information available.

(Contd. on page 7)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 12.05.2014

Revision: 12.05.2014

Trade name: Burst v.3

(Contd. of page 6)

10 Stability and reactivity

- **10.1 Reactivity**
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**
No decomposition if used and stored according to specifications.
- **10.3 Possibility of hazardous reactions**
Reacts with strong acids and oxidizing agents.
As the product is supplied it is not capable of dust explosion; however enrichment with fine dust causes risk of dust explosion.
Toxic fumes may be released if heated above the decomposition point.
- **10.4 Conditions to avoid**
Store away from oxidizing agents.
Moisture.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:**
Carbon monoxide and carbon dioxide
Chlorine compounds

11 Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity:**
- **Primary irritant effect:**
- **on the skin:** Slight irritant effect on skin and mucous membranes.
- **on the eye:** Irritating effect.
- **Sensitization:** No sensitizing effects known.
- **Additional toxicological information:**
The product shows the following dangers according to the calculation method of the General EU Classification Guidelines for Preparations as issued in the latest version:
Irritant

12 Ecological information

- **12.1 Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Ecotoxicological effects:**
- **Remark:** After neutralization a reduction of the harming action may be recognized
- **Additional ecological information:**
- **General notes:**
Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.
Rinse off of bigger amounts into drains or the aquatic environment may lead to increased pH-values. A high pH-value harms aquatic organisms. In the dilution of the use-level the pH-value is considerably

(Contd. on page 8)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 12.05.2014

Revision: 12.05.2014

Trade name: **Burst v.3**

(Contd. of page 7)

reduced, so that after the use of the product the aqueous waste, emptied into drains, is only low water-dangerous.

- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

13 Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation**

Small amounts may be diluted with plenty of water and washed away. Dispose of bigger amounts in accordance with Local Authority requirements.

Can be disposed of with household garbage with prior chemical-physical or biological treatment following consultation with the waste disposal facility operator and the pertinent authorities and adhering to the necessary technical regulations.

- **Uncleaned packaging:**
- **Recommendation:** Disposal must be made according to official regulations.
- **Recommended cleansing agents:** Water, if necessary together with cleansing agents.

14 Transport information

- **14.1 UN-Number**
- **DOT, ADR, ADN, IMDG, IATA** Not Regulated
- **14.2 UN proper shipping name**
- **DOT, ADR, ADN, IMDG, IATA** Not Regulated
- **14.3 Transport hazard class(es)**
- **DOT, ADR, ADN, IMDG, IATA**
- **Class** Not Regulated
- **14.4 Packing group**
- **DOT, ADR, IMDG, IATA** Not Regulated
- **14.5 Environmental hazards:**
- **Marine pollutant:** No
- **14.6 Special precautions for user** Not applicable.
- **14.7 Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code** Not applicable.
- **UN "Model Regulation":** -

(Contd. on page 9)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 12.05.2014

Revision: 12.05.2014

Trade name: Burst v.3

(Contd. of page 8)

15 Regulatory information

- 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture
- United States (USA)
- SARA

- Section 355 (extremely hazardous substances):

None of the ingredients is listed.

- Section 313 (Specific toxic chemical listings):

None of the ingredients is listed.

- TSCA (Toxic Substances Control Act):

All ingredients are listed.

- Proposition 65 (California):

- Chemicals known to cause cancer:

None of the ingredients is listed.

- Chemicals known to cause reproductive toxicity for females:

None of the ingredients is listed.

- Chemicals known to cause reproductive toxicity for males:

None of the ingredients is listed.

- Chemicals known to cause developmental toxicity:

None of the ingredients is listed.

- Carcinogenic Categories

- EPA (Environmental Protection Agency)

None of the ingredients is listed.

- IARC (International Agency for Research on Cancer)

None of the ingredients is listed.

- TLV (Threshold Limit Value established by ACGIH)

None of the ingredients is listed.

- NIOSH-Ca (National Institute for Occupational Safety and Health)

None of the ingredients is listed.

- Canada

- Canadian Domestic Substances List (DSL)

All ingredients are listed.

- Canadian Ingredient Disclosure list (limit 0.1%)

None of the ingredients is listed.

- Canadian Ingredient Disclosure list (limit 1%)

497-19-8 | sodium carbonate

(Contd. on page 10)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 12.05.2014

Revision: 12.05.2014

Trade name: **Burst v.3**

(Contd. of page 9)

- **Other regulations, limitations and prohibitive regulations**

- **Substances of very high concern (SVHC) according to REACH, Article 57**

None of the ingredients is listed.

- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Relevant phrases**

H314 Causes severe skin burns and eye damage.

H319 Causes serious eye irritation.

H335 May cause respiratory irritation.

R34 Causes burns.

R36 Irritating to eyes.

R37 Irritating to respiratory system.

- **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

DOT: US Department of Transportation

IATA: International Air Transport Association

GHS: Globally Harmonized System of Classification and Labelling of Chemicals

ACGIH: American Conference of Governmental Industrial Hygienists

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

NFPA: National Fire Protection Association (USA)

HMIS: Hazardous Materials Identification System (USA)

WHMIS: Workplace Hazardous Materials Information System (Canada)

DNEL: Derived No-Effect Level (REACH)

PNEC: Predicted No-Effect Concentration (REACH)

Skin Corr. 1B: Skin corrosion/irritation, Hazard Category 1B

Eye Irrit. 2: Serious eye damage/eye irritation, Hazard Category 2

STOT SE 3: Specific target organ toxicity - Single exposure, Hazard Category 3

- **Sources**

SDS Prepared by:

ChemTel Inc.

1305 North Florida Avenue

Tampa, Florida USA 33602-2902

Toll Free North America 1-888-255-3924 Intl. +01 813-248-0573

Website: www.chemtelinc.com