

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 30.04.2014

Revision: 30.04.2014

1 Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name:** D-O v.3
- **Article number:** 101553
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
No further relevant information available.
- **Application of the substance / the mixture** Odour neutralising agent
- **1.3 Details of the supplier of the Safety Data Sheet**
- **Manufacturer/Supplier:**
Theochem Laboratories
7373 Rowlett Park Drive
Tampa, FL 33610
Phone: 813-237-6463
- **Further information obtainable from:** Product Safety Department
- **1.4 Emergency telephone number:**
ChemTel Inc.
(800)255-3924, +1 (813)248-0585



2 Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**
The product is not classified as hazardous according to GHS regulations.
The product is not classified as hazardous according to the CLP regulation.
- **Classification according to Directive 67/548/EEC or Directive 1999/45/EC** Not applicable.
- **Information concerning particular hazards for human and environment:**
The product does not have to be labelled due to the calculation procedure of the "General Classification guideline for preparations of the EU" in the latest valid version.
- **Classification system:**
The classification is according to the latest editions of the EU-lists, and extended by company and literature data.
The classification is in accordance with the latest editions of international substances lists, and is supplemented by information from technical literature and by information provided by the company.
- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008** Not Regulated
- **Hazard pictograms** Not Regulated
- **Signal word** Not Regulated
- **Hazard-determining components of labelling:** None.
- **Hazard statements** Not Regulated
- **Additional information:**
Safety data sheet available on request.
- **Hazard description:**
- **WHMIS-symbols:** Not hazardous under WHMIS.

(Contd. on page 2)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 30.04.2014

Revision: 30.04.2014

Trade name: D-O v.3

(Contd. of page 1)

- **NFPA ratings (scale 0 - 4)**



- **HMIS-ratings (scale 0 - 4)**



- **HMIS Long Term Health Hazard Substances**

None of the ingredients is listed.

- **2.3 Other hazards**
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

3 Composition/information on ingredients

- **3.2 Mixtures**

- **Description:** Mixture of substances listed below with nonhazardous additions.

- **Dangerous components:**

None in reportable quantities.

CAS: 64-17-5 EINECS: 200-578-6 Index number: 603-002-00-5	ethanol F R11 Flam. Liq. 2, H225	< 10%
CAS: 68439-46-3 NLP: 500-446-0	alcohols, C9-11, ethoxylated Xi R38-41 Eye Dam. 1, H318 Skin Irrit. 2, H315	< 10%
CAS: 68424-85-1 EINECS: 270-325-2	Alkyl (C12,C14,C16) Dimethyl Benzyl Ammonium Chloride C R34; Xn R22; Xi R41; N R50 Flam. Liq. 3, H226 Skin Corr. 1B, H314 Aquatic Acute 1, H400 Acute Tox. 4, H302	< 10%

- **Additional information:** For the wording of the listed risk phrases refer to section 16.

4 First aid measures

- **4.1 Description of first aid measures**

- **General information:** No special measures required.
- **After inhalation:** Supply fresh air; consult doctor in case of complaints.

(Contd. on page 3)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 30.04.2014

Revision: 30.04.2014

Trade name: D-O v.3

(Contd. of page 2)

- **After skin contact:**
Immediately wash with water and soap and rinse thoroughly.
If skin irritation continues, consult a doctor.
- **After eye contact:**
Remove contact lenses if worn.
Rinse opened eye for several minutes under running water. Then consult a doctor.
- **After swallowing:**
Rinse out mouth and then drink plenty of water.
Do not induce vomiting; call for medical help immediately.
- **4.2 Most important symptoms and effects, both acute and delayed**
Headache
Dizziness
- **Hazards** Condition may deteriorate with alcohol consumption.
- **4.3 Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

5 Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:** Use fire extinguishing methods suitable to surrounding conditions.
- **For safety reasons unsuitable extinguishing agents:** None.
- **5.2 Special hazards arising from the substance or mixture**
Under certain fire conditions, traces of other toxic gases cannot be excluded.
- **5.3 Advice for firefighters**
- **Protective equipment:**
Wear self-contained respiratory protective device.
Wear fully protective suit.
- **Additional information** Cool endangered receptacles with water spray.

6 Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**
Ensure adequate ventilation
Particular danger of slipping on leaked/spilled product.
Wear protective equipment. Keep unprotected persons away.
- **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
Pick up mechanically.
Clean the affected area carefully; suitable cleaners are:
Warm water
- **6.4 Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.

(Contd. on page 4)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 30.04.2014

Revision: 30.04.2014

Trade name: D-O v.3

See Section 13 for disposal information.

(Contd. of page 3)

7 Handling and storage

- **7.1 Precautions for safe handling** Ensure good ventilation/exhaustion at the workplace.
- **Information about fire - and explosion protection:** No special measures required.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:**
Store in a cool location.
Avoid storage near extreme heat, ignition sources or open flame.
- **Information about storage in one common storage facility:**
Store away from foodstuffs.
Do not store together with oxidizing and acidic materials.
- **Further information about storage conditions:**
Keep container tightly sealed.
Protect from frost.
- **7.3 Specific end use(s)** No further relevant information available.

8 Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see item 7.
- **8.1 Control parameters**

· **Ingredients with limit values that require monitoring at the workplace:**

64-17-5 ethanol

PEL (USA)	1900 mg/m ³ , 1000 ppm
REL (USA)	1900 mg/m ³ , 1000 ppm
TLV (USA)	Short-term value: 1880 mg/m ³ , 1000 ppm
EL (Canada)	Short-term value: 1000 ppm
EV (Canada)	1,900 mg/m ³ , 1,000 ppm

- **DNELs** No further relevant information available.
- **PNECs** No further relevant information available.
- **Additional information:** The lists valid during the making were used as basis.
- **8.2 Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**
Keep away from foodstuffs, beverages and feed.
Immediately remove all soiled and contaminated clothing.
Wash hands before breaks and at the end of work.
Avoid contact with the eyes and skin.
Do not inhale gases / fumes / aerosols.
- **Respiratory protection:** Use suitable respiratory protective device in case of insufficient ventilation.

(Contd. on page 5)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 30.04.2014

Revision: 30.04.2014

Trade name: D-O v.3

(Contd. of page 4)

- **Protection of hands:**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation. Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation.

- **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

- **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

- **For the permanent contact gloves made of the following materials are suitable:** Rubber gloves

- **Eye protection:**

Contact lenses should not be worn.



Safety glasses

- **Body protection:** Protective work clothing

- **Limitation and supervision of exposure into the environment**

No further relevant information available.

- **Risk management measures**

See Section 7 for additional information.

No further relevant information available.

9 Physical and chemical properties

- **9.1 Information on basic physical and chemical properties**

- **General Information**

- **Appearance:**

Form: Liquid

Colour: Yellow

- **Odour:** Pleasant

- **Odour threshold:** Not determined.

- **pH-value at 20 °C:** 5,0 - 8,0

- **Change in condition**

Melting point/Melting range: Not Determined.

Boiling point/Boiling range: 212 °F / 100 °C

(Contd. on page 6)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 30.04.2014

Revision: 30.04.2014

Trade name: D-O v.3

(Contd. of page 5)

- **Flash point:** Not applicable.
- **Flammability (solid, gaseous):** Not applicable.
- **Auto/Self-ignition temperature:** Not determined.
- **Decomposition temperature:** Not determined.
- **Self-igniting:** Product is not self-igniting.
- **Danger of explosion:** Product does not present an explosion hazard.
- **Explosion limits:**
 - Lower:** Not determined.
 - Upper:** Not determined.
- **Vapour pressure at 20 °C:** 23 hPa
- **Density at 20 °C:** 0,98 - 1,00 g/cm³
- **Relative density** Not determined.
- **Vapour density** Not determined.
- **Evaporation rate** Not determined.
- **Solubility in / Miscibility with water:** Fully miscible.
- **Partition coefficient (n-octanol/water):** Not determined.
- **Viscosity:**
 - Dynamic:** Not determined.
 - Kinematic:** Not determined.
- **9.2 Other information** No further relevant information available.

10 Stability and reactivity

- **10.1 Reactivity**
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**
No decomposition if used and stored according to specifications.
- **10.3 Possibility of hazardous reactions**
Reacts with strong acids and oxidizing agents.
Contact with acids releases toxic gases.
- **10.4 Conditions to avoid** Store away from oxidizing agents.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:**
Carbon monoxide and carbon dioxide
Nitrogen oxides
Hydrogen chloride (HCl)
Chlorine compounds

(Contd. on page 7)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 30.04.2014

Revision: 30.04.2014

Trade name: D-O v.3

(Contd. of page 6)

11 Toxicological information

- **11.1 Information on toxicological effects**

- **Acute toxicity:**

- **Primary irritant effect:**

- **on the skin:** No irritant effect.

- **on the eye:** Slight irritant effect on eyes.

- **Sensitization:** No sensitizing effects known.

- **Additional toxicological information:**

The product is not subject to classification according to the calculation method of the General EU Classification Guidelines for Preparations as issued in the latest version.

When used and handled according to specifications, the product does not have any harmful effects to our experience and the information provided to us.

12 Ecological information

- **12.1 Toxicity**

- **Aquatic toxicity:** The product contains materials that are harmful to the environment.

- **12.2 Persistence and degradability** No further relevant information available.

- **12.3 Bioaccumulative potential** No further relevant information available.

- **12.4 Mobility in soil** No further relevant information available.

- **Additional ecological information:**

- **General notes:**

This statement was deduced from the properties of the single components.

Avoid transfer into the environment.

Due to available data on eliminability/decomposition and bioaccumulation potential prolonged term damage of the environment can not be excluded.

Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

- **12.5 Results of PBT and vPvB assessment**

- **PBT:** Not applicable.

- **vPvB:** Not applicable.

- **12.6 Other adverse effects** No further relevant information available.

13 Disposal considerations

- **13.1 Waste treatment methods**

- **Recommendation**

Must not be disposed together with household garbage. Do not allow product to reach sewage system.

Small amounts may be diluted with plenty of water and washed away. Dispose of bigger amounts in accordance with Local Authority requirements.

Can be burned with household garbage after consulting with the waste disposal facility operator and the pertinent authorities and adhering to the necessary technical regulations.

- **Uncleaned packaging:**

- **Recommendation:** Disposal must be made according to official regulations.

(Contd. on page 8)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 30.04.2014

Revision: 30.04.2014

Trade name: D-O v.3

(Contd. of page 7)

- **Recommended cleansing agents:** Water, if necessary together with cleansing agents.

14 Transport information

- **14.1 UN-Number**
- **DOT, ADR, ADN, IMDG, IATA** Not Regulated
- **14.2 UN proper shipping name**
- **DOT, ADR, ADN, IMDG, IATA** Not Regulated
- **14.3 Transport hazard class(es)**
- **DOT, ADR, ADN, IMDG, IATA**
- **Class** Not Regulated
- **14.4 Packing group**
- **DOT, ADR, IMDG, IATA** Not Regulated
- **14.5 Environmental hazards:**
- **Marine pollutant:** No
- **14.6 Special precautions for user** Not applicable.
- **Danger code (Kemler):** -
- **14.7 Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code** Not applicable.
- **UN "Model Regulation":** -

15 Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **United States (USA)**
- **SARA**

- **Section 355 (extremely hazardous substances):**

None of the ingredients is listed.

- **Section 313 (Specific toxic chemical listings):**

None of the ingredients is listed.

- **TSCA (Toxic Substances Control Act):**

All ingredients are listed.

- **Proposition 65 (California):**

- **Chemicals known to cause cancer:**

None of the ingredients is listed.

- **Chemicals known to cause reproductive toxicity for females:**

None of the ingredients is listed.

- **Chemicals known to cause reproductive toxicity for males:**

None of the ingredients is listed.

- **Chemicals known to cause developmental toxicity:**

Ethanol - listing refers specifically to alcoholic beverage consumption and is not applicable for product.

(Contd. on page 9)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 30.04.2014

Revision: 30.04.2014

Trade name: D-O v.3

(Contd. of page 8)

64-17-5 ethanol

- **Carcinogenic Categories**

- **EPA (Environmental Protection Agency)**

None of the ingredients is listed.

- **IARC (International Agency for Research on Cancer)**

None of the ingredients is listed.

- **TLV (Threshold Limit Value established by ACGIH)**

64-17-5 ethanol

A3

- **NIOSH-Ca (National Institute for Occupational Safety and Health)**

None of the ingredients is listed.

- **Canada**

- **Canadian Domestic Substances List (DSL)**

All ingredients are listed.

- **Canadian Ingredient Disclosure list (limit 0.1%)**

64-17-5 ethanol

- **Canadian Ingredient Disclosure list (limit 1%)**

None of the ingredients is listed.

- **Other regulations, limitations and prohibitive regulations**

- **Substances of very high concern (SVHC) according to REACH, Article 57**

None of the ingredients is listed.

- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Relevant phrases**

H225 Highly flammable liquid and vapour.

H226 Flammable liquid and vapour.

H302 Harmful if swallowed.

H314 Causes severe skin burns and eye damage.

H315 Causes skin irritation.

H318 Causes serious eye damage.

H400 Very toxic to aquatic life.

R11 Highly flammable.

R22 Harmful if swallowed.

R34 Causes burns.

R38 Irritating to skin.

R41 Risk of serious damage to eyes.

R50 Very toxic to aquatic organisms.

(Contd. on page 10)

Safety Data Sheet
according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and
GHS

Printing date 30.04.2014

Revision: 30.04.2014

Trade name: D-O v.3

(Contd. of page 9)

· Abbreviations and acronyms:

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)
IMDG: International Maritime Code for Dangerous Goods
DOT: US Department of Transportation
IATA: International Air Transport Association
GHS: Globally Harmonized System of Classification and Labelling of Chemicals
ACGIH: American Conference of Governmental Industrial Hygienists
EINECS: European Inventory of Existing Commercial Chemical Substances
ELINCS: European List of Notified Chemical Substances
CAS: Chemical Abstracts Service (division of the American Chemical Society)
NFPA: National Fire Protection Association (USA)
HMIS: Hazardous Materials Identification System (USA)
WHMIS: Workplace Hazardous Materials Information System (Canada)
DNEL: Derived No-Effect Level (REACH)
PNEC: Predicted No-Effect Concentration (REACH)
Flam. Liq. 2: Flammable liquids, Hazard Category 2
Flam. Liq. 3: Flammable liquids, Hazard Category 3
Acute Tox. 4: Acute toxicity, Hazard Category 4
Skin Corr. 1B: Skin corrosion/irritation, Hazard Category 1B
Skin Irrit. 2: Skin corrosion/irritation, Hazard Category 2
Eye Dam. 1: Serious eye damage/eye irritation, Hazard Category 1
Aquatic Acute 1: Hazardous to the aquatic environment - AcuteHazard, Category 1

· Sources

SDS Prepared by:
ChemTel Inc.
1305 North Florida Avenue
Tampa, Florida USA 33602-2902
Toll Free North America 1-888-255-3924 Intl. +01 813-248-0573
Website: www.chemtelinc.com