

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA
GHS

Printing date: 06 February 2020


Revision: 06 February 2020

SECTION 1: Identification of the substance/mixture and of the company/ undertaking

- **1.1 Product identifier**
- **Trade name:** Clean Step v.7
- **Article number:** 200000; 100120
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
No further relevant information available.
- **Application of the substance / the mixture:** Detergents
- **1.3 Details of the supplier of the Safety Data Sheet**
- **Manufacturer/Supplier:**
Theochem Laboratories
7373 Rowlett Park Drive
Tampa, FL 33610
Phone: 813-237-6463
- **1.4 Emergency telephone number:**
ChemTel Inc.
(800)255-3924 (North America)
+1 (813)248-0585 (International)



SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**
Skin Irrit. 2 H315 Causes skin irritation.
Eye Irrit. 2 H319 Causes serious eye irritation.
- **Additional information:**
There are no other hazards not otherwise classified that have been identified.
0 % of the mixture consists of component(s) of unknown toxicity.
- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008**
The product is classified and labelled according to the Globally Harmonized System within the United States.
The product is classified and labelled according to the CLP regulation.
- **Hazard pictograms**

GHS07
- **Signal word** Warning
- **Hazard-determining components of labelling:**
sodium dodecylbenzenesulphonate
- **Hazard statements**
H315 Causes skin irritation.
H319 Causes serious eye irritation.
- **Precautionary statements**
P264 Wash thoroughly after handling.

(Cont'd. on page 2)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA
GHS

Printing date: 06 February 2020


Revision: 06 February 2020

Trade name: Clean Step v.7

(Cont'd. from page 1)

P280 Wear protective gloves / eye protection / face protection.
 P302+P352 IF ON SKIN: Wash with plenty of water.
 P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
 P332+P313 If skin irritation occurs: Get medical advice/attention.
 P337+P313 If eye irritation persists: Get medical advice/attention.

- **NFPA ratings (scale 0 - 4)**



- **HMS-ratings (scale 0 - 4)**



- **2.3 Other hazards** There are no other hazards not otherwise classified that have been identified.
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

SECTION 3: Composition/information on ingredients

- **3.2 Mixtures**

- **Components:**

| | | |
|--|--|--------|
| CAS: 497-19-8 EINECS: 207-838-8 Index number: 011-005-00-2 Reg.nr.: 01-2119485498-19-XXXX | sodium carbonate Eye Irrit. 2, H319 | 10-25% |
| CAS: 25155-30-0 EINECS: 246-680-4 Reg.nr.: 01-2120088038-51-XXXX | sodium dodecylbenzenesulphonate Eye Dam. 1, H318 Acute Tox. 4, H302; Skin Irrit. 2, H315 | <10% |
| CAS: 1344-09-8 Reg.nr.: 01-2119448725-31-XXXX | silicic acid, sodium salt Met. Corr.1, H290; Skin Corr. 1B, H314; Eye Dam. 1, H318 | <10% |

- **Additional information:**

For the listed ingredient(s), the identity and/or exact percentages are being withheld as a trade secret.

SECTION 4: First aid measures

- **4.1 Description of first aid measures**

- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:**
Immediately wash with water and soap and rinse thoroughly.
If skin irritation continues, consult a doctor.

(Cont'd. on page 3)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA
GHS

Printing date: 06 February 2020

Revision: 06 February 2020

Trade name: Clean Step v.7

(Cont'd. from page 2)

- **After eye contact:**
Remove contact lenses if worn.
Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.
- **After swallowing:**
Rinse out mouth and then drink plenty of water.
Do not induce vomiting; call for medical help immediately.
- **4.2 Most important symptoms and effects, both acute and delayed**
Nausea
Cramp
Coughing
Dizziness
Irritating to eyes and skin.
- **4.3 Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:**
CO₂, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **For safety reasons unsuitable extinguishing agents:** None.
- **5.2 Special hazards arising from the substance or mixture**
Formation of toxic gases is possible during heating or in case of fire.
- **5.3 Advice for firefighters**
- **Protective equipment:**
Wear self-contained respiratory protective device.
Wear fully protective suit.

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**
Wear protective equipment. Keep unprotected persons away.
Product forms slippery surface when combined with water.
Ensure adequate ventilation
- **6.2 Environmental precautions**
Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.
- **6.3 Methods and material for containment and cleaning up**
Pick up mechanically.
Send for recovery or disposal in suitable receptacles.
- **6.4 Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

(Cont'd. on page 4)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA
GHS

Printing date: 06 February 2020

Revision: 06 February 2020

Trade name: Clean Step v.7

(Cont'd. from page 3)

SECTION 7: Handling and storage

- **7.1 Precautions for safe handling**
 - Prevent formation of dust.
 - Avoid breathing dust.
 - Keep out of reach of children.
- **Information about fire - and explosion protection:** No special measures required.
- **7.2 Conditions for safe storage, including any incompatibilities**
 - **Storage:**
 - **Requirements to be met by storerooms and receptacles:**
 - Protect from humidity and water.
 - Avoid storage near extreme heat, ignition sources or open flame.
 - **Information about storage in one common storage facility:**
 - Store away from foodstuffs.
 - Store away from oxidising agents.
 - **Further information about storage conditions:**
 - Store in cool, dry conditions in well sealed receptacles.
 - This product is hygroscopic.
 - Protect from humidity and water.
- **7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

- **8.1 Control parameters**
- **Ingredients with limit values that require monitoring at the workplace:**
 - The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.
- **DNELs:** No further relevant information available.
- **PNECs:** No further relevant information available.
- **8.2 Exposure controls**
 - **Personal protective equipment:**
 - **General protective and hygienic measures:**
 - The usual precautionary measures are to be adhered to when handling chemicals.
 - Keep away from foodstuffs, beverages and feed.
 - Immediately remove all soiled and contaminated clothing.
 - Wash hands before breaks and at the end of work.
 - Avoid contact with the eyes and skin.
 - **Respiratory protection:**
 - Not required under normal conditions of use.
 - For spills, respiratory protection may be advisable.
 - **Protection of hands:**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

- **For the permanent contact gloves made of the following materials are suitable:**

(Cont'd. on page 5)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA
GHS

Printing date: 06 February 2020

Revision: 06 February 2020

Trade name: Clean Step v.7

(Cont'd. from page 4)

Butyl rubber, BR
Neoprene gloves

- **Eye protection:**



Safety glasses

- **Body protection:**

Protection may be required for spills.
Not required under normal conditions of use.

- **Limitation and supervision of exposure into the environment:**

No further relevant information available.

- **Risk management measures:** No further relevant information available.

SECTION 9: Physical and chemical properties

- **9.1 Information on basic physical and chemical properties**

- **Appearance**

| | |
|------------------|-----------------|
| Form: | Beads |
| Colour: | Light Green. |
| Odour: | Fresh Island. |
| Odour threshold: | Not determined. |

- pH-value at 20 °C (68 °F): <11.0 (1% solution)

- Melting point/freezing point: Not determined.

- Initial boiling point and boiling range: Not determined.

- Flash point: Not applicable.

- Flammability (solid, gas): Not determined.

- Auto/Self-ignition temperature: Not determined.

- Decomposition temperature: Not determined.

- Explosive properties: Product does not present an explosion hazard.

- **Explosion limits**

- Lower: Not determined.

- Upper: Not determined.

- Oxidising properties: Non-oxidising.

- Vapour pressure: Not applicable.

- **Density:**

- Relative density: 0.5

- Vapour density: Not applicable.

- Evaporation rate: Not applicable.

- Solubility in / Miscibility with water:

Soluble.

(Cont'd. on page 6)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA
GHS

Printing date: 06 February 2020

Revision: 06 February 2020

Trade name: Clean Step v.7

(Cont'd. from page 5)

- **Partition coefficient: n-octanol/water:** Not determined.
- **Viscosity**
 - Dynamic:** Not applicable.
 - Kinematic:** Not applicable.
- **9.2 Other information** No further relevant information available.

SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**
No decomposition if used and stored according to specifications.
- **10.3 Possibility of hazardous reactions**
Exothermic reaction with acids.
As the product is supplied it is not capable of dust explosion; however enrichment with fine dust causes risk of dust explosion.
Reacts with light alloys in the presence of moisture to form hydrogen.
- **10.4 Conditions to avoid** Prevent formation of dust.
- **10.5 Incompatible materials** No further relevant information available.
- **10.6 Hazardous decomposition products**
Carbon monoxide and carbon dioxide
Sulphur oxides (SO_x)

SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity:** Based on available data, the classification criteria are not met.
- **LD/LC50 values relevant for classification:** None.
- **Primary irritant effect**
- **Skin corrosion/irritation:**
Causes skin irritation.
- **Serious eye damage/irritation:**
Causes serious eye irritation.
- **Respiratory or skin sensitisation:** Based on available data, the classification criteria are not met.
- **Carcinogenic categories**

· **IARC (International Agency for Research on Cancer):**

None of the ingredients are listed.

· **NTP (National Toxicology Program):**

None of the ingredients are listed.

· **OSHA-Ca (Occupational Safety & Health Administration):**

None of the ingredients are listed.

· **Probable routes of exposure:**

(Cont'd. on page 7)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA
GHS

Printing date: 06 February 2020

Revision: 06 February 2020

Trade name: Clean Step v.7

(Cont'd. from page 6)

Ingestion.

Inhalation.

Eye contact.

Skin contact.

- **Germ cell mutagenicity:** Based on available data, the classification criteria are not met.
- **Carcinogenicity:** Based on available data, the classification criteria are not met.
- **Reproductive toxicity:** Based on available data, the classification criteria are not met.
- **STOT-single exposure:** Based on available data, the classification criteria are not met.
- **STOT-repeated exposure:** Based on available data, the classification criteria are not met.
- **Aspiration hazard:** Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

- **12.1 Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** Does not accumulate in organisms.
- **12.4 Mobility in soil** No further relevant information available.
- **Ecotoxicological effects:**
- **Remark:**
The product is oxygen-consuming. The declared action may be partly caused by lack of oxygen. Due to mechanical actions of the product (e.g. agglutinations), damages may occur.
- **Additional ecological information:**
- **General notes:**
Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.
Rinse off of bigger amounts into drains or the aquatic environment may lead to increased pH-values. A high pH-value harms aquatic organisms. If the dilution of the use-level pH-value is considerably reduced, the aqueous waste, emptied into drains, is only low water-dangerous.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation**
Small amounts may be diluted with plenty of water and washed away. Dispose of larger amounts in accordance with Local Authority requirements.
The user of this material has the responsibility to dispose of unused material, residues and containers in compliance with all relevant local, state and federal laws and regulations regarding treatment, storage and disposal for hazardous and nonhazardous wastes.
- **Uncleaned packaging:**
- **Recommendation:** Disposal must be made according to official regulations.
- **Recommended cleansing agents:** Water, if necessary together with cleansing agents.

(Cont'd. on page 8)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA
GHS

Printing date: 06 February 2020

Revision: 06 February 2020

Trade name: Clean Step v.7

(Cont'd. from page 7)

SECTION 14: Transport information

- | | |
|--|-----------------|
| · 14.1 UN-Number | |
| · DOT, ADR, IMDG, IATA | Not Regulated |
| · 14.2 UN proper shipping name | |
| · DOT, ADR, IMDG, IATA | Not Regulated |
| · 14.3 Transport hazard class(es) | |
| · DOT, ADR, IMDG, IATA | |
| · Class | Not Regulated |
| · 14.4 Packing group | |
| · DOT, ADR, IMDG, IATA | Not Regulated |
| · 14.5 Environmental hazards: | |
| · Marine pollutant: | No |
| · 14.6 Special precautions for user | Not applicable. |
| · 14.7 Transport in bulk according to Annex II of Marpol and the IBC Code | Not applicable. |

SECTION 15: Regulatory information

- | |
|--|
| · 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture |
| · United States (USA) |
| · SARA |
| · Section 355 (extremely hazardous substances): |
| None of the ingredients are listed. |
| · Section 313 (Specific toxic chemical listings): |
| None of the ingredients are listed. |
| · TSCA (Toxic Substances Control Act): |
| All ingredients are listed. |
| · Proposition 65 (California): |
| · Chemicals known to cause cancer: |
| None of the ingredients are listed. |
| · Chemicals known to cause reproductive toxicity for females: |
| None of the ingredients are listed. |
| · Chemicals known to cause reproductive toxicity for males: |
| None of the ingredients are listed. |
| · Chemicals known to cause developmental toxicity: |
| None of the ingredients are listed. |
| · Carcinogenic Categories |

(Cont'd. on page 9)

Safety Data Sheet

according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA
GHS

Printing date: 06 February 2020

Revision: 06 February 2020

Trade name: Clean Step v.7

(Cont'd. from page 8)

- **EPA (Environmental Protection Agency)**

None of the ingredients are listed.

- **IARC (International Agency for Research on Cancer)**

None of the ingredients are listed.

- **NIOSH-Ca (National Institute for Occupational Safety and Health)**

None of the ingredients are listed.

- **Canadian Domestic Substances List (DSL)**

All ingredients are listed.

- **Other regulations, limitations and prohibitive regulations**

- **Substances of very high concern (SVHC) according to REACH, Article 57**

None of the ingredients are listed.

- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Relevant phrases**

H290 May be corrosive to metals.

H302 Harmful if swallowed.

H314 Causes severe skin burns and eye damage.

H315 Causes skin irritation.

H318 Causes serious eye damage.

H319 Causes serious eye irritation.

- **Abbreviations and acronyms:**

ADR: European Agreement concerning the International Carriage of Dangerous Goods by Road

IMDG: International Maritime Code for Dangerous Goods

DOT: US Department of Transportation

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

NFPA: National Fire Protection Association (USA)

HMIS: Hazardous Materials Identification System (USA)

DNEL: Derived No-Effect Level (REACH)

PNEC: Predicted No-Effect Concentration (REACH)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

PBT: Persistent, Bio-accumulable, Toxique

SVHC: Substances of Very High Concern

vPvB: very Persistent and very Bioaccumulative

Met. Corr. 1: Corrosive to metals – Category 1

Acute Tox. 4: Acute toxicity – Category 4

Skin Corr. 1B: Skin corrosion/irritation – Category 1B

Skin Irrit. 2: Skin corrosion/irritation – Category 2

Eye Dam. 1: Serious eye damage/eye irritation – Category 1

Eye Irrit. 2: Serious eye damage/eye irritation – Category 2

- **Sources**

(Cont'd. on page 10)

Safety Data Sheet
according to 1907/2006/EC (REACH), 1272/2008/EC (CLP), and OSHA
GHS

Printing date: 06 February 2020

Revision: 06 February 2020

Trade name: Clean Step v.7

(Cont'd. from page 9)

Website, European Chemicals Agency (echa.europa.eu)Website, US EPA Substance Registry Services (ofmpub.epa.gov/sorinternet/registry/substreg/home/overview/home.do)Website, Chemical Abstracts Registry, American Chemical Society (www.cas.org)

Patty's Industrial Hygiene, 6th ed., Rose, Vernon, ed. ISBN: 978-0-470-07488-6

Casarett and Doull's Toxicology: The Basic Science of Poisons, 8th Ed., Klaasen, Curtis D., ed., ISBN: 978-0-07-176923-5.

Safety Data Sheets, Individual Manufacturers

SDS Prepared by:

ChemTel Inc.

1305 North Florida Avenue

Tampa, Florida USA 33602-2902

Toll Free North America 1-888-255-3924 Intl. +01 813-248-0573

Website: www.chemtelinc.com